

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584489

Luminaire Tested: **HCC8W35D010SL-HM82555935-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010SL-HM82555935-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3649.7 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584489
CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584489

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	55956	55956	55956
5°	58005	55773	53857
10°	59643	55284	51652
15°	60975	54312	49374
20°	61073	52186	47369
25°	59899	49287	45694
30°	56811	45708	43689
35°	51625	41627	41725
40°	45133	37356	39328
45°	39122	33274	36645
50°	34253	29551	33384
55°	30488	26193	30209
60°	27500	23522	26544
65°	24823	20693	23130
70°	22314	17437	17193
75°	19658	13821	12903
80°	16479	11454	12360
85°	12772	10048	10933



TEST NUMBER: P584489
 CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	4.7
10°-20°	482.2	13.2
20°-30°	689.1	18.9
30°-40°	732.2	20.1
40°-50°	630.4	17.3
50°-60°	471.3	12.9
60°-70°	300.6	8.2
70°-80°	136.8	3.7
80°-90°	35.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1342.5	36.8
0°-40°	2074.6	56.8
0°-60°	3176.3	87.0
0°-90°	3649.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3649.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1815	1815	1815	1815	1815	
5°	1874	1848	1802	1755	1740	180
15°	1910	1846	1701	1585	1547	538
25°	1760	1650	1449	1361	1343	806
35°	1371	1276	1106	1078	1108	854
45°	897	848	763	784	840	697
55°	567	521	487	528	562	510
65°	340	302	284	296	317	339
75°	165	142	116	106	108	175
85°	36	31	28	31	31	43
90°	0	0	0	0	0	



TEST NUMBER: P584489

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6
2.5°	1848.2	1843.0	1845.5	1843.0	1845.5	1845.5	1840.4	1840.4	1840.4	1840.4	1832.7
5°	1873.9	1871.4	1871.4	1868.8	1866.2	1868.8	1866.2	1863.6	1858.5	1855.9	1848.2
7.5°	1889.4	1889.4	1889.4	1889.4	1886.8	1884.2	1881.7	1876.5	1871.4	1866.2	1861.1
10°	1904.8	1907.5	1904.8	1902.3	1899.7	1894.5	1892.0	1886.8	1879.1	1871.4	1866.2
12.5°	1912.6	1912.6	1910.0	1910.0	1904.8	1902.3	1894.5	1886.8	1879.1	1871.4	1858.5
15°	1910.0	1910.0	1907.5	1904.8	1897.2	1894.5	1889.4	1881.7	1868.8	1858.5	1845.5
17.5°	1894.5	1892.0	1886.8	1886.8	1876.5	1873.9	1868.8	1858.5	1845.5	1830.1	1814.6
20°	1861.1	1861.1	1858.5	1855.9	1845.5	1837.9	1832.7	1819.8	1809.5	1791.5	1776.0
22.5°	1814.6	1819.8	1814.6	1809.5	1796.6	1794.0	1786.3	1770.9	1755.3	1734.7	1716.7
25°	1760.5	1757.9	1755.3	1750.2	1739.9	1734.7	1724.4	1708.9	1693.5	1670.3	1649.6
27.5°	1691.0	1680.6	1680.6	1670.3	1662.6	1654.8	1649.6	1634.2	1613.6	1595.5	1569.7
30°	1595.5	1598.1	1585.2	1582.7	1569.7	1564.6	1554.3	1538.8	1520.7	1500.1	1479.5
32.5°	1492.5	1484.7	1484.7	1474.4	1464.1	1456.4	1453.8	1435.7	1420.2	1399.6	1379.0
35°	1371.4	1371.4	1363.6	1360.9	1350.6	1345.5	1337.8	1327.5	1309.4	1291.4	1275.9
37.5°	1252.7	1247.6	1245.0	1239.8	1232.1	1224.4	1224.4	1206.4	1203.8	1183.1	1162.5
40°	1121.2	1126.5	1121.2	1113.5	1110.9	1105.8	1103.2	1092.9	1085.1	1067.2	1054.2
42.5°	1010.4	1005.2	1005.2	1002.7	992.4	992.4	987.3	982.1	969.2	964.0	948.6
45°	897.1	902.2	894.4	897.1	886.8	886.8	886.8	876.3	866.0	858.4	848.1
47.5°	799.1	801.6	801.6	793.9	791.3	791.3	786.1	781.0	773.3	763.0	755.2
50°	714.0	716.5	711.4	708.9	703.7	701.1	701.1	690.8	685.6	675.3	670.2
52.5°	636.6	636.6	634.1	634.1	626.3	626.3	621.2	613.5	608.3	603.2	590.3
55°	567.1	567.1	564.5	561.9	561.9	554.2	551.6	543.9	538.7	528.4	520.7
57.5°	500.0	502.7	500.0	497.5	494.9	492.4	487.2	479.4	474.3	466.5	461.3
60°	445.9	445.9	443.4	440.7	435.6	433.1	430.4	425.3	417.6	412.5	404.7
62.5°	394.4	391.7	389.2	386.6	381.4	381.4	376.3	371.1	363.5	358.3	353.2
65°	340.2	340.2	337.7	337.7	335.1	329.9	327.4	324.8	314.5	311.8	301.5
67.5°	291.2	293.9	288.7	288.7	283.6	283.6	280.9	273.3	270.6	265.5	260.3
70°	247.5	247.5	247.5	244.9	239.7	237.1	234.6	229.4	226.8	221.6	216.5
72.5°	203.7	203.7	201.0	201.0	198.5	195.9	193.4	188.2	188.2	183.1	177.9
75°	165.0	165.0	162.4	159.8	157.2	157.2	154.7	152.0	146.9	144.4	141.7
77.5°	126.3	126.3	126.3	123.8	121.1	121.1	121.1	116.0	110.8	110.8	108.3
80°	92.8	92.8	90.2	90.2	87.7	87.7	87.7	85.1	82.5	79.9	77.3
82.5°	61.8	61.8	61.8	61.8	59.3	59.3	59.3	56.7	54.1	54.1	54.1
85°	36.1	36.1	36.1	36.1	33.5	33.5	33.5	33.5	33.5	30.9	30.9
87.5°	15.5	12.9	15.5	12.9	15.5	12.9	15.5	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584489

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6
2.5°	1835.2	1832.7	1830.1	1827.5	1827.5	1824.9	1819.8	1817.2	1814.6	1812.1	1812.1
5°	1845.5	1843.0	1837.9	1832.7	1830.1	1824.9	1819.8	1814.6	1809.5	1801.8	1799.2
7.5°	1853.3	1845.5	1840.4	1830.1	1827.5	1822.4	1814.6	1806.9	1796.6	1786.3	1778.6
10°	1853.3	1843.0	1835.2	1822.4	1817.2	1812.1	1801.8	1788.9	1776.0	1765.6	1752.8
12.5°	1848.2	1835.2	1822.4	1809.5	1801.8	1794.0	1778.6	1765.6	1750.2	1734.7	1724.4
15°	1830.1	1814.6	1799.2	1783.7	1776.0	1765.6	1750.2	1732.2	1716.7	1701.3	1683.2
17.5°	1796.6	1781.2	1763.1	1745.0	1734.7	1727.0	1703.8	1691.0	1667.7	1652.3	1636.8
20°	1752.8	1734.7	1711.6	1693.5	1680.6	1672.9	1654.8	1631.7	1613.6	1590.3	1574.9
22.5°	1696.1	1672.9	1649.6	1631.7	1618.7	1608.4	1585.2	1562.1	1546.6	1526.0	1507.9
25°	1629.0	1605.9	1582.7	1556.9	1544.0	1533.7	1513.1	1492.5	1471.9	1448.6	1433.2
27.5°	1549.1	1523.4	1502.8	1479.5	1466.7	1451.3	1428.0	1407.4	1386.8	1371.4	1350.6
30°	1461.6	1433.2	1412.6	1389.3	1376.5	1363.6	1340.3	1319.7	1301.7	1283.7	1273.4
32.5°	1355.8	1335.2	1314.6	1291.4	1281.0	1273.4	1250.1	1229.5	1208.9	1193.4	1185.7
35°	1255.3	1232.1	1214.1	1193.4	1180.5	1172.8	1152.2	1134.1	1123.8	1105.8	1095.5
37.5°	1149.6	1131.6	1110.9	1090.3	1082.6	1074.8	1059.4	1041.3	1025.8	1013.0	1007.9
40°	1038.8	1023.3	1005.2	992.4	984.6	977.0	964.0	951.1	940.8	928.0	922.8
42.5°	933.1	922.8	907.4	891.9	884.1	881.5	866.0	855.7	850.6	845.4	840.3
45°	837.8	822.3	812.0	801.6	793.9	788.8	781.0	773.3	768.2	763.0	757.9
47.5°	744.9	732.1	721.7	714.0	706.2	703.7	698.6	690.8	685.6	685.6	685.6
50°	659.9	649.6	639.3	634.1	631.5	626.3	621.2	618.6	616.0	616.0	616.0
52.5°	585.1	574.8	567.1	561.9	561.9	556.7	551.6	549.0	549.0	549.0	549.0
55°	515.5	507.8	502.7	497.5	492.4	489.7	489.7	489.7	487.2	487.2	489.7
57.5°	453.7	448.5	440.7	435.6	433.1	433.1	430.4	427.9	430.4	433.1	435.6
60°	396.9	391.7	389.2	381.4	381.4	381.4	378.9	378.9	378.9	381.4	384.1
62.5°	345.4	342.9	337.7	335.1	332.6	332.6	329.9	329.9	329.9	329.9	332.6
65°	299.0	293.9	288.7	288.7	288.7	286.1	286.1	280.9	283.6	283.6	280.9
67.5°	255.2	250.0	247.5	244.9	242.4	242.4	239.7	237.1	234.6	234.6	234.6
70°	214.0	208.8	208.8	203.7	203.7	201.0	198.5	198.5	195.9	193.4	190.7
72.5°	172.8	170.1	167.6	165.0	165.0	165.0	162.4	159.8	157.2	154.7	149.5
75°	136.6	136.6	131.4	128.9	128.9	126.3	123.8	121.1	118.6	116.0	113.5
77.5°	105.7	103.1	98.0	95.4	95.4	95.4	92.8	90.2	87.7	85.1	82.5
80°	77.3	74.8	72.1	69.6	69.6	69.6	67.0	67.0	64.5	64.5	64.5
82.5°	51.5	51.5	49.0	49.0	49.0	49.0	46.4	46.4	46.4	46.4	46.4
85°	30.9	30.9	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
87.5°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584489

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6
2.5°	1806.9	1806.9	1801.8	1799.2	1796.6	1799.2	1794.0	1791.5	1788.9	1788.9	1786.3
5°	1791.5	1788.9	1778.6	1776.0	1773.4	1770.9	1765.6	1760.5	1755.3	1752.8	1750.2
7.5°	1770.9	1763.1	1752.8	1750.2	1747.6	1739.9	1732.2	1727.0	1719.2	1716.7	1711.6
10°	1742.5	1732.2	1724.4	1716.7	1711.6	1703.8	1696.1	1688.3	1678.0	1675.4	1667.7
12.5°	1708.9	1696.1	1680.6	1678.0	1670.3	1659.9	1649.6	1642.0	1634.2	1629.0	1621.4
15°	1667.7	1654.8	1639.3	1631.7	1623.9	1616.2	1603.3	1593.0	1585.2	1577.5	1569.7
17.5°	1618.7	1603.3	1590.3	1582.7	1577.5	1564.6	1554.3	1541.5	1533.7	1526.0	1518.2
20°	1559.4	1546.6	1528.5	1520.7	1518.2	1507.9	1495.0	1489.8	1479.5	1471.9	1466.7
22.5°	1492.5	1479.5	1464.1	1458.9	1448.6	1443.5	1430.5	1425.4	1420.2	1412.6	1409.9
25°	1417.7	1404.8	1392.0	1389.3	1381.7	1376.5	1368.7	1360.9	1360.9	1353.3	1353.3
27.5°	1340.3	1327.5	1317.2	1312.0	1309.4	1304.3	1296.6	1294.0	1291.4	1288.8	1288.8
30°	1257.9	1242.4	1237.3	1234.7	1232.1	1227.0	1224.4	1219.2	1221.8	1224.4	1221.8
32.5°	1170.2	1165.1	1154.8	1149.6	1152.2	1149.6	1144.4	1149.6	1147.1	1152.2	1154.8
35°	1085.1	1080.0	1074.8	1074.8	1069.7	1069.7	1069.7	1072.3	1077.5	1080.0	1085.1
37.5°	1002.7	994.9	992.4	989.8	992.4	992.4	992.4	997.6	1002.7	1007.9	1015.5
40°	915.0	909.9	909.9	909.9	909.9	917.7	915.0	920.2	925.3	933.1	940.8
42.5°	832.6	832.6	835.1	835.1	835.1	835.1	840.3	848.1	855.7	863.5	871.2
45°	755.2	755.2	755.2	760.4	760.4	763.0	773.3	778.5	783.6	791.3	799.1
47.5°	683.1	683.1	685.6	688.3	690.8	695.9	701.1	708.9	716.5	721.7	729.5
50°	616.0	618.6	623.8	628.9	628.9	631.5	639.3	644.4	649.6	657.3	659.9
52.5°	551.6	556.7	561.9	564.5	567.1	572.3	574.8	582.6	585.1	592.9	595.4
55°	492.4	494.9	502.7	505.2	505.2	510.3	515.5	520.7	528.4	528.4	533.6
57.5°	438.2	440.7	445.9	448.5	445.9	453.7	456.2	461.3	464.0	469.1	471.7
60°	384.1	389.2	391.7	391.7	394.4	396.9	402.2	402.2	407.3	412.5	412.5
62.5°	332.6	335.1	337.7	340.2	342.9	340.2	348.0	348.0	353.2	355.7	360.8
65°	283.6	286.1	286.1	288.7	288.7	291.2	291.2	293.9	296.4	301.5	304.2
67.5°	234.6	234.6	234.6	237.1	234.6	237.1	237.1	239.7	239.7	244.9	247.5
70°	190.7	188.2	185.6	185.6	185.6	185.6	183.1	185.6	185.6	188.2	188.2
72.5°	146.9	144.4	141.7	139.2	139.2	136.6	134.1	136.6	136.6	139.2	139.2
75°	110.8	105.7	105.7	105.7	103.1	103.1	103.1	105.7	105.7	105.7	108.3
77.5°	82.5	82.5	79.9	79.9	79.9	82.5	82.5	85.1	85.1	85.1	85.1
80°	61.8	64.5	64.5	64.5	64.5	67.0	67.0	67.0	67.0	69.6	69.6
82.5°	46.4	46.4	46.4	46.4	49.0	49.0	49.0	49.0	49.0	49.0	49.0
85°	28.4	30.9	30.9	28.4	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584489

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6	1814.6
2.5°	1783.7	1783.7	1783.7	1783.7	1781.2	1781.2	1781.2	1778.6
5°	1745.0	1745.0	1745.0	1739.9	1742.5	1742.5	1737.3	1739.9
7.5°	1706.4	1703.8	1701.3	1701.3	1698.6	1696.1	1693.5	1696.1
10°	1662.6	1654.8	1654.8	1652.3	1652.3	1647.1	1647.1	1649.6
12.5°	1613.6	1608.4	1608.4	1605.9	1603.3	1600.6	1598.1	1598.1
15°	1564.6	1559.4	1556.9	1554.3	1551.8	1546.6	1549.1	1546.6
17.5°	1515.6	1507.9	1507.9	1505.3	1502.8	1497.6	1497.6	1495.0
20°	1458.9	1456.4	1451.3	1453.8	1451.3	1446.1	1443.5	1443.5
22.5°	1402.3	1402.3	1399.6	1399.6	1397.1	1394.5	1392.0	1392.0
25°	1348.1	1345.5	1348.1	1348.1	1340.3	1340.3	1340.3	1343.0
27.5°	1286.3	1288.8	1286.3	1286.3	1286.3	1286.3	1288.8	1286.3
30°	1224.4	1224.4	1224.4	1227.0	1232.1	1229.5	1229.5	1227.0
32.5°	1157.4	1159.9	1159.9	1162.5	1165.1	1170.2	1170.2	1172.8
35°	1090.3	1095.5	1098.1	1095.5	1103.2	1103.2	1108.4	1108.4
37.5°	1020.7	1023.3	1028.5	1031.0	1036.2	1038.8	1041.3	1041.3
40°	945.9	956.2	958.9	961.4	969.2	969.2	971.8	977.0
42.5°	876.3	886.8	889.3	891.9	897.1	904.7	902.2	907.4
45°	809.4	817.2	819.7	822.3	830.0	832.6	832.6	840.3
47.5°	737.2	742.4	744.9	750.1	755.2	760.4	765.5	763.0
50°	665.0	672.8	677.9	680.5	688.3	690.8	693.4	695.9
52.5°	600.6	605.7	608.3	610.9	618.6	621.2	623.8	628.9
55°	538.7	541.3	546.4	543.9	551.6	554.2	556.7	561.9
57.5°	476.8	479.4	482.1	482.1	487.2	492.4	494.9	497.5
60°	417.6	422.8	425.3	425.3	425.3	430.4	430.4	430.4
62.5°	363.5	363.5	366.0	366.0	371.1	371.1	371.1	371.1
65°	306.7	309.3	311.8	311.8	317.0	314.5	319.6	317.0
67.5°	247.5	247.5	252.7	252.7	250.0	252.7	252.7	252.7
70°	188.2	188.2	190.7	190.7	190.7	190.7	190.7	190.7
72.5°	139.2	139.2	139.2	141.7	139.2	139.2	141.7	139.2
75°	108.3	108.3	108.3	108.3	108.3	108.3	108.3	108.3
77.5°	85.1	85.1	87.7	87.7	87.7	87.7	87.7	87.7
80°	69.6	69.6	69.6	69.6	72.1	69.6	69.6	69.6
82.5°	51.5	49.0	51.5	49.0	51.5	51.5	51.5	51.5
85°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)