

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584668

Luminaire Tested: **HCC8S45D010MW-HM82555830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MW-HM82555830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4450.8 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584668
CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584668

CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73212	73212	73212
5°	74587	72894	71198
10°	75750	71623	68598
15°	76512	69834	65626
20°	76220	67143	62599
25°	74213	63264	59107
30°	70679	58648	55671
35°	63818	53526	51712
40°	56070	48043	47910
45°	48402	42227	44054
50°	42130	37040	39510
55°	37359	32165	34418
60°	33328	27179	28567
65°	30040	22065	22539
70°	26678	16526	13344
75°	23006	9591	5743
80°	17705	3445	1705
85°	11357	1132	1132



TEST NUMBER: P584668
 CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.9	5.0
10°-20°	620.4	13.9
20°-30°	877.5	19.7
30°-40°	924.7	20.8
40°-50°	785.9	17.7
50°-60°	565.9	12.7
60°-70°	326.4	7.3
70°-80°	111.7	2.5
80°-90°	15.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.8	38.7
0°-40°	2645.5	59.4
0°-60°	3997.3	89.8
0°-90°	4450.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4450.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2374	2374	2374	2374	2374	
5°	2410	2394	2355	2313	2300	230
15°	2397	2323	2188	2091	2056	675
25°	2181	2069	1859	1763	1737	1000
35°	1695	1596	1422	1370	1374	1056
45°	1110	1058	968	975	1010	862
55°	695	640	598	621	640	625
65°	412	354	302	296	309	410
75°	193	145	80	52	48	204
85°	32	19	3	3	3	43
90°	0	0	0	0	0	



TEST NUMBER: P584668

CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2
2.5°	2396.7	2399.8	2396.7	2396.7	2393.5	2390.2	2387.1	2383.8	2377.3	2371.0	2371.0
5°	2409.6	2416.0	2409.6	2409.6	2399.8	2393.5	2387.1	2377.3	2364.5	2354.9	2354.9
7.5°	2419.2	2419.2	2419.2	2409.6	2403.1	2393.5	2377.3	2361.2	2345.2	2329.1	2322.7
10°	2419.2	2419.2	2416.0	2403.1	2396.7	2377.3	2361.2	2338.7	2316.2	2293.7	2287.4
12.5°	2409.6	2412.7	2406.3	2393.5	2377.3	2354.9	2332.4	2303.4	2277.6	2251.9	2239.0
15°	2396.7	2393.5	2387.1	2371.0	2351.6	2322.7	2300.1	2268.0	2232.6	2200.4	2187.5
17.5°	2364.5	2364.5	2354.9	2338.7	2313.0	2280.9	2245.5	2210.0	2171.5	2136.2	2120.0
20°	2322.7	2322.7	2309.9	2290.5	2264.8	2223.0	2184.4	2142.5	2097.4	2062.1	2046.1
22.5°	2261.5	2264.8	2248.6	2226.1	2197.3	2148.9	2110.3	2058.8	2013.8	1972.0	1959.1
25°	2181.2	2187.5	2171.5	2148.9	2110.3	2068.6	2020.3	1972.0	1920.6	1878.8	1859.4
27.5°	2087.8	2091.1	2074.9	2052.5	2013.8	1968.8	1920.6	1869.1	1820.8	1775.8	1756.5
30°	1985.0	1972.0	1965.6	1936.6	1894.9	1856.3	1801.5	1759.7	1708.2	1669.6	1647.1
32.5°	1840.1	1846.5	1827.3	1804.8	1772.5	1727.6	1682.6	1634.2	1586.0	1557.0	1541.0
35°	1695.3	1701.8	1692.2	1669.6	1634.2	1595.6	1550.6	1515.2	1473.4	1438.0	1421.9
37.5°	1544.1	1544.1	1537.7	1524.9	1499.1	1463.8	1418.7	1383.3	1347.9	1318.9	1309.3
40°	1392.9	1386.5	1383.3	1373.7	1351.2	1318.9	1290.1	1261.1	1225.7	1206.4	1193.5
42.5°	1245.0	1245.0	1238.6	1229.0	1206.4	1190.2	1161.4	1129.1	1103.4	1084.1	1084.1
45°	1109.9	1113.1	1103.4	1097.0	1084.1	1058.4	1032.7	1010.2	987.7	974.8	968.3
47.5°	990.8	990.8	981.2	974.8	961.9	939.3	916.8	897.6	881.5	871.8	868.6
50°	878.2	878.2	878.2	862.2	846.1	830.0	813.9	791.4	781.7	775.4	772.1
52.5°	781.7	778.5	778.5	765.6	749.5	730.3	714.1	694.9	685.3	678.8	682.0
55°	694.9	694.9	691.6	675.5	659.5	640.2	624.2	608.0	601.6	595.2	598.3
56°	659.5	659.5	656.3	643.4	624.2	608.0	588.7	572.7	562.9	566.2	566.2
57°	633.8	627.3	627.3	611.3	595.2	572.7	556.6	540.4	534.1	530.8	530.8
58°	601.6	598.3	595.2	579.1	562.9	543.7	527.6	511.5	501.8	501.8	498.6
59°	569.4	569.4	562.9	550.1	534.1	514.7	498.6	482.6	473.0	469.7	469.7
60°	540.4	543.7	534.1	521.2	508.3	485.7	466.5	453.6	444.0	440.7	440.7
61°	514.7	514.7	508.3	492.2	476.1	460.1	440.7	424.6	418.2	411.7	411.7
62°	492.2	485.7	482.6	466.5	450.4	431.1	415.0	398.9	389.2	382.9	386.0
63°	463.2	460.1	453.6	440.7	424.6	405.4	386.0	373.1	363.5	353.9	357.1
64°	440.7	437.5	427.9	415.0	398.9	379.6	360.3	347.4	341.0	331.4	328.1
65°	411.7	408.6	405.4	389.2	373.1	353.9	337.8	324.9	315.3	308.9	302.4
66°	386.0	389.2	382.9	370.0	350.6	334.5	312.0	299.2	292.8	283.0	276.7
67°	363.5	363.5	357.1	344.3	324.9	308.9	292.8	276.7	267.0	257.4	254.2
67.5°	350.6	350.6	344.3	328.1	315.3	295.9	279.9	267.0	254.2	247.7	241.3
68°	337.8	337.8	334.5	321.8	305.6	286.3	270.3	254.2	241.3	231.7	228.4
69°	315.3	318.5	312.0	299.2	283.0	263.8	247.7	234.8	221.9	212.3	205.9
70°	295.9	292.8	286.3	273.4	257.4	244.5	228.4	212.3	199.4	186.6	183.3
71°	270.3	270.3	263.8	254.2	238.0	221.9	205.9	193.1	180.2	164.1	160.8
72°	250.9	250.9	244.5	231.7	218.8	202.7	186.6	170.6	160.8	144.7	138.3
72.5°	238.0	241.3	234.8	221.9	209.1	189.8	176.9	164.1	148.0	135.1	128.7
73°	231.7	228.4	225.2	212.3	196.2	183.3	167.3	154.4	138.3	125.5	119.1



TEST NUMBER: P584668
 CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	144.7	144.7	141.6	128.7	115.8	103.0	90.1	77.2	64.4	51.5	45.0
80°	99.7	103.0	96.5	90.1	80.5	67.6	54.7	45.0	32.1	25.7	19.4
82.5°	64.4	64.4	61.1	54.7	48.2	38.6	32.1	22.5	16.1	12.9	9.6
85°	32.1	35.4	32.1	29.0	22.5	19.4	16.1	9.6	6.5	3.2	3.2
87.5°	12.9	12.9	12.9	9.6	9.6	6.5	3.2	3.2	3.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584668

CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2	2374.2
2.5°	2364.5	2364.5	2358.1	2354.9	2351.6	2348.5	2345.2	2342.0	2342.0	2345.2
5°	2345.2	2338.7	2325.9	2322.7	2313.0	2309.9	2303.4	2300.1	2303.4	2300.1
7.5°	2316.2	2303.4	2287.4	2280.9	2268.0	2261.5	2251.9	2251.9	2245.5	2248.6
10°	2277.6	2258.4	2239.0	2226.1	2216.5	2206.9	2200.4	2194.0	2190.8	2190.8
12.5°	2229.4	2206.9	2187.5	2168.3	2152.2	2145.8	2132.9	2132.9	2126.4	2123.2
15°	2174.7	2145.8	2123.2	2103.9	2091.1	2078.2	2068.6	2062.1	2055.7	2055.7
17.5°	2103.9	2078.2	2055.7	2033.2	2013.8	2004.2	1994.6	1985.0	1985.0	1978.5
20°	2026.7	1997.7	1978.5	1956.0	1939.9	1923.7	1910.9	1910.9	1904.5	1907.6
22.5°	1939.9	1904.5	1885.1	1869.1	1853.0	1840.1	1827.3	1827.3	1824.0	1820.8
25°	1843.4	1814.4	1791.9	1772.5	1762.9	1750.1	1746.8	1740.4	1737.2	1737.2
27.5°	1740.4	1717.9	1688.9	1679.3	1666.4	1660.0	1660.0	1656.7	1650.3	1653.6
30°	1631.1	1605.3	1589.2	1582.7	1569.9	1569.9	1566.7	1560.2	1560.2	1563.5
32.5°	1524.9	1499.1	1486.3	1483.0	1470.1	1470.1	1467.0	1470.1	1470.1	1473.4
35°	1409.0	1386.5	1383.3	1373.7	1370.4	1370.4	1370.4	1376.9	1383.3	1373.7
37.5°	1299.7	1283.6	1274.0	1270.7	1274.0	1274.0	1277.2	1286.8	1283.6	1280.3
40°	1187.1	1174.2	1167.7	1167.7	1174.2	1180.6	1180.6	1190.2	1193.5	1190.2
42.5°	1074.5	1064.8	1064.8	1068.0	1074.5	1077.8	1087.4	1097.0	1100.3	1103.4
45°	968.3	968.3	968.3	971.6	974.8	981.2	994.1	1003.7	1006.9	1010.2
47.5°	865.3	862.2	871.8	875.1	884.7	887.8	897.6	910.4	913.6	916.8
50°	768.9	775.4	778.5	788.1	794.6	794.6	807.5	813.9	823.6	823.6
52.5°	678.8	688.4	691.6	701.3	704.5	707.8	714.1	723.9	730.3	730.3
55°	598.3	601.6	608.0	611.3	620.9	624.2	630.5	633.8	643.4	640.2
56°	562.9	569.4	572.7	579.1	585.4	588.7	595.2	598.3	604.8	608.0
57°	530.8	534.1	543.7	546.9	553.3	553.3	556.6	566.2	566.2	569.4
58°	498.6	505.1	508.3	511.5	518.0	521.2	527.6	530.8	534.1	530.8
59°	469.7	473.0	476.1	476.1	482.6	482.6	492.2	498.6	501.8	501.8
60°	440.7	440.7	444.0	447.1	453.6	456.8	456.8	463.2	463.2	463.2
61°	411.7	411.7	415.0	418.2	421.5	421.5	427.9	427.9	431.1	434.2
62°	386.0	382.9	382.9	386.0	386.0	392.5	395.7	398.9	402.1	398.9
63°	357.1	353.9	353.9	353.9	353.9	360.3	360.3	363.5	370.0	366.8
64°	324.9	324.9	324.9	324.9	328.1	328.1	334.5	337.8	341.0	344.3
65°	302.4	295.9	292.8	292.8	295.9	299.2	302.4	305.6	308.9	308.9
66°	276.7	270.3	267.0	267.0	267.0	267.0	273.4	273.4	279.9	279.9
67°	247.7	241.3	238.0	234.8	234.8	234.8	244.5	241.3	241.3	241.3
67.5°	238.0	228.4	225.2	221.9	218.8	225.2	221.9	225.2	225.2	221.9
68°	225.2	218.8	212.3	205.9	205.9	205.9	209.1	212.3	209.1	205.9
69°	199.4	196.2	186.6	180.2	176.9	180.2	176.9	180.2	176.9	180.2
70°	176.9	167.3	157.7	154.4	151.2	151.2	151.2	148.0	151.2	148.0
71°	154.4	144.7	135.1	128.7	125.5	125.5	122.2	125.5	122.2	125.5
72°	131.8	122.2	109.3	103.0	103.0	103.0	103.0	99.7	103.0	99.7
72.5°	122.2	109.3	99.7	93.3	90.1	90.1	90.1	90.1	86.8	90.1
73°	112.6	99.7	86.8	83.6	83.6	83.6	80.5	77.2	80.5	80.5



TEST NUMBER: P584668
CATALOG NUMBER: HCC8S45D010MW-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	38.6	29.0	25.7	25.7	25.7	25.7	25.7	25.7	22.5	22.5
80°	16.1	12.9	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
82.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	209.1	209.1	202.7	193.1	176.9	160.8	148.0	135.1	119.1	103.0	96.5
75°	193.1	189.8	183.3	173.7	160.8	144.7	131.8	115.8	103.0	86.8	80.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	93.3	77.2	70.7	64.4	64.4	64.4	61.1	61.1	61.1	64.4
75°	74.0	61.1	54.7	48.2	51.5	48.2	51.5	48.2	48.2	48.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)