

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584492

Luminaire Tested: **HCC8S35D010SL-HM82555940-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584492  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010SL-HM82555940-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4219.4 lumens  
Efficiency: N/A  
Efficacy: 125.2 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584492  
CATALOG NUMBER: HCC8S35D010SL-HM82555940-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584492

CATALOG NUMBER: HCC8S35D010SL-HM82555940-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	107890
5°	104953
10°	98761
15°	93506
20°	89944
25°	86469
30°	76800
35°	48907
40°	27296
45°	22860
50°	20638
55°	19451
60°	17749
65°	16009
70°	14128
75°	12558
80°	11134
85°	10084



TEST NUMBER: P584492  
 CATALOG NUMBER: HCC8S35D010SL-HM82555940-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	316.1	7.5
10°-20°	826.0	19.6
20°-30°	1152.4	27.3
30°-40°	829.2	19.7
40°-50°	410.9	9.7
50°-60°	321.5	7.6
60°-70°	217.7	5.2
70°-80°	113.1	2.7
80°-90°	32.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2294.5	54.4
0°-40°	3123.7	74.0
0°-60°	3856.1	91.4
0°-90°	4219.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4219.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3499	
5°	3391	316
15°	2929	826
25°	2541	1152
35°	1299	829
45°	524	411
55°	362	322
65°	219	218
75°	105	113
85°	28	33
90°	0	



TEST NUMBER: P584492  
CATALOG NUMBER: HCC8S35D010SL-HM82555940-81MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3498.8
2.5°	3467.5
5°	3390.6
7.5°	3282.3
10°	3154.1
12.5°	3034.4
15°	2929.0
17.5°	2829.2
20°	2740.9
22.5°	2652.6
25°	2541.4
27.5°	2382.0
30°	2156.9
32.5°	1803.6
35°	1299.2
37.5°	886.0
40°	678.1
42.5°	584.0
45°	524.2
47.5°	473.0
50°	430.2
52.5°	393.2
55°	361.8
57.5°	324.8
60°	287.8
62.5°	250.7
65°	219.4
67.5°	188.1
70°	156.7
72.5°	131.1
75°	105.4
77.5°	82.7
80°	62.7
82.5°	45.6
85°	28.5
87.5°	14.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)