

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593714

Luminaire Tested: **HCC8S35D010SL-HM82555950-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010SL-HM82555950-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4376.1 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593714
CATALOG NUMBER: HCC8S35D010SL-HM82555950-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593714

CATALOG NUMBER: HCC8S35D010SL-HM82555950-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																											
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																											
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																											
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																											
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																											
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52																											
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48																											
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																											
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40																											
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87489
5°	87383
10°	86518
15°	85480
20°	84693
25°	83740
30°	79015
35°	64341
40°	35544
45°	23728
50°	21046
55°	19752
60°	19501
65°	19328
70°	17464
75°	15620
80°	13656
85°	12065



TEST NUMBER: P593714
 CATALOG NUMBER: HCC8S35D010SL-HM82555950-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.5	6.1
10°-20°	756.1	17.3
20°-30°	1123.4	25.7
30°-40°	1011.7	23.1
40°-50°	448.5	10.2
50°-60°	332.1	7.6
60°-70°	258.3	5.9
70°-80°	140.0	3.2
80°-90°	38.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2147.0	49.1
0°-40°	3158.8	72.2
0°-60°	3939.4	90.0
0°-90°	4376.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4376.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2837	
5°	2823	268
15°	2678	756
25°	2461	1123
35°	1709	1012
45°	544	449
55°	367	332
65°	265	258
75°	131	140
85°	34	38
90°	0	



TEST NUMBER: P593714
CATALOG NUMBER: HCC8S35D010SL-HM82555950-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2837.2
2.5°	2831.5
5°	2823.0
7.5°	2800.1
10°	2763.1
12.5°	2720.4
15°	2677.6
17.5°	2634.9
20°	2580.9
22.5°	2526.7
25°	2461.2
27.5°	2361.5
30°	2219.1
32.5°	2014.0
35°	1709.2
37.5°	1276.1
40°	883.0
42.5°	652.3
45°	544.1
47.5°	481.4
50°	438.7
52.5°	398.8
55°	367.4
57.5°	341.8
60°	316.2
62.5°	293.4
65°	264.9
67.5°	230.7
70°	193.7
72.5°	162.3
75°	131.1
77.5°	102.5
80°	76.9
82.5°	54.1
85°	34.1
87.5°	14.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)