

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584519

Luminaire Tested: **HCC8W40D010BZ-HM82555827-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010BZ-HM82555827-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4751.9 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584519  
CATALOG NUMBER: HCC8W40D010BZ-HM82555827-81WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584519

CATALOG NUMBER: HCC8W40D010BZ-HM82555827-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95001
5°	94884
10°	93945
15°	92819
20°	91962
25°	90929
30°	85794
35°	69864
40°	38600
45°	25764
50°	22854
55°	21451
60°	21172
65°	20985
70°	18970
75°	16954
80°	14828
85°	13126



TEST NUMBER: P584519  
 CATALOG NUMBER: HCC8W40D010BZ-HM82555827-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.5	6.1
10°-20°	821.0	17.3
20°-30°	1219.9	25.7
30°-40°	1098.6	23.1
40°-50°	487.0	10.2
50°-60°	360.7	7.6
60°-70°	280.5	5.9
70°-80°	152.1	3.2
80°-90°	41.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.4	49.1
0°-40°	3430.0	72.2
0°-60°	4277.7	90.0
0°-90°	4751.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4751.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3081	
5°	3065	291
15°	2908	821
25°	2672	1220
35°	1856	1099
45°	591	487
55°	399	361
65°	288	280
75°	142	152
85°	37	42
90°	0	



TEST NUMBER: P584519  
CATALOG NUMBER: HCC8W40D010BZ-HM82555827-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3080.8
2.5°	3074.6
5°	3065.3
7.5°	3040.6
10°	3000.3
12.5°	2953.9
15°	2907.5
17.5°	2861.1
20°	2802.4
22.5°	2743.7
25°	2672.5
27.5°	2564.2
30°	2409.5
32.5°	2186.9
35°	1855.9
37.5°	1385.8
40°	958.9
42.5°	708.3
45°	590.8
47.5°	522.8
50°	476.4
52.5°	433.0
55°	399.0
57.5°	371.2
60°	343.3
62.5°	318.6
65°	287.6
67.5°	250.5
70°	210.4
72.5°	176.4
75°	142.3
77.5°	111.4
80°	83.5
82.5°	58.8
85°	37.1
87.5°	15.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)