

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584531

Luminaire Tested: **HCC8W40D010SL-HM82555830-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010SL-HM82555830-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4301.9 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584531
CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584531

CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69798	69798	69798
5°	70721	69504	68848
10°	71441	68792	67753
15°	72164	67341	65987
20°	71797	64856	63366
25°	70124	60971	60151
30°	66609	56600	56383
35°	60637	51648	52103
40°	53163	46228	47930
45°	45859	41115	44019
50°	40153	36095	39870
55°	35585	31031	35090
60°	32057	26088	29079
65°	28887	20948	22269
70°	25344	15255	12262
75°	21612	7923	3253
80°	16639	2149	533
85°	10685	0	0



TEST NUMBER: P584531
 CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.6	5.0
10°-20°	600.4	14.0
20°-30°	852.1	19.8
30°-40°	897.0	20.9
40°-50°	763.0	17.7
50°-60°	551.4	12.8
60°-70°	313.6	7.3
70°-80°	98.8	2.3
80°-90°	12.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1666.0	38.7
0°-40°	2563.0	59.6
0°-60°	3877.5	90.1
0°-90°	4301.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4301.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2264	2264	2264	2264	2264	
5°	2285	2272	2245	2230	2224	218
15°	2260	2203	2109	2070	2067	637
25°	2061	1958	1792	1762	1768	944
35°	1611	1517	1372	1363	1384	1002
45°	1052	1012	943	967	1009	817
55°	662	613	577	610	653	597
65°	396	342	287	284	305	393
75°	181	139	66	30	27	195
85°	30	18	0	0	0	39
90°	0	0	0	0	0	



TEST NUMBER: P584531

CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5
2.5°	2275.5	2278.6	2272.5	2272.5	2278.6	2272.5	2275.5	2275.5	2272.5	2272.5	2269.6
5°	2284.7	2281.6	2281.6	2281.6	2284.7	2278.6	2275.5	2278.6	2272.5	2272.5	2272.5
7.5°	2287.7	2287.7	2284.7	2281.6	2281.6	2281.6	2278.6	2275.5	2272.5	2266.5	2263.5
10°	2281.6	2281.6	2284.7	2278.6	2278.6	2272.5	2272.5	2266.5	2266.5	2260.5	2251.4
12.5°	2275.5	2272.5	2272.5	2266.5	2266.5	2260.5	2260.5	2251.4	2248.4	2239.3	2230.3
15°	2260.5	2257.4	2251.4	2248.4	2245.4	2242.3	2236.2	2233.3	2224.2	2212.1	2203.0
17.5°	2230.3	2227.2	2224.2	2218.2	2212.1	2209.1	2206.0	2197.0	2185.0	2175.8	2160.7
20°	2187.9	2185.0	2185.0	2175.8	2172.8	2163.8	2160.7	2148.7	2139.6	2121.4	2109.4
22.5°	2130.6	2133.6	2127.5	2121.4	2115.5	2106.3	2100.4	2088.2	2073.1	2055.0	2039.9
25°	2061.0	2064.1	2058.0	2051.9	2042.9	2036.8	2030.7	2012.6	1997.5	1976.4	1958.3
27.5°	1973.4	1973.4	1973.4	1967.3	1952.2	1949.2	1943.2	1925.1	1903.9	1885.8	1867.6
30°	1870.7	1867.6	1867.6	1858.5	1852.5	1840.5	1831.3	1816.2	1801.1	1780.0	1758.8
32.5°	1746.7	1749.8	1740.7	1734.7	1725.6	1725.6	1713.5	1701.3	1683.3	1662.1	1641.0
35°	1610.8	1613.8	1607.7	1604.7	1589.6	1586.5	1583.5	1568.4	1556.3	1541.2	1517.0
37.5°	1471.7	1468.7	1465.7	1465.7	1456.6	1450.6	1444.5	1435.5	1417.3	1405.3	1393.1
40°	1320.7	1320.7	1320.7	1317.6	1314.6	1308.5	1305.5	1299.5	1287.3	1275.3	1266.3
42.5°	1184.6	1184.6	1181.6	1178.6	1172.5	1175.6	1169.5	1163.5	1151.4	1142.3	1136.3
45°	1051.6	1051.6	1051.6	1054.7	1048.6	1039.6	1039.6	1033.5	1027.4	1021.5	1012.3
47.5°	933.8	942.8	936.8	933.8	936.8	924.7	924.7	918.7	912.6	906.7	894.5
50°	837.0	837.0	837.0	831.1	828.0	828.0	819.0	812.9	809.9	803.8	791.8
52.5°	749.5	743.4	743.4	740.4	737.3	731.4	731.4	725.3	713.2	707.1	698.1
55°	661.9	661.9	658.8	655.8	652.7	649.7	646.8	637.6	631.7	622.5	613.4
57.5°	583.2	589.3	586.3	580.2	574.2	574.2	568.1	562.0	553.0	543.9	534.9
60°	519.8	516.8	516.8	513.7	507.7	504.7	501.7	492.5	483.5	474.5	465.4
62.5°	453.3	453.3	453.3	447.2	441.3	438.2	435.2	429.1	417.1	407.9	402.0
65°	395.9	392.8	389.8	386.9	383.8	377.7	374.7	368.7	359.6	350.6	341.5
67.5°	338.4	335.5	335.5	332.4	323.3	320.3	320.3	311.3	302.3	293.1	284.1
70°	281.1	281.1	281.1	275.0	272.0	268.9	266.0	259.9	250.9	241.8	232.6
72.5°	232.6	229.7	229.7	226.7	217.5	214.6	211.6	205.5	196.5	190.4	184.3
75°	181.4	181.4	178.3	175.3	172.3	169.2	166.2	160.2	151.1	142.1	139.0
77.5°	139.0	136.0	136.0	132.9	127.0	123.9	123.9	117.8	108.8	102.7	96.7
80°	93.7	96.7	93.7	90.7	87.6	84.6	81.6	78.5	72.5	66.5	60.5
82.5°	57.5	60.5	57.5	57.5	54.4	51.4	51.4	45.3	42.4	39.3	36.3
85°	30.2	30.2	30.2	30.2	27.3	27.3	27.3	24.2	21.2	18.1	18.1
87.5°	9.0	12.1	9.0	9.0	9.0	9.0	9.0	9.0	6.1	6.1	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584531

CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5
2.5°	2272.5	2269.6	2266.5	2266.5	2266.5	2266.5	2266.5	2263.5	2260.5	2260.5	2260.5
5°	2266.5	2266.5	2266.5	2263.5	2260.5	2260.5	2254.5	2251.4	2248.4	2245.4	2242.3
7.5°	2260.5	2254.5	2251.4	2248.4	2245.4	2245.4	2239.3	2233.3	2233.3	2227.2	2221.1
10°	2242.3	2239.3	2233.3	2227.2	2224.2	2221.1	2215.2	2206.0	2203.0	2197.0	2190.9
12.5°	2221.1	2215.2	2209.1	2197.0	2194.0	2190.9	2178.9	2169.8	2163.8	2160.7	2145.7
15°	2194.0	2181.9	2172.8	2157.7	2154.7	2148.7	2139.6	2130.6	2118.4	2109.4	2103.3
17.5°	2145.7	2133.6	2118.4	2103.3	2097.3	2097.3	2082.1	2070.1	2055.0	2048.9	2036.8
20°	2088.2	2073.1	2061.0	2042.9	2033.8	2024.8	2015.7	1997.5	1985.5	1976.4	1961.2
22.5°	2021.7	2000.6	1985.5	1967.3	1952.2	1943.2	1928.0	1912.9	1897.8	1888.8	1876.6
25°	1937.1	1919.0	1894.8	1876.6	1867.6	1855.6	1837.4	1822.2	1807.1	1792.0	1786.0
27.5°	1843.4	1819.3	1798.1	1776.9	1767.9	1758.8	1737.6	1719.6	1707.4	1692.3	1686.2
30°	1740.7	1716.5	1692.3	1674.2	1665.2	1650.1	1637.9	1616.7	1601.6	1589.6	1574.5
32.5°	1622.8	1604.7	1583.5	1556.3	1550.3	1538.2	1520.1	1511.1	1492.9	1483.8	1471.7
35°	1495.9	1483.8	1462.6	1441.4	1432.4	1426.3	1411.3	1393.1	1381.1	1372.0	1366.0
37.5°	1375.0	1359.9	1338.8	1323.6	1317.6	1308.5	1290.4	1281.4	1269.3	1263.2	1251.2
40°	1245.1	1230.0	1214.9	1205.8	1196.7	1190.7	1178.6	1169.5	1157.4	1148.4	1145.4
42.5°	1118.1	1109.1	1096.9	1084.9	1081.8	1072.8	1066.7	1057.7	1048.6	1045.7	1036.6
45°	1003.3	994.2	982.1	970.1	967.0	961.0	958.0	948.9	942.8	942.8	942.8
47.5°	888.5	879.4	867.3	861.3	864.3	852.2	852.2	849.2	843.1	843.1	846.2
50°	785.8	773.6	770.6	764.6	758.5	752.4	755.5	746.5	746.5	752.4	749.5
52.5°	689.0	676.9	673.9	667.8	664.9	664.9	661.9	661.9	658.8	661.9	661.9
55°	601.4	592.3	586.3	580.2	577.2	577.2	577.2	574.2	571.2	577.2	580.2
57.5°	522.8	519.8	513.7	504.7	501.7	498.6	495.6	495.6	495.6	495.6	498.6
60°	453.3	447.2	441.3	432.1	432.1	429.1	426.1	423.0	423.0	423.0	423.0
62.5°	392.8	383.8	374.7	368.7	365.7	362.6	359.6	353.5	353.5	353.5	353.5
65°	332.4	323.3	317.3	311.3	305.2	305.2	299.2	296.2	290.1	287.1	281.1
67.5°	275.0	268.9	262.9	253.8	250.9	247.8	241.8	238.7	229.7	226.7	223.6
70°	223.6	214.6	208.5	202.4	199.4	193.4	187.3	181.4	175.3	169.2	163.1
72.5°	175.3	166.2	160.2	154.1	148.0	148.0	139.0	132.9	123.9	117.8	108.8
75°	129.9	120.9	114.8	105.8	102.7	99.7	90.7	84.6	75.6	66.5	60.5
77.5°	87.6	81.6	75.6	66.5	60.5	60.5	51.4	45.3	39.3	30.2	27.3
80°	54.4	48.3	42.4	36.3	36.3	30.2	27.3	21.2	15.1	12.1	9.0
82.5°	30.2	27.3	24.2	18.1	18.1	15.1	12.1	9.0	6.1	3.0	3.0
85°	15.1	12.1	9.0	9.0	6.1	6.1	6.1	3.0	3.0	0.0	0.0
87.5°	6.1	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584531

CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5
2.5°	2257.4	2257.4	2254.5	2254.5	2254.5	2251.4	2254.5	2251.4	2251.4	2251.4	2254.5
5°	2245.4	2239.3	2239.3	2236.2	2236.2	2233.3	2236.2	2233.3	2230.3	2227.2	2230.3
7.5°	2221.1	2215.2	2212.1	2209.1	2209.1	2209.1	2206.0	2203.0	2206.0	2197.0	2203.0
10°	2187.9	2185.0	2178.9	2175.8	2172.8	2175.8	2172.8	2166.8	2166.8	2166.8	2163.8
12.5°	2145.7	2139.6	2136.5	2133.6	2127.5	2127.5	2130.6	2124.5	2124.5	2118.4	2118.4
15°	2094.3	2088.2	2082.1	2082.1	2076.1	2076.1	2073.1	2073.1	2070.1	2067.0	2067.0
17.5°	2030.7	2021.7	2015.7	2018.7	2015.7	2012.6	2012.6	2006.6	2003.6	2006.6	2006.6
20°	1955.3	1949.2	1943.2	1946.1	1940.2	1937.1	1940.2	1931.0	1934.1	1934.1	1934.1
22.5°	1870.7	1867.6	1858.5	1858.5	1852.5	1849.5	1852.5	1852.5	1855.6	1852.5	1852.5
25°	1776.9	1771.0	1764.9	1764.9	1761.8	1758.8	1761.8	1764.9	1761.8	1764.9	1764.9
27.5°	1677.2	1668.1	1668.1	1662.1	1662.1	1665.2	1662.1	1665.2	1668.1	1668.1	1674.2
30°	1568.4	1565.4	1562.4	1559.4	1559.4	1562.4	1562.4	1562.4	1565.4	1571.4	1571.4
32.5°	1465.7	1459.7	1453.6	1453.6	1459.7	1456.6	1459.7	1459.7	1465.7	1465.7	1471.7
35°	1353.9	1353.9	1347.8	1350.9	1350.9	1350.9	1350.9	1356.8	1362.9	1366.0	1372.0
37.5°	1251.2	1242.0	1245.1	1245.1	1248.1	1245.1	1254.1	1254.1	1260.2	1260.2	1266.3
40°	1139.3	1139.3	1142.3	1139.3	1142.3	1142.3	1148.4	1154.4	1157.4	1163.5	1166.6
42.5°	1033.5	1039.6	1033.5	1036.6	1039.6	1042.6	1045.7	1048.6	1060.8	1066.7	1075.9
45°	936.8	939.9	942.8	945.9	942.8	948.9	951.9	958.0	967.0	970.1	973.1
47.5°	843.1	846.2	849.2	852.2	852.2	858.2	861.3	867.3	873.3	876.4	879.4
50°	752.4	758.5	761.6	761.6	764.6	770.6	776.7	776.7	782.7	791.8	794.8
52.5°	670.9	670.9	676.9	680.0	682.9	682.9	692.0	695.1	698.1	704.1	710.2
55°	580.2	589.3	592.3	592.3	598.3	604.4	607.4	610.5	610.5	622.5	622.5
57.5°	501.7	504.7	510.7	510.7	510.7	519.8	519.8	525.9	528.8	531.9	537.9
60°	423.0	429.1	429.1	432.1	429.1	435.2	438.2	444.2	447.2	450.3	453.3
62.5°	350.6	350.6	353.5	353.5	353.5	353.5	359.6	359.6	365.7	368.7	371.8
65°	281.1	281.1	281.1	281.1	281.1	281.1	281.1	281.1	284.1	284.1	290.1
67.5°	217.5	214.6	208.5	211.6	208.5	208.5	205.5	205.5	208.5	208.5	214.6
70°	157.2	154.1	148.0	148.0	145.1	142.1	139.0	136.0	132.9	132.9	132.9
72.5°	102.7	96.7	87.6	84.6	84.6	78.5	72.5	69.5	69.5	69.5	69.5
75°	51.4	45.3	39.3	36.3	36.3	30.2	33.2	30.2	30.2	30.2	30.2
77.5°	21.2	15.1	12.1	12.1	12.1	9.0	9.0	9.0	9.0	9.0	9.0
80°	6.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584531

CATALOG NUMBER: HCC8W40D010SL-HM82555830-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5	2263.5
2.5°	2251.4	2251.4	2245.4	2248.4	2248.4	2248.4	2248.4	2248.4
5°	2224.2	2227.2	2224.2	2227.2	2227.2	2224.2	2224.2	2224.2
7.5°	2197.0	2200.1	2197.0	2200.1	2200.1	2200.1	2197.0	2197.0
10°	2163.8	2163.8	2163.8	2163.8	2163.8	2160.7	2163.8	2163.8
12.5°	2118.4	2118.4	2118.4	2121.4	2121.4	2118.4	2118.4	2115.5
15°	2070.1	2064.1	2067.0	2070.1	2067.0	2067.0	2067.0	2067.0
17.5°	2003.6	2006.6	2003.6	2003.6	2003.6	2003.6	2006.6	2003.6
20°	1934.1	1934.1	1937.1	1934.1	1934.1	1934.1	1934.1	1931.0
22.5°	1855.6	1852.5	1852.5	1855.6	1855.6	1852.5	1855.6	1855.6
25°	1767.9	1771.0	1767.9	1767.9	1771.0	1771.0	1771.0	1767.9
27.5°	1674.2	1677.2	1680.3	1677.2	1677.2	1677.2	1680.3	1683.3
30°	1577.5	1583.5	1577.5	1577.5	1583.5	1580.6	1583.5	1583.5
32.5°	1474.8	1483.8	1477.7	1483.8	1483.8	1486.8	1483.8	1486.8
35°	1372.0	1381.1	1381.1	1381.1	1384.1	1387.1	1387.1	1384.1
37.5°	1275.3	1278.3	1278.3	1284.4	1287.3	1290.4	1290.4	1287.3
40°	1175.6	1181.6	1184.6	1184.6	1184.6	1190.7	1196.7	1190.7
42.5°	1078.9	1081.8	1084.9	1084.9	1091.0	1094.0	1096.9	1096.9
45°	985.2	991.3	994.2	997.2	1000.3	1006.4	1003.3	1009.4
47.5°	888.5	897.5	900.6	903.6	909.6	912.6	915.7	918.7
50°	800.9	806.8	806.8	812.9	821.9	821.9	828.0	831.1
52.5°	713.2	716.3	719.2	722.2	728.3	734.3	734.3	740.4
55°	628.6	631.7	631.7	634.6	637.6	649.7	652.7	652.7
57.5°	541.0	541.0	547.0	550.0	553.0	559.1	559.1	559.1
60°	456.4	459.3	459.3	462.3	465.4	471.5	474.5	471.5
62.5°	371.8	374.7	374.7	377.7	383.8	386.9	383.8	383.8
65°	293.1	296.2	296.2	299.2	305.2	305.2	302.3	305.2
67.5°	214.6	214.6	214.6	214.6	214.6	214.6	214.6	214.6
70°	136.0	132.9	129.9	132.9	132.9	132.9	129.9	136.0
72.5°	66.5	69.5	69.5	69.5	69.5	69.5	69.5	66.5
75°	30.2	30.2	27.3	27.3	27.3	30.2	30.2	27.3
77.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)