

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584744

Luminaire Tested: **HCC8S45D010BZ-HM82555930-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010BZ-HM82555930-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4477.3 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584744
CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584744

CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57				
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50				
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45				
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37				
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33				
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68645	68645	68645
5°	71157	68418	66068
10°	73173	67825	63369
15°	74805	66626	60570
20°	74917	64026	58109
25°	73482	60464	56055
30°	69697	56073	53595
35°	63325	51068	51185
40°	55373	45825	48244
45°	47987	40814	44952
50°	42019	36258	40959
55°	37402	32128	37063
60°	33741	28863	32569
65°	30456	25377	28383
70°	27372	21386	21097
75°	24103	16954	15822
80°	20209	14047	15165
85°	15638	12312	13409



TEST NUMBER: P584744
 CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.0	4.7
10°-20°	591.5	13.2
20°-30°	845.4	18.9
30°-40°	898.2	20.1
40°-50°	773.3	17.3
50°-60°	578.2	12.9
60°-70°	368.8	8.2
70°-80°	167.8	3.7
80°-90°	44.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1646.9	36.8
0°-40°	2545.1	56.8
0°-60°	3896.7	87.0
0°-90°	4477.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4477.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2226	2226	2226	2226	2226	
5°	2299	2267	2210	2153	2134	220
15°	2343	2264	2087	1945	1897	660
25°	2160	2024	1777	1670	1648	989
35°	1682	1565	1357	1322	1360	1048
45°	1100	1040	936	961	1031	855
55°	696	639	598	648	689	626
65°	417	370	348	364	389	416
75°	202	174	142	130	133	215
85°	44	38	35	38	38	53
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584744

CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1
2.5°	2267.3	2261.0	2264.1	2261.0	2264.1	2264.1	2257.8	2257.8	2257.8	2257.8	2248.3
5°	2298.8	2295.7	2295.7	2292.5	2289.3	2292.5	2289.3	2286.2	2279.8	2276.8	2267.3
7.5°	2317.8	2317.8	2317.8	2317.8	2314.7	2311.5	2308.3	2302.0	2295.7	2289.3	2283.0
10°	2336.9	2340.0	2336.9	2333.7	2330.5	2324.2	2321.0	2314.7	2305.2	2295.7	2289.3
12.5°	2346.4	2346.4	2343.2	2343.2	2336.9	2333.7	2324.2	2314.7	2305.2	2295.7	2279.8
15°	2343.2	2343.2	2340.0	2336.9	2327.3	2324.2	2317.8	2308.3	2292.5	2279.8	2264.1
17.5°	2324.2	2321.0	2314.7	2314.7	2302.0	2298.8	2292.5	2279.8	2264.1	2245.1	2226.1
20°	2283.0	2283.0	2279.8	2276.8	2264.1	2254.6	2248.3	2232.5	2219.8	2197.7	2178.7
22.5°	2226.1	2232.5	2226.1	2219.8	2204.1	2200.9	2191.4	2172.4	2153.4	2128.2	2106.0
25°	2159.7	2156.6	2153.4	2147.1	2134.4	2128.2	2115.5	2096.5	2077.5	2049.1	2023.8
27.5°	2074.3	2061.7	2061.7	2049.1	2039.6	2030.1	2023.8	2004.8	1979.6	1957.4	1925.7
30°	1957.4	1960.6	1944.7	1941.5	1925.7	1919.4	1906.7	1887.8	1865.7	1840.3	1815.1
32.5°	1830.8	1821.4	1821.4	1808.8	1796.1	1786.6	1783.4	1761.3	1742.4	1717.0	1691.7
35°	1682.2	1682.2	1672.8	1669.6	1657.0	1650.6	1641.1	1628.5	1606.4	1584.3	1565.3
37.5°	1536.7	1530.5	1527.4	1521.0	1511.5	1502.0	1502.0	1479.9	1476.7	1451.5	1426.1
40°	1375.6	1381.9	1375.6	1366.1	1362.9	1356.6	1353.4	1340.7	1331.2	1309.1	1293.3
42.5°	1239.5	1233.2	1233.2	1230.1	1217.5	1217.5	1211.1	1204.8	1189.0	1182.6	1163.6
45°	1100.4	1106.7	1097.2	1100.4	1087.7	1087.7	1087.7	1075.2	1062.5	1053.0	1040.3
47.5°	980.3	983.4	983.4	973.9	970.8	970.8	964.4	958.1	948.6	935.9	926.6
50°	875.9	879.0	872.7	869.5	863.2	860.0	860.0	847.5	841.2	828.5	822.2
52.5°	781.1	781.1	777.9	777.9	768.4	768.4	762.1	752.6	746.3	739.9	724.1
55°	695.7	695.7	692.5	689.4	689.4	679.9	676.7	667.2	660.9	648.2	638.7
57.5°	613.5	616.6	613.5	610.3	607.1	604.0	597.6	588.1	581.8	572.3	566.0
60°	547.1	547.1	543.9	540.8	534.4	531.3	528.1	521.8	512.2	505.9	496.4
62.5°	483.9	480.7	477.5	474.4	468.0	468.0	461.7	455.4	445.9	439.5	433.2
65°	417.4	417.4	414.2	414.2	411.0	404.8	401.6	398.5	385.8	382.6	370.0
67.5°	357.3	360.5	354.1	354.1	347.8	347.8	344.6	335.2	332.1	325.7	319.4
70°	303.6	303.6	303.6	300.4	294.1	290.9	287.7	281.4	278.2	271.9	265.6
72.5°	249.8	249.8	246.7	246.7	243.5	240.3	237.2	230.8	230.8	224.5	218.2
75°	202.3	202.3	199.2	196.0	192.8	192.8	189.7	186.6	180.3	177.1	174.0
77.5°	155.0	155.0	155.0	151.8	148.6	148.6	148.6	142.3	136.0	136.0	132.8
80°	113.8	113.8	110.7	110.7	107.6	107.6	107.6	104.4	101.2	98.1	94.9
82.5°	75.9	75.9	75.9	75.9	72.7	72.7	72.7	69.6	66.4	66.4	66.4
85°	44.2	44.2	44.2	44.2	41.1	41.1	41.1	41.1	41.1	37.9	37.9
87.5°	19.0	15.8	19.0	15.8	19.0	15.8	19.0	15.8	15.8	15.8	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584744

CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1
2.5°	2251.5	2248.3	2245.1	2242.0	2242.0	2238.8	2232.5	2229.3	2226.1	2223.0	2223.0
5°	2264.1	2261.0	2254.6	2248.3	2245.1	2238.8	2232.5	2226.1	2219.8	2210.3	2207.1
7.5°	2273.6	2264.1	2257.8	2245.1	2242.0	2235.6	2226.1	2216.6	2204.1	2191.4	2181.9
10°	2273.6	2261.0	2251.5	2235.6	2229.3	2223.0	2210.3	2194.6	2178.7	2166.1	2150.2
12.5°	2267.3	2251.5	2235.6	2219.8	2210.3	2200.9	2181.9	2166.1	2147.1	2128.2	2115.5
15°	2245.1	2226.1	2207.1	2188.2	2178.7	2166.1	2147.1	2125.0	2106.0	2087.0	2064.8
17.5°	2204.1	2185.1	2162.9	2140.7	2128.2	2118.7	2090.2	2074.3	2045.9	2026.9	2007.9
20°	2150.2	2128.2	2099.7	2077.5	2061.7	2052.3	2030.1	2001.6	1979.6	1951.1	1932.0
22.5°	2080.7	2052.3	2023.8	2001.6	1985.8	1973.2	1944.7	1916.2	1897.3	1872.0	1849.8
25°	1998.4	1970.1	1941.5	1909.9	1894.2	1881.5	1856.2	1830.8	1805.6	1777.1	1758.1
27.5°	1900.5	1868.8	1843.5	1815.1	1799.3	1780.3	1751.9	1726.5	1701.2	1682.2	1657.0
30°	1792.9	1758.1	1732.9	1704.4	1688.5	1672.8	1644.3	1619.0	1596.9	1574.8	1562.1
32.5°	1663.3	1638.0	1612.6	1584.3	1571.6	1562.1	1533.6	1508.4	1483.0	1464.0	1454.6
35°	1539.9	1511.5	1489.4	1464.0	1448.3	1438.8	1413.5	1391.3	1378.7	1356.6	1343.9
37.5°	1410.3	1388.1	1362.9	1337.6	1328.1	1318.6	1299.7	1277.5	1258.5	1242.7	1236.3
40°	1274.3	1255.3	1233.2	1217.5	1208.0	1198.5	1182.6	1166.8	1154.2	1138.4	1132.1
42.5°	1144.7	1132.1	1113.1	1094.1	1084.6	1081.5	1062.5	1049.8	1043.5	1037.2	1030.8
45°	1027.7	1008.8	996.1	983.4	973.9	967.6	958.1	948.6	942.3	935.9	929.7
47.5°	913.9	898.0	885.4	875.9	866.4	863.2	857.0	847.5	841.2	841.2	841.2
50°	809.5	796.8	784.3	777.9	774.8	768.4	762.1	758.9	755.8	755.8	755.8
52.5°	717.8	705.2	695.7	689.4	689.4	683.0	676.7	673.5	673.5	673.5	673.5
55°	632.5	623.0	616.6	610.3	604.0	600.8	600.8	600.8	597.6	597.6	600.8
57.5°	556.6	550.3	540.8	534.4	531.3	531.3	528.1	524.9	528.1	531.3	534.4
60°	486.9	480.7	477.5	468.0	468.0	468.0	464.9	464.9	464.9	468.0	471.2
62.5°	423.7	420.5	414.2	411.0	408.0	408.0	404.8	404.8	404.8	404.8	408.0
65°	366.8	360.5	354.1	354.1	354.1	351.0	351.0	344.6	347.8	347.8	344.6
67.5°	313.1	306.7	303.6	300.4	297.2	297.2	294.1	290.9	287.7	287.7	287.7
70°	262.4	256.2	256.2	249.8	249.8	246.7	243.5	243.5	240.3	237.2	234.0
72.5°	211.8	208.7	205.5	202.3	202.3	202.3	199.2	196.0	192.8	189.7	183.5
75°	167.6	167.6	161.3	158.1	158.1	155.0	151.8	148.6	145.5	142.3	139.1
77.5°	129.6	126.4	120.1	116.9	116.9	116.9	113.8	110.7	107.6	104.4	101.2
80°	94.9	91.7	88.6	85.4	85.4	85.4	82.2	82.2	79.1	79.1	79.1
82.5°	63.2	63.2	60.1	60.1	60.1	60.1	56.9	56.9	56.9	56.9	56.9
85°	37.9	37.9	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
87.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584744

CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1
2.5°	2216.6	2216.6	2210.3	2207.1	2204.1	2207.1	2200.9	2197.7	2194.6	2194.6	2191.4
5°	2197.7	2194.6	2181.9	2178.7	2175.6	2172.4	2166.1	2159.7	2153.4	2150.2	2147.1
7.5°	2172.4	2162.9	2150.2	2147.1	2143.9	2134.4	2125.0	2118.7	2109.2	2106.0	2099.7
10°	2137.6	2125.0	2115.5	2106.0	2099.7	2090.2	2080.7	2071.2	2058.5	2055.3	2045.9
12.5°	2096.5	2080.7	2061.7	2058.5	2049.1	2036.4	2023.8	2014.3	2004.8	1998.4	1988.9
15°	2045.9	2030.1	2011.1	2001.6	1992.1	1982.6	1966.9	1954.2	1944.7	1935.2	1925.7
17.5°	1985.8	1966.9	1951.1	1941.5	1935.2	1919.4	1906.7	1891.0	1881.5	1872.0	1862.5
20°	1913.0	1897.3	1875.2	1865.7	1862.5	1849.8	1834.0	1827.8	1815.1	1805.6	1799.3
22.5°	1830.8	1815.1	1796.1	1789.8	1777.1	1770.8	1755.0	1748.7	1742.4	1732.9	1729.7
25°	1739.2	1723.4	1707.5	1704.4	1694.9	1688.5	1679.1	1669.6	1669.6	1660.1	1660.1
27.5°	1644.3	1628.5	1615.8	1609.5	1606.4	1600.1	1590.6	1587.4	1584.3	1581.1	1581.1
30°	1543.1	1524.2	1517.9	1514.7	1511.5	1505.2	1502.0	1495.7	1498.9	1502.0	1498.9
32.5°	1435.6	1429.3	1416.6	1410.3	1413.5	1410.3	1404.0	1410.3	1407.1	1413.5	1416.6
35°	1331.2	1324.9	1318.6	1318.6	1312.2	1312.2	1312.2	1315.4	1321.7	1324.9	1331.2
37.5°	1230.1	1220.6	1217.5	1214.3	1217.5	1217.5	1217.5	1223.8	1230.1	1236.3	1245.8
40°	1122.6	1116.2	1116.2	1116.2	1116.2	1125.7	1122.6	1128.9	1135.2	1144.7	1154.2
42.5°	1021.3	1021.3	1024.5	1024.5	1024.5	1024.5	1030.8	1040.3	1049.8	1059.3	1068.8
45°	926.6	926.6	926.6	932.9	932.9	935.9	948.6	954.9	961.3	970.8	980.3
47.5°	838.0	838.0	841.2	844.3	847.5	853.8	860.0	869.5	879.0	885.4	894.9
50°	755.8	758.9	765.3	771.6	771.6	774.8	784.3	790.5	796.8	806.3	809.5
52.5°	676.7	683.0	689.4	692.5	695.7	702.0	705.2	714.6	717.8	727.3	730.4
55°	604.0	607.1	616.6	619.8	619.8	626.1	632.5	638.7	648.2	648.2	654.5
57.5°	537.6	540.8	547.1	550.3	547.1	556.6	559.8	566.0	569.1	575.5	578.6
60°	471.2	477.5	480.7	480.7	483.9	486.9	493.2	493.2	499.6	505.9	505.9
62.5°	408.0	411.0	414.2	417.4	420.5	417.4	426.9	426.9	433.2	436.4	442.7
65°	347.8	351.0	351.0	354.1	354.1	357.3	357.3	360.5	363.6	370.0	373.1
67.5°	287.7	287.7	287.7	290.9	287.7	290.9	290.9	294.1	294.1	300.4	303.6
70°	234.0	230.8	227.7	227.7	227.7	227.7	224.5	227.7	227.7	230.8	230.8
72.5°	180.3	177.1	174.0	170.8	170.8	167.6	164.5	167.6	167.6	170.8	170.8
75°	136.0	129.6	129.6	129.6	126.4	126.4	126.4	129.6	129.6	129.6	132.8
77.5°	101.2	101.2	98.1	98.1	98.1	101.2	101.2	104.4	104.4	104.4	104.4
80°	75.9	79.1	79.1	79.1	79.1	82.2	82.2	82.2	82.2	85.4	85.4
82.5°	56.9	56.9	56.9	56.9	60.1	60.1	60.1	60.1	60.1	60.1	60.1
85°	34.8	37.9	37.9	34.8	37.9	37.9	37.9	37.9	37.9	37.9	37.9
87.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584744

CATALOG NUMBER: HCC8S45D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1	2226.1
2.5°	2188.2	2188.2	2188.2	2188.2	2185.1	2185.1	2185.1	2181.9
5°	2140.7	2140.7	2140.7	2134.4	2137.6	2137.6	2131.2	2134.4
7.5°	2093.3	2090.2	2087.0	2087.0	2083.8	2080.7	2077.5	2080.7
10°	2039.6	2030.1	2030.1	2026.9	2026.9	2020.6	2020.6	2023.8
12.5°	1979.6	1973.2	1973.2	1970.1	1966.9	1963.7	1960.6	1960.6
15°	1919.4	1913.0	1909.9	1906.7	1903.7	1897.3	1900.5	1897.3
17.5°	1859.3	1849.8	1849.8	1846.7	1843.5	1837.2	1837.2	1834.0
20°	1789.8	1786.6	1780.3	1783.4	1780.3	1773.9	1770.8	1770.8
22.5°	1720.2	1720.2	1717.0	1717.0	1713.9	1710.7	1707.5	1707.5
25°	1653.8	1650.6	1653.8	1653.8	1644.3	1644.3	1644.3	1647.5
27.5°	1577.9	1581.1	1577.9	1577.9	1577.9	1577.9	1581.1	1577.9
30°	1502.0	1502.0	1502.0	1505.2	1511.5	1508.4	1508.4	1505.2
32.5°	1419.8	1423.0	1423.0	1426.1	1429.3	1435.6	1435.6	1438.8
35°	1337.6	1343.9	1347.1	1343.9	1353.4	1353.4	1359.7	1359.7
37.5°	1252.2	1255.3	1261.7	1264.8	1271.2	1274.3	1277.5	1277.5
40°	1160.4	1173.1	1176.3	1179.5	1189.0	1189.0	1192.1	1198.5
42.5°	1075.2	1087.7	1090.9	1094.1	1100.4	1109.9	1106.7	1113.1
45°	992.9	1002.4	1005.6	1008.8	1018.2	1021.3	1021.3	1030.8
47.5°	904.4	910.7	913.9	920.2	926.6	932.9	939.1	935.9
50°	815.8	825.3	831.7	834.8	844.3	847.5	850.7	853.8
52.5°	736.8	743.1	746.3	749.4	758.9	762.1	765.3	771.6
55°	660.9	664.0	670.4	667.2	676.7	679.9	683.0	689.4
57.5°	585.0	588.1	591.3	591.3	597.6	604.0	607.1	610.3
60°	512.2	518.6	521.8	521.8	521.8	528.1	528.1	528.1
62.5°	445.9	445.9	449.0	449.0	455.4	455.4	455.4	455.4
65°	376.3	379.5	382.6	382.6	389.0	385.8	392.1	389.0
67.5°	303.6	303.6	309.9	309.9	306.7	309.9	309.9	309.9
70°	230.8	230.8	234.0	234.0	234.0	234.0	234.0	234.0
72.5°	170.8	170.8	170.8	174.0	170.8	170.8	174.0	170.8
75°	132.8	132.8	132.8	132.8	132.8	132.8	132.8	132.8
77.5°	104.4	104.4	107.6	107.6	107.6	107.6	107.6	107.6
80°	85.4	85.4	85.4	85.4	88.6	85.4	85.4	85.4
82.5°	63.2	60.1	63.2	60.1	63.2	63.2	63.2	63.2
85°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9
87.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)