

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584736

Luminaire Tested: **HCC8S45D010MB-HM82555930-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MB-HM82555930-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4376.1 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584736
CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584736

CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	71984	71984	71984
5°	73333	71671	70003
10°	74479	70421	67449
15°	75226	68666	64525
20°	74940	66015	61552
25°	72968	62203	58113
30°	69490	57662	54735
35°	62753	52630	50842
40°	55132	47238	47109
45°	47586	41520	43313
50°	41429	36421	38844
55°	36735	31633	33837
60°	32773	26723	28092
65°	29544	21700	22159
70°	26236	16256	13118
75°	22613	9424	5647
80°	17421	3374	1687
85°	11216	1132	1132



TEST NUMBER: P584736
 CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	5.0
10°-20°	610.0	13.9
20°-30°	862.8	19.7
30°-40°	909.2	20.8
40°-50°	772.7	17.7
50°-60°	556.4	12.7
60°-70°	321.0	7.3
70°-80°	109.8	2.5
80°-90°	15.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1692.0	38.7
0°-40°	2601.2	59.4
0°-60°	3930.2	89.8
0°-90°	4376.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4376.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2334	2334	2334	2334	2334	
5°	2369	2353	2315	2274	2262	226
15°	2356	2284	2151	2056	2021	664
25°	2145	2034	1828	1733	1708	984
35°	1667	1569	1398	1347	1351	1038
45°	1091	1041	952	958	993	848
55°	683	629	588	610	629	615
65°	405	348	297	291	304	403
75°	190	142	79	51	47	200
85°	32	19	3	3	3	43
90°	0	0	0	0	0	



TEST NUMBER: P584736

CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4
2.5°	2356.4	2359.6	2356.4	2356.4	2353.3	2350.1	2347.1	2343.9	2337.6	2331.2	2331.2
5°	2369.1	2375.4	2369.1	2369.1	2359.6	2353.3	2347.1	2337.6	2324.9	2315.4	2315.4
7.5°	2378.6	2378.6	2378.6	2369.1	2362.8	2353.3	2337.6	2321.7	2305.9	2290.0	2283.7
10°	2378.6	2378.6	2375.4	2362.8	2356.4	2337.6	2321.7	2299.5	2277.4	2255.3	2249.0
12.5°	2369.1	2372.3	2365.9	2353.3	2337.6	2315.4	2293.2	2264.7	2239.5	2214.2	2201.5
15°	2356.4	2353.3	2347.1	2331.2	2312.2	2283.7	2261.5	2230.0	2195.2	2163.6	2150.9
17.5°	2324.9	2324.9	2315.4	2299.5	2274.2	2242.7	2207.8	2173.0	2135.1	2100.3	2084.4
20°	2283.7	2283.7	2271.0	2252.2	2226.8	2185.7	2147.8	2106.6	2062.4	2027.5	2011.7
22.5°	2223.7	2226.8	2211.0	2188.8	2160.4	2112.9	2074.9	2024.4	1980.0	1939.0	1926.3
25°	2144.6	2150.9	2135.1	2112.9	2074.9	2033.9	1986.4	1939.0	1888.3	1847.2	1828.2
27.5°	2052.9	2056.0	2040.2	2018.0	1980.0	1935.8	1888.3	1837.7	1790.3	1746.0	1727.0
30°	1951.6	1939.0	1932.6	1904.1	1863.1	1825.1	1771.3	1730.2	1679.6	1641.6	1619.4
32.5°	1809.2	1815.6	1796.6	1774.5	1742.8	1698.6	1654.3	1606.9	1559.4	1530.9	1515.2
35°	1667.0	1673.3	1663.8	1641.6	1606.9	1568.9	1524.5	1489.8	1448.7	1413.9	1398.1
37.5°	1518.3	1518.3	1512.0	1499.3	1474.0	1439.2	1394.9	1360.1	1325.4	1296.9	1287.4
40°	1369.6	1363.3	1360.1	1350.6	1328.5	1296.9	1268.4	1240.0	1205.1	1186.1	1173.5
42.5°	1224.1	1224.1	1217.8	1208.3	1186.1	1170.3	1141.9	1110.2	1084.9	1065.9	1065.9
45°	1091.2	1094.4	1084.9	1078.6	1065.9	1040.7	1015.3	993.2	971.0	958.5	952.1
47.5°	974.2	974.2	964.8	958.5	945.8	923.6	901.5	882.4	866.7	857.2	854.1
50°	863.6	863.6	863.6	847.7	831.9	816.1	800.2	778.2	768.7	762.3	759.2
52.5°	768.7	765.5	765.5	752.8	737.0	718.0	702.2	683.3	673.8	667.4	670.6
55°	683.3	683.3	680.1	664.3	648.4	629.4	613.6	597.9	591.5	585.2	588.4
56°	648.4	648.4	645.3	632.6	613.6	597.9	578.9	563.0	553.5	556.7	556.7
57°	623.1	616.8	616.8	600.9	585.2	563.0	547.2	531.4	525.0	521.9	521.9
58°	591.5	588.4	585.2	569.4	553.5	534.5	518.7	503.0	493.5	493.5	490.3
59°	559.9	559.9	553.5	540.9	525.0	506.1	490.3	474.5	465.0	461.8	461.8
60°	531.4	534.5	525.0	512.4	499.8	477.6	458.6	446.0	436.5	433.3	433.3
61°	506.1	506.1	499.8	484.0	468.1	452.3	433.3	417.5	411.3	404.9	404.9
62°	484.0	477.6	474.5	458.6	442.8	423.8	408.1	392.3	382.7	376.4	379.6
63°	455.5	452.3	446.0	433.3	417.5	398.6	379.6	366.9	357.4	347.9	351.1
64°	433.3	430.1	420.6	408.1	392.3	373.2	354.2	341.6	335.2	325.7	322.6
65°	404.9	401.8	398.6	382.7	366.9	347.9	332.1	319.5	310.0	303.7	297.4
66°	379.6	382.7	376.4	363.7	344.7	328.9	306.9	294.2	287.9	278.4	272.0
67°	357.4	357.4	351.1	338.4	319.5	303.7	287.9	272.0	262.5	253.0	249.8
67.5°	344.7	344.7	338.4	322.6	310.0	291.0	275.2	262.5	249.8	243.5	237.2
68°	332.1	332.1	328.9	316.4	300.5	281.5	265.7	249.8	237.2	227.8	224.6
69°	310.0	313.2	306.9	294.2	278.4	259.4	243.5	230.8	218.3	208.8	202.5
70°	291.0	287.9	281.5	268.9	253.0	240.3	224.6	208.8	196.1	183.5	180.3
71°	265.7	265.7	259.4	249.8	234.0	218.3	202.5	189.8	177.1	161.3	158.1
72°	246.7	246.7	240.3	227.8	215.1	199.3	183.5	167.6	158.1	142.3	136.1
72.5°	234.0	237.2	230.8	218.3	205.6	186.6	174.0	161.3	145.5	132.9	126.6
73°	227.8	224.6	221.5	208.8	193.0	180.3	164.5	151.8	136.1	123.4	117.1



TEST NUMBER: P584736
 CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	142.3	142.3	139.1	126.6	113.9	101.2	88.6	75.9	63.2	50.6	44.3
80°	98.1	101.2	94.9	88.6	79.1	66.4	53.7	44.3	31.7	25.3	19.0
82.5°	63.2	63.2	60.1	53.7	47.4	38.0	31.7	22.2	15.8	12.7	9.5
85°	31.7	34.8	31.7	28.5	22.2	19.0	15.8	9.5	6.3	3.2	3.2
87.5°	12.7	12.7	12.7	9.5	9.5	6.3	3.2	3.2	3.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584736

CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4	2334.4
2.5°	2324.9	2324.9	2318.6	2315.4	2312.2	2309.1	2305.9	2302.7	2302.7	2305.9
5°	2305.9	2299.5	2286.9	2283.7	2274.2	2271.0	2264.7	2261.5	2264.7	2261.5
7.5°	2277.4	2264.7	2249.0	2242.7	2230.0	2223.7	2214.2	2214.2	2207.8	2211.0
10°	2239.5	2220.5	2201.5	2188.8	2179.3	2169.8	2163.6	2157.3	2154.1	2154.1
12.5°	2192.0	2169.8	2150.9	2131.9	2116.1	2109.8	2097.1	2097.1	2090.8	2087.6
15°	2138.3	2109.8	2087.6	2068.7	2056.0	2043.4	2033.9	2027.5	2021.2	2021.2
17.5°	2068.7	2043.4	2021.2	1999.0	1980.0	1970.6	1961.1	1951.6	1951.6	1945.3
20°	1992.7	1964.3	1945.3	1923.1	1907.3	1891.5	1878.9	1878.9	1872.6	1875.7
22.5°	1907.3	1872.6	1853.6	1837.7	1821.9	1809.2	1796.6	1796.6	1793.5	1790.3
25°	1812.4	1784.0	1761.8	1742.8	1733.3	1720.7	1717.5	1711.2	1708.0	1708.0
27.5°	1711.2	1689.1	1660.6	1651.1	1638.4	1632.1	1632.1	1628.9	1622.6	1625.8
30°	1603.7	1578.4	1562.6	1556.2	1543.6	1543.6	1540.4	1534.0	1534.0	1537.2
32.5°	1499.3	1474.0	1461.3	1458.2	1445.5	1445.5	1442.3	1445.5	1445.5	1448.7
35°	1385.4	1363.3	1360.1	1350.6	1347.4	1347.4	1347.4	1353.8	1360.1	1350.6
37.5°	1277.9	1262.0	1252.5	1249.4	1252.5	1252.5	1255.7	1265.2	1262.0	1258.9
40°	1167.1	1154.5	1148.2	1148.2	1154.5	1160.8	1160.8	1170.3	1173.5	1170.3
42.5°	1056.5	1047.0	1047.0	1050.2	1056.5	1059.6	1069.1	1078.6	1081.7	1084.9
45°	952.1	952.1	952.1	955.3	958.5	964.8	977.3	986.8	990.0	993.2
47.5°	850.9	847.7	857.2	860.4	869.9	873.1	882.4	895.1	898.3	901.5
50°	756.0	762.3	765.5	775.0	781.3	781.3	793.9	800.2	809.7	809.7
52.5°	667.4	676.9	680.1	689.6	692.7	695.8	702.2	711.7	718.0	718.0
55°	588.4	591.5	597.9	600.9	610.4	613.6	619.9	623.1	632.6	629.4
56°	553.5	559.9	563.0	569.4	575.7	578.9	585.2	588.4	594.7	597.9
57°	521.9	525.0	534.5	537.7	544.0	544.0	547.2	556.7	556.7	559.9
58°	490.3	496.6	499.8	503.0	509.2	512.4	518.7	521.9	525.0	521.9
59°	461.8	465.0	468.1	468.1	474.5	474.5	484.0	490.3	493.5	493.5
60°	433.3	433.3	436.5	439.6	446.0	449.1	449.1	455.5	455.5	455.5
61°	404.9	404.9	408.1	411.3	414.4	414.4	420.6	420.6	423.8	427.0
62°	379.6	376.4	376.4	379.6	379.6	385.9	389.1	392.3	395.4	392.3
63°	351.1	347.9	347.9	347.9	347.9	354.2	354.2	357.4	363.7	360.6
64°	319.5	319.5	319.5	319.5	322.6	322.6	328.9	332.1	335.2	338.4
65°	297.4	291.0	287.9	287.9	291.0	294.2	297.4	300.5	303.7	303.7
66°	272.0	265.7	262.5	262.5	262.5	262.5	268.9	268.9	275.2	275.2
67°	243.5	237.2	234.0	230.8	230.8	230.8	240.3	237.2	237.2	237.2
67.5°	234.0	224.6	221.5	218.3	215.1	221.5	218.3	221.5	221.5	218.3
68°	221.5	215.1	208.8	202.5	202.5	202.5	205.6	208.8	205.6	202.5
69°	196.1	193.0	183.5	177.1	174.0	177.1	174.0	177.1	174.0	177.1
70°	174.0	164.5	155.0	151.8	148.6	148.6	148.6	145.5	148.6	145.5
71°	151.8	142.3	132.9	126.6	123.4	123.4	120.2	123.4	120.2	123.4
72°	129.7	120.2	107.6	101.2	101.2	101.2	101.2	98.1	101.2	98.1
72.5°	120.2	107.6	98.1	91.7	88.6	88.6	88.6	88.6	85.4	88.6
73°	110.7	98.1	85.4	82.2	82.2	82.2	79.1	75.9	79.1	79.1



TEST NUMBER: P584736

CATALOG NUMBER: HCC8S45D010MB-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	38.0	28.5	25.3	25.3	25.3	25.3	25.3	25.3	22.2	22.2
80°	15.8	12.7	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	205.6	205.6	199.3	189.8	174.0	158.1	145.5	132.9	117.1	101.2	94.9
75°	189.8	186.6	180.3	170.8	158.1	142.3	129.7	113.9	101.2	85.4	79.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	91.7	75.9	69.6	63.2	63.2	63.2	60.1	60.1	60.1	63.2
75°	72.7	60.1	53.7	47.4	50.6	47.4	50.6	47.4	47.4	47.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)