

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584735

Luminaire Tested: **HCC8W45D010SL-HM82555930-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555930-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4502.6 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584735
CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584735

CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73054	73054	73054
5°	74021	72745	72058
10°	74776	72002	70912
15°	75529	70482	69068
20°	75147	67882	66326
25°	73393	63816	62958
30°	69714	59242	59015
35°	63461	54057	54535
40°	55643	48385	50164
45°	48001	43033	46069
50°	42029	37783	41727
55°	37241	32477	36730
60°	33550	27309	30435
65°	30229	21926	23305
70°	26525	15967	12830
75°	22613	8292	3396
80°	17421	2255	568
85°	11216	0	0



TEST NUMBER: P584735
 CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.5	5.0
10°-20°	628.4	14.0
20°-30°	891.9	19.8
30°-40°	938.8	20.9
40°-50°	798.6	17.7
50°-60°	577.1	12.8
60°-70°	328.3	7.3
70°-80°	103.4	2.3
80°-90°	12.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1743.8	38.7
0°-40°	2682.6	59.6
0°-60°	4058.4	90.1
0°-90°	4502.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4502.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2369	2369	2369	2369	2369	
5°	2391	2379	2350	2334	2328	228
15°	2366	2306	2208	2167	2164	666
25°	2157	2050	1876	1844	1850	988
35°	1686	1588	1436	1426	1449	1049
45°	1101	1060	987	1012	1056	856
55°	693	642	604	639	683	625
65°	414	357	300	297	319	411
75°	190	146	70	32	28	204
85°	32	19	0	0	0	41
90°	0	0	0	0	0	



TEST NUMBER: P584735

CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1
2.5°	2381.8	2384.9	2378.6	2378.6	2384.9	2378.6	2381.8	2381.8	2378.6	2378.6	2375.4
5°	2391.3	2388.1	2388.1	2388.1	2391.3	2384.9	2381.8	2384.9	2378.6	2378.6	2378.6
7.5°	2394.4	2394.4	2391.3	2388.1	2388.1	2388.1	2384.9	2381.8	2378.6	2372.3	2369.1
10°	2388.1	2388.1	2391.3	2384.9	2384.9	2378.6	2378.6	2372.3	2372.3	2365.9	2356.4
12.5°	2381.8	2378.6	2378.6	2372.3	2372.3	2365.9	2365.9	2356.4	2353.3	2343.8	2334.3
15°	2365.9	2362.8	2356.4	2353.3	2350.1	2346.9	2340.6	2337.4	2327.9	2315.3	2305.9
17.5°	2334.3	2331.1	2327.9	2321.6	2315.3	2312.2	2309.1	2299.5	2286.9	2277.4	2261.5
20°	2290.0	2286.9	2286.9	2277.4	2274.2	2264.7	2261.5	2248.9	2239.4	2220.5	2207.8
22.5°	2229.9	2233.0	2226.7	2220.5	2214.2	2204.7	2198.3	2185.7	2169.8	2150.8	2135.0
25°	2157.1	2160.3	2154.0	2147.6	2138.1	2131.9	2125.6	2106.6	2090.8	2068.6	2049.6
27.5°	2065.4	2065.4	2065.4	2059.1	2043.2	2040.2	2033.9	2014.9	1992.7	1973.7	1954.7
30°	1957.9	1954.7	1954.7	1945.3	1939.0	1926.3	1916.8	1901.0	1885.1	1863.0	1840.9
32.5°	1828.2	1831.4	1821.9	1815.6	1806.1	1806.1	1793.4	1780.7	1761.8	1739.7	1717.5
35°	1685.8	1689.0	1682.7	1679.6	1663.8	1660.6	1657.4	1641.6	1628.9	1613.1	1587.9
37.5°	1540.4	1537.2	1534.0	1534.0	1524.5	1518.2	1511.9	1502.4	1483.5	1470.8	1458.2
40°	1382.3	1382.3	1382.3	1379.1	1375.9	1369.6	1366.4	1360.1	1347.4	1334.8	1325.3
42.5°	1239.9	1239.9	1236.7	1233.5	1227.2	1230.4	1224.1	1217.8	1205.1	1195.6	1189.3
45°	1100.7	1100.7	1100.7	1103.9	1097.6	1088.1	1088.1	1081.7	1075.4	1069.1	1059.6
47.5°	977.3	986.8	980.5	977.3	980.5	967.8	967.8	961.5	955.2	949.0	936.3
50°	876.1	876.1	876.1	869.8	866.6	866.6	857.2	850.9	847.7	841.4	828.7
52.5°	784.4	778.1	778.1	774.9	771.7	765.5	765.5	759.2	746.5	740.2	730.7
55°	692.7	692.7	689.5	686.3	683.2	680.1	676.9	667.4	661.1	651.6	642.1
57.5°	610.4	616.8	613.6	607.3	600.9	600.9	594.6	588.4	578.9	569.4	559.9
60°	544.0	540.9	540.9	537.7	531.4	528.2	525.0	515.5	506.0	496.6	487.1
62.5°	474.5	474.5	474.5	468.1	461.8	458.6	455.5	449.1	436.5	427.0	420.6
65°	414.3	411.1	408.1	404.9	401.8	395.4	392.3	385.9	376.4	366.9	357.4
67.5°	354.2	351.1	351.1	347.9	338.4	335.2	335.2	325.7	316.4	306.9	297.4
70°	294.2	294.2	294.2	287.9	284.7	281.5	278.4	272.0	262.5	253.0	243.5
72.5°	243.5	240.3	240.3	237.2	227.7	224.6	221.5	215.1	205.6	199.3	193.0
75°	189.8	189.8	186.6	183.5	180.3	177.1	174.0	167.6	158.1	148.6	145.5
77.5°	145.5	142.3	142.3	139.1	132.9	129.7	129.7	123.4	113.9	107.6	101.2
80°	98.1	101.2	98.1	94.9	91.7	88.6	85.4	82.2	75.9	69.6	63.2
82.5°	60.1	63.2	60.1	60.1	56.9	53.7	53.7	47.4	44.3	41.2	38.0
85°	31.7	31.7	31.7	31.7	28.5	28.5	28.5	25.3	22.2	19.0	19.0
87.5°	9.5	12.7	9.5	9.5	9.5	9.5	9.5	9.5	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584735

CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1
2.5°	2378.6	2375.4	2372.3	2372.3	2372.3	2372.3	2372.3	2369.1	2365.9	2365.9	2365.9
5°	2372.3	2372.3	2372.3	2369.1	2365.9	2365.9	2359.6	2356.4	2353.3	2350.1	2346.9
7.5°	2365.9	2359.6	2356.4	2353.3	2350.1	2350.1	2343.8	2337.4	2337.4	2331.1	2324.8
10°	2346.9	2343.8	2337.4	2331.1	2327.9	2324.8	2318.4	2309.1	2305.9	2299.5	2293.2
12.5°	2324.8	2318.4	2312.2	2299.5	2296.4	2293.2	2280.5	2271.0	2264.7	2261.5	2245.7
15°	2296.4	2283.7	2274.2	2258.4	2255.2	2248.9	2239.4	2229.9	2217.3	2207.8	2201.5
17.5°	2245.7	2233.0	2217.3	2201.5	2195.2	2195.2	2179.3	2166.6	2150.8	2144.5	2131.9
20°	2185.7	2169.8	2157.1	2138.1	2128.8	2119.3	2109.8	2090.8	2078.1	2068.6	2052.8
22.5°	2116.1	2093.9	2078.1	2059.1	2043.2	2033.9	2018.0	2002.2	1986.4	1976.9	1964.2
25°	2027.5	2008.5	1983.2	1964.2	1954.7	1942.1	1923.1	1907.3	1891.5	1875.6	1869.3
27.5°	1929.5	1904.1	1882.0	1859.9	1850.4	1840.9	1818.7	1799.7	1787.1	1771.2	1765.0
30°	1821.9	1796.6	1771.2	1752.3	1742.8	1727.0	1714.3	1692.2	1676.5	1663.8	1647.9
32.5°	1698.5	1679.6	1657.4	1628.9	1622.6	1609.9	1590.9	1581.6	1562.6	1553.1	1540.4
35°	1565.7	1553.1	1530.9	1508.7	1499.2	1493.0	1477.2	1458.2	1445.5	1436.0	1429.7
37.5°	1439.2	1423.3	1401.3	1385.4	1379.1	1369.6	1350.6	1341.1	1328.4	1322.1	1309.5
40°	1303.2	1287.4	1271.5	1262.0	1252.5	1246.2	1233.5	1224.1	1211.5	1202.0	1198.8
42.5°	1170.3	1160.8	1148.1	1135.5	1132.4	1122.9	1116.6	1107.1	1097.6	1094.4	1084.9
45°	1050.1	1040.7	1028.0	1015.3	1012.2	1005.8	1002.7	993.2	986.8	986.8	986.8
47.5°	930.0	920.5	907.8	901.5	904.6	891.9	891.9	888.8	882.4	882.4	885.6
50°	822.4	809.7	806.6	800.2	793.9	787.6	790.7	781.2	781.2	787.6	784.4
52.5°	721.2	708.5	705.3	699.0	695.8	695.8	692.7	692.7	689.5	692.7	692.7
55°	629.4	619.9	613.6	607.3	604.1	604.1	604.1	600.9	597.8	604.1	607.3
57.5°	547.2	544.0	537.7	528.2	525.0	521.9	518.7	518.7	518.7	518.7	521.9
60°	474.5	468.1	461.8	452.3	452.3	449.1	446.0	442.8	442.8	442.8	442.8
62.5°	411.1	401.8	392.3	385.9	382.7	379.6	376.4	370.1	370.1	370.1	370.1
65°	347.9	338.4	332.1	325.7	319.4	319.4	313.2	310.0	303.7	300.5	294.2
67.5°	287.9	281.5	275.2	265.7	262.5	259.4	253.0	249.8	240.3	237.2	234.0
70°	234.0	224.6	218.3	212.0	208.8	202.5	196.1	189.8	183.5	177.1	170.8
72.5°	183.5	174.0	167.6	161.3	155.0	155.0	145.5	139.1	129.7	123.4	113.9
75°	136.1	126.6	120.2	110.7	107.6	104.4	94.9	88.6	79.1	69.6	63.2
77.5°	91.7	85.4	79.1	69.6	63.2	63.2	53.7	47.4	41.2	31.7	28.5
80°	56.9	50.6	44.3	38.0	38.0	31.7	28.5	22.2	15.8	12.7	9.5
82.5°	31.7	28.5	25.3	19.0	19.0	15.8	12.7	9.5	6.3	3.2	3.2
85°	15.8	12.7	9.5	9.5	6.3	6.3	6.3	3.2	3.2	0.0	0.0
87.5°	6.3	3.2	3.2	3.2	3.2	3.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584735

CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1
2.5°	2362.8	2362.8	2359.6	2359.6	2359.6	2356.4	2359.6	2356.4	2356.4	2356.4	2359.6
5°	2350.1	2343.8	2343.8	2340.6	2340.6	2337.4	2340.6	2337.4	2334.3	2331.1	2334.3
7.5°	2324.8	2318.4	2315.3	2312.2	2312.2	2312.2	2309.1	2305.9	2309.1	2299.5	2305.9
10°	2290.0	2286.9	2280.5	2277.4	2274.2	2277.4	2274.2	2267.9	2267.9	2267.9	2264.7
12.5°	2245.7	2239.4	2236.2	2233.0	2226.7	2226.7	2229.9	2223.7	2223.7	2217.3	2217.3
15°	2192.0	2185.7	2179.3	2179.3	2173.0	2173.0	2169.8	2169.8	2166.6	2163.5	2163.5
17.5°	2125.6	2116.1	2109.8	2112.9	2109.8	2106.6	2106.6	2100.3	2097.1	2100.3	2100.3
20°	2046.4	2040.2	2033.9	2037.0	2030.7	2027.5	2030.7	2021.2	2024.4	2024.4	2024.4
22.5°	1957.9	1954.7	1945.3	1945.3	1939.0	1935.8	1939.0	1939.0	1942.1	1939.0	1939.0
25°	1859.9	1853.6	1847.2	1847.2	1844.1	1840.9	1844.1	1847.2	1844.1	1847.2	1847.2
27.5°	1755.5	1746.0	1746.0	1739.7	1739.7	1742.8	1739.7	1742.8	1746.0	1746.0	1752.3
30°	1641.6	1638.4	1635.3	1632.1	1632.1	1635.3	1635.3	1635.3	1638.4	1644.8	1644.8
32.5°	1534.0	1527.7	1521.4	1521.4	1527.7	1524.5	1527.7	1527.7	1534.0	1534.0	1540.4
35°	1417.0	1417.0	1410.6	1413.8	1413.8	1413.8	1413.8	1420.2	1426.5	1429.7	1436.0
37.5°	1309.5	1300.0	1303.2	1303.2	1306.4	1303.2	1312.7	1312.7	1318.9	1318.9	1325.3
40°	1192.5	1192.5	1195.6	1192.5	1195.6	1195.6	1202.0	1208.3	1211.5	1217.8	1221.0
42.5°	1081.7	1088.1	1081.7	1084.9	1088.1	1091.2	1094.4	1097.6	1110.2	1116.6	1126.1
45°	980.5	983.7	986.8	990.0	986.8	993.2	996.3	1002.7	1012.2	1015.3	1018.5
47.5°	882.4	885.6	888.8	891.9	891.9	898.3	901.5	907.8	914.1	917.3	920.5
50°	787.6	793.9	797.1	797.1	800.2	806.6	812.9	812.9	819.2	828.7	831.9
52.5°	702.2	702.2	708.5	711.7	714.8	714.8	724.3	727.5	730.7	737.0	743.3
55°	607.3	616.8	619.9	619.9	626.3	632.6	635.8	638.9	638.9	651.6	651.6
57.5°	525.0	528.2	534.5	534.5	534.5	544.0	544.0	550.4	553.5	556.7	563.0
60°	442.8	449.1	449.1	452.3	449.1	455.5	458.6	465.0	468.1	471.3	474.5
62.5°	366.9	366.9	370.1	370.1	370.1	370.1	376.4	376.4	382.7	385.9	389.1
65°	294.2	294.2	294.2	294.2	294.2	294.2	294.2	294.2	297.4	297.4	303.7
67.5°	227.7	224.6	218.3	221.5	218.3	218.3	215.1	215.1	218.3	218.3	224.6
70°	164.5	161.3	155.0	155.0	151.8	148.6	145.5	142.3	139.1	139.1	139.1
72.5°	107.6	101.2	91.7	88.6	88.6	82.2	75.9	72.7	72.7	72.7	72.7
75°	53.7	47.4	41.2	38.0	38.0	31.7	34.8	31.7	31.7	31.7	31.7
77.5°	22.2	15.8	12.7	12.7	12.7	9.5	9.5	9.5	9.5	9.5	9.5
80°	6.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584735

CATALOG NUMBER: HCC8W45D010SL-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1	2369.1
2.5°	2356.4	2356.4	2350.1	2353.3	2353.3	2353.3	2353.3	2353.3
5°	2327.9	2331.1	2327.9	2331.1	2331.1	2327.9	2327.9	2327.9
7.5°	2299.5	2302.7	2299.5	2302.7	2302.7	2302.7	2299.5	2299.5
10°	2264.7	2264.7	2264.7	2264.7	2264.7	2261.5	2264.7	2264.7
12.5°	2217.3	2217.3	2217.3	2220.5	2220.5	2217.3	2217.3	2214.2
15°	2166.6	2160.3	2163.5	2166.6	2163.5	2163.5	2163.5	2163.5
17.5°	2097.1	2100.3	2097.1	2097.1	2097.1	2097.1	2100.3	2097.1
20°	2024.4	2024.4	2027.5	2024.4	2024.4	2024.4	2024.4	2021.2
22.5°	1942.1	1939.0	1939.0	1942.1	1942.1	1939.0	1942.1	1942.1
25°	1850.4	1853.6	1850.4	1850.4	1853.6	1853.6	1853.6	1850.4
27.5°	1752.3	1755.5	1758.7	1755.5	1755.5	1755.5	1758.7	1761.8
30°	1651.1	1657.4	1651.1	1651.1	1657.4	1654.3	1657.4	1657.4
32.5°	1543.6	1553.1	1546.7	1553.1	1553.1	1556.2	1553.1	1556.2
35°	1436.0	1445.5	1445.5	1445.5	1448.7	1451.8	1451.8	1448.7
37.5°	1334.8	1337.9	1337.9	1344.3	1347.4	1350.6	1350.6	1347.4
40°	1230.4	1236.7	1239.9	1239.9	1239.9	1246.2	1252.5	1246.2
42.5°	1129.2	1132.4	1135.5	1135.5	1141.8	1145.0	1148.1	1148.1
45°	1031.2	1037.5	1040.7	1043.9	1046.9	1053.2	1050.1	1056.4
47.5°	930.0	939.5	942.6	945.8	952.1	955.2	958.3	961.5
50°	838.2	844.6	844.6	850.9	860.4	860.4	866.6	869.8
52.5°	746.5	749.7	752.8	756.0	762.3	768.7	768.7	774.9
55°	657.9	661.1	661.1	664.3	667.4	680.1	683.2	683.2
57.5°	566.2	566.2	572.5	575.7	578.9	585.2	585.2	585.2
60°	477.6	480.8	480.8	484.0	487.1	493.5	496.6	493.5
62.5°	389.1	392.3	392.3	395.4	401.8	404.9	401.8	401.8
65°	306.9	310.0	310.0	313.2	319.4	319.4	316.4	319.4
67.5°	224.6	224.6	224.6	224.6	224.6	224.6	224.6	224.6
70°	142.3	139.1	136.1	139.1	139.1	139.1	136.1	142.3
72.5°	69.6	72.7	72.7	72.7	72.7	72.7	72.7	69.6
75°	31.7	31.7	28.5	28.5	28.5	31.7	31.7	28.5
77.5°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
80°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)