

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584573

Luminaire Tested: **HCC8W40D010BZ-HM82555840-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584573  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010BZ-HM82555840-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4716.9 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584573  
CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	78811	78811	78811
5°	81583	78360	75246
10°	83393	76990	71016
15°	84580	74396	66316
20°	84326	70783	61568
25°	82240	66194	56517
30°	77915	60877	51865
35°	70888	55092	47127
40°	62257	49001	42577
45°	54293	43099	37962
50°	47244	37764	33437
55°	42133	33187	29085
60°	38280	29085	24805
65°	34410	25304	22524
70°	30645	21575	20322
75°	26855	18181	17359
80°	22783	14775	15414
85°	17195	11039	12242



TEST NUMBER: P584573  
 CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	239.4	5.1
10°-20°	659.6	14.0
20°-30°	915.6	19.4
30°-40°	946.6	20.1
40°-50°	792.6	16.8
50°-60°	575.4	12.2
60°-70°	363.1	7.7
70°-80°	179.9	3.8
80°-90°	44.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1814.6	38.5
0°-40°	2761.2	58.5
0°-60°	4129.2	87.5
0°-90°	4716.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4716.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2556	2556	2556	2556	2556	
5°	2636	2604	2532	2462	2431	252
15°	2649	2549	2330	2143	2077	746
25°	2417	2261	1946	1734	1661	1108
35°	1883	1744	1464	1297	1252	1173
45°	1245	1155	988	891	870	963
55°	784	714	617	565	541	707
65°	472	413	347	305	309	470
75°	225	187	153	146	146	242
85°	49	38	31	35	35	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2597.4	2597.4	2600.9	2597.4	2597.4	2597.4	2594.0	2594.0	2590.5	2590.5	2583.6
5°	2635.6	2628.6	2635.6	2628.6	2628.6	2628.6	2625.1	2618.2	2614.8	2607.9	2604.3
7.5°	2652.9	2649.4	2649.4	2646.0	2646.0	2642.5	2639.1	2635.6	2621.7	2618.2	2607.9
10°	2663.3	2659.9	2659.9	2656.4	2649.4	2649.4	2642.5	2639.1	2621.7	2614.8	2600.9
12.5°	2659.9	2659.9	2659.9	2656.4	2646.0	2642.5	2635.6	2625.1	2611.3	2597.4	2583.6
15°	2649.4	2649.4	2642.5	2639.1	2628.6	2621.7	2618.2	2600.9	2587.1	2569.7	2548.9
17.5°	2614.8	2614.8	2611.3	2604.3	2594.0	2587.1	2580.0	2562.8	2548.9	2521.1	2500.3
20°	2569.7	2566.2	2562.8	2552.3	2542.0	2538.5	2528.0	2503.8	2486.5	2465.7	2438.0
22.5°	2503.8	2500.3	2496.9	2490.0	2472.6	2465.7	2458.8	2441.4	2410.2	2389.4	2354.7
25°	2417.1	2417.1	2410.2	2399.8	2382.4	2375.5	2365.1	2347.8	2320.0	2288.8	2261.0
27.5°	2316.6	2313.1	2302.6	2295.7	2281.8	2271.5	2254.1	2233.3	2205.5	2181.3	2146.6
30°	2188.2	2188.2	2181.3	2170.9	2153.5	2146.6	2132.7	2108.4	2080.7	2049.5	2025.3
32.5°	2042.5	2042.5	2032.2	2025.3	2014.8	1997.5	1994.1	1966.2	1942.0	1917.7	1890.0
35°	1883.1	1886.5	1879.6	1865.7	1848.4	1848.4	1841.4	1817.1	1789.4	1765.1	1744.3
37.5°	1723.5	1713.1	1709.7	1702.8	1692.3	1678.5	1671.5	1661.1	1636.8	1619.5	1588.3
40°	1546.6	1550.1	1543.2	1536.3	1532.8	1522.4	1518.9	1501.5	1484.3	1463.5	1449.5
42.5°	1387.2	1387.2	1387.2	1380.2	1373.3	1362.9	1359.5	1349.0	1328.2	1314.4	1293.5
45°	1245.0	1234.5	1234.5	1231.1	1227.6	1220.7	1210.2	1203.3	1189.5	1179.1	1154.8
47.5°	1106.2	1109.7	1106.2	1102.8	1092.4	1089.0	1085.4	1071.6	1057.7	1047.3	1029.9
50°	984.8	991.9	984.8	984.8	977.9	974.5	967.6	957.1	946.8	929.4	912.0
52.5°	884.3	884.3	880.8	877.4	866.9	860.0	856.6	853.1	835.7	821.9	808.0
55°	783.7	787.2	787.2	776.8	773.4	766.4	762.9	752.6	745.5	724.8	714.4
57.5°	697.0	693.5	697.0	690.1	683.2	676.3	672.8	665.8	655.5	641.5	627.7
60°	620.7	613.8	613.8	610.4	603.4	600.0	593.0	582.6	572.2	558.3	547.9
62.5°	544.4	541.0	537.5	534.1	527.2	523.6	520.1	509.8	499.3	489.0	478.6
65°	471.6	471.6	468.1	461.2	457.8	454.3	450.8	443.9	430.1	423.0	412.7
67.5°	405.8	402.2	402.2	395.3	388.4	385.0	385.0	377.9	367.6	357.2	350.2
70°	339.9	343.3	339.9	336.4	329.4	329.4	322.5	319.0	305.1	301.7	291.3
72.5°	280.8	280.8	277.4	277.4	270.5	267.0	267.0	260.1	253.1	246.2	239.3
75°	225.4	225.4	225.4	221.9	218.5	211.6	211.6	208.1	201.1	194.2	187.3
77.5°	176.8	173.4	173.4	169.9	166.5	163.0	163.0	159.6	152.6	149.1	142.2
80°	128.3	124.8	124.8	124.8	117.9	121.4	117.9	114.5	111.0	107.5	104.0
82.5°	83.2	86.8	86.8	83.2	79.7	79.7	79.7	76.3	76.3	72.8	69.4
85°	48.6	48.6	48.6	48.6	45.1	45.1	45.1	41.6	41.6	41.6	38.2
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2583.6	2576.6	2573.1	2569.7	2569.7	2566.2	2562.8	2555.8	2555.8	2548.9	2545.4
5°	2597.4	2587.1	2580.0	2573.1	2569.7	2562.8	2555.8	2545.4	2542.0	2531.5	2521.1
7.5°	2600.9	2583.6	2576.6	2562.8	2555.8	2548.9	2535.1	2524.6	2510.8	2500.3	2486.5
10°	2587.1	2573.1	2555.8	2538.5	2535.1	2524.6	2503.8	2490.0	2472.6	2458.8	2438.0
12.5°	2566.2	2545.4	2528.0	2507.2	2496.9	2486.5	2465.7	2444.9	2420.6	2396.3	2375.5
15°	2531.5	2507.2	2483.1	2458.8	2444.9	2434.5	2410.2	2386.0	2361.7	2330.4	2309.6
17.5°	2479.5	2451.8	2427.5	2396.3	2382.4	2372.0	2340.8	2313.1	2281.8	2250.6	2229.8
20°	2413.7	2378.9	2351.2	2316.6	2306.1	2288.8	2257.5	2226.4	2191.7	2157.0	2132.7
22.5°	2326.9	2292.3	2261.0	2226.4	2209.0	2191.7	2160.4	2122.4	2087.6	2059.9	2035.6
25°	2226.4	2195.2	2157.0	2125.8	2105.0	2084.2	2049.5	2018.4	1987.1	1945.5	1921.3
27.5°	2115.3	2077.3	2049.5	2007.9	1987.1	1973.3	1935.1	1893.4	1865.7	1827.6	1799.9
30°	1990.5	1955.9	1924.7	1883.1	1862.2	1848.4	1813.7	1775.6	1747.8	1709.7	1681.9
32.5°	1858.8	1820.6	1782.5	1754.8	1730.5	1716.6	1678.5	1654.2	1619.5	1588.3	1557.1
35°	1716.6	1678.5	1650.6	1612.6	1598.6	1584.8	1553.7	1522.4	1491.2	1463.5	1439.2
37.5°	1564.0	1536.3	1505.1	1477.3	1466.9	1453.0	1414.9	1387.2	1362.9	1335.2	1314.4
40°	1414.9	1390.6	1369.8	1342.1	1324.7	1314.4	1286.6	1262.4	1234.5	1217.3	1196.4
42.5°	1279.6	1251.9	1231.1	1210.2	1193.0	1182.5	1158.2	1141.0	1120.1	1102.8	1078.5
45°	1137.4	1123.6	1099.3	1081.9	1071.6	1057.7	1040.4	1019.6	1002.2	988.3	971.0
47.5°	1012.6	998.8	981.4	960.6	953.7	943.3	925.9	912.0	898.2	884.3	866.9
50°	898.2	880.8	866.9	853.1	846.2	835.7	818.4	811.5	801.1	787.2	776.8
52.5°	794.1	780.3	766.4	749.1	745.5	738.6	728.3	714.4	704.0	697.0	690.1
55°	700.6	686.6	676.3	662.4	658.9	652.0	638.1	631.2	624.3	617.3	610.4
57.5°	617.3	603.4	589.5	582.6	575.7	568.7	565.2	554.9	547.9	544.4	537.5
60°	541.0	527.2	516.7	506.3	502.9	499.3	492.4	485.5	478.6	471.6	468.1
62.5°	468.1	454.3	447.3	440.4	433.5	433.5	426.5	419.6	412.7	409.2	402.2
65°	402.2	395.3	385.0	374.5	371.0	371.0	360.7	357.2	353.7	346.8	339.9
67.5°	339.9	333.0	322.5	319.0	315.6	312.1	308.7	301.7	294.8	291.3	284.4
70°	284.4	277.4	270.5	267.0	263.6	260.1	253.1	249.7	242.8	239.3	235.9
72.5°	228.8	225.4	218.5	215.0	211.6	208.1	204.6	201.1	194.2	190.8	187.3
75°	183.9	180.3	173.4	169.9	166.5	166.5	163.0	156.0	152.6	152.6	149.1
77.5°	138.8	135.3	131.7	128.3	124.8	124.8	121.4	117.9	114.5	114.5	111.0
80°	100.6	97.1	93.7	93.7	93.7	90.2	86.8	86.8	83.2	83.2	79.7
82.5°	65.9	65.9	62.5	62.5	62.5	58.9	58.9	55.5	55.5	55.5	55.5
85°	38.2	38.2	38.2	34.6	34.6	34.6	34.6	34.6	34.6	31.2	34.6
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2542.0	2538.5	2531.5	2531.5	2524.6	2524.6	2521.1	2517.7	2514.2	2510.8	2507.2
5°	2517.7	2503.8	2496.9	2493.4	2486.5	2483.1	2472.6	2465.7	2462.2	2455.2	2448.3
7.5°	2472.6	2458.8	2444.9	2441.4	2438.0	2424.0	2413.7	2403.2	2396.3	2389.4	2382.4
10°	2420.6	2406.7	2389.4	2382.4	2375.5	2358.1	2344.3	2333.8	2320.0	2306.1	2302.6
12.5°	2358.1	2337.4	2316.6	2309.6	2299.2	2281.8	2268.0	2250.6	2240.3	2222.9	2219.5
15°	2285.3	2261.0	2243.7	2226.4	2219.5	2202.1	2177.8	2163.9	2143.2	2136.2	2118.9
17.5°	2198.6	2174.4	2150.1	2143.2	2132.7	2108.4	2084.2	2066.8	2046.1	2035.6	2025.3
20°	2108.4	2077.3	2053.0	2046.1	2032.2	2011.3	1987.1	1969.8	1952.4	1931.6	1921.3
22.5°	2004.4	1969.8	1949.0	1931.6	1928.2	1903.9	1876.2	1862.2	1848.4	1831.1	1817.1
25°	1890.0	1858.8	1834.5	1820.6	1813.7	1792.9	1772.0	1754.8	1733.9	1723.5	1706.2
27.5°	1772.0	1751.3	1720.0	1706.2	1695.8	1678.5	1654.2	1643.7	1622.9	1609.1	1598.6
30°	1657.7	1626.4	1609.1	1591.7	1581.4	1564.0	1543.2	1532.8	1515.5	1501.5	1491.2
32.5°	1532.8	1512.0	1487.7	1480.8	1466.9	1449.5	1435.7	1418.4	1404.4	1390.6	1387.2
35°	1418.4	1390.6	1366.4	1359.5	1349.0	1331.6	1324.7	1314.4	1297.0	1293.5	1279.6
37.5°	1293.5	1279.6	1251.9	1241.5	1238.1	1224.2	1210.2	1203.3	1193.0	1182.5	1179.1
40°	1175.6	1158.2	1144.4	1134.0	1127.0	1116.7	1102.8	1099.3	1092.4	1078.5	1075.0
42.5°	1064.7	1047.3	1033.4	1029.9	1019.6	1009.1	1002.2	991.9	988.3	984.8	977.9
45°	957.1	946.8	932.8	929.4	925.9	912.0	905.1	898.2	891.2	887.7	880.8
47.5°	860.0	849.7	839.2	835.7	828.8	825.4	814.9	811.5	801.1	797.7	794.1
50°	766.4	759.5	752.6	749.1	742.1	738.6	731.7	724.8	717.8	714.4	710.9
52.5°	683.2	676.3	669.3	665.8	662.4	655.5	648.6	641.5	638.1	634.6	631.2
55°	603.4	596.4	593.0	589.5	586.1	582.6	572.2	568.7	565.2	561.8	554.9
57.5°	530.6	523.6	516.7	516.7	513.2	509.8	502.9	495.9	495.9	489.0	482.1
60°	464.7	457.8	450.8	447.3	443.9	437.0	433.5	430.1	426.5	423.0	416.1
62.5°	395.3	391.9	385.0	385.0	377.9	374.5	371.0	367.6	364.1	357.2	353.7
65°	336.4	333.0	325.9	322.5	322.5	319.0	312.1	308.7	305.1	305.1	301.7
67.5°	280.8	277.4	270.5	267.0	267.0	263.6	260.1	260.1	256.6	253.1	256.6
70°	232.3	225.4	225.4	221.9	221.9	218.5	215.0	215.0	215.0	218.5	218.5
72.5°	183.9	180.3	176.8	176.8	176.8	176.8	173.4	173.4	176.8	180.3	180.3
75°	145.7	142.2	142.2	142.2	138.8	138.8	142.2	142.2	145.7	145.7	145.7
77.5°	107.5	107.5	107.5	107.5	107.5	107.5	111.0	111.0	114.5	114.5	114.5
80°	79.7	79.7	79.7	79.7	79.7	83.2	83.2	83.2	83.2	83.2	86.8
82.5°	55.5	55.5	55.5	55.5	55.5	55.5	55.5	58.9	58.9	58.9	58.9
85°	31.2	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2503.8	2503.8	2503.8	2507.2	2500.3	2500.3	2500.3	2500.3
5°	2444.9	2441.4	2438.0	2441.4	2434.5	2434.5	2430.9	2430.9
7.5°	2372.0	2368.6	2365.1	2365.1	2358.1	2358.1	2354.7	2351.2
10°	2292.3	2285.3	2288.8	2281.8	2278.4	2274.9	2271.5	2268.0
12.5°	2205.5	2198.6	2195.2	2188.2	2181.3	2177.8	2181.3	2174.4
15°	2111.9	2101.5	2098.1	2091.1	2084.2	2080.7	2080.7	2077.3
17.5°	2007.9	2001.0	1997.5	1990.5	1987.1	1980.2	1976.7	1973.3
20°	1910.8	1893.4	1897.0	1890.0	1886.5	1872.7	1872.7	1876.2
22.5°	1803.3	1792.9	1786.0	1779.0	1775.6	1768.6	1768.6	1765.1
25°	1695.8	1685.4	1681.9	1674.9	1671.5	1664.6	1661.1	1661.1
27.5°	1591.7	1577.9	1577.9	1570.9	1564.0	1560.6	1557.1	1553.7
30°	1480.8	1470.4	1466.9	1466.9	1463.5	1463.5	1453.0	1456.6
32.5°	1376.7	1369.8	1366.4	1359.5	1359.5	1355.9	1355.9	1345.5
35°	1272.7	1262.4	1265.8	1258.8	1255.3	1251.9	1255.3	1251.9
37.5°	1172.1	1165.2	1165.2	1158.2	1158.2	1154.8	1151.3	1158.2
40°	1071.6	1068.1	1064.7	1061.1	1064.7	1061.1	1054.2	1057.7
42.5°	971.0	971.0	967.6	967.6	964.0	964.0	964.0	964.0
45°	880.8	877.4	877.4	873.9	873.9	873.9	873.9	870.5
47.5°	790.6	787.2	787.2	787.2	783.7	783.7	780.3	783.7
50°	704.0	704.0	700.6	700.6	704.0	700.6	697.0	697.0
52.5°	624.3	624.3	620.7	620.7	617.3	613.8	617.3	617.3
55°	551.4	547.9	544.4	544.4	541.0	537.5	537.5	541.0
57.5°	482.1	478.6	475.0	475.0	468.1	464.7	464.7	464.7
60°	416.1	409.2	409.2	405.8	405.8	402.2	402.2	402.2
62.5°	353.7	350.2	350.2	350.2	350.2	346.8	346.8	346.8
65°	301.7	301.7	301.7	305.1	305.1	308.7	308.7	308.7
67.5°	260.1	263.6	263.6	263.6	267.0	267.0	267.0	263.6
70°	221.9	221.9	221.9	225.4	225.4	225.4	225.4	225.4
72.5°	183.9	183.9	183.9	183.9	183.9	183.9	183.9	183.9
75°	145.7	149.1	149.1	149.1	145.7	149.1	149.1	145.7
77.5°	114.5	114.5	114.5	114.5	114.5	114.5	114.5	114.5
80°	86.8	86.8	86.8	86.8	86.8	86.8	86.8	86.8
82.5°	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9
85°	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)