

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584573

Luminaire Tested: **HCC8W40D010SL-HM82555840-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010SL-HM82555840-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4716.9 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584573
CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78811	78811	78811
5°	81583	78360	75246
10°	83393	76990	71016
15°	84580	74396	66316
20°	84326	70783	61568
25°	82240	66194	56517
30°	77915	60877	51865
35°	70888	55092	47127
40°	62257	49001	42577
45°	54293	43099	37962
50°	47244	37764	33437
55°	42133	33187	29085
60°	38280	29085	24805
65°	34410	25304	22524
70°	30645	21575	20322
75°	26855	18181	17359
80°	22783	14775	15414
85°	17195	11039	12242



TEST NUMBER: P584573
 CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.4	5.1
10°-20°	659.6	14.0
20°-30°	915.6	19.4
30°-40°	946.6	20.1
40°-50°	792.6	16.8
50°-60°	575.4	12.2
60°-70°	363.1	7.7
70°-80°	179.9	3.8
80°-90°	44.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1814.6	38.5
0°-40°	2761.2	58.5
0°-60°	4129.2	87.5
0°-90°	4716.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4716.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2556	2556	2556	2556	2556	
5°	2636	2604	2532	2462	2431	252
15°	2649	2549	2330	2143	2077	746
25°	2417	2261	1946	1734	1661	1108
35°	1883	1744	1464	1297	1252	1173
45°	1245	1155	988	891	870	963
55°	784	714	617	565	541	707
65°	472	413	347	305	309	470
75°	225	187	153	146	146	242
85°	49	38	31	35	35	59
90°	0	0	0	0	0	



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2597.4	2597.4	2600.9	2597.4	2597.4	2597.4	2594.0	2594.0	2590.5	2590.5	2583.6
5°	2635.6	2628.6	2635.6	2628.6	2628.6	2628.6	2625.1	2618.2	2614.8	2607.9	2604.3
7.5°	2652.9	2649.4	2649.4	2646.0	2646.0	2642.5	2639.1	2635.6	2621.7	2618.2	2607.9
10°	2663.3	2659.9	2659.9	2656.4	2649.4	2649.4	2642.5	2639.1	2621.7	2614.8	2600.9
12.5°	2659.9	2659.9	2659.9	2656.4	2646.0	2642.5	2635.6	2625.1	2611.3	2597.4	2583.6
15°	2649.4	2649.4	2642.5	2639.1	2628.6	2621.7	2618.2	2600.9	2587.1	2569.7	2548.9
17.5°	2614.8	2614.8	2611.3	2604.3	2594.0	2587.1	2580.0	2562.8	2548.9	2521.1	2500.3
20°	2569.7	2566.2	2562.8	2552.3	2542.0	2538.5	2528.0	2503.8	2486.5	2465.7	2438.0
22.5°	2503.8	2500.3	2496.9	2490.0	2472.6	2465.7	2458.8	2441.4	2410.2	2389.4	2354.7
25°	2417.1	2417.1	2410.2	2399.8	2382.4	2375.5	2365.1	2347.8	2320.0	2288.8	2261.0
27.5°	2316.6	2313.1	2302.6	2295.7	2281.8	2271.5	2254.1	2233.3	2205.5	2181.3	2146.6
30°	2188.2	2188.2	2181.3	2170.9	2153.5	2146.6	2132.7	2108.4	2080.7	2049.5	2025.3
32.5°	2042.5	2042.5	2032.2	2025.3	2014.8	1997.5	1994.1	1966.2	1942.0	1917.7	1890.0
35°	1883.1	1886.5	1879.6	1865.7	1848.4	1848.4	1841.4	1817.1	1789.4	1765.1	1744.3
37.5°	1723.5	1713.1	1709.7	1702.8	1692.3	1678.5	1671.5	1661.1	1636.8	1619.5	1588.3
40°	1546.6	1550.1	1543.2	1536.3	1532.8	1522.4	1518.9	1501.5	1484.3	1463.5	1449.5
42.5°	1387.2	1387.2	1387.2	1380.2	1373.3	1362.9	1359.5	1349.0	1328.2	1314.4	1293.5
45°	1245.0	1234.5	1234.5	1231.1	1227.6	1220.7	1210.2	1203.3	1189.5	1179.1	1154.8
47.5°	1106.2	1109.7	1106.2	1102.8	1092.4	1089.0	1085.4	1071.6	1057.7	1047.3	1029.9
50°	984.8	991.9	984.8	984.8	977.9	974.5	967.6	957.1	946.8	929.4	912.0
52.5°	884.3	884.3	880.8	877.4	866.9	860.0	856.6	853.1	835.7	821.9	808.0
55°	783.7	787.2	787.2	776.8	773.4	766.4	762.9	752.6	745.5	724.8	714.4
57.5°	697.0	693.5	697.0	690.1	683.2	676.3	672.8	665.8	655.5	641.5	627.7
60°	620.7	613.8	613.8	610.4	603.4	600.0	593.0	582.6	572.2	558.3	547.9
62.5°	544.4	541.0	537.5	534.1	527.2	523.6	520.1	509.8	499.3	489.0	478.6
65°	471.6	471.6	468.1	461.2	457.8	454.3	450.8	443.9	430.1	423.0	412.7
67.5°	405.8	402.2	402.2	395.3	388.4	385.0	385.0	377.9	367.6	357.2	350.2
70°	339.9	343.3	339.9	336.4	329.4	329.4	322.5	319.0	305.1	301.7	291.3
72.5°	280.8	280.8	277.4	277.4	270.5	267.0	267.0	260.1	253.1	246.2	239.3
75°	225.4	225.4	225.4	221.9	218.5	211.6	211.6	208.1	201.1	194.2	187.3
77.5°	176.8	173.4	173.4	169.9	166.5	163.0	163.0	159.6	152.6	149.1	142.2
80°	128.3	124.8	124.8	124.8	117.9	121.4	117.9	114.5	111.0	107.5	104.0
82.5°	83.2	86.8	86.8	83.2	79.7	79.7	79.7	76.3	76.3	72.8	69.4
85°	48.6	48.6	48.6	48.6	45.1	45.1	45.1	41.6	41.6	41.6	38.2
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2583.6	2576.6	2573.1	2569.7	2569.7	2566.2	2562.8	2555.8	2555.8	2548.9	2545.4
5°	2597.4	2587.1	2580.0	2573.1	2569.7	2562.8	2555.8	2545.4	2542.0	2531.5	2521.1
7.5°	2600.9	2583.6	2576.6	2562.8	2555.8	2548.9	2535.1	2524.6	2510.8	2500.3	2486.5
10°	2587.1	2573.1	2555.8	2538.5	2535.1	2524.6	2503.8	2490.0	2472.6	2458.8	2438.0
12.5°	2566.2	2545.4	2528.0	2507.2	2496.9	2486.5	2465.7	2444.9	2420.6	2396.3	2375.5
15°	2531.5	2507.2	2483.1	2458.8	2444.9	2434.5	2410.2	2386.0	2361.7	2330.4	2309.6
17.5°	2479.5	2451.8	2427.5	2396.3	2382.4	2372.0	2340.8	2313.1	2281.8	2250.6	2229.8
20°	2413.7	2378.9	2351.2	2316.6	2306.1	2288.8	2257.5	2226.4	2191.7	2157.0	2132.7
22.5°	2326.9	2292.3	2261.0	2226.4	2209.0	2191.7	2160.4	2122.4	2087.6	2059.9	2035.6
25°	2226.4	2195.2	2157.0	2125.8	2105.0	2084.2	2049.5	2018.4	1987.1	1945.5	1921.3
27.5°	2115.3	2077.3	2049.5	2007.9	1987.1	1973.3	1935.1	1893.4	1865.7	1827.6	1799.9
30°	1990.5	1955.9	1924.7	1883.1	1862.2	1848.4	1813.7	1775.6	1747.8	1709.7	1681.9
32.5°	1858.8	1820.6	1782.5	1754.8	1730.5	1716.6	1678.5	1654.2	1619.5	1588.3	1557.1
35°	1716.6	1678.5	1650.6	1612.6	1598.6	1584.8	1553.7	1522.4	1491.2	1463.5	1439.2
37.5°	1564.0	1536.3	1505.1	1477.3	1466.9	1453.0	1414.9	1387.2	1362.9	1335.2	1314.4
40°	1414.9	1390.6	1369.8	1342.1	1324.7	1314.4	1286.6	1262.4	1234.5	1217.3	1196.4
42.5°	1279.6	1251.9	1231.1	1210.2	1193.0	1182.5	1158.2	1141.0	1120.1	1102.8	1078.5
45°	1137.4	1123.6	1099.3	1081.9	1071.6	1057.7	1040.4	1019.6	1002.2	988.3	971.0
47.5°	1012.6	998.8	981.4	960.6	953.7	943.3	925.9	912.0	898.2	884.3	866.9
50°	898.2	880.8	866.9	853.1	846.2	835.7	818.4	811.5	801.1	787.2	776.8
52.5°	794.1	780.3	766.4	749.1	745.5	738.6	728.3	714.4	704.0	697.0	690.1
55°	700.6	686.6	676.3	662.4	658.9	652.0	638.1	631.2	624.3	617.3	610.4
57.5°	617.3	603.4	589.5	582.6	575.7	568.7	565.2	554.9	547.9	544.4	537.5
60°	541.0	527.2	516.7	506.3	502.9	499.3	492.4	485.5	478.6	471.6	468.1
62.5°	468.1	454.3	447.3	440.4	433.5	433.5	426.5	419.6	412.7	409.2	402.2
65°	402.2	395.3	385.0	374.5	371.0	371.0	360.7	357.2	353.7	346.8	339.9
67.5°	339.9	333.0	322.5	319.0	315.6	312.1	308.7	301.7	294.8	291.3	284.4
70°	284.4	277.4	270.5	267.0	263.6	260.1	253.1	249.7	242.8	239.3	235.9
72.5°	228.8	225.4	218.5	215.0	211.6	208.1	204.6	201.1	194.2	190.8	187.3
75°	183.9	180.3	173.4	169.9	166.5	166.5	163.0	156.0	152.6	152.6	149.1
77.5°	138.8	135.3	131.7	128.3	124.8	124.8	121.4	117.9	114.5	114.5	111.0
80°	100.6	97.1	93.7	93.7	93.7	90.2	86.8	86.8	83.2	83.2	79.7
82.5°	65.9	65.9	62.5	62.5	62.5	58.9	58.9	55.5	55.5	55.5	55.5
85°	38.2	38.2	38.2	34.6	34.6	34.6	34.6	34.6	34.6	31.2	34.6
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2542.0	2538.5	2531.5	2531.5	2524.6	2524.6	2521.1	2517.7	2514.2	2510.8	2507.2
5°	2517.7	2503.8	2496.9	2493.4	2486.5	2483.1	2472.6	2465.7	2462.2	2455.2	2448.3
7.5°	2472.6	2458.8	2444.9	2441.4	2438.0	2424.0	2413.7	2403.2	2396.3	2389.4	2382.4
10°	2420.6	2406.7	2389.4	2382.4	2375.5	2358.1	2344.3	2333.8	2320.0	2306.1	2302.6
12.5°	2358.1	2337.4	2316.6	2309.6	2299.2	2281.8	2268.0	2250.6	2240.3	2222.9	2219.5
15°	2285.3	2261.0	2243.7	2226.4	2219.5	2202.1	2177.8	2163.9	2143.2	2136.2	2118.9
17.5°	2198.6	2174.4	2150.1	2143.2	2132.7	2108.4	2084.2	2066.8	2046.1	2035.6	2025.3
20°	2108.4	2077.3	2053.0	2046.1	2032.2	2011.3	1987.1	1969.8	1952.4	1931.6	1921.3
22.5°	2004.4	1969.8	1949.0	1931.6	1928.2	1903.9	1876.2	1862.2	1848.4	1831.1	1817.1
25°	1890.0	1858.8	1834.5	1820.6	1813.7	1792.9	1772.0	1754.8	1733.9	1723.5	1706.2
27.5°	1772.0	1751.3	1720.0	1706.2	1695.8	1678.5	1654.2	1643.7	1622.9	1609.1	1598.6
30°	1657.7	1626.4	1609.1	1591.7	1581.4	1564.0	1543.2	1532.8	1515.5	1501.5	1491.2
32.5°	1532.8	1512.0	1487.7	1480.8	1466.9	1449.5	1435.7	1418.4	1404.4	1390.6	1387.2
35°	1418.4	1390.6	1366.4	1359.5	1349.0	1331.6	1324.7	1314.4	1297.0	1293.5	1279.6
37.5°	1293.5	1279.6	1251.9	1241.5	1238.1	1224.2	1210.2	1203.3	1193.0	1182.5	1179.1
40°	1175.6	1158.2	1144.4	1134.0	1127.0	1116.7	1102.8	1099.3	1092.4	1078.5	1075.0
42.5°	1064.7	1047.3	1033.4	1029.9	1019.6	1009.1	1002.2	991.9	988.3	984.8	977.9
45°	957.1	946.8	932.8	929.4	925.9	912.0	905.1	898.2	891.2	887.7	880.8
47.5°	860.0	849.7	839.2	835.7	828.8	825.4	814.9	811.5	801.1	797.7	794.1
50°	766.4	759.5	752.6	749.1	742.1	738.6	731.7	724.8	717.8	714.4	710.9
52.5°	683.2	676.3	669.3	665.8	662.4	655.5	648.6	641.5	638.1	634.6	631.2
55°	603.4	596.4	593.0	589.5	586.1	582.6	572.2	568.7	565.2	561.8	554.9
57.5°	530.6	523.6	516.7	516.7	513.2	509.8	502.9	495.9	495.9	489.0	482.1
60°	464.7	457.8	450.8	447.3	443.9	437.0	433.5	430.1	426.5	423.0	416.1
62.5°	395.3	391.9	385.0	385.0	377.9	374.5	371.0	367.6	364.1	357.2	353.7
65°	336.4	333.0	325.9	322.5	322.5	319.0	312.1	308.7	305.1	305.1	301.7
67.5°	280.8	277.4	270.5	267.0	267.0	263.6	260.1	260.1	256.6	253.1	256.6
70°	232.3	225.4	225.4	221.9	221.9	218.5	215.0	215.0	215.0	218.5	218.5
72.5°	183.9	180.3	176.8	176.8	176.8	176.8	173.4	173.4	176.8	180.3	180.3
75°	145.7	142.2	142.2	142.2	138.8	138.8	142.2	142.2	145.7	145.7	145.7
77.5°	107.5	107.5	107.5	107.5	107.5	107.5	111.0	111.0	114.5	114.5	114.5
80°	79.7	79.7	79.7	79.7	79.7	83.2	83.2	83.2	83.2	83.2	86.8
82.5°	55.5	55.5	55.5	55.5	55.5	55.5	55.5	58.9	58.9	58.9	58.9
85°	31.2	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584573

CATALOG NUMBER: HCC8W40D010SL-HM82555840-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8	2555.8
2.5°	2503.8	2503.8	2503.8	2507.2	2500.3	2500.3	2500.3	2500.3
5°	2444.9	2441.4	2438.0	2441.4	2434.5	2434.5	2430.9	2430.9
7.5°	2372.0	2368.6	2365.1	2365.1	2358.1	2358.1	2354.7	2351.2
10°	2292.3	2285.3	2288.8	2281.8	2278.4	2274.9	2271.5	2268.0
12.5°	2205.5	2198.6	2195.2	2188.2	2181.3	2177.8	2181.3	2174.4
15°	2111.9	2101.5	2098.1	2091.1	2084.2	2080.7	2080.7	2077.3
17.5°	2007.9	2001.0	1997.5	1990.5	1987.1	1980.2	1976.7	1973.3
20°	1910.8	1893.4	1897.0	1890.0	1886.5	1872.7	1872.7	1876.2
22.5°	1803.3	1792.9	1786.0	1779.0	1775.6	1768.6	1768.6	1765.1
25°	1695.8	1685.4	1681.9	1674.9	1671.5	1664.6	1661.1	1661.1
27.5°	1591.7	1577.9	1577.9	1570.9	1564.0	1560.6	1557.1	1553.7
30°	1480.8	1470.4	1466.9	1466.9	1463.5	1463.5	1453.0	1456.6
32.5°	1376.7	1369.8	1366.4	1359.5	1359.5	1355.9	1355.9	1345.5
35°	1272.7	1262.4	1265.8	1258.8	1255.3	1251.9	1255.3	1251.9
37.5°	1172.1	1165.2	1165.2	1158.2	1158.2	1154.8	1151.3	1158.2
40°	1071.6	1068.1	1064.7	1061.1	1064.7	1061.1	1054.2	1057.7
42.5°	971.0	971.0	967.6	967.6	964.0	964.0	964.0	964.0
45°	880.8	877.4	877.4	873.9	873.9	873.9	873.9	870.5
47.5°	790.6	787.2	787.2	787.2	783.7	783.7	780.3	783.7
50°	704.0	704.0	700.6	700.6	704.0	700.6	697.0	697.0
52.5°	624.3	624.3	620.7	620.7	617.3	613.8	617.3	617.3
55°	551.4	547.9	544.4	544.4	541.0	537.5	537.5	541.0
57.5°	482.1	478.6	475.0	475.0	468.1	464.7	464.7	464.7
60°	416.1	409.2	409.2	405.8	405.8	402.2	402.2	402.2
62.5°	353.7	350.2	350.2	350.2	350.2	346.8	346.8	346.8
65°	301.7	301.7	301.7	305.1	305.1	308.7	308.7	308.7
67.5°	260.1	263.6	263.6	263.6	267.0	267.0	267.0	263.6
70°	221.9	221.9	221.9	225.4	225.4	225.4	225.4	225.4
72.5°	183.9	183.9	183.9	183.9	183.9	183.9	183.9	183.9
75°	145.7	149.1	149.1	149.1	145.7	149.1	149.1	145.7
77.5°	114.5	114.5	114.5	114.5	114.5	114.5	114.5	114.5
80°	86.8	86.8	86.8	86.8	86.8	86.8	86.8	86.8
82.5°	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9
85°	34.6	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)