

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584752

Luminaire Tested: **HCC8W45D010MB-HM82555935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010MB-HM82555935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4526.9 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584752
CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584752

CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73449	73449	73449
5°	74417	73138	72448
10°	75177	72390	71294
15°	75938	70862	69441
20°	75554	68246	66684
25°	73791	64159	63298
30°	70088	59559	59335
35°	63807	54347	54829
40°	55941	48643	50434
45°	48258	43265	46322
50°	42259	37985	41952
55°	37439	32655	36929
60°	33735	27457	30596
65°	30390	22035	23436
70°	26660	16057	12902
75°	22732	8328	3407
80°	17492	2255	568
85°	11251	0	0



TEST NUMBER: P584752
 CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.7	5.0
10°-20°	631.7	14.0
20°-30°	896.7	19.8
30°-40°	943.9	20.9
40°-50°	803.0	17.7
50°-60°	580.2	12.8
60°-70°	330.0	7.3
70°-80°	104.0	2.3
80°-90°	12.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1753.2	38.7
0°-40°	2697.0	59.6
0°-60°	4080.2	90.1
0°-90°	4526.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4526.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2382	2382	2382	2382	2382	
5°	2404	2391	2363	2347	2340	229
15°	2379	2318	2220	2178	2175	670
25°	2169	2061	1886	1854	1860	993
35°	1695	1596	1444	1434	1456	1055
45°	1107	1065	992	1018	1062	860
55°	696	646	607	642	687	628
65°	416	359	302	299	321	413
75°	191	146	70	32	29	205
85°	32	19	0	0	0	41
90°	0	0	0	0	0	



TEST NUMBER: P584752

CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9
2.5°	2394.6	2397.7	2391.4	2391.4	2397.7	2391.4	2394.6	2394.6	2391.4	2391.4	2388.2
5°	2404.1	2400.9	2400.9	2400.9	2404.1	2397.7	2394.6	2397.7	2391.4	2391.4	2391.4
7.5°	2407.3	2407.3	2404.1	2400.9	2400.9	2400.9	2397.7	2394.6	2391.4	2385.1	2381.9
10°	2400.9	2400.9	2404.1	2397.7	2397.7	2391.4	2391.4	2385.1	2385.1	2378.7	2369.1
12.5°	2394.6	2391.4	2391.4	2385.1	2385.1	2378.7	2378.7	2369.1	2365.9	2356.4	2346.8
15°	2378.7	2375.4	2369.1	2365.9	2362.8	2359.6	2353.3	2350.1	2340.5	2327.8	2318.2
17.5°	2346.8	2343.7	2340.5	2334.2	2327.8	2324.7	2321.5	2311.9	2299.2	2289.6	2273.7
20°	2302.4	2299.2	2299.2	2289.6	2286.4	2276.9	2273.7	2261.0	2251.5	2232.3	2219.7
22.5°	2242.0	2245.1	2238.8	2232.3	2226.0	2216.5	2210.2	2197.4	2181.5	2162.4	2146.6
25°	2168.8	2171.9	2165.6	2159.3	2149.8	2143.3	2137.0	2118.0	2102.0	2079.7	2060.7
27.5°	2076.6	2076.6	2076.6	2070.2	2054.3	2051.1	2044.8	2025.7	2003.5	1984.4	1965.2
30°	1968.4	1965.2	1965.2	1955.7	1949.4	1936.6	1927.1	1911.2	1895.3	1873.0	1850.8
32.5°	1838.1	1841.3	1831.8	1825.3	1815.8	1815.8	1803.1	1790.3	1771.2	1749.1	1726.8
35°	1695.0	1698.2	1691.8	1688.7	1672.7	1669.5	1666.4	1650.4	1637.7	1621.8	1596.3
37.5°	1548.7	1545.5	1542.4	1542.4	1532.8	1526.4	1520.1	1510.5	1491.5	1478.7	1466.0
40°	1389.7	1389.7	1389.7	1386.5	1383.3	1377.0	1373.8	1367.4	1354.7	1342.0	1332.4
42.5°	1246.5	1246.5	1243.4	1240.2	1233.9	1237.0	1230.7	1224.4	1211.6	1202.1	1195.8
45°	1106.6	1106.6	1106.6	1109.9	1103.4	1093.9	1093.9	1087.6	1081.3	1074.8	1065.3
47.5°	982.6	992.1	985.8	982.6	985.8	973.1	973.1	966.8	960.3	954.0	941.3
50°	880.9	880.9	880.9	874.5	871.3	871.3	861.8	855.5	852.3	845.9	833.2
52.5°	788.6	782.3	782.3	779.1	775.9	769.6	769.6	763.2	750.5	744.2	734.6
55°	696.4	696.4	693.2	690.1	686.9	683.7	680.6	671.0	664.6	655.1	645.5
57.5°	613.7	620.2	616.9	610.5	604.2	604.2	597.9	591.5	581.9	572.4	562.9
60°	547.0	543.8	543.8	540.6	534.3	531.0	527.8	518.3	508.8	499.2	489.7
62.5°	477.1	477.1	477.1	470.6	464.3	461.1	457.9	451.6	438.8	429.3	423.0
65°	416.5	413.4	410.2	407.0	403.9	397.5	394.4	387.9	378.4	368.9	359.3
67.5°	356.1	353.0	353.0	349.8	340.3	337.1	337.1	327.5	318.0	308.5	298.9
70°	295.7	295.7	295.7	289.4	286.2	283.0	279.9	273.4	263.9	254.4	244.9
72.5°	244.9	241.6	241.6	238.5	229.0	225.8	222.6	216.3	206.7	200.3	194.0
75°	190.8	190.8	187.7	184.4	181.2	178.1	174.9	168.6	159.1	149.4	146.3
77.5°	146.3	143.1	143.1	139.9	133.6	130.4	130.4	124.0	114.5	108.2	101.8
80°	98.5	101.8	98.5	95.4	92.2	89.0	85.9	82.7	76.4	69.9	63.6
82.5°	60.4	63.6	60.4	60.4	57.2	54.1	54.1	47.7	44.6	41.3	38.1
85°	31.8	31.8	31.8	31.8	28.6	28.6	28.6	25.5	22.3	19.1	19.1
87.5°	9.5	12.7	9.5	9.5	9.5	9.5	9.5	9.5	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584752

CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9
2.5°	2391.4	2388.2	2385.1	2385.1	2385.1	2385.1	2385.1	2381.9	2378.7	2378.7	2378.7
5°	2385.1	2385.1	2385.1	2381.9	2378.7	2378.7	2372.3	2369.1	2365.9	2362.8	2359.6
7.5°	2378.7	2372.3	2369.1	2365.9	2362.8	2362.8	2356.4	2350.1	2350.1	2343.7	2337.3
10°	2359.6	2356.4	2350.1	2343.7	2340.5	2337.3	2331.0	2321.5	2318.2	2311.9	2305.5
12.5°	2337.3	2331.0	2324.7	2311.9	2308.7	2305.5	2292.9	2283.2	2276.9	2273.7	2257.8
15°	2308.7	2296.0	2286.4	2270.6	2267.4	2261.0	2251.5	2242.0	2229.2	2219.7	2213.3
17.5°	2257.8	2245.1	2229.2	2213.3	2207.0	2207.0	2191.0	2178.4	2162.4	2156.1	2143.3
20°	2197.4	2181.5	2168.8	2149.8	2140.1	2130.6	2121.1	2102.0	2089.3	2079.7	2063.9
22.5°	2127.5	2105.2	2089.3	2070.2	2054.3	2044.8	2028.8	2013.0	1997.0	1987.5	1974.9
25°	2038.4	2019.3	1993.9	1974.9	1965.2	1952.6	1933.5	1917.6	1901.7	1885.7	1879.4
27.5°	1939.8	1914.3	1892.2	1869.9	1860.4	1850.8	1828.5	1809.5	1796.7	1780.8	1774.5
30°	1831.8	1806.3	1780.8	1761.7	1752.2	1736.3	1723.6	1701.3	1685.5	1672.7	1656.9
32.5°	1707.7	1688.7	1666.4	1637.7	1631.4	1618.6	1599.6	1590.0	1571.0	1561.4	1548.7
35°	1574.2	1561.4	1539.1	1516.9	1507.3	1501.0	1485.1	1466.0	1453.2	1443.7	1437.4
37.5°	1446.9	1431.1	1408.8	1392.8	1386.5	1377.0	1357.9	1348.4	1335.6	1329.2	1316.6
40°	1310.1	1294.3	1278.3	1268.8	1259.3	1252.9	1240.2	1230.7	1217.9	1208.4	1205.3
42.5°	1176.6	1167.1	1154.3	1141.7	1138.5	1128.9	1122.6	1113.1	1103.4	1100.3	1090.8
45°	1055.8	1046.2	1033.5	1020.7	1017.6	1011.2	1008.1	998.6	992.1	992.1	992.1
47.5°	934.9	925.4	912.7	906.3	909.5	896.8	896.8	893.6	887.3	887.3	890.4
50°	826.8	814.1	810.9	804.6	798.2	791.8	795.1	785.4	785.4	791.8	788.6
52.5°	725.0	712.4	709.2	702.7	699.6	699.6	696.4	696.4	693.2	696.4	696.4
55°	632.8	623.3	616.9	610.5	607.4	607.4	607.4	604.2	601.0	607.4	610.5
57.5°	550.1	547.0	540.6	531.0	527.8	524.7	521.5	521.5	521.5	521.5	524.7
60°	477.1	470.6	464.3	454.8	454.8	451.6	448.4	445.2	445.2	445.2	445.2
62.5°	413.4	403.9	394.4	387.9	384.7	381.6	378.4	372.1	372.1	372.1	372.1
65°	349.8	340.3	334.0	327.5	321.2	321.2	314.8	311.7	305.3	302.0	295.7
67.5°	289.4	283.0	276.7	267.1	263.9	260.8	254.4	251.3	241.6	238.5	235.3
70°	235.3	225.8	219.5	213.0	209.8	203.5	197.2	190.8	184.4	178.1	171.7
72.5°	184.4	174.9	168.6	162.2	155.8	155.8	146.3	139.9	130.4	124.0	114.5
75°	136.8	127.2	120.8	111.3	108.2	105.0	95.4	89.0	79.5	69.9	63.6
77.5°	92.2	85.9	79.5	69.9	63.6	63.6	54.1	47.7	41.3	31.8	28.6
80°	57.2	50.9	44.6	38.1	38.1	31.8	28.6	22.3	16.0	12.7	9.5
82.5°	31.8	28.6	25.5	19.1	19.1	16.0	12.7	9.5	6.3	3.2	3.2
85°	16.0	12.7	9.5	9.5	6.3	6.3	6.3	3.2	3.2	0.0	0.0
87.5°	6.3	3.2	3.2	3.2	3.2	3.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584752

CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9
2.5°	2375.4	2375.4	2372.3	2372.3	2372.3	2369.1	2372.3	2369.1	2369.1	2369.1	2372.3
5°	2362.8	2356.4	2356.4	2353.3	2353.3	2350.1	2353.3	2350.1	2346.8	2343.7	2346.8
7.5°	2337.3	2331.0	2327.8	2324.7	2324.7	2324.7	2321.5	2318.2	2321.5	2311.9	2318.2
10°	2302.4	2299.2	2292.9	2289.6	2286.4	2289.6	2286.4	2280.1	2280.1	2280.1	2276.9
12.5°	2257.8	2251.5	2248.3	2245.1	2238.8	2238.8	2242.0	2235.6	2235.6	2229.2	2229.2
15°	2203.8	2197.4	2191.0	2191.0	2184.7	2184.7	2181.5	2181.5	2178.4	2175.2	2175.2
17.5°	2137.0	2127.5	2121.1	2124.3	2121.1	2118.0	2118.0	2111.5	2108.4	2111.5	2111.5
20°	2057.4	2051.1	2044.8	2047.9	2041.6	2038.4	2041.6	2032.1	2035.3	2035.3	2035.3
22.5°	1968.4	1965.2	1955.7	1955.7	1949.4	1946.2	1949.4	1949.4	1952.6	1949.4	1949.4
25°	1869.9	1863.5	1857.1	1857.1	1853.9	1850.8	1853.9	1857.1	1853.9	1857.1	1857.1
27.5°	1764.9	1755.4	1755.4	1749.1	1749.1	1752.2	1749.1	1752.2	1755.4	1755.4	1761.7
30°	1650.4	1647.2	1644.1	1640.9	1640.9	1644.1	1644.1	1644.1	1647.2	1653.6	1653.6
32.5°	1542.4	1535.9	1529.6	1529.6	1535.9	1532.8	1535.9	1535.9	1542.4	1542.4	1548.7
35°	1424.6	1424.6	1418.3	1421.4	1421.4	1421.4	1421.4	1427.9	1434.2	1437.4	1443.7
37.5°	1316.6	1307.0	1310.1	1310.1	1313.4	1310.1	1319.7	1319.7	1326.1	1326.1	1332.4
40°	1198.9	1198.9	1202.1	1198.9	1202.1	1202.1	1208.4	1214.8	1217.9	1224.4	1227.5
42.5°	1087.6	1093.9	1087.6	1090.8	1093.9	1097.1	1100.3	1103.4	1116.2	1122.6	1132.1
45°	985.8	989.0	992.1	995.4	992.1	998.6	1001.7	1008.1	1017.6	1020.7	1024.0
47.5°	887.3	890.4	893.6	896.8	896.8	903.1	906.3	912.7	919.0	922.2	925.4
50°	791.8	798.2	801.4	801.4	804.6	810.9	817.2	817.2	823.7	833.2	836.3
52.5°	706.0	706.0	712.4	715.5	718.7	718.7	728.2	731.4	734.6	741.0	747.3
55°	610.5	620.2	623.3	623.3	629.7	636.0	639.2	642.3	642.3	655.1	655.1
57.5°	527.8	531.0	537.5	537.5	537.5	547.0	547.0	553.3	556.5	559.6	566.1
60°	445.2	451.6	451.6	454.8	451.6	457.9	461.1	467.4	470.6	473.8	477.1
62.5°	368.9	368.9	372.1	372.1	372.1	372.1	378.4	378.4	384.7	387.9	391.2
65°	295.7	295.7	295.7	295.7	295.7	295.7	295.7	295.7	298.9	298.9	305.3
67.5°	229.0	225.8	219.5	222.6	219.5	219.5	216.3	216.3	219.5	219.5	225.8
70°	165.4	162.2	155.8	155.8	152.6	149.4	146.3	143.1	139.9	139.9	139.9
72.5°	108.2	101.8	92.2	89.0	89.0	82.7	76.4	73.2	73.2	73.2	73.2
75°	54.1	47.7	41.3	38.1	38.1	31.8	35.0	31.8	31.8	31.8	31.8
77.5°	22.3	16.0	12.7	12.7	12.7	9.5	9.5	9.5	9.5	9.5	9.5
80°	6.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584752

CATALOG NUMBER: HCC8W45D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9	2381.9
2.5°	2369.1	2369.1	2362.8	2365.9	2365.9	2365.9	2365.9	2365.9
5°	2340.5	2343.7	2340.5	2343.7	2343.7	2340.5	2340.5	2340.5
7.5°	2311.9	2315.0	2311.9	2315.0	2315.0	2315.0	2311.9	2311.9
10°	2276.9	2276.9	2276.9	2276.9	2276.9	2273.7	2276.9	2276.9
12.5°	2229.2	2229.2	2229.2	2232.3	2232.3	2229.2	2229.2	2226.0
15°	2178.4	2171.9	2175.2	2178.4	2175.2	2175.2	2175.2	2175.2
17.5°	2108.4	2111.5	2108.4	2108.4	2108.4	2108.4	2111.5	2108.4
20°	2035.3	2035.3	2038.4	2035.3	2035.3	2035.3	2035.3	2032.1
22.5°	1952.6	1949.4	1949.4	1952.6	1952.6	1949.4	1952.6	1952.6
25°	1860.4	1863.5	1860.4	1860.4	1863.5	1863.5	1863.5	1860.4
27.5°	1761.7	1764.9	1768.1	1764.9	1764.9	1764.9	1768.1	1771.2
30°	1660.0	1666.4	1660.0	1660.0	1666.4	1663.2	1666.4	1666.4
32.5°	1551.9	1561.4	1555.0	1561.4	1561.4	1564.5	1561.4	1564.5
35°	1443.7	1453.2	1453.2	1453.2	1456.5	1459.7	1459.7	1456.5
37.5°	1342.0	1345.2	1345.2	1351.5	1354.7	1357.9	1357.9	1354.7
40°	1237.0	1243.4	1246.5	1246.5	1246.5	1252.9	1259.3	1252.9
42.5°	1135.2	1138.5	1141.7	1141.7	1148.0	1151.2	1154.3	1154.3
45°	1036.7	1043.0	1046.2	1049.4	1052.7	1059.0	1055.8	1062.2
47.5°	934.9	944.5	947.7	950.8	957.2	960.3	963.5	966.8
50°	842.7	849.0	849.0	855.5	865.0	865.0	871.3	874.5
52.5°	750.5	753.7	756.8	760.0	766.4	772.8	772.8	779.1
55°	661.5	664.6	664.6	667.8	671.0	683.7	686.9	686.9
57.5°	569.3	569.3	575.6	578.8	581.9	588.3	588.3	588.3
60°	480.2	483.4	483.4	486.6	489.7	496.1	499.2	496.1
62.5°	391.2	394.4	394.4	397.5	403.9	407.0	403.9	403.9
65°	308.5	311.7	311.7	314.8	321.2	321.2	318.0	321.2
67.5°	225.8	225.8	225.8	225.8	225.8	225.8	225.8	225.8
70°	143.1	139.9	136.8	139.9	139.9	139.9	136.8	143.1
72.5°	69.9	73.2	73.2	73.2	73.2	73.2	73.2	69.9
75°	31.8	31.8	28.6	28.6	28.6	31.8	31.8	28.6
77.5°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
80°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)