

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593787

Luminaire Tested: **HCC8S45D010BZ-HM82555950-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010BZ-HM82555950-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4975.7 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593787
CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57				
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50				
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45				
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37				
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33				
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	76289	76289	76289
5°	79082	76036	73423
10°	81314	75371	70421
15°	83127	74045	67312
20°	83259	71150	64577
25°	81665	67198	62291
30°	77452	62312	59559
35°	70376	56749	56884
40°	61536	50925	53610
45°	53334	45362	49959
50°	46697	40292	45517
55°	41563	35708	41187
60°	37497	32076	36196
65°	33848	28201	31543
70°	30420	23766	23450
75°	26795	18836	17585
80°	22482	15609	16852
85°	17372	13692	14931



TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.4	4.7
10°-20°	657.4	13.2
20°-30°	939.4	18.9
30°-40°	998.2	20.1
40°-50°	859.4	17.3
50°-60°	642.6	12.9
60°-70°	409.8	8.2
70°-80°	186.5	3.7
80°-90°	49.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1830.2	36.8
0°-40°	2828.4	56.8
0°-60°	4330.4	87.0
0°-90°	4975.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4975.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2474	2474	2474	2474	2474	
5°	2555	2520	2456	2393	2372	245
15°	2604	2516	2319	2161	2108	733
25°	2400	2249	1975	1856	1831	1099
35°	1870	1739	1508	1469	1511	1164
45°	1223	1156	1040	1068	1146	951
55°	773	710	664	720	766	695
65°	464	411	386	404	432	463
75°	225	193	158	144	148	239
85°	49	42	39	42	42	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0
2.5°	2519.6	2512.6	2516.1	2512.6	2516.1	2516.1	2509.0	2509.0	2509.0	2509.0	2498.5
5°	2554.8	2551.3	2551.3	2547.8	2544.2	2547.8	2544.2	2540.7	2533.7	2530.2	2519.6
7.5°	2575.8	2575.8	2575.8	2575.8	2572.4	2568.9	2565.4	2558.3	2551.3	2544.2	2537.2
10°	2596.9	2600.4	2596.9	2593.4	2589.9	2582.8	2579.3	2572.4	2561.8	2551.3	2544.2
12.5°	2607.5	2607.5	2603.9	2603.9	2596.9	2593.4	2582.8	2572.4	2561.8	2551.3	2533.7
15°	2603.9	2603.9	2600.4	2596.9	2586.3	2582.8	2575.8	2565.4	2547.8	2533.7	2516.1
17.5°	2582.8	2579.3	2572.4	2572.4	2558.3	2554.8	2547.8	2533.7	2516.1	2495.0	2474.0
20°	2537.2	2537.2	2533.7	2530.2	2516.1	2505.5	2498.5	2481.0	2466.9	2442.3	2421.2
22.5°	2474.0	2481.0	2474.0	2466.9	2449.3	2445.8	2435.3	2414.2	2393.2	2365.0	2340.4
25°	2400.2	2396.7	2393.2	2386.1	2372.0	2365.0	2350.9	2329.8	2308.8	2277.1	2249.0
27.5°	2305.3	2291.2	2291.2	2277.1	2266.6	2256.0	2249.0	2228.0	2199.8	2175.2	2140.1
30°	2175.2	2178.7	2161.1	2157.6	2140.1	2133.1	2119.0	2097.9	2073.3	2045.2	2017.1
32.5°	2034.7	2024.1	2024.1	2010.1	1996.0	1985.4	1982.0	1957.4	1936.3	1908.1	1880.1
35°	1869.5	1869.5	1859.0	1855.5	1841.4	1834.3	1823.8	1809.8	1785.2	1760.6	1739.4
37.5°	1707.9	1700.8	1697.3	1690.3	1679.7	1669.2	1669.2	1644.7	1641.1	1613.0	1584.8
40°	1528.7	1535.7	1528.7	1518.1	1514.6	1507.5	1504.0	1489.9	1479.4	1454.9	1437.3
42.5°	1377.6	1370.5	1370.5	1367.0	1352.9	1352.9	1345.9	1338.9	1321.3	1314.2	1293.2
45°	1223.0	1229.9	1219.5	1223.0	1208.9	1208.9	1208.9	1194.8	1180.7	1170.2	1156.1
47.5°	1089.4	1092.9	1092.9	1082.3	1078.8	1078.8	1071.8	1064.7	1054.3	1040.2	1029.7
50°	973.4	976.9	970.0	966.4	959.4	955.9	955.9	941.8	934.8	920.7	913.6
52.5°	868.0	868.0	864.5	864.5	853.9	853.9	846.9	836.3	829.3	822.3	804.7
55°	773.1	773.1	769.6	766.1	766.1	755.5	752.0	741.5	734.4	720.3	709.9
57.5°	681.7	685.3	681.7	678.2	674.7	671.2	664.2	653.6	646.6	636.0	629.1
60°	608.0	608.0	604.4	600.9	593.9	590.4	586.9	579.8	569.3	562.2	551.7
62.5°	537.7	534.2	530.7	527.1	520.1	520.1	513.1	506.0	495.5	488.4	481.4
65°	463.9	463.9	460.4	460.4	456.9	449.8	446.3	442.8	428.7	425.2	411.1
67.5°	397.1	400.6	393.5	393.5	386.5	386.5	383.0	372.5	369.0	362.0	354.9
70°	337.4	337.4	337.4	333.8	326.8	323.3	319.8	312.7	309.2	302.2	295.2
72.5°	277.6	277.6	274.1	274.1	270.6	267.1	263.6	256.5	256.5	249.5	242.5
75°	224.9	224.9	221.3	217.8	214.3	214.3	210.9	207.4	200.3	196.8	193.3
77.5°	172.2	172.2	172.2	168.7	165.2	165.2	165.2	158.1	151.1	151.1	147.6
80°	126.6	126.6	123.0	123.0	119.5	119.5	119.5	116.0	112.5	109.0	105.5
82.5°	84.3	84.3	84.3	84.3	80.8	80.8	80.8	77.3	73.8	73.8	73.8
85°	49.1	49.1	49.1	49.1	45.6	45.6	45.6	45.6	45.6	42.2	42.2
87.5°	21.1	17.6	21.1	17.6	21.1	17.6	21.1	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0
2.5°	2502.0	2498.5	2495.0	2491.5	2491.5	2488.1	2481.0	2477.5	2474.0	2470.5	2470.5
5°	2516.1	2512.6	2505.5	2498.5	2495.0	2488.1	2481.0	2474.0	2466.9	2456.4	2452.9
7.5°	2526.6	2516.1	2509.0	2495.0	2491.5	2484.5	2474.0	2463.4	2449.3	2435.3	2424.7
10°	2526.6	2512.6	2502.0	2484.5	2477.5	2470.5	2456.4	2438.8	2421.2	2407.1	2389.6
12.5°	2519.6	2502.0	2484.5	2466.9	2456.4	2445.8	2424.7	2407.1	2386.1	2365.0	2350.9
15°	2495.0	2474.0	2452.9	2431.7	2421.2	2407.1	2386.1	2361.5	2340.4	2319.4	2294.7
17.5°	2449.3	2428.2	2403.7	2379.1	2365.0	2354.4	2322.8	2305.3	2273.6	2252.5	2231.5
20°	2389.6	2365.0	2333.3	2308.8	2291.2	2280.7	2256.0	2224.5	2199.8	2168.2	2147.2
22.5°	2312.3	2280.7	2249.0	2224.5	2206.9	2192.8	2161.1	2129.6	2108.5	2080.3	2055.8
25°	2221.0	2189.3	2157.6	2122.5	2104.9	2090.9	2062.8	2034.7	2006.5	1975.0	1953.9
27.5°	2112.0	2076.8	2048.8	2017.1	1999.5	1978.5	1946.8	1918.7	1890.6	1869.5	1841.4
30°	1992.5	1953.9	1925.7	1894.2	1876.6	1859.0	1827.3	1799.3	1774.6	1750.0	1735.9
32.5°	1848.4	1820.3	1792.2	1760.6	1746.5	1735.9	1704.4	1676.2	1648.1	1627.1	1616.5
35°	1711.4	1679.7	1655.1	1627.1	1609.5	1598.9	1570.8	1546.2	1532.2	1507.5	1493.5
37.5°	1567.2	1542.7	1514.6	1486.4	1476.0	1465.4	1444.3	1419.7	1398.6	1381.1	1374.1
40°	1416.2	1395.0	1370.5	1352.9	1342.4	1331.8	1314.2	1296.8	1282.7	1265.1	1258.0
42.5°	1272.1	1258.0	1236.9	1215.9	1205.4	1201.9	1180.7	1166.7	1159.6	1152.6	1145.6
45°	1142.0	1121.0	1107.0	1092.9	1082.3	1075.3	1064.7	1054.3	1047.3	1040.2	1033.2
47.5°	1015.6	998.0	983.9	973.4	962.9	959.4	952.4	941.8	934.8	934.8	934.8
50°	899.6	885.6	871.5	864.5	861.0	853.9	846.9	843.4	839.9	839.9	839.9
52.5°	797.8	783.7	773.1	766.1	766.1	759.0	752.0	748.5	748.5	748.5	748.5
55°	702.9	692.3	685.3	678.2	671.2	667.7	667.7	667.7	664.2	664.2	667.7
57.5°	618.5	611.5	600.9	593.9	590.4	590.4	586.9	583.3	586.9	590.4	593.9
60°	541.2	534.2	530.7	520.1	520.1	520.1	516.6	516.6	516.6	520.1	523.6
62.5°	470.8	467.3	460.4	456.9	453.4	453.4	449.8	449.8	449.8	449.8	453.4
65°	407.6	400.6	393.5	393.5	393.5	390.0	390.0	383.0	386.5	386.5	383.0
67.5°	347.9	340.9	337.4	333.8	330.3	330.3	326.8	323.3	319.8	319.8	319.8
70°	291.7	284.7	284.7	277.6	277.6	274.1	270.6	270.6	267.1	263.6	260.1
72.5°	235.4	231.9	228.4	224.9	224.9	224.9	221.3	217.8	214.3	210.9	203.9
75°	186.3	186.3	179.2	175.7	175.7	172.2	168.7	165.2	161.6	158.1	154.6
77.5°	144.0	140.5	133.5	130.0	130.0	130.0	126.6	123.0	119.5	116.0	112.5
80°	105.5	101.9	98.4	94.9	94.9	94.9	91.4	91.4	87.9	87.9	87.9
82.5°	70.3	70.3	66.7	66.7	66.7	66.7	63.2	63.2	63.2	63.2	63.2
85°	42.2	42.2	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0
2.5°	2463.4	2463.4	2456.4	2452.9	2449.3	2452.9	2445.8	2442.3	2438.8	2438.8	2435.3
5°	2442.3	2438.8	2424.7	2421.2	2417.7	2414.2	2407.1	2400.2	2393.2	2389.6	2386.1
7.5°	2414.2	2403.7	2389.6	2386.1	2382.6	2372.0	2361.5	2354.4	2343.9	2340.4	2333.3
10°	2375.6	2361.5	2350.9	2340.4	2333.3	2322.8	2312.3	2301.8	2287.7	2284.2	2273.6
12.5°	2329.8	2312.3	2291.2	2287.7	2277.1	2263.1	2249.0	2238.4	2228.0	2221.0	2210.4
15°	2273.6	2256.0	2235.0	2224.5	2213.9	2203.4	2185.8	2171.7	2161.1	2150.7	2140.1
17.5°	2206.9	2185.8	2168.2	2157.6	2150.7	2133.1	2119.0	2101.4	2090.9	2080.3	2069.8
20°	2126.1	2108.5	2083.8	2073.3	2069.8	2055.8	2038.2	2031.2	2017.1	2006.5	1999.5
22.5°	2034.7	2017.1	1996.0	1988.9	1975.0	1967.9	1950.3	1943.3	1936.3	1925.7	1922.2
25°	1932.8	1915.2	1897.7	1894.2	1883.6	1876.6	1866.0	1855.5	1855.5	1844.9	1844.9
27.5°	1827.3	1809.8	1795.7	1788.7	1785.2	1778.2	1767.6	1764.1	1760.6	1757.0	1757.0
30°	1714.9	1693.8	1686.8	1683.3	1679.7	1672.7	1669.2	1662.1	1665.7	1669.2	1665.7
32.5°	1595.4	1588.4	1574.3	1567.2	1570.8	1567.2	1560.3	1567.2	1563.7	1570.8	1574.3
35°	1479.4	1472.5	1465.4	1465.4	1458.4	1458.4	1458.4	1461.9	1468.9	1472.5	1479.4
37.5°	1367.0	1356.5	1352.9	1349.4	1352.9	1352.9	1352.9	1360.0	1367.0	1374.1	1384.6
40°	1247.5	1240.4	1240.4	1240.4	1240.4	1251.0	1247.5	1254.5	1261.6	1272.1	1282.7
42.5°	1135.1	1135.1	1138.6	1138.6	1138.6	1138.6	1145.6	1156.1	1166.7	1177.2	1187.8
45°	1029.7	1029.7	1029.7	1036.7	1036.7	1040.2	1054.3	1061.2	1068.3	1078.8	1089.4
47.5°	931.2	931.2	934.8	938.3	941.8	948.8	955.9	966.4	976.9	983.9	994.5
50°	839.9	843.4	850.4	857.5	857.5	861.0	871.5	878.6	885.6	896.1	899.6
52.5°	752.0	759.0	766.1	769.6	773.1	780.2	783.7	794.2	797.8	808.2	811.7
55°	671.2	674.7	685.3	688.8	688.8	695.8	702.9	709.9	720.3	720.3	727.4
57.5°	597.4	600.9	608.0	611.5	608.0	618.5	622.0	629.1	632.6	639.5	643.0
60°	523.6	530.7	534.2	534.2	537.7	541.2	548.3	548.3	555.2	562.2	562.2
62.5°	453.4	456.9	460.4	463.9	467.3	463.9	474.4	474.4	481.4	484.9	492.0
65°	386.5	390.0	390.0	393.5	393.5	397.1	397.1	400.6	404.1	411.1	414.7
67.5°	319.8	319.8	319.8	323.3	319.8	323.3	323.3	326.8	326.8	333.8	337.4
70°	260.1	256.5	253.0	253.0	253.0	253.0	249.5	253.0	253.0	256.5	256.5
72.5°	200.3	196.8	193.3	189.8	189.8	186.3	182.8	186.3	186.3	189.8	189.8
75°	151.1	144.0	144.0	144.0	140.5	140.5	140.5	144.0	144.0	144.0	147.6
77.5°	112.5	112.5	109.0	109.0	109.0	112.5	112.5	116.0	116.0	116.0	116.0
80°	84.3	87.9	87.9	87.9	87.9	91.4	91.4	91.4	91.4	94.9	94.9
82.5°	63.2	63.2	63.2	63.2	66.7	66.7	66.7	66.7	66.7	66.7	66.7
85°	38.7	42.2	42.2	38.7	42.2	42.2	42.2	42.2	42.2	42.2	42.2
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593787

CATALOG NUMBER: HCC8S45D010BZ-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0	2474.0
2.5°	2431.7	2431.7	2431.7	2431.7	2428.2	2428.2	2428.2	2424.7
5°	2379.1	2379.1	2379.1	2372.0	2375.6	2375.6	2368.5	2372.0
7.5°	2326.3	2322.8	2319.4	2319.4	2315.9	2312.3	2308.8	2312.3
10°	2266.6	2256.0	2256.0	2252.5	2252.5	2245.5	2245.5	2249.0
12.5°	2199.8	2192.8	2192.8	2189.3	2185.8	2182.2	2178.7	2178.7
15°	2133.1	2126.1	2122.5	2119.0	2115.5	2108.5	2112.0	2108.5
17.5°	2066.4	2055.8	2055.8	2052.3	2048.8	2041.7	2041.7	2038.2
20°	1988.9	1985.4	1978.5	1982.0	1978.5	1971.5	1967.9	1967.9
22.5°	1911.6	1911.6	1908.1	1908.1	1904.6	1901.1	1897.7	1897.7
25°	1837.9	1834.3	1837.9	1837.9	1827.3	1827.3	1827.3	1830.8
27.5°	1753.5	1757.0	1753.5	1753.5	1753.5	1753.5	1757.0	1753.5
30°	1669.2	1669.2	1669.2	1672.7	1679.7	1676.2	1676.2	1672.7
32.5°	1577.8	1581.3	1581.3	1584.8	1588.4	1595.4	1595.4	1598.9
35°	1486.4	1493.5	1497.0	1493.5	1504.0	1504.0	1511.1	1511.1
37.5°	1391.6	1395.0	1402.1	1405.6	1412.6	1416.2	1419.7	1419.7
40°	1289.7	1303.8	1307.3	1310.7	1321.3	1321.3	1324.8	1331.8
42.5°	1194.8	1208.9	1212.4	1215.9	1223.0	1233.4	1229.9	1236.9
45°	1103.4	1114.0	1117.5	1121.0	1131.6	1135.1	1135.1	1145.6
47.5°	1005.0	1012.1	1015.6	1022.6	1029.7	1036.7	1043.7	1040.2
50°	906.6	917.2	924.2	927.7	938.3	941.8	945.3	948.8
52.5°	818.8	825.8	829.3	832.8	843.4	846.9	850.4	857.5
55°	734.4	737.9	745.0	741.5	752.0	755.5	759.0	766.1
57.5°	650.1	653.6	657.1	657.1	664.2	671.2	674.7	678.2
60°	569.3	576.3	579.8	579.8	579.8	586.9	586.9	586.9
62.5°	495.5	495.5	499.0	499.0	506.0	506.0	506.0	506.0
65°	418.2	421.7	425.2	425.2	432.3	428.7	435.8	432.3
67.5°	337.4	337.4	344.4	344.4	340.9	344.4	344.4	344.4
70°	256.5	256.5	260.1	260.1	260.1	260.1	260.1	260.1
72.5°	189.8	189.8	189.8	193.3	189.8	189.8	193.3	189.8
75°	147.6	147.6	147.6	147.6	147.6	147.6	147.6	147.6
77.5°	116.0	116.0	119.5	119.5	119.5	119.5	119.5	119.5
80°	94.9	94.9	94.9	94.9	98.4	94.9	94.9	94.9
82.5°	70.3	66.7	70.3	66.7	70.3	70.3	70.3	70.3
85°	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)