

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593785

Luminaire Tested: **HCC8W45D010BZ-HM82555950-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010BZ-HM82555950-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4378.3 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593785
CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72484	72484	72484
5°	75478	72324	69278
10°	78001	71401	65899
15°	79976	69767	62475
20°	80135	66874	59379
25°	78779	62642	56306
30°	74560	57797	53670
35°	67985	51983	50391
40°	59117	45825	46534
45°	50717	39684	42597
50°	43319	34219	38258
55°	37972	29467	33246
60°	33803	25138	27950
65°	29996	20510	22305
70°	26606	15210	12667
75°	22196	7947	3777
80°	17474	2504	622
85°	12454	1238	0



TEST NUMBER: P593785
 CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.5	5.1
10°-20°	620.8	14.2
20°-30°	878.6	20.1
30°-40°	919.2	21.0
40°-50°	766.7	17.5
50°-60°	543.7	12.4
60°-70°	313.1	7.2
70°-80°	100.8	2.3
80°-90°	13.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.9	39.3
0°-40°	2640.1	60.3
0°-60°	3950.6	90.2
0°-90°	4378.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4378.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2351	2351	2351	2351	2351	
5°	2438	2407	2336	2266	2238	234
15°	2505	2403	2185	2013	1957	704
25°	2315	2143	1841	1694	1655	1057
35°	1806	1648	1381	1307	1339	1120
45°	1163	1068	910	921	977	901
55°	706	632	548	576	618	638
65°	411	344	281	281	306	411
75°	186	137	67	32	32	202
85°	35	18	4	0	0	44
90°	0	0	0	0	0	



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2399.7	2396.2	2392.7	2396.2	2392.7	2396.2	2392.7	2392.7	2389.2	2385.6	2385.6
5°	2438.4	2434.9	2434.9	2434.9	2431.4	2427.9	2427.9	2424.4	2417.3	2413.8	2406.8
7.5°	2462.9	2466.5	2466.5	2466.5	2459.4	2459.4	2452.4	2445.4	2438.4	2431.4	2420.8
10°	2491.1	2491.1	2487.6	2484.1	2477.0	2473.5	2470.0	2462.9	2452.4	2438.4	2427.9
12.5°	2501.7	2501.7	2498.1	2491.1	2487.6	2484.1	2480.5	2470.0	2455.9	2438.4	2424.4
15°	2505.2	2498.1	2494.6	2491.1	2484.1	2473.5	2473.5	2459.4	2442.0	2420.8	2403.2
17.5°	2477.0	2480.5	2473.5	2466.5	2455.9	2448.9	2438.4	2427.9	2406.8	2382.1	2364.7
20°	2442.0	2438.4	2434.9	2424.4	2410.3	2406.8	2396.2	2378.6	2361.1	2333.0	2308.3
22.5°	2385.6	2382.1	2375.1	2368.1	2354.1	2347.1	2336.5	2315.4	2290.9	2262.7	2234.6
25°	2315.4	2308.3	2297.8	2283.8	2273.3	2266.2	2252.2	2231.0	2203.0	2171.3	2143.2
27.5°	2203.0	2213.6	2206.5	2185.4	2174.9	2160.8	2157.3	2129.2	2104.6	2072.9	2041.4
30°	2094.0	2094.0	2083.5	2072.9	2055.4	2044.9	2030.8	2009.7	1985.2	1946.5	1921.8
32.5°	1957.0	1953.5	1939.4	1935.9	1921.8	1900.8	1897.3	1869.2	1844.5	1816.5	1784.8
35°	1806.0	1798.9	1784.8	1774.3	1767.2	1756.8	1746.2	1721.6	1697.0	1668.9	1647.8
37.5°	1633.8	1633.8	1630.2	1612.8	1605.7	1598.7	1588.1	1563.5	1549.4	1521.4	1500.3
40°	1468.6	1465.2	1454.6	1451.1	1444.1	1433.5	1426.5	1412.4	1391.3	1370.3	1349.2
42.5°	1307.1	1310.6	1296.5	1300.0	1286.0	1278.9	1275.4	1254.3	1243.7	1222.7	1205.1
45°	1163.0	1159.5	1152.5	1149.0	1141.9	1134.9	1127.8	1117.3	1099.7	1078.7	1068.1
47.5°	1029.4	1018.9	1018.9	1015.3	1011.9	997.9	994.4	983.8	973.2	952.1	938.2
50°	903.0	903.0	903.0	899.5	888.9	885.4	878.3	867.8	857.3	843.3	822.2
52.5°	801.0	801.0	801.0	797.5	783.6	780.0	776.5	762.4	748.4	737.8	723.7
55°	706.3	709.8	706.3	699.2	688.7	688.7	678.1	671.1	657.0	646.4	632.5
57.5°	625.4	625.4	618.4	614.9	607.8	604.3	597.3	590.3	572.7	562.2	544.6
60°	548.1	544.6	544.6	537.6	530.5	523.5	520.0	509.4	502.4	484.9	470.8
62.5°	477.9	477.9	470.8	470.8	456.8	456.8	453.2	442.7	432.1	414.5	407.6
65°	411.1	411.1	407.6	404.1	393.5	390.0	386.5	375.9	365.4	354.8	344.3
67.5°	351.3	351.3	344.3	340.8	333.8	330.3	323.3	316.2	305.7	295.1	284.6
70°	295.1	291.6	288.1	284.6	277.5	274.0	267.0	260.1	249.5	242.5	231.9
72.5°	238.9	238.9	235.4	228.4	224.9	221.3	217.8	210.8	200.2	189.7	182.8
75°	186.3	186.3	186.3	179.2	172.2	168.7	168.7	161.6	154.6	144.0	137.0
77.5°	144.0	140.5	137.0	137.0	130.0	126.4	122.9	119.4	109.0	105.5	98.4
80°	98.4	101.9	98.4	94.9	91.4	87.9	87.9	80.8	77.3	70.3	63.2
82.5°	66.7	63.2	63.2	59.7	59.7	56.2	56.2	49.1	45.6	42.1	38.6
85°	35.2	35.2	31.7	31.7	31.7	28.2	28.2	24.6	24.6	21.1	17.6
87.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2382.1	2375.1	2371.6	2371.6	2368.1	2364.7	2361.1	2357.6	2350.6	2350.6	2343.5
5°	2399.7	2392.7	2389.2	2378.6	2371.6	2371.6	2357.6	2354.1	2343.5	2336.5	2329.5
7.5°	2413.8	2399.7	2389.2	2378.6	2371.6	2364.7	2350.6	2336.5	2322.4	2308.3	2301.3
10°	2413.8	2399.7	2382.1	2364.7	2357.6	2350.6	2333.0	2311.9	2294.3	2280.3	2262.7
12.5°	2406.8	2385.6	2364.7	2350.6	2336.5	2325.9	2304.8	2283.8	2262.7	2234.6	2220.5
15°	2385.6	2357.6	2336.5	2311.9	2301.3	2283.8	2266.2	2234.6	2210.0	2185.4	2167.8
17.5°	2343.5	2308.3	2283.8	2259.2	2241.6	2231.0	2203.0	2174.9	2146.7	2118.7	2097.6
20°	2280.3	2248.6	2220.5	2188.9	2174.9	2160.8	2125.7	2097.6	2069.4	2037.9	2016.7
22.5°	2203.0	2171.3	2132.7	2108.1	2087.0	2069.4	2037.9	2006.2	1978.1	1950.0	1921.8
25°	2108.1	2076.4	2041.4	2002.7	1988.7	1971.1	1935.9	1904.4	1872.7	1841.1	1816.5
27.5°	2006.2	1964.1	1935.9	1893.8	1879.7	1862.1	1823.5	1788.4	1760.3	1735.7	1707.5
30°	1883.3	1851.6	1813.0	1774.3	1760.3	1742.7	1711.1	1679.5	1651.3	1623.2	1595.2
32.5°	1749.8	1718.1	1679.5	1651.3	1630.2	1616.2	1584.6	1556.5	1528.4	1500.3	1475.6
35°	1609.2	1574.0	1545.9	1517.9	1500.3	1482.7	1451.1	1426.5	1405.4	1380.9	1356.2
37.5°	1465.2	1440.6	1412.4	1380.9	1363.3	1349.2	1324.6	1296.5	1278.9	1257.8	1240.3
40°	1324.6	1296.5	1271.9	1243.7	1229.8	1219.2	1194.6	1173.5	1156.0	1138.4	1127.8
42.5°	1180.5	1156.0	1131.4	1113.8	1103.2	1092.6	1075.2	1050.5	1040.0	1022.4	1011.9
45°	1047.0	1025.9	1008.4	983.8	976.8	969.7	948.6	931.1	920.6	910.0	903.0
47.5°	920.6	906.5	885.4	871.3	860.9	853.8	839.8	825.7	815.1	808.1	801.0
50°	811.6	794.0	780.0	766.0	758.9	748.4	734.3	727.3	720.2	713.3	713.3
52.5°	709.8	692.2	678.1	667.6	660.5	653.5	642.9	639.4	632.5	632.5	629.0
55°	614.9	604.3	590.3	576.2	572.7	569.1	562.2	555.2	551.7	548.1	551.7
57.5°	534.1	523.5	509.4	498.9	495.4	491.8	488.4	481.4	477.9	477.9	477.9
60°	460.3	449.7	439.2	428.6	428.6	421.6	418.1	414.5	411.1	407.6	407.6
62.5°	393.5	383.0	372.4	365.4	361.9	358.4	351.3	347.8	344.3	344.3	340.8
65°	333.8	319.8	316.2	305.7	302.2	298.6	295.1	288.1	284.6	281.1	277.5
67.5°	274.0	267.0	256.5	249.5	246.0	242.5	238.9	231.9	228.4	224.9	217.8
70°	221.3	214.3	207.3	200.2	196.7	193.2	186.3	179.2	175.7	168.7	158.1
72.5°	172.2	165.2	158.1	151.1	147.6	144.0	137.0	130.0	122.9	115.9	109.0
75°	130.0	122.9	112.5	105.5	101.9	101.9	91.4	84.3	77.3	66.7	59.7
77.5°	91.4	80.8	77.3	70.3	66.7	59.7	52.7	45.6	38.6	35.2	28.2
80°	59.7	52.7	45.6	42.1	38.6	35.2	31.7	24.6	17.6	14.1	10.6
82.5°	35.2	31.7	28.2	24.6	21.1	17.6	14.1	14.1	10.6	7.0	3.5
85°	17.6	14.1	10.6	10.6	7.0	7.0	7.0	3.5	3.5	3.5	3.5
87.5°	7.0	3.5	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2340.0	2336.5	2333.0	2329.5	2329.5	2322.4	2322.4	2318.9	2311.9	2308.3	2308.3
5°	2318.9	2308.3	2301.3	2297.8	2294.3	2283.8	2280.3	2273.3	2266.2	2259.2	2255.7
7.5°	2287.4	2269.8	2262.7	2259.2	2248.6	2238.1	2231.0	2220.5	2210.0	2199.5	2196.0
10°	2248.6	2231.0	2213.6	2206.5	2196.0	2188.9	2174.9	2160.8	2150.2	2139.8	2129.2
12.5°	2199.5	2178.4	2160.8	2153.7	2143.2	2129.2	2108.1	2101.1	2083.5	2076.4	2062.5
15°	2143.2	2118.7	2101.1	2090.5	2080.0	2059.0	2044.9	2030.8	2013.2	2006.2	1992.1
17.5°	2072.9	2044.9	2027.3	2016.7	2009.7	1992.1	1971.1	1953.5	1935.9	1928.9	1918.3
20°	1988.7	1971.1	1946.5	1935.9	1928.9	1907.9	1886.8	1879.7	1865.7	1851.6	1841.1
22.5°	1893.8	1876.2	1851.6	1841.1	1837.6	1820.0	1802.4	1791.9	1781.3	1770.8	1760.3
25°	1795.4	1774.3	1753.3	1746.2	1739.2	1725.1	1711.1	1704.0	1693.5	1686.5	1679.5
27.5°	1690.1	1668.9	1651.3	1640.8	1633.8	1623.2	1616.2	1609.2	1602.2	1595.2	1591.6
30°	1577.6	1556.5	1542.4	1535.5	1528.4	1524.9	1514.3	1510.8	1507.3	1500.3	1503.8
32.5°	1465.2	1447.6	1433.5	1423.0	1423.0	1415.9	1412.4	1412.4	1408.9	1408.9	1408.9
35°	1342.1	1331.6	1321.0	1317.5	1314.1	1310.6	1307.1	1310.6	1307.1	1310.6	1314.1
37.5°	1229.8	1219.2	1212.2	1208.7	1205.1	1208.7	1205.1	1205.1	1208.7	1215.7	1219.2
40°	1113.8	1106.7	1099.7	1103.2	1099.7	1099.7	1099.7	1110.2	1113.8	1117.3	1120.8
42.5°	1004.9	997.9	994.4	994.4	997.9	994.4	1001.4	1004.9	1011.9	1022.4	1029.4
45°	899.5	895.9	895.9	899.5	895.9	903.0	903.0	910.0	920.6	927.6	934.6
47.5°	801.0	801.0	801.0	804.6	804.6	808.1	815.1	818.6	825.7	832.7	839.8
50°	709.8	713.3	716.7	716.7	716.7	723.7	730.8	734.3	737.8	741.3	751.9
52.5°	629.0	632.5	632.5	636.0	639.4	642.9	646.4	653.5	657.0	664.0	667.6
55°	551.7	551.7	558.7	562.2	562.2	562.2	569.1	569.1	576.2	579.7	586.7
57.5°	477.9	481.4	481.4	484.9	484.9	488.4	491.8	495.4	498.9	502.4	505.9
60°	407.6	407.6	407.6	411.1	414.5	418.1	414.5	421.6	421.6	428.6	432.1
62.5°	340.8	344.3	344.3	344.3	344.3	344.3	344.3	347.8	351.3	354.8	358.4
65°	277.5	277.5	277.5	274.0	277.5	274.0	277.5	281.1	281.1	284.6	288.1
67.5°	214.3	214.3	207.3	207.3	210.8	210.8	210.8	210.8	207.3	214.3	214.3
70°	154.6	151.1	147.6	144.0	144.0	140.5	140.5	137.0	137.0	137.0	137.0
72.5°	101.9	94.9	87.9	84.3	80.8	80.8	73.8	70.3	73.8	73.8	73.8
75°	52.7	45.6	42.1	38.6	35.2	35.2	31.7	31.7	31.7	31.7	31.7
77.5°	21.1	17.6	14.1	14.1	10.6	10.6	10.6	10.6	10.6	10.6	10.6
80°	7.0	7.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	3.5	0.0	0.0	3.5	0.0	3.5	3.5	3.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010BZ-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2304.8	2304.8	2301.3	2304.8	2297.8	2301.3	2297.8	2297.8
5°	2252.2	2245.1	2245.1	2245.1	2241.6	2241.6	2238.1	2238.1
7.5°	2188.9	2185.4	2181.9	2178.4	2174.9	2171.3	2171.3	2171.3
10°	2125.7	2118.7	2118.7	2115.2	2108.1	2104.6	2104.6	2104.6
12.5°	2051.9	2048.4	2044.9	2044.9	2030.8	2034.3	2030.8	2030.8
15°	1981.7	1978.1	1978.1	1967.6	1960.6	1960.6	1960.6	1957.0
17.5°	1907.9	1904.4	1900.8	1893.8	1886.8	1886.8	1883.3	1886.8
20°	1830.6	1827.1	1820.0	1820.0	1816.5	1813.0	1806.0	1809.5
22.5°	1753.3	1746.2	1742.7	1742.7	1739.2	1739.2	1732.2	1732.2
25°	1672.5	1668.9	1665.4	1668.9	1661.9	1661.9	1654.9	1654.9
27.5°	1588.1	1584.6	1584.6	1584.6	1581.1	1584.6	1581.1	1581.1
30°	1503.8	1503.8	1500.3	1500.3	1503.8	1500.3	1503.8	1507.3
32.5°	1412.4	1412.4	1415.9	1415.9	1419.4	1419.4	1419.4	1419.4
35°	1317.5	1324.6	1324.6	1328.1	1331.6	1335.1	1335.1	1338.6
37.5°	1229.8	1233.3	1236.8	1240.3	1247.3	1247.3	1247.3	1247.3
40°	1134.9	1138.4	1145.4	1141.9	1156.0	1159.5	1156.0	1156.0
42.5°	1036.5	1043.5	1047.0	1054.1	1057.6	1064.6	1068.1	1068.1
45°	945.1	948.6	955.6	962.7	966.2	976.8	976.8	976.8
47.5°	850.3	857.3	860.9	867.8	871.3	881.9	885.4	881.9
50°	758.9	766.0	773.0	773.0	783.6	787.1	794.0	797.5
52.5°	671.1	674.6	681.6	685.1	692.2	699.2	702.7	706.3
55°	586.7	590.3	597.3	597.3	607.8	611.4	618.4	618.4
57.5°	509.4	513.0	520.0	516.5	523.5	530.5	530.5	527.0
60°	435.7	435.7	435.7	442.7	446.2	449.7	453.2	453.2
62.5°	358.4	365.4	368.9	368.9	372.4	375.9	375.9	372.4
65°	288.1	295.1	298.6	298.6	302.2	302.2	302.2	305.7
67.5°	217.8	217.8	217.8	221.3	217.8	217.8	217.8	217.8
70°	137.0	137.0	137.0	137.0	133.5	137.0	137.0	140.5
72.5°	73.8	73.8	73.8	73.8	73.8	73.8	73.8	73.8
75°	31.7	31.7	31.7	35.2	31.7	31.7	31.7	31.7
77.5°	14.1	10.6	14.1	14.1	10.6	10.6	10.6	10.6
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	0.0	3.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)