

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584606

Luminaire Tested: **HCC8S40D010BZ-HM82555930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010BZ-HM82555930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3701.1 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584606
CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584606

CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61269	61269	61269
5°	63803	61134	58562
10°	65934	60357	55704
15°	67602	58977	52812
20°	67737	56528	50191
25°	66592	52952	47593
30°	63027	48860	45367
35°	57464	43942	42598
40°	49971	38732	39332
45°	42872	33544	36004
50°	36618	28923	32338
55°	32096	24908	28106
60°	28573	21246	23633
65°	25355	17336	18847
70°	22486	12857	10711
75°	18753	6720	3193
80°	14775	2113	533
85°	10543	1061	0



TEST NUMBER: P584606
 CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	5.1
10°-20°	524.8	14.2
20°-30°	742.7	20.1
30°-40°	777.0	21.0
40°-50°	648.1	17.5
50°-60°	459.6	12.4
60°-70°	264.7	7.2
70°-80°	85.2	2.3
80°-90°	11.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.7	39.3
0°-40°	2231.7	60.3
0°-60°	3339.4	90.2
0°-90°	3701.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3701.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1987	1987	1987	1987	1987	
5°	2061	2034	1975	1916	1892	198
15°	2118	2031	1847	1702	1654	595
25°	1957	1812	1556	1432	1399	893
35°	1526	1393	1167	1105	1132	946
45°	983	903	769	778	826	762
55°	597	534	463	487	523	539
65°	348	291	238	238	258	347
75°	157	116	56	27	27	171
85°	30	15	3	0	0	37
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584606

CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9
2.5°	2028.5	2025.5	2022.5	2025.5	2022.5	2025.5	2022.5	2022.5	2019.5	2016.7	2016.7
5°	2061.2	2058.2	2058.2	2058.2	2055.2	2052.3	2052.3	2049.3	2043.3	2040.4	2034.4
7.5°	2082.0	2085.0	2085.0	2085.0	2079.0	2079.0	2073.1	2067.1	2061.2	2055.2	2046.3
10°	2105.7	2105.7	2102.7	2099.8	2093.8	2090.8	2088.0	2082.0	2073.1	2061.2	2052.3
12.5°	2114.6	2114.6	2111.7	2105.7	2102.7	2099.8	2096.8	2088.0	2076.1	2061.2	2049.3
15°	2117.6	2111.7	2108.7	2105.7	2099.8	2090.8	2090.8	2079.0	2064.2	2046.3	2031.4
17.5°	2093.8	2096.8	2090.8	2085.0	2076.1	2070.1	2061.2	2052.3	2034.4	2013.7	1998.8
20°	2064.2	2061.2	2058.2	2049.3	2037.4	2034.4	2025.5	2010.7	1995.9	1972.1	1951.2
22.5°	2016.7	2013.7	2007.8	2001.8	1989.9	1984.0	1975.0	1957.2	1936.5	1912.7	1888.9
25°	1957.2	1951.2	1942.4	1930.5	1921.6	1915.7	1903.8	1885.9	1862.2	1835.5	1811.7
27.5°	1862.2	1871.2	1865.2	1847.4	1838.4	1826.5	1823.6	1799.9	1779.0	1752.3	1725.6
30°	1770.1	1770.1	1761.2	1752.3	1737.4	1728.6	1716.7	1698.8	1678.0	1645.4	1624.6
32.5°	1654.3	1651.4	1639.5	1636.5	1624.6	1606.7	1603.8	1580.1	1559.3	1535.5	1508.8
35°	1526.5	1520.7	1508.8	1499.9	1493.9	1485.0	1476.1	1455.3	1434.5	1410.7	1392.9
37.5°	1381.0	1381.0	1378.1	1363.3	1357.3	1351.4	1342.4	1321.6	1309.7	1286.0	1268.2
40°	1241.4	1238.6	1229.6	1226.7	1220.7	1211.8	1205.8	1193.9	1176.1	1158.3	1140.5
42.5°	1104.8	1107.8	1096.0	1098.8	1087.1	1081.1	1078.1	1060.3	1051.4	1033.5	1018.8
45°	983.1	980.1	974.1	971.2	965.2	959.3	953.4	944.5	929.6	911.8	902.9
47.5°	870.2	861.3	861.3	858.3	855.4	843.5	840.5	831.6	822.6	804.9	793.0
50°	763.3	763.3	763.3	760.3	751.4	748.4	742.6	733.6	724.7	712.8	695.0
52.5°	677.1	677.1	677.1	674.1	662.4	659.4	656.4	644.5	632.6	623.7	611.8
55°	597.0	600.0	597.0	591.1	582.1	582.1	573.2	567.3	555.4	546.4	534.5
57.5°	528.7	528.7	522.8	519.8	513.8	510.9	504.9	499.0	484.1	475.2	460.3
60°	463.3	460.3	460.3	454.5	448.5	442.6	439.6	430.7	424.7	409.8	397.9
62.5°	403.9	403.9	397.9	397.9	386.2	386.2	383.2	374.3	365.3	350.5	344.5
65°	347.5	347.5	344.5	341.5	332.6	329.6	326.7	317.8	308.9	300.0	291.1
67.5°	297.0	297.0	291.1	288.1	282.1	279.2	273.2	267.3	258.3	249.4	240.6
70°	249.4	246.6	243.6	240.6	234.7	231.7	225.7	219.8	210.9	204.9	196.0
72.5°	201.9	201.9	199.0	193.0	190.0	187.1	184.1	178.1	169.3	160.4	154.5
75°	157.4	157.4	157.4	151.5	145.5	142.6	142.6	136.6	130.7	121.7	115.8
77.5°	121.7	118.8	115.8	115.8	109.8	106.9	104.0	101.0	92.1	89.1	83.2
80°	83.2	86.2	83.2	80.2	77.2	74.3	74.3	68.3	65.3	59.4	53.4
82.5°	56.4	53.4	53.4	50.5	50.5	47.5	47.5	41.5	38.6	35.6	32.7
85°	29.8	29.8	26.8	26.8	26.8	23.8	23.8	20.8	20.8	17.8	14.9
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584606

CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9
2.5°	2013.7	2007.8	2004.8	2004.8	2001.8	1998.8	1995.9	1992.9	1986.9	1986.9	1981.0
5°	2028.5	2022.5	2019.5	2010.7	2004.8	2004.8	1992.9	1989.9	1981.0	1975.0	1969.1
7.5°	2040.4	2028.5	2019.5	2010.7	2004.8	1998.8	1986.9	1975.0	1963.1	1951.2	1945.4
10°	2040.4	2028.5	2013.7	1998.8	1992.9	1986.9	1972.1	1954.2	1939.5	1927.6	1912.7
12.5°	2034.4	2016.7	1998.8	1986.9	1975.0	1966.1	1948.3	1930.5	1912.7	1888.9	1877.0
15°	2016.7	1992.9	1975.0	1954.2	1945.4	1930.5	1915.7	1888.9	1868.2	1847.4	1832.5
17.5°	1981.0	1951.2	1930.5	1909.7	1894.8	1885.9	1862.2	1838.4	1814.6	1791.0	1773.1
20°	1927.6	1900.8	1877.0	1850.3	1838.4	1826.5	1796.9	1773.1	1749.3	1722.6	1704.8
22.5°	1862.2	1835.5	1802.8	1782.0	1764.2	1749.3	1722.6	1695.9	1672.1	1648.4	1624.6
25°	1782.0	1755.2	1725.6	1692.9	1681.0	1666.1	1636.5	1609.7	1583.1	1556.3	1535.5
27.5°	1695.9	1660.3	1636.5	1600.8	1589.0	1574.1	1541.4	1511.8	1488.0	1467.2	1443.5
30°	1592.0	1565.2	1532.5	1499.9	1488.0	1473.1	1446.4	1419.7	1395.9	1372.2	1348.4
32.5°	1479.1	1452.3	1419.7	1395.9	1378.1	1366.2	1339.5	1315.7	1292.0	1268.2	1247.4
35°	1360.3	1330.5	1306.9	1283.1	1268.2	1253.3	1226.7	1205.8	1188.0	1167.3	1146.4
37.5°	1238.6	1217.7	1193.9	1167.3	1152.4	1140.5	1119.7	1096.0	1081.1	1063.3	1048.4
40°	1119.7	1096.0	1075.2	1051.4	1039.5	1030.5	1009.8	992.0	977.1	962.2	953.4
42.5°	997.9	977.1	956.3	941.5	932.6	923.7	908.8	888.0	879.2	864.3	855.4
45°	885.0	867.3	852.4	831.6	825.6	819.7	801.9	787.1	778.1	769.2	763.3
47.5°	778.1	766.2	748.4	736.6	727.7	721.7	709.8	697.9	689.0	683.1	677.1
50°	686.0	671.3	659.4	647.5	641.5	632.6	620.7	614.8	608.8	602.9	602.9
52.5°	600.0	585.1	573.2	564.3	558.3	552.4	543.5	540.5	534.5	534.5	531.6
55°	519.8	510.9	499.0	487.1	484.1	481.1	475.2	469.2	466.2	463.3	466.2
57.5°	451.5	442.6	430.7	421.7	418.8	415.8	412.8	406.9	403.9	403.9	403.9
60°	389.1	380.2	371.3	362.4	362.4	356.4	353.4	350.5	347.5	344.5	344.5
62.5°	332.6	323.7	314.9	308.9	305.9	303.0	297.0	294.0	291.1	291.1	288.1
65°	282.1	270.2	267.3	258.3	255.4	252.4	249.4	243.6	240.6	237.6	234.7
67.5°	231.7	225.7	216.8	210.9	207.9	204.9	201.9	196.0	193.0	190.0	184.1
70°	187.1	181.1	175.3	169.3	166.4	163.4	157.4	151.5	148.5	142.6	133.6
72.5°	145.5	139.6	133.6	127.7	124.7	121.7	115.8	109.8	104.0	98.1	92.1
75°	109.8	104.0	95.1	89.1	86.2	86.2	77.2	71.3	65.3	56.4	50.5
77.5°	77.2	68.3	65.3	59.4	56.4	50.5	44.5	38.6	32.7	29.8	23.8
80°	50.5	44.5	38.6	35.6	32.7	29.8	26.8	20.8	14.9	11.9	8.9
82.5°	29.8	26.8	23.8	20.8	17.8	14.9	11.9	11.9	8.9	5.9	3.0
85°	14.9	11.9	8.9	8.9	5.9	5.9	5.9	3.0	3.0	3.0	3.0
87.5°	5.9	3.0	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584606

CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9
2.5°	1978.0	1975.0	1972.1	1969.1	1969.1	1963.1	1963.1	1960.2	1954.2	1951.2	1951.2
5°	1960.2	1951.2	1945.4	1942.4	1939.5	1930.5	1927.6	1921.6	1915.7	1909.7	1906.7
7.5°	1933.5	1918.6	1912.7	1909.7	1900.8	1891.9	1885.9	1877.0	1868.2	1859.3	1856.3
10°	1900.8	1885.9	1871.2	1865.2	1856.3	1850.3	1838.4	1826.5	1817.6	1808.7	1799.9
12.5°	1859.3	1841.4	1826.5	1820.6	1811.7	1799.9	1782.0	1776.1	1761.2	1755.2	1743.4
15°	1811.7	1791.0	1776.1	1767.2	1758.2	1740.4	1728.6	1716.7	1701.8	1695.9	1684.0
17.5°	1752.3	1728.6	1713.7	1704.8	1698.8	1684.0	1666.1	1651.4	1636.5	1630.5	1621.6
20°	1681.0	1666.1	1645.4	1636.5	1630.5	1612.7	1594.8	1589.0	1577.1	1565.2	1556.3
22.5°	1600.8	1586.0	1565.2	1556.3	1553.3	1538.4	1523.6	1514.8	1505.8	1496.9	1488.0
25°	1517.7	1499.9	1482.0	1476.1	1470.1	1458.2	1446.4	1440.5	1431.6	1425.6	1419.7
27.5°	1428.6	1410.7	1395.9	1386.9	1381.0	1372.2	1366.2	1360.3	1354.3	1348.4	1345.4
30°	1333.5	1315.7	1303.9	1297.9	1292.0	1289.0	1280.1	1277.1	1274.1	1268.2	1271.2
32.5°	1238.6	1223.7	1211.8	1202.9	1202.9	1196.9	1193.9	1193.9	1191.0	1191.0	1191.0
35°	1134.5	1125.6	1116.7	1113.7	1110.7	1107.8	1104.8	1107.8	1104.8	1107.8	1110.7
37.5°	1039.5	1030.5	1024.7	1021.7	1018.8	1021.7	1018.8	1018.8	1021.7	1027.6	1030.5
40°	941.5	935.6	929.6	932.6	929.6	929.6	929.6	938.6	941.5	944.5	947.5
42.5°	849.4	843.5	840.5	840.5	843.5	840.5	846.4	849.4	855.4	864.3	870.2
45°	760.3	757.3	757.3	760.3	757.3	763.3	763.3	769.2	778.1	784.1	790.0
47.5°	677.1	677.1	677.1	680.1	680.1	683.1	689.0	692.0	697.9	703.9	709.8
50°	600.0	602.9	605.8	605.8	605.8	611.8	617.7	620.7	623.7	626.7	635.6
52.5°	531.6	534.5	534.5	537.5	540.5	543.5	546.4	552.4	555.4	561.3	564.3
55°	466.2	466.2	472.2	475.2	475.2	475.2	481.1	481.1	487.1	490.0	496.0
57.5°	403.9	406.9	406.9	409.8	409.8	412.8	415.8	418.8	421.7	424.7	427.7
60°	344.5	344.5	344.5	347.5	350.5	353.4	350.5	356.4	356.4	362.4	365.3
62.5°	288.1	291.1	291.1	291.1	291.1	291.1	291.1	294.0	297.0	300.0	303.0
65°	234.7	234.7	234.7	231.7	234.7	231.7	234.7	237.6	237.6	240.6	243.6
67.5°	181.1	181.1	175.3	175.3	178.1	178.1	178.1	178.1	175.3	181.1	181.1
70°	130.7	127.7	124.7	121.7	121.7	118.8	118.8	115.8	115.8	115.8	115.8
72.5°	86.2	80.2	74.3	71.3	68.3	68.3	62.4	59.4	62.4	62.4	62.4
75°	44.5	38.6	35.6	32.7	29.8	29.8	26.8	26.8	26.8	26.8	26.8
77.5°	17.8	14.9	11.9	11.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
80°	5.9	5.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	3.0	0.0	0.0	3.0	0.0	3.0	3.0	3.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584606

CATALOG NUMBER: HCC8S40D010BZ-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9	1986.9
2.5°	1948.3	1948.3	1945.4	1948.3	1942.4	1945.4	1942.4	1942.4
5°	1903.8	1897.8	1897.8	1897.8	1894.8	1894.8	1891.9	1891.9
7.5°	1850.3	1847.4	1844.4	1841.4	1838.4	1835.5	1835.5	1835.5
10°	1796.9	1791.0	1791.0	1788.0	1782.0	1779.0	1779.0	1779.0
12.5°	1734.4	1731.6	1728.6	1728.6	1716.7	1719.7	1716.7	1716.7
15°	1675.0	1672.1	1672.1	1663.3	1657.3	1657.3	1657.3	1654.3
17.5°	1612.7	1609.7	1606.7	1600.8	1594.8	1594.8	1592.0	1594.8
20°	1547.4	1544.4	1538.4	1538.4	1535.5	1532.5	1526.5	1529.5
22.5°	1482.0	1476.1	1473.1	1473.1	1470.1	1470.1	1464.2	1464.2
25°	1413.7	1410.7	1407.8	1410.7	1404.8	1404.8	1398.8	1398.8
27.5°	1342.4	1339.5	1339.5	1339.5	1336.5	1339.5	1336.5	1336.5
30°	1271.2	1271.2	1268.2	1268.2	1271.2	1268.2	1271.2	1274.1
32.5°	1193.9	1193.9	1196.9	1196.9	1199.9	1199.9	1199.9	1199.9
35°	1113.7	1119.7	1119.7	1122.6	1125.6	1128.6	1128.6	1131.6
37.5°	1039.5	1042.4	1045.4	1048.4	1054.3	1054.3	1054.3	1054.3
40°	959.3	962.2	968.2	965.2	977.1	980.1	977.1	977.1
42.5°	876.2	882.1	885.0	891.0	893.9	899.9	902.9	902.9
45°	799.0	801.9	807.9	813.8	816.7	825.6	825.6	825.6
47.5°	718.8	724.7	727.7	733.6	736.6	745.4	748.4	745.4
50°	641.5	647.5	653.4	653.4	662.4	665.3	671.3	674.1
52.5°	567.3	570.2	576.2	579.2	585.1	591.1	594.0	597.0
55°	496.0	499.0	504.9	504.9	513.8	516.8	522.8	522.8
57.5°	430.7	433.6	439.6	436.6	442.6	448.5	448.5	445.5
60°	368.3	368.3	368.3	374.3	377.2	380.2	383.2	383.2
62.5°	303.0	308.9	311.9	311.9	314.9	317.8	317.8	314.9
65°	243.6	249.4	252.4	252.4	255.4	255.4	255.4	258.3
67.5°	184.1	184.1	184.1	187.1	184.1	184.1	184.1	184.1
70°	115.8	115.8	115.8	115.8	112.8	115.8	115.8	118.8
72.5°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
75°	26.8	26.8	26.8	29.8	26.8	26.8	26.8	26.8
77.5°	11.9	8.9	11.9	11.9	8.9	8.9	8.9	8.9
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	0.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)