

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584600

Luminaire Tested: **HCC8W40D010BZ-HM82555930-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010BZ-HM82555930-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4111.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584600
CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584600

CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90				88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67621	67621	67621
5°	68888	67328	65762
10°	69967	66150	63360
15°	70667	64503	60617
20°	70399	62014	57821
25°	68545	58433	54595
30°	65278	54168	51420
35°	58947	49442	47763
40°	51791	44376	44255
45°	44708	39004	40687
50°	38916	34214	36488
55°	34504	29709	31789
60°	30787	25107	26390
65°	27749	20379	20810
70°	24641	15264	12325
75°	21243	8852	5314
80°	16355	3161	1580
85°	10543	1061	1061



TEST NUMBER: P584600
 CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.9	5.0
10°-20°	573.1	13.9
20°-30°	810.5	19.7
30°-40°	854.1	20.8
40°-50°	725.9	17.7
50°-60°	522.7	12.7
60°-70°	301.5	7.3
70°-80°	103.2	2.5
80°-90°	14.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1589.4	38.7
0°-40°	2443.5	59.4
0°-60°	3692.1	89.8
0°-90°	4111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4111.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2193	2193	2193	2193	2193	
5°	2226	2211	2175	2136	2124	213
15°	2214	2145	2020	1931	1899	623
25°	2015	1910	1717	1628	1605	924
35°	1566	1474	1313	1266	1269	975
45°	1025	978	894	900	933	796
55°	642	591	553	574	591	578
65°	380	327	279	273	285	378
75°	178	134	74	48	45	188
85°	30	18	3	3	3	40
90°	0	0	0	0	0	



TEST NUMBER: P584600

CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9
2.5°	2213.6	2216.6	2213.6	2213.6	2210.7	2207.7	2204.7	2201.9	2195.9	2190.0	2190.0
5°	2225.5	2231.5	2225.5	2225.5	2216.6	2210.7	2204.7	2195.9	2184.0	2175.1	2175.1
7.5°	2234.5	2234.5	2234.5	2225.5	2219.6	2210.7	2195.9	2181.0	2166.2	2151.3	2145.3
10°	2234.5	2234.5	2231.5	2219.6	2213.6	2195.9	2181.0	2160.2	2139.4	2118.6	2112.6
12.5°	2225.5	2228.5	2222.6	2210.7	2195.9	2175.1	2154.3	2127.5	2103.8	2080.0	2068.1
15°	2213.6	2210.7	2204.7	2190.0	2172.1	2145.3	2124.5	2094.9	2062.2	2032.4	2020.5
17.5°	2184.0	2184.0	2175.1	2160.2	2136.4	2106.7	2074.1	2041.3	2005.7	1973.0	1958.1
20°	2145.3	2145.3	2133.4	2115.6	2091.9	2053.2	2017.5	1979.0	1937.3	1904.7	1889.8
22.5°	2088.9	2091.9	2077.0	2056.2	2029.4	1984.9	1949.2	1901.7	1860.1	1821.4	1809.6
25°	2014.6	2020.5	2005.7	1984.9	1949.2	1910.5	1866.0	1821.4	1773.9	1735.3	1717.4
27.5°	1928.4	1931.4	1916.5	1895.8	1860.1	1818.4	1773.9	1726.3	1681.8	1640.2	1622.3
30°	1833.3	1821.4	1815.5	1788.8	1750.1	1714.6	1664.0	1625.3	1577.8	1542.1	1521.3
32.5°	1699.7	1705.6	1687.8	1667.0	1637.2	1595.7	1554.0	1509.5	1464.9	1438.1	1423.2
35°	1565.9	1571.9	1562.9	1542.1	1509.5	1473.8	1432.2	1399.6	1360.9	1328.2	1313.4
37.5°	1426.2	1426.2	1420.4	1408.5	1384.7	1352.0	1310.4	1277.7	1245.0	1218.3	1209.4
40°	1286.6	1280.7	1277.7	1268.8	1248.0	1218.3	1191.5	1164.8	1132.0	1114.3	1102.4
42.5°	1149.9	1149.9	1143.9	1135.0	1114.3	1099.4	1072.7	1042.9	1019.2	1001.4	1001.4
45°	1025.2	1028.2	1019.2	1013.3	1001.4	977.6	953.8	933.0	912.3	900.4	894.4
47.5°	915.2	915.2	906.3	900.4	888.5	867.6	846.8	829.1	814.2	805.3	802.3
50°	811.2	811.2	811.2	796.3	781.5	766.6	751.7	731.0	722.1	716.1	713.2
52.5°	722.1	719.1	719.1	707.2	692.3	674.5	659.6	641.8	633.0	627.0	630.0
55°	641.8	641.8	638.8	624.0	609.2	591.3	576.4	561.6	555.6	549.7	552.6
56°	609.2	609.2	606.2	594.3	576.4	561.6	543.7	529.0	520.0	523.0	523.0
57°	585.4	579.4	579.4	564.5	549.7	529.0	514.1	499.2	493.3	490.3	490.3
58°	555.6	552.6	549.7	534.9	520.0	502.2	487.3	472.4	463.5	463.5	460.5
59°	526.0	526.0	520.0	508.1	493.3	475.4	460.5	445.7	436.8	433.9	433.9
60°	499.2	502.2	493.3	481.4	469.5	448.6	430.9	419.0	410.1	407.1	407.1
61°	475.4	475.4	469.5	454.6	439.8	424.9	407.1	392.2	386.3	380.3	380.3
62°	454.6	448.6	445.7	430.9	416.0	398.2	383.3	368.4	359.5	353.5	356.5
63°	427.9	424.9	419.0	407.1	392.2	374.4	356.5	344.6	335.8	326.9	329.9
64°	407.1	404.1	395.2	383.3	368.4	350.6	332.8	320.9	315.0	306.1	303.1
65°	380.3	377.3	374.4	359.5	344.6	326.9	312.0	300.1	291.2	285.2	279.3
66°	356.5	359.5	353.5	341.8	323.9	309.0	288.2	276.3	270.4	261.4	255.5
67°	335.8	335.8	329.9	318.0	300.1	285.2	270.4	255.5	246.6	237.8	234.8
67.5°	323.9	323.9	318.0	303.1	291.2	273.3	258.5	246.6	234.8	228.8	222.9
68°	312.0	312.0	309.0	297.1	282.3	264.4	249.5	234.8	222.9	214.0	211.0
69°	291.2	294.2	288.2	276.3	261.4	243.7	228.8	216.9	205.0	196.1	190.2
70°	273.3	270.4	264.4	252.5	237.8	225.9	211.0	196.1	184.2	172.3	169.3
71°	249.5	249.5	243.7	234.8	219.9	205.0	190.2	178.3	166.4	151.5	148.5
72°	231.8	231.8	225.9	214.0	202.1	187.2	172.3	157.4	148.5	133.8	127.8
72.5°	219.9	222.9	216.9	205.0	193.1	175.3	163.4	151.5	136.7	124.8	118.9
73°	214.0	211.0	208.0	196.1	181.2	169.3	154.5	142.7	127.8	115.9	110.0



TEST NUMBER: P584600
 CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	133.8	133.8	130.8	118.9	107.0	95.1	83.2	71.3	59.4	47.6	41.6
80°	92.1	95.1	89.1	83.2	74.3	62.4	50.5	41.6	29.8	23.8	17.8
82.5°	59.4	59.4	56.4	50.5	44.6	35.7	29.8	20.8	14.9	11.9	8.9
85°	29.8	32.7	29.8	26.8	20.8	17.8	14.9	8.9	5.9	3.0	3.0
87.5°	11.9	11.9	11.9	8.9	8.9	5.9	3.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584600

CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9	2192.9
2.5°	2184.0	2184.0	2178.1	2175.1	2172.1	2169.1	2166.2	2163.2	2163.2	2166.2
5°	2166.2	2160.2	2148.3	2145.3	2136.4	2133.4	2127.5	2124.5	2127.5	2124.5
7.5°	2139.4	2127.5	2112.6	2106.7	2094.9	2088.9	2080.0	2080.0	2074.1	2077.0
10°	2103.8	2086.0	2068.1	2056.2	2047.3	2038.4	2032.4	2026.5	2023.5	2023.5
12.5°	2059.2	2038.4	2020.5	2002.8	1987.9	1981.9	1970.0	1970.0	1964.1	1961.1
15°	2008.6	1981.9	1961.1	1943.3	1931.4	1919.5	1910.5	1904.7	1898.8	1898.8
17.5°	1943.3	1919.5	1898.8	1877.9	1860.1	1851.2	1842.2	1833.3	1833.3	1827.4
20°	1872.0	1845.2	1827.4	1806.7	1791.8	1776.9	1765.0	1765.0	1759.1	1762.0
22.5°	1791.8	1759.1	1741.2	1726.3	1711.6	1699.7	1687.8	1687.8	1684.8	1681.8
25°	1702.7	1675.9	1655.1	1637.2	1628.3	1616.5	1613.5	1607.6	1604.6	1604.6
27.5°	1607.6	1586.7	1560.0	1551.0	1539.1	1533.2	1533.2	1530.2	1524.3	1527.2
30°	1506.5	1482.7	1467.9	1461.9	1450.0	1450.0	1447.0	1441.1	1441.1	1444.1
32.5°	1408.5	1384.7	1372.8	1369.8	1357.9	1357.9	1354.9	1357.9	1357.9	1360.9
35°	1301.5	1280.7	1277.7	1268.8	1265.8	1265.8	1265.8	1271.8	1277.7	1268.8
37.5°	1200.5	1185.6	1176.7	1173.7	1176.7	1176.7	1179.6	1188.6	1185.6	1182.6
40°	1096.5	1084.6	1078.6	1078.6	1084.6	1090.5	1090.5	1099.4	1102.4	1099.4
42.5°	992.5	983.5	983.5	986.5	992.5	995.4	1004.4	1013.3	1016.3	1019.2
45°	894.4	894.4	894.4	897.4	900.4	906.3	918.2	927.1	930.1	933.0
47.5°	799.3	796.3	805.3	808.2	817.2	820.1	829.1	840.9	843.8	846.8
50°	710.2	716.1	719.1	728.0	734.0	734.0	745.8	751.7	760.6	760.6
52.5°	627.0	635.9	638.8	647.7	650.7	653.7	659.6	668.5	674.5	674.5
55°	552.6	555.6	561.6	564.5	573.5	576.4	582.4	585.4	594.3	591.3
56°	520.0	526.0	529.0	534.9	540.7	543.7	549.7	552.6	558.6	561.6
57°	490.3	493.3	502.2	505.2	511.1	511.1	514.1	523.0	523.0	526.0
58°	460.5	466.5	469.5	472.4	478.4	481.4	487.3	490.3	493.3	490.3
59°	433.9	436.8	439.8	439.8	445.7	445.7	454.6	460.5	463.5	463.5
60°	407.1	407.1	410.1	413.0	419.0	422.0	422.0	427.9	427.9	427.9
61°	380.3	380.3	383.3	386.3	389.2	389.2	395.2	395.2	398.2	401.1
62°	356.5	353.5	353.5	356.5	356.5	362.5	365.4	368.4	371.4	368.4
63°	329.9	326.9	326.9	326.9	326.9	332.8	332.8	335.8	341.8	338.8
64°	300.1	300.1	300.1	300.1	303.1	303.1	309.0	312.0	315.0	318.0
65°	279.3	273.3	270.4	270.4	273.3	276.3	279.3	282.3	285.2	285.2
66°	255.5	249.5	246.6	246.6	246.6	246.6	252.5	252.5	258.5	258.5
67°	228.8	222.9	219.9	216.9	216.9	216.9	225.9	222.9	222.9	222.9
67.5°	219.9	211.0	208.0	205.0	202.1	208.0	205.0	208.0	208.0	205.0
68°	208.0	202.1	196.1	190.2	190.2	190.2	193.1	196.1	193.1	190.2
69°	184.2	181.2	172.3	166.4	163.4	166.4	163.4	166.4	163.4	166.4
70°	163.4	154.5	145.7	142.7	139.7	139.7	139.7	136.7	139.7	136.7
71°	142.7	133.8	124.8	118.9	115.9	115.9	112.9	115.9	112.9	115.9
72°	121.9	112.9	101.0	95.1	95.1	95.1	95.1	92.1	95.1	92.1
72.5°	112.9	101.0	92.1	86.2	83.2	83.2	83.2	83.2	80.2	83.2
73°	104.0	92.1	80.2	77.2	77.2	77.2	74.3	71.3	74.3	74.3



TEST NUMBER: P584600
CATALOG NUMBER: HCC8W40D010BZ-HM82555930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	35.7	26.8	23.8	23.8	23.8	23.8	23.8	23.8	20.8	20.8
80°	14.9	11.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
82.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
85°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	193.1	193.1	187.2	178.3	163.4	148.5	136.7	124.8	110.0	95.1	89.1
75°	178.3	175.3	169.3	160.4	148.5	133.8	121.9	107.0	95.1	80.2	74.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	86.2	71.3	65.3	59.4	59.4	59.4	56.4	56.4	56.4	59.4
75°	68.3	56.4	50.5	44.6	47.6	44.6	47.6	44.6	44.6	44.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)