

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584795

Luminaire Tested: **HCC8S50D010SL-HM82555827-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010SL-HM82555827-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4911.8 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584795
CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584795

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57				
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50				
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45				
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37				
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33				
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75308	75308	75308
5°	78066	75061	72482
10°	80271	74404	69519
15°	82061	73090	66447
20°	82189	70235	63747
25°	80613	66330	61495
30°	76458	61511	58794
35°	69472	56026	56150
40°	60747	50269	52926
45°	52645	44778	49318
50°	46097	39774	44931
55°	41025	35251	40654
60°	37016	31663	35733
65°	33411	27843	31134
70°	30023	23459	23144
75°	26450	18598	17359
80°	22162	15396	16621
85°	17160	13480	14718



TEST NUMBER: P584795
 CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.4	4.7
10°-20°	648.9	13.2
20°-30°	927.4	18.9
30°-40°	985.4	20.1
40°-50°	848.4	17.3
50°-60°	634.3	12.9
60°-70°	404.6	8.2
70°-80°	184.1	3.7
80°-90°	48.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1806.7	36.8
0°-40°	2792.1	56.8
0°-60°	4274.8	87.0
0°-90°	4911.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4911.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2442	2442	2442	2442	2442	
5°	2522	2487	2425	2362	2342	242
15°	2570	2484	2290	2133	2081	724
25°	2369	2220	1950	1832	1807	1085
35°	1846	1717	1488	1450	1492	1149
45°	1207	1141	1027	1055	1131	938
55°	763	701	656	711	756	686
65°	458	406	382	399	427	457
75°	222	191	156	142	146	236
85°	48	42	38	42	42	58
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584795

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2
2.5°	2487.3	2480.4	2483.8	2480.4	2483.8	2483.8	2476.9	2476.9	2476.9	2476.9	2466.5
5°	2522.0	2518.5	2518.5	2515.0	2511.6	2515.0	2511.6	2508.1	2501.2	2497.7	2487.3
7.5°	2542.8	2542.8	2542.8	2542.8	2539.3	2535.8	2532.4	2525.4	2518.5	2511.6	2504.6
10°	2563.6	2567.0	2563.6	2560.1	2556.6	2549.7	2546.2	2539.3	2528.9	2518.5	2511.6
12.5°	2574.0	2574.0	2570.5	2570.5	2563.6	2560.1	2549.7	2539.3	2528.9	2518.5	2501.2
15°	2570.5	2570.5	2567.0	2563.6	2553.2	2549.7	2542.8	2532.4	2515.0	2501.2	2483.8
17.5°	2549.7	2546.2	2539.3	2539.3	2525.4	2522.0	2515.0	2501.2	2483.8	2463.0	2442.2
20°	2504.6	2504.6	2501.2	2497.7	2483.8	2473.4	2466.5	2449.1	2435.3	2410.9	2390.1
22.5°	2442.2	2449.1	2442.2	2435.3	2417.8	2414.5	2404.0	2383.2	2362.4	2334.6	2310.3
25°	2369.3	2365.8	2362.4	2355.4	2341.6	2334.6	2320.8	2299.9	2279.1	2247.9	2220.2
27.5°	2275.7	2261.8	2261.8	2247.9	2237.5	2227.1	2220.2	2199.4	2171.5	2147.3	2112.6
30°	2147.3	2150.7	2133.4	2129.9	2112.6	2105.7	2091.8	2071.0	2046.7	2019.0	1991.2
32.5°	2008.6	1998.2	1998.2	1984.3	1970.3	1959.9	1956.6	1932.2	1911.4	1883.6	1855.9
35°	1845.5	1845.5	1835.1	1831.6	1817.8	1810.8	1800.4	1786.6	1762.3	1738.0	1717.1
37.5°	1685.9	1679.0	1675.5	1668.6	1658.2	1647.8	1647.8	1623.5	1620.0	1592.3	1564.5
40°	1509.1	1516.0	1509.1	1498.7	1495.2	1488.3	1484.7	1470.8	1460.4	1436.1	1418.8
42.5°	1359.9	1352.9	1352.9	1349.5	1335.6	1335.6	1328.6	1321.7	1304.4	1297.4	1276.5
45°	1207.2	1214.1	1203.7	1207.2	1193.3	1193.3	1193.3	1179.4	1165.6	1155.2	1141.3
47.5°	1075.4	1078.9	1078.9	1068.5	1065.0	1065.0	1058.1	1051.0	1040.6	1026.8	1016.4
50°	960.9	964.4	957.4	954.0	947.0	943.6	943.6	929.7	922.8	908.9	901.9
52.5°	856.9	856.9	853.4	853.4	843.0	843.0	836.1	825.7	818.7	811.8	794.5
55°	763.1	763.1	759.7	756.2	756.2	745.8	742.3	731.9	725.0	711.1	700.7
57.5°	673.0	676.5	673.0	669.5	666.1	662.6	655.7	645.3	638.3	627.9	621.0
60°	600.2	600.2	596.7	593.2	586.3	582.7	579.4	572.3	561.9	555.0	544.6
62.5°	530.7	527.3	523.8	520.3	513.4	513.4	506.5	499.5	489.1	482.2	475.2
65°	457.9	457.9	454.4	454.4	451.0	444.0	440.6	437.1	423.2	419.8	405.9
67.5°	392.0	395.5	388.6	388.6	381.6	381.6	378.2	367.8	364.3	357.4	350.3
70°	333.0	333.0	333.0	329.5	322.6	319.1	315.6	308.7	305.2	298.3	291.4
72.5°	274.0	274.0	270.6	270.6	267.1	263.6	260.2	253.2	253.2	246.3	239.4
75°	222.0	222.0	218.6	215.1	211.6	211.6	208.1	204.7	197.7	194.3	190.8
77.5°	170.0	170.0	170.0	166.5	163.1	163.1	163.1	156.1	149.2	149.2	145.7
80°	124.8	124.8	121.5	121.5	118.0	118.0	118.0	114.4	111.1	107.5	104.0
82.5°	83.2	83.2	83.2	83.2	79.8	79.8	79.8	76.3	72.8	72.8	72.8
85°	48.5	48.5	48.5	48.5	45.1	45.1	45.1	45.1	45.1	41.6	41.6
87.5°	20.8	17.3	20.8	17.3	20.8	17.3	20.8	17.3	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584795

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2
2.5°	2470.0	2466.5	2463.0	2459.5	2459.5	2456.1	2449.1	2445.7	2442.2	2438.7	2438.7
5°	2483.8	2480.4	2473.4	2466.5	2463.0	2456.1	2449.1	2442.2	2435.3	2424.9	2421.3
7.5°	2494.2	2483.8	2476.9	2463.0	2459.5	2452.6	2442.2	2431.8	2417.8	2404.0	2393.6
10°	2494.2	2480.4	2470.0	2452.6	2445.7	2438.7	2424.9	2407.4	2390.1	2376.2	2358.9
12.5°	2487.3	2470.0	2452.6	2435.3	2424.9	2414.5	2393.6	2376.2	2355.4	2334.6	2320.8
15°	2463.0	2442.2	2421.3	2400.5	2390.1	2376.2	2355.4	2331.2	2310.3	2289.5	2265.3
17.5°	2417.8	2397.0	2372.8	2348.5	2334.6	2324.2	2293.0	2275.7	2244.5	2223.7	2202.9
20°	2358.9	2334.6	2303.4	2279.1	2261.8	2251.4	2227.1	2195.8	2171.5	2140.3	2119.5
22.5°	2282.6	2251.4	2220.2	2195.8	2178.5	2164.6	2133.4	2102.2	2081.4	2053.7	2029.4
25°	2192.5	2161.1	2129.9	2095.3	2077.9	2064.1	2036.3	2008.6	1980.8	1949.5	1928.7
27.5°	2084.9	2050.2	2022.4	1991.2	1973.9	1953.0	1921.8	1894.0	1866.3	1845.5	1817.8
30°	1967.0	1928.7	1901.0	1869.8	1852.4	1835.1	1803.9	1776.2	1751.9	1727.5	1713.6
32.5°	1824.7	1797.0	1769.2	1738.0	1724.0	1713.6	1682.4	1654.7	1627.0	1606.1	1595.7
35°	1689.4	1658.2	1633.9	1606.1	1588.8	1578.4	1550.7	1526.4	1512.5	1488.3	1474.3
37.5°	1547.2	1522.9	1495.2	1467.3	1456.9	1446.5	1425.7	1401.5	1380.7	1363.3	1356.4
40°	1398.0	1377.2	1352.9	1335.6	1325.2	1314.8	1297.4	1280.1	1266.1	1248.8	1241.9
42.5°	1255.7	1241.9	1221.1	1200.3	1189.8	1186.4	1165.6	1151.7	1144.8	1137.8	1130.9
45°	1127.4	1106.6	1092.8	1078.9	1068.5	1061.6	1051.0	1040.6	1033.7	1026.8	1019.8
47.5°	1002.5	985.2	971.3	960.9	950.5	947.0	940.1	929.7	922.8	922.8	922.8
50°	888.1	874.2	860.3	853.4	849.9	843.0	836.1	832.6	829.1	829.1	829.1
52.5°	787.4	773.6	763.1	756.2	756.2	749.3	742.3	738.9	738.9	738.9	738.9
55°	693.8	683.4	676.5	669.5	662.6	659.1	659.1	659.1	655.7	655.7	659.1
57.5°	610.6	603.6	593.2	586.3	582.7	582.7	579.4	575.8	579.4	582.7	586.3
60°	534.2	527.3	523.8	513.4	513.4	513.4	509.9	509.9	509.9	513.4	516.9
62.5°	464.8	461.4	454.4	451.0	447.5	447.5	444.0	444.0	444.0	444.0	447.5
65°	402.4	395.5	388.6	388.6	388.6	385.1	385.1	378.2	381.6	381.6	378.2
67.5°	343.5	336.4	333.0	329.5	326.0	326.0	322.6	319.1	315.6	315.6	315.6
70°	287.9	281.0	281.0	274.0	274.0	270.6	267.1	267.1	263.6	260.2	256.7
72.5°	232.4	229.0	225.5	222.0	222.0	222.0	218.6	215.1	211.6	208.1	201.2
75°	183.9	183.9	176.9	173.5	173.5	170.0	166.5	163.1	159.6	156.1	152.7
77.5°	142.3	138.8	131.9	128.4	128.4	128.4	124.8	121.5	118.0	114.4	111.1
80°	104.0	100.7	97.1	93.6	93.6	93.6	90.2	90.2	86.7	86.7	86.7
82.5°	69.3	69.3	65.9	65.9	65.9	65.9	62.4	62.4	62.4	62.4	62.4
85°	41.6	41.6	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584795

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2
2.5°	2431.8	2431.8	2424.9	2421.3	2417.8	2421.3	2414.5	2410.9	2407.4	2407.4	2404.0
5°	2410.9	2407.4	2393.6	2390.1	2386.6	2383.2	2376.2	2369.3	2362.4	2358.9	2355.4
7.5°	2383.2	2372.8	2358.9	2355.4	2352.0	2341.6	2331.2	2324.2	2313.8	2310.3	2303.4
10°	2345.0	2331.2	2320.8	2310.3	2303.4	2293.0	2282.6	2272.2	2258.3	2254.9	2244.5
12.5°	2299.9	2282.6	2261.8	2258.3	2247.9	2234.1	2220.2	2209.8	2199.4	2192.5	2182.1
15°	2244.5	2227.1	2206.3	2195.8	2185.4	2175.0	2157.7	2143.8	2133.4	2123.0	2112.6
17.5°	2178.5	2157.7	2140.3	2129.9	2123.0	2105.7	2091.8	2074.5	2064.1	2053.7	2043.3
20°	2098.7	2081.4	2057.1	2046.7	2043.3	2029.4	2012.0	2005.1	1991.2	1980.8	1973.9
22.5°	2008.6	1991.2	1970.3	1963.5	1949.5	1942.6	1925.3	1918.3	1911.4	1901.0	1897.5
25°	1907.9	1890.6	1873.2	1869.8	1859.4	1852.4	1842.0	1831.6	1831.6	1821.2	1821.2
27.5°	1803.9	1786.6	1772.7	1765.8	1762.3	1755.3	1744.8	1741.5	1738.0	1734.4	1734.4
30°	1692.8	1672.0	1665.1	1661.6	1658.2	1651.2	1647.8	1640.8	1644.3	1647.8	1644.3
32.5°	1574.9	1568.0	1554.1	1547.2	1550.7	1547.2	1540.3	1547.2	1543.7	1550.7	1554.1
35°	1460.4	1453.5	1446.5	1446.5	1439.6	1439.6	1439.6	1443.1	1450.0	1453.5	1460.4
37.5°	1349.5	1339.1	1335.6	1332.1	1335.6	1335.6	1335.6	1342.5	1349.5	1356.4	1366.8
40°	1231.5	1224.5	1224.5	1224.5	1224.5	1234.9	1231.5	1238.4	1245.3	1255.7	1266.1
42.5°	1120.5	1120.5	1124.0	1124.0	1124.0	1124.0	1130.9	1141.3	1151.7	1162.1	1172.5
45°	1016.4	1016.4	1016.4	1023.3	1023.3	1026.8	1040.6	1047.7	1054.6	1065.0	1075.4
47.5°	919.3	919.3	922.8	926.2	929.7	936.6	943.6	954.0	964.4	971.3	981.7
50°	829.1	832.6	839.5	846.5	846.5	849.9	860.3	867.3	874.2	884.6	888.1
52.5°	742.3	749.3	756.2	759.7	763.1	770.1	773.6	784.0	787.4	797.8	801.3
55°	662.6	666.1	676.5	679.9	679.9	686.9	693.8	700.7	711.1	711.1	718.1
57.5°	589.8	593.2	600.2	603.6	600.2	610.6	614.0	621.0	624.4	631.4	634.9
60°	516.9	523.8	527.3	527.3	530.7	534.2	541.1	541.1	548.1	555.0	555.0
62.5°	447.5	451.0	454.4	457.9	461.4	457.9	468.3	468.3	475.2	478.7	485.6
65°	381.6	385.1	385.1	388.6	388.6	392.0	392.0	395.5	399.0	405.9	409.4
67.5°	315.6	315.6	315.6	319.1	315.6	319.1	319.1	322.6	322.6	329.5	333.0
70°	256.7	253.2	249.8	249.8	249.8	249.8	246.3	249.8	249.8	253.2	253.2
72.5°	197.7	194.3	190.8	187.3	187.3	183.9	180.4	183.9	183.9	187.3	187.3
75°	149.2	142.3	142.3	142.3	138.8	138.8	138.8	142.3	142.3	142.3	145.7
77.5°	111.1	111.1	107.5	107.5	107.5	111.1	111.1	114.4	114.4	114.4	114.4
80°	83.2	86.7	86.7	86.7	86.7	90.2	90.2	90.2	90.2	93.6	93.6
82.5°	62.4	62.4	62.4	62.4	65.9	65.9	65.9	65.9	65.9	65.9	65.9
85°	38.1	41.6	41.6	38.1	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584795

CATALOG NUMBER: HCC8S50D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2	2442.2
2.5°	2400.5	2400.5	2400.5	2400.5	2397.0	2397.0	2397.0	2393.6
5°	2348.5	2348.5	2348.5	2341.6	2345.0	2345.0	2338.1	2341.6
7.5°	2296.5	2293.0	2289.5	2289.5	2286.1	2282.6	2279.1	2282.6
10°	2237.5	2227.1	2227.1	2223.7	2223.7	2216.7	2216.7	2220.2
12.5°	2171.5	2164.6	2164.6	2161.1	2157.7	2154.2	2150.7	2150.7
15°	2105.7	2098.7	2095.3	2091.8	2088.3	2081.4	2084.9	2081.4
17.5°	2039.8	2029.4	2029.4	2025.9	2022.4	2015.5	2015.5	2012.0
20°	1963.5	1959.9	1953.0	1956.6	1953.0	1946.2	1942.6	1942.6
22.5°	1887.1	1887.1	1883.6	1883.6	1880.2	1876.7	1873.2	1873.2
25°	1814.3	1810.8	1814.3	1814.3	1803.9	1803.9	1803.9	1807.4
27.5°	1731.1	1734.4	1731.1	1731.1	1731.1	1731.1	1734.4	1731.1
30°	1647.8	1647.8	1647.8	1651.2	1658.2	1654.7	1654.7	1651.2
32.5°	1557.6	1561.1	1561.1	1564.5	1568.0	1574.9	1574.9	1578.4
35°	1467.3	1474.3	1477.8	1474.3	1484.7	1484.7	1491.6	1491.6
37.5°	1373.7	1377.2	1384.1	1387.6	1394.5	1398.0	1401.5	1401.5
40°	1273.2	1287.0	1290.5	1294.0	1304.4	1304.4	1307.8	1314.8
42.5°	1179.4	1193.3	1196.8	1200.3	1207.2	1217.6	1214.1	1221.1
45°	1089.3	1099.7	1103.2	1106.6	1117.0	1120.5	1120.5	1130.9
47.5°	992.1	999.0	1002.5	1009.4	1016.4	1023.3	1030.2	1026.8
50°	895.0	905.4	912.3	915.8	926.2	929.7	933.2	936.6
52.5°	808.2	815.3	818.7	822.2	832.6	836.1	839.5	846.5
55°	725.0	728.5	735.4	731.9	742.3	745.8	749.3	756.2
57.5°	641.8	645.3	648.7	648.7	655.7	662.6	666.1	669.5
60°	561.9	569.0	572.3	572.3	572.3	579.4	579.4	579.4
62.5°	489.1	489.1	492.6	492.6	499.5	499.5	499.5	499.5
65°	412.8	416.3	419.8	419.8	426.7	423.2	430.2	426.7
67.5°	333.0	333.0	339.9	339.9	336.4	339.9	339.9	339.9
70°	253.2	253.2	256.7	256.7	256.7	256.7	256.7	256.7
72.5°	187.3	187.3	187.3	190.8	187.3	187.3	190.8	187.3
75°	145.7	145.7	145.7	145.7	145.7	145.7	145.7	145.7
77.5°	114.4	114.4	118.0	118.0	118.0	118.0	118.0	118.0
80°	93.6	93.6	93.6	93.6	97.1	93.6	93.6	93.6
82.5°	69.3	65.9	69.3	65.9	69.3	69.3	69.3	69.3
85°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)