

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584793

Luminaire Tested: **HCC8W50D010SL-HM82555827-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010SL-HM82555827-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4322.1 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584793
CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584793

CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	71550	71550	71550
5°	74510	71393	68390
10°	76999	70483	65051
15°	78948	68873	61674
20°	79105	66015	58615
25°	77766	61835	55582
30°	73603	57053	52979
35°	67108	51313	49743
40°	58360	45237	45934
45°	50068	39174	42048
50°	42763	33778	37769
55°	37482	29085	32821
60°	33365	24817	27592
65°	29609	20248	22014
70°	26263	15012	12514
75°	21910	7851	3717
80°	17243	2468	622
85°	12277	1238	0



TEST NUMBER: P584793
 CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.6	5.1
10°-20°	612.8	14.2
20°-30°	867.4	20.1
30°-40°	907.4	21.0
40°-50°	756.9	17.5
50°-60°	536.7	12.4
60°-70°	309.1	7.2
70°-80°	99.5	2.3
80°-90°	13.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1698.8	39.3
0°-40°	2606.2	60.3
0°-60°	3899.8	90.2
0°-90°	4322.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4322.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2320	2320	2320	2320	2320	
5°	2407	2376	2306	2237	2209	231
15°	2473	2372	2157	1987	1932	695
25°	2286	2116	1817	1672	1634	1043
35°	1783	1627	1363	1290	1321	1105
45°	1148	1054	898	909	964	890
55°	697	624	541	569	610	630
65°	406	340	278	278	302	406
75°	184	135	66	31	31	199
85°	35	17	4	0	0	43
90°	0	0	0	0	0	



TEST NUMBER: P584793

CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3
2.5°	2369.0	2365.5	2362.0	2365.5	2362.0	2365.5	2362.0	2362.0	2358.5	2355.1	2355.1
5°	2407.1	2403.6	2403.6	2403.6	2400.2	2396.7	2396.7	2393.2	2386.3	2382.8	2375.9
7.5°	2431.4	2434.8	2434.8	2434.8	2427.9	2427.9	2421.0	2414.0	2407.1	2400.2	2389.8
10°	2459.1	2459.1	2455.6	2452.2	2445.2	2441.8	2438.3	2431.4	2421.0	2407.1	2396.7
12.5°	2469.5	2469.5	2466.0	2459.1	2455.6	2452.2	2448.7	2438.3	2424.4	2407.1	2393.2
15°	2473.0	2466.0	2462.6	2459.1	2452.2	2441.8	2441.8	2427.9	2410.6	2389.8	2372.4
17.5°	2445.2	2448.7	2441.8	2434.8	2424.4	2417.5	2407.1	2396.7	2375.9	2351.6	2334.3
20°	2410.6	2407.1	2403.6	2393.2	2379.4	2375.9	2365.5	2348.1	2330.8	2303.0	2278.7
22.5°	2355.1	2351.6	2344.7	2337.6	2323.9	2316.8	2306.4	2285.6	2261.4	2233.6	2205.9
25°	2285.6	2278.7	2268.3	2254.4	2244.0	2237.1	2223.2	2202.4	2174.7	2143.5	2115.8
27.5°	2174.7	2185.1	2178.2	2157.4	2147.0	2133.1	2129.6	2101.9	2077.5	2046.3	2015.1
30°	2067.1	2067.1	2056.7	2046.3	2029.0	2018.6	2004.7	1983.9	1959.6	1921.5	1897.2
32.5°	1931.9	1928.4	1914.6	1911.1	1897.2	1876.4	1873.0	1845.1	1821.0	1793.1	1761.9
35°	1782.7	1775.8	1761.9	1751.5	1744.6	1734.2	1723.8	1699.5	1675.3	1647.5	1626.7
37.5°	1612.8	1612.8	1609.4	1591.9	1585.0	1578.2	1567.7	1543.4	1529.5	1501.8	1481.0
40°	1449.8	1446.3	1435.9	1432.5	1425.5	1415.1	1408.2	1394.3	1373.5	1352.6	1331.8
42.5°	1290.2	1293.7	1279.8	1283.3	1269.4	1262.5	1259.0	1238.2	1227.8	1207.0	1189.7
45°	1148.1	1144.6	1137.7	1134.2	1127.3	1120.3	1113.4	1103.0	1085.7	1064.8	1054.4
47.5°	1016.2	1005.8	1005.8	1002.4	998.9	985.0	981.6	971.2	960.8	940.0	926.1
50°	891.4	891.4	891.4	887.9	877.5	874.1	867.0	856.6	846.2	832.4	811.6
52.5°	790.8	790.8	790.8	787.3	773.4	770.0	766.5	752.6	738.8	728.4	714.5
55°	697.2	700.6	697.2	690.2	679.8	679.8	669.4	662.5	648.6	638.2	624.4
57.5°	617.3	617.3	610.5	606.9	600.0	596.5	589.6	582.7	565.3	554.9	537.6
60°	541.0	537.6	537.6	530.6	523.7	516.8	513.3	502.9	496.0	478.6	464.8
62.5°	471.7	471.7	464.8	464.8	450.9	450.9	447.4	437.0	426.6	409.3	402.4
65°	405.8	405.8	402.4	398.9	388.5	385.0	381.6	371.2	360.8	350.3	339.9
67.5°	346.8	346.8	339.9	336.4	329.5	326.0	319.1	312.1	301.7	291.3	280.9
70°	291.3	287.9	284.4	280.9	274.0	270.5	263.6	256.7	246.3	239.3	228.9
72.5°	235.9	235.9	232.4	225.5	222.0	218.5	215.1	208.1	197.7	187.3	180.4
75°	183.9	183.9	183.9	176.9	170.0	166.5	166.5	159.6	152.6	142.2	135.3
77.5°	142.2	138.8	135.3	135.3	128.4	124.8	121.3	118.0	107.5	104.0	97.1
80°	97.1	100.5	97.1	93.6	90.1	86.7	86.7	79.7	76.3	69.3	62.4
82.5°	65.9	62.4	62.4	58.9	58.9	55.5	55.5	48.5	45.1	41.6	38.1
85°	34.7	34.7	31.2	31.2	31.2	27.7	27.7	24.3	24.3	20.8	17.3
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584793

CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3
2.5°	2351.6	2344.7	2341.2	2341.2	2337.6	2334.3	2330.8	2327.2	2320.3	2320.3	2313.5
5°	2369.0	2362.0	2358.5	2348.1	2341.2	2341.2	2327.2	2323.9	2313.5	2306.4	2299.5
7.5°	2382.8	2369.0	2358.5	2348.1	2341.2	2334.3	2320.3	2306.4	2292.6	2278.7	2271.8
10°	2382.8	2369.0	2351.6	2334.3	2327.2	2320.3	2303.0	2282.2	2264.8	2251.0	2233.6
12.5°	2375.9	2355.1	2334.3	2320.3	2306.4	2296.0	2275.2	2254.4	2233.6	2205.9	2192.0
15°	2355.1	2327.2	2306.4	2282.2	2271.8	2254.4	2237.1	2205.9	2181.6	2157.4	2140.0
17.5°	2313.5	2278.7	2254.4	2230.2	2212.8	2202.4	2174.7	2147.0	2119.2	2091.5	2070.6
20°	2251.0	2219.8	2192.0	2160.8	2147.0	2133.1	2098.4	2070.6	2042.9	2011.7	1990.8
22.5°	2174.7	2143.5	2105.4	2081.1	2060.2	2042.9	2011.7	1980.4	1952.7	1925.0	1897.2
25°	2081.1	2049.8	2015.1	1977.0	1963.1	1945.8	1911.1	1879.9	1848.7	1817.4	1793.1
27.5°	1980.4	1938.8	1911.1	1869.5	1855.6	1838.3	1800.1	1765.4	1737.7	1713.4	1685.7
30°	1859.1	1827.8	1789.7	1751.5	1737.7	1720.3	1689.1	1657.9	1630.2	1602.3	1574.6
32.5°	1727.3	1696.1	1657.9	1630.2	1609.4	1595.5	1564.2	1536.5	1508.7	1481.0	1456.7
35°	1588.6	1553.8	1526.1	1498.3	1481.0	1463.7	1432.5	1408.2	1387.4	1363.1	1338.9
37.5°	1446.3	1422.1	1394.3	1363.1	1345.8	1331.8	1307.6	1279.8	1262.5	1241.7	1224.3
40°	1307.6	1279.8	1255.5	1227.8	1213.9	1203.5	1179.3	1158.5	1141.1	1123.8	1113.4
42.5°	1165.4	1141.1	1116.9	1099.4	1089.0	1078.6	1061.3	1037.0	1026.6	1009.3	998.9
45°	1033.6	1012.8	995.4	971.2	964.2	957.3	936.5	919.2	908.7	898.3	891.4
47.5°	908.7	894.9	874.1	860.2	849.7	842.8	828.9	815.0	804.6	797.7	790.8
50°	801.2	783.8	770.0	756.1	749.2	738.8	724.9	718.0	711.0	704.1	704.1
52.5°	700.6	683.3	669.4	659.0	652.1	645.2	634.8	631.3	624.4	624.4	620.9
55°	606.9	596.5	582.7	568.8	565.3	561.9	554.9	548.0	544.5	541.0	544.5
57.5°	527.2	516.8	502.9	492.5	489.0	485.6	482.1	475.2	471.7	471.7	471.7
60°	454.4	444.0	433.6	423.2	423.2	416.2	412.8	409.3	405.8	402.4	402.4
62.5°	388.5	378.1	367.7	360.8	357.2	353.7	346.8	343.3	339.9	339.9	336.4
65°	329.5	315.6	312.1	301.7	298.3	294.8	291.3	284.4	280.9	277.5	274.0
67.5°	270.5	263.6	253.2	246.3	242.8	239.3	235.9	228.9	225.5	222.0	215.1
70°	218.5	211.6	204.7	197.7	194.3	190.8	183.9	176.9	173.4	166.5	156.1
72.5°	170.0	163.0	156.1	149.2	145.7	142.2	135.3	128.4	121.3	114.4	107.5
75°	128.4	121.3	110.9	104.0	100.5	100.5	90.1	83.2	76.3	65.9	58.9
77.5°	90.1	79.7	76.3	69.3	65.9	58.9	52.0	45.1	38.1	34.7	27.7
80°	58.9	52.0	45.1	41.6	38.1	34.7	31.2	24.3	17.3	13.9	10.4
82.5°	34.7	31.2	27.7	24.3	20.8	17.3	13.9	13.9	10.4	6.9	3.5
85°	17.3	13.9	10.4	10.4	6.9	6.9	6.9	3.5	3.5	3.5	3.5
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584793

CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3
2.5°	2309.9	2306.4	2303.0	2299.5	2299.5	2292.6	2292.6	2289.1	2282.2	2278.7	2278.7
5°	2289.1	2278.7	2271.8	2268.3	2264.8	2254.4	2251.0	2244.0	2237.1	2230.2	2226.7
7.5°	2257.9	2240.6	2233.6	2230.2	2219.8	2209.4	2202.4	2192.0	2181.6	2171.2	2167.8
10°	2219.8	2202.4	2185.1	2178.2	2167.8	2160.8	2147.0	2133.1	2122.7	2112.3	2101.9
12.5°	2171.2	2150.4	2133.1	2126.2	2115.8	2101.9	2081.1	2074.2	2056.7	2049.8	2035.9
15°	2115.8	2091.5	2074.2	2063.8	2053.3	2032.5	2018.6	2004.7	1987.4	1980.4	1966.6
17.5°	2046.3	2018.6	2001.2	1990.8	1983.9	1966.6	1945.8	1928.4	1911.1	1904.2	1893.8
20°	1963.1	1945.8	1921.5	1911.1	1904.2	1883.4	1862.6	1855.6	1841.8	1827.8	1817.4
22.5°	1869.5	1852.2	1827.8	1817.4	1813.9	1796.6	1779.3	1768.9	1758.5	1748.1	1737.7
25°	1772.3	1751.5	1730.7	1723.8	1716.9	1703.0	1689.1	1682.2	1671.8	1664.9	1657.9
27.5°	1668.3	1647.5	1630.2	1619.8	1612.8	1602.3	1595.5	1588.6	1581.5	1574.6	1571.1
30°	1557.3	1536.5	1522.6	1515.7	1508.7	1505.3	1494.9	1491.4	1487.9	1481.0	1484.5
32.5°	1446.3	1429.0	1415.1	1404.7	1404.7	1397.8	1394.3	1394.3	1390.9	1390.9	1390.9
35°	1324.9	1314.5	1304.1	1300.6	1297.2	1293.7	1290.2	1293.7	1290.2	1293.7	1297.2
37.5°	1213.9	1203.5	1196.6	1193.1	1189.7	1193.1	1189.7	1189.7	1193.1	1200.1	1203.5
40°	1099.4	1092.5	1085.7	1089.0	1085.7	1085.7	1085.7	1096.1	1099.4	1103.0	1106.5
42.5°	992.0	985.0	981.6	981.6	985.0	981.6	988.5	992.0	998.9	1009.3	1016.2
45°	887.9	884.5	884.5	887.9	884.5	891.4	891.4	898.3	908.7	915.7	922.6
47.5°	790.8	790.8	790.8	794.2	794.2	797.7	804.6	808.1	815.0	822.0	828.9
50°	700.6	704.1	707.6	707.6	707.6	714.5	721.4	724.9	728.4	731.8	742.2
52.5°	620.9	624.4	624.4	627.8	631.3	634.8	638.2	645.2	648.6	655.6	659.0
55°	544.5	544.5	551.5	554.9	554.9	554.9	561.9	561.9	568.8	572.3	579.2
57.5°	471.7	475.2	475.2	478.6	478.6	482.1	485.6	489.0	492.5	496.0	499.4
60°	402.4	402.4	402.4	405.8	409.3	412.8	409.3	416.2	416.2	423.2	426.6
62.5°	336.4	339.9	339.9	339.9	339.9	339.9	339.9	343.3	346.8	350.3	353.7
65°	274.0	274.0	274.0	270.5	274.0	270.5	274.0	277.5	277.5	280.9	284.4
67.5°	211.6	211.6	204.7	204.7	208.1	208.1	208.1	208.1	204.7	211.6	211.6
70°	152.6	149.2	145.7	142.2	142.2	138.8	138.8	135.3	135.3	135.3	135.3
72.5°	100.5	93.6	86.7	83.2	79.7	79.7	72.8	69.3	72.8	72.8	72.8
75°	52.0	45.1	41.6	38.1	34.7	34.7	31.2	31.2	31.2	31.2	31.2
77.5°	20.8	17.3	13.9	13.9	10.4	10.4	10.4	10.4	10.4	10.4	10.4
80°	6.9	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	3.5	0.0	0.0	3.5	0.0	3.5	3.5	3.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584793

CATALOG NUMBER: HCC8W50D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3	2320.3
2.5°	2275.2	2275.2	2271.8	2275.2	2268.3	2271.8	2268.3	2268.3
5°	2223.2	2216.3	2216.3	2216.3	2212.8	2212.8	2209.4	2209.4
7.5°	2160.8	2157.4	2153.9	2150.4	2147.0	2143.5	2143.5	2143.5
10°	2098.4	2091.5	2091.5	2088.0	2081.1	2077.5	2077.5	2077.5
12.5°	2025.5	2022.1	2018.6	2018.6	2004.7	2008.2	2004.7	2004.7
15°	1956.2	1952.7	1952.7	1942.3	1935.4	1935.4	1935.4	1931.9
17.5°	1883.4	1879.9	1876.4	1869.5	1862.6	1862.6	1859.1	1862.6
20°	1807.0	1803.5	1796.6	1796.6	1793.1	1789.7	1782.7	1786.2
22.5°	1730.7	1723.8	1720.3	1720.3	1716.9	1716.9	1709.9	1709.9
25°	1651.0	1647.5	1644.1	1647.5	1640.6	1640.6	1633.6	1633.6
27.5°	1567.7	1564.2	1564.2	1564.2	1560.7	1564.2	1560.7	1560.7
30°	1484.5	1484.5	1481.0	1481.0	1484.5	1481.0	1484.5	1487.9
32.5°	1394.3	1394.3	1397.8	1397.8	1401.3	1401.3	1401.3	1401.3
35°	1300.6	1307.6	1307.6	1311.0	1314.5	1318.0	1318.0	1321.4
37.5°	1213.9	1217.4	1220.9	1224.3	1231.3	1231.3	1231.3	1231.3
40°	1120.3	1123.8	1130.7	1127.3	1141.1	1144.6	1141.1	1141.1
42.5°	1023.2	1030.1	1033.6	1040.5	1044.0	1050.9	1054.4	1054.4
45°	933.0	936.5	943.4	950.4	953.8	964.2	964.2	964.2
47.5°	839.3	846.2	849.7	856.6	860.2	870.6	874.1	870.6
50°	749.2	756.1	763.0	763.0	773.4	776.9	783.8	787.3
52.5°	662.5	666.0	672.9	676.4	683.3	690.2	693.7	697.2
55°	579.2	582.7	589.6	589.6	600.0	603.6	610.5	610.5
57.5°	502.9	506.4	513.3	509.8	516.8	523.7	523.7	520.2
60°	430.1	430.1	430.1	437.0	440.5	444.0	447.4	447.4
62.5°	353.7	360.8	364.1	364.1	367.7	371.2	371.2	367.7
65°	284.4	291.3	294.8	294.8	298.3	298.3	298.3	301.7
67.5°	215.1	215.1	215.1	218.5	215.1	215.1	215.1	215.1
70°	135.3	135.3	135.3	135.3	131.7	135.3	135.3	138.8
72.5°	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.8
75°	31.2	31.2	31.2	34.7	31.2	31.2	31.2	31.2
77.5°	13.9	10.4	13.9	13.9	10.4	10.4	10.4	10.4
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	0.0	3.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)