

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584785

Luminaire Tested: **HCC8S50D010MW-HM82555827-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584785  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MW-HM82555827-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5158.1 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584785  
CATALOG NUMBER: HCC8S50D010MW-HM82555827-81PSMDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584785

CATALOG NUMBER: HCC8S50D010MW-HM82555827-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79	79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121076
5°	119498
10°	115125
15°	110620
20°	107562
25°	104325
30°	93617
35°	61371
40°	33926
45°	28289
50°	25790
55°	24617
60°	22893
65°	20751
70°	18762
75°	16954
80°	15396
85°	14718



TEST NUMBER: P584785  
 CATALOG NUMBER: HCC8S50D010MW-HM82555827-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	362.7	7.0
10°-20°	977.6	19.0
20°-30°	1391.3	27.0
30°-40°	1029.7	20.0
40°-50°	510.0	9.9
50°-60°	407.1	7.9
60°-70°	282.6	5.5
70°-80°	152.3	3.0
80°-90°	44.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2731.6	53.0
0°-40°	3761.4	72.9
0°-60°	4678.4	90.7
0°-90°	5158.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5158.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3926	
5°	3860	363
15°	3465	978
25°	3066	1391
35°	1630	1030
45°	649	510
55°	458	407
65°	284	283
75°	142	152
85°	42	45
90°	0	



TEST NUMBER: P584785  
CATALOG NUMBER: HCC8S50D010MW-HM82555827-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3926.4
2.5°	3909.1
5°	3860.5
7.5°	3784.2
10°	3676.7
12.5°	3565.7
15°	3465.1
17.5°	3368.0
20°	3277.8
22.5°	3187.6
25°	3066.2
27.5°	2889.3
30°	2629.2
32.5°	2230.3
35°	1630.3
37.5°	1113.4
40°	842.8
42.5°	721.5
45°	648.7
47.5°	589.6
50°	537.6
52.5°	492.5
55°	457.9
57.5°	416.3
60°	371.2
62.5°	326.0
65°	284.4
67.5°	242.8
70°	208.1
72.5°	173.5
75°	142.3
77.5°	114.4
80°	86.7
82.5°	62.4
85°	41.6
87.5°	17.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)