

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584629

Luminaire Tested: **HCC8S40D010BZ-HM82555940-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010BZ-HM82555940-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4902.0 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584629
CATALOG NUMBER: HCC8S40D010BZ-HM82555940-81NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584629

CATALOG NUMBER: HCC8S40D010BZ-HM82555940-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96						96													
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91						91													
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87						87													
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83						83													
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80						80													
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76						76													
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73						73													
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71						71													
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68						68													
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66						66													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	922641
5°	591805
10°	267339
15°	161303
20°	122923
25°	99265
30°	72741
35°	26340
40°	9830
45°	4461
50°	1430
55°	349
60°	204
65°	241
70°	0
75°	0
80°	586
85°	1168



TEST NUMBER: P584629
 CATALOG NUMBER: HCC8S40D010BZ-HM82555940-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1458.2	29.7
10°-20°	1481.1	30.2
20°-30°	1325.8	27.0
30°-40°	534.1	10.9
40°-50°	87.6	1.8
50°-60°	7.9	0.2
60°-70°	2.9	0.1
70°-80°	2.2	0.0
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4265.0	87.0
0°-40°	4799.1	97.9
0°-60°	4894.6	99.9
0°-90°	4902.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4902.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29921	
5°	19119	###
15°	5053	1481
25°	2918	1326
35°	700	534
45°	102	88
55°	6	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584629
CATALOG NUMBER: HCC8S40D010BZ-HM82555940-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	29920.6
0.5°	29828.3
1°	29442.1
1.5°	28821.7
2°	27881.1
2.5°	26768.8
3°	25376.2
3.5°	23848.1
4°	22336.5
4.5°	20643.5
5°	19118.8
5.5°	17458.7
6°	16112.1
6.5°	14709.5
7°	13607.2
7.5°	12442.2
8°	11504.9
8.5°	10564.3
9°	9858.1
9.5°	9079.2
10°	8537.9
12.5°	6297.0
15°	5052.7
17.5°	4316.8
20°	3745.9
22.5°	3290.5
25°	2917.5
27.5°	2544.6
30°	2042.9
32.5°	1313.5
35°	699.7
37.5°	386.2
40°	244.2
42.5°	161.7
45°	102.3
47.5°	62.7
50°	29.8
52.5°	9.9
55°	6.5
57.5°	3.3
60°	3.3
62.5°	3.3
65°	3.3



TEST NUMBER: P584629
CATALOG NUMBER: HCC8S40D010BZ-HM82555940-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.3
80°	3.3
82.5°	3.3
85°	3.3
87.5°	3.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.3
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)