

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584633

Luminaire Tested: **HCC8W40D010SL-HM82555940-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010SL-HM82555940-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4700.6 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584633
CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584633

CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	76267	76267	76267
5°	77274	75943	75228
10°	78061	75168	74031
15°	78853	73579	72104
20°	78452	70868	69240
25°	76626	66623	65724
30°	72777	61845	61610
35°	66254	56436	56933
40°	58086	50507	52370
45°	50111	44930	48097
50°	43876	39443	43564
55°	38880	33907	38348
60°	35030	28511	31774
65°	31565	22889	24341
70°	27688	16670	13398
75°	23602	8650	3550
80°	18166	2344	586
85°	11676	0	0



TEST NUMBER: P584633
 CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.3	5.0
10°-20°	656.0	14.0
20°-30°	931.1	19.8
30°-40°	980.1	20.9
40°-50°	833.8	17.7
50°-60°	602.5	12.8
60°-70°	342.7	7.3
70°-80°	108.0	2.3
80°-90°	13.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1820.4	38.7
0°-40°	2800.5	59.6
0°-60°	4236.8	90.1
0°-90°	4700.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4700.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2473	2473	2473	2473	2473	
5°	2496	2483	2453	2437	2430	238
15°	2470	2407	2305	2262	2259	696
25°	2252	2140	1958	1925	1932	1031
35°	1760	1658	1499	1489	1512	1095
45°	1149	1106	1030	1057	1103	893
55°	723	670	631	667	713	652
65°	433	373	314	310	334	429
75°	198	152	73	33	30	213
85°	33	20	0	0	0	43
90°	0	0	0	0	0	



TEST NUMBER: P584633

CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3
2.5°	2486.5	2489.7	2483.2	2483.2	2489.7	2483.2	2486.5	2486.5	2483.2	2483.2	2479.8
5°	2496.4	2493.0	2493.0	2493.0	2496.4	2489.7	2486.5	2489.7	2483.2	2483.2	2483.2
7.5°	2499.7	2499.7	2496.4	2493.0	2493.0	2493.0	2489.7	2486.5	2483.2	2476.5	2473.3
10°	2493.0	2493.0	2496.4	2489.7	2489.7	2483.2	2483.2	2476.5	2476.5	2470.0	2460.1
12.5°	2486.5	2483.2	2483.2	2476.5	2476.5	2470.0	2470.0	2460.1	2456.8	2446.9	2436.9
15°	2470.0	2466.6	2460.1	2456.8	2453.4	2450.1	2443.5	2440.2	2430.3	2417.1	2407.3
17.5°	2436.9	2433.7	2430.3	2423.7	2417.1	2413.8	2410.5	2400.6	2387.4	2377.5	2361.0
20°	2390.7	2387.4	2387.4	2377.5	2374.2	2364.3	2361.0	2347.8	2337.9	2318.0	2304.8
22.5°	2328.0	2331.2	2324.7	2318.0	2311.5	2301.6	2294.9	2281.7	2265.3	2245.4	2228.9
25°	2252.1	2255.3	2248.7	2242.1	2232.2	2225.7	2219.0	2199.2	2182.7	2159.6	2139.7
27.5°	2156.3	2156.3	2156.3	2149.6	2133.2	2129.9	2123.2	2103.4	2080.4	2060.5	2040.7
30°	2043.9	2040.7	2040.7	2030.7	2024.2	2011.0	2001.1	1984.6	1968.0	1944.9	1921.8
32.5°	1908.6	1911.9	1902.0	1895.4	1885.4	1885.4	1872.2	1859.0	1839.3	1816.2	1793.0
35°	1760.0	1763.3	1756.7	1753.3	1736.9	1733.6	1730.3	1713.7	1700.6	1684.1	1657.7
37.5°	1608.2	1604.8	1601.5	1601.5	1591.6	1585.0	1578.4	1568.5	1548.7	1535.5	1522.2
40°	1443.0	1443.0	1443.0	1439.7	1436.4	1429.8	1426.5	1419.9	1406.7	1393.5	1383.6
42.5°	1294.4	1294.4	1291.1	1287.8	1281.2	1284.5	1277.9	1271.3	1258.1	1248.2	1241.5
45°	1149.1	1149.1	1149.1	1152.4	1145.9	1136.0	1136.0	1129.3	1122.8	1116.1	1106.2
47.5°	1020.3	1030.3	1023.6	1020.3	1023.6	1010.4	1010.4	1003.9	997.2	990.7	977.5
50°	914.6	914.6	914.6	908.1	904.8	904.8	894.9	888.2	885.0	878.3	865.1
52.5°	819.0	812.3	812.3	809.0	805.7	799.1	799.1	792.5	779.3	772.7	762.8
55°	723.2	723.2	719.8	716.5	713.3	710.0	706.6	696.7	690.1	680.2	670.3
57.5°	637.2	643.9	640.6	634.0	627.4	627.4	620.8	614.2	604.3	594.4	584.4
60°	568.0	564.7	564.7	561.3	554.8	551.4	548.1	538.2	528.4	518.5	508.5
62.5°	495.3	495.3	495.3	488.7	482.1	478.9	475.5	468.9	455.7	445.8	439.2
65°	432.6	429.2	426.0	422.7	419.4	412.8	409.5	402.8	392.9	383.1	373.2
67.5°	369.9	366.5	366.5	363.2	353.3	350.0	350.0	340.1	330.2	320.3	310.4
70°	307.1	307.1	307.1	300.5	297.1	293.9	290.6	283.9	274.1	264.2	254.3
72.5°	254.3	251.0	251.0	247.6	237.8	234.4	231.1	224.6	214.7	208.0	201.5
75°	198.1	198.1	194.8	191.5	188.3	184.9	181.6	175.0	165.1	155.2	151.8
77.5°	151.8	148.6	148.6	145.3	138.6	135.4	135.4	128.8	118.9	112.2	105.7
80°	102.3	105.7	102.3	99.0	95.8	92.5	89.1	85.8	79.3	72.6	66.0
82.5°	62.7	66.0	62.7	62.7	59.4	56.2	56.2	49.5	46.2	43.0	39.6
85°	33.0	33.0	33.0	33.0	29.8	29.8	29.8	26.4	23.1	19.8	19.8
87.5°	9.9	13.2	9.9	9.9	9.9	9.9	9.9	9.9	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584633

CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3
2.5°	2483.2	2479.8	2476.5	2476.5	2476.5	2476.5	2476.5	2473.3	2470.0	2470.0	2470.0
5°	2476.5	2476.5	2476.5	2473.3	2470.0	2470.0	2463.3	2460.1	2456.8	2453.4	2450.1
7.5°	2470.0	2463.3	2460.1	2456.8	2453.4	2453.4	2446.9	2440.2	2440.2	2433.7	2427.0
10°	2450.1	2446.9	2440.2	2433.7	2430.3	2427.0	2420.5	2410.5	2407.3	2400.6	2394.0
12.5°	2427.0	2420.5	2413.8	2400.6	2397.3	2394.0	2380.8	2370.8	2364.3	2361.0	2344.4
15°	2397.3	2384.0	2374.2	2357.6	2354.4	2347.8	2337.9	2328.0	2314.8	2304.8	2298.2
17.5°	2344.4	2331.2	2314.8	2298.2	2291.6	2291.6	2275.2	2262.0	2245.4	2238.9	2225.7
20°	2281.7	2265.3	2252.1	2232.2	2222.3	2212.4	2202.5	2182.7	2169.5	2159.6	2143.1
22.5°	2209.1	2186.0	2169.5	2149.6	2133.2	2123.2	2106.8	2090.2	2073.7	2063.8	2050.6
25°	2116.7	2096.8	2070.4	2050.6	2040.7	2027.5	2007.6	1991.1	1974.7	1958.1	1951.5
27.5°	2014.3	1987.9	1964.7	1941.6	1931.7	1921.8	1898.6	1878.9	1865.7	1849.1	1842.6
30°	1902.0	1875.6	1849.1	1829.4	1819.4	1803.0	1789.8	1766.6	1750.1	1736.9	1720.4
32.5°	1773.2	1753.3	1730.3	1700.6	1694.0	1680.8	1661.0	1651.0	1631.3	1621.4	1608.2
35°	1634.6	1621.4	1598.2	1575.1	1565.2	1558.5	1542.1	1522.2	1509.0	1499.2	1492.5
37.5°	1502.5	1486.0	1462.9	1446.3	1439.7	1429.8	1410.0	1400.0	1386.8	1380.3	1367.1
40°	1360.4	1344.0	1327.4	1317.6	1307.6	1301.0	1287.8	1277.9	1264.7	1254.7	1251.5
42.5°	1221.8	1211.9	1198.7	1185.5	1182.1	1172.3	1165.6	1155.7	1145.9	1142.5	1132.6
45°	1096.3	1086.4	1073.1	1059.9	1056.7	1050.1	1046.7	1036.8	1030.3	1030.3	1030.3
47.5°	970.8	960.9	947.7	941.1	944.4	931.2	931.2	927.8	921.3	921.3	924.6
50°	858.6	845.4	842.0	835.4	828.8	822.2	825.5	815.6	815.6	822.2	819.0
52.5°	752.9	739.7	736.4	729.7	726.5	726.5	723.2	723.2	719.8	723.2	723.2
55°	657.1	647.2	640.6	634.0	630.7	630.7	630.7	627.4	624.0	630.7	634.0
57.5°	571.2	568.0	561.3	551.4	548.1	544.9	541.6	541.6	541.6	541.6	544.9
60°	495.3	488.7	482.1	472.2	472.2	468.9	465.6	462.3	462.3	462.3	462.3
62.5°	429.2	419.4	409.5	402.8	399.6	396.3	392.9	386.4	386.4	386.4	386.4
65°	363.2	353.3	346.8	340.1	333.6	333.6	326.9	323.6	317.0	313.7	307.1
67.5°	300.5	293.9	287.3	277.4	274.1	270.7	264.2	260.8	251.0	247.6	244.3
70°	244.3	234.4	227.9	221.2	217.9	211.3	204.7	198.1	191.5	184.9	178.3
72.5°	191.5	181.6	175.0	168.4	161.8	161.8	151.8	145.3	135.4	128.8	118.9
75°	142.0	132.1	125.4	115.5	112.2	109.0	99.0	92.5	82.6	72.6	66.0
77.5°	95.8	89.1	82.6	72.6	66.0	66.0	56.2	49.5	43.0	33.0	29.8
80°	59.4	52.8	46.2	39.6	39.6	33.0	29.8	23.1	16.5	13.2	9.9
82.5°	33.0	29.8	26.4	19.8	19.8	16.5	13.2	9.9	6.5	3.3	3.3
85°	16.5	13.2	9.9	9.9	6.5	6.5	6.5	3.3	3.3	0.0	0.0
87.5°	6.5	3.3	3.3	3.3	3.3	3.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584633

CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3
2.5°	2466.6	2466.6	2463.3	2463.3	2463.3	2460.1	2463.3	2460.1	2460.1	2460.1	2463.3
5°	2453.4	2446.9	2446.9	2443.5	2443.5	2440.2	2443.5	2440.2	2436.9	2433.7	2436.9
7.5°	2427.0	2420.5	2417.1	2413.8	2413.8	2413.8	2410.5	2407.3	2410.5	2400.6	2407.3
10°	2390.7	2387.4	2380.8	2377.5	2374.2	2377.5	2374.2	2367.6	2367.6	2367.6	2364.3
12.5°	2344.4	2337.9	2334.5	2331.2	2324.7	2324.7	2328.0	2321.3	2321.3	2314.8	2314.8
15°	2288.4	2281.7	2275.2	2275.2	2268.5	2268.5	2265.3	2265.3	2262.0	2258.6	2258.6
17.5°	2219.0	2209.1	2202.5	2205.8	2202.5	2199.2	2199.2	2192.6	2189.2	2192.6	2192.6
20°	2136.4	2129.9	2123.2	2126.5	2120.0	2116.7	2120.0	2110.0	2113.3	2113.3	2113.3
22.5°	2043.9	2040.7	2030.7	2030.7	2024.2	2020.9	2024.2	2024.2	2027.5	2024.2	2024.2
25°	1941.6	1935.1	1928.4	1928.4	1925.1	1921.8	1925.1	1928.4	1925.1	1928.4	1928.4
27.5°	1832.6	1822.7	1822.7	1816.2	1816.2	1819.4	1816.2	1819.4	1822.7	1822.7	1829.4
30°	1713.7	1710.5	1707.2	1703.8	1703.8	1707.2	1707.2	1707.2	1710.5	1717.1	1717.1
32.5°	1601.5	1595.0	1588.3	1588.3	1595.0	1591.6	1595.0	1595.0	1601.5	1601.5	1608.2
35°	1479.3	1479.3	1472.7	1476.1	1476.1	1476.1	1476.1	1482.6	1489.3	1492.5	1499.2
37.5°	1367.1	1357.2	1360.4	1360.4	1363.7	1360.4	1370.4	1370.4	1376.9	1376.9	1383.6
40°	1244.9	1244.9	1248.2	1244.9	1248.2	1248.2	1254.7	1261.4	1264.7	1271.3	1274.6
42.5°	1129.3	1136.0	1129.3	1132.6	1136.0	1139.2	1142.5	1145.9	1159.1	1165.6	1175.5
45°	1023.6	1027.0	1030.3	1033.5	1030.3	1036.8	1040.2	1046.7	1056.7	1059.9	1063.3
47.5°	921.3	924.6	927.8	931.2	931.2	937.8	941.1	947.7	954.3	957.6	960.9
50°	822.2	828.8	832.2	832.2	835.4	842.0	848.6	848.6	855.3	865.1	868.5
52.5°	733.0	733.0	739.7	742.9	746.2	746.2	756.1	759.5	762.8	769.3	776.0
55°	634.0	643.9	647.2	647.2	653.8	660.4	663.7	667.0	667.0	680.2	680.2
57.5°	548.1	551.4	558.1	558.1	558.1	568.0	568.0	574.5	577.9	581.2	587.7
60°	462.3	468.9	468.9	472.2	468.9	475.5	478.9	485.4	488.7	492.1	495.3
62.5°	383.1	383.1	386.4	386.4	386.4	386.4	392.9	392.9	399.6	402.8	406.1
65°	307.1	307.1	307.1	307.1	307.1	307.1	307.1	307.1	310.4	310.4	317.0
67.5°	237.8	234.4	227.9	231.1	227.9	227.9	224.6	224.6	227.9	227.9	234.4
70°	171.7	168.4	161.8	161.8	158.5	155.2	151.8	148.6	145.3	145.3	145.3
72.5°	112.2	105.7	95.8	92.5	92.5	85.8	79.3	75.9	75.9	75.9	75.9
75°	56.2	49.5	43.0	39.6	39.6	33.0	36.3	33.0	33.0	33.0	33.0
77.5°	23.1	16.5	13.2	13.2	13.2	9.9	9.9	9.9	9.9	9.9	9.9
80°	6.5	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584633

CATALOG NUMBER: HCC8W40D010SL-HM82555940-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3	2473.3
2.5°	2460.1	2460.1	2453.4	2456.8	2456.8	2456.8	2456.8	2456.8
5°	2430.3	2433.7	2430.3	2433.7	2433.7	2430.3	2430.3	2430.3
7.5°	2400.6	2403.9	2400.6	2403.9	2403.9	2403.9	2400.6	2400.6
10°	2364.3	2364.3	2364.3	2364.3	2364.3	2361.0	2364.3	2364.3
12.5°	2314.8	2314.8	2314.8	2318.0	2318.0	2314.8	2314.8	2311.5
15°	2262.0	2255.3	2258.6	2262.0	2258.6	2258.6	2258.6	2258.6
17.5°	2189.2	2192.6	2189.2	2189.2	2189.2	2189.2	2192.6	2189.2
20°	2113.3	2113.3	2116.7	2113.3	2113.3	2113.3	2113.3	2110.0
22.5°	2027.5	2024.2	2024.2	2027.5	2027.5	2024.2	2027.5	2027.5
25°	1931.7	1935.1	1931.7	1931.7	1935.1	1935.1	1935.1	1931.7
27.5°	1829.4	1832.6	1835.9	1832.6	1832.6	1832.6	1835.9	1839.3
30°	1723.7	1730.3	1723.7	1723.7	1730.3	1726.9	1730.3	1730.3
32.5°	1611.4	1621.4	1614.7	1621.4	1621.4	1624.6	1621.4	1624.6
35°	1499.2	1509.0	1509.0	1509.0	1512.4	1515.7	1515.7	1512.4
37.5°	1393.5	1396.8	1396.8	1403.4	1406.7	1410.0	1410.0	1406.7
40°	1284.5	1291.1	1294.4	1294.4	1294.4	1301.0	1307.6	1301.0
42.5°	1178.8	1182.1	1185.5	1185.5	1192.0	1195.4	1198.7	1198.7
45°	1076.5	1083.1	1086.4	1089.7	1093.0	1099.6	1096.3	1102.9
47.5°	970.8	980.7	984.0	987.3	993.9	997.2	1000.6	1003.9
50°	875.0	881.7	881.7	888.2	898.2	898.2	904.8	908.1
52.5°	779.3	782.5	785.9	789.2	795.8	802.4	802.4	809.0
55°	686.9	690.1	690.1	693.4	696.7	710.0	713.3	713.3
57.5°	591.1	591.1	597.6	600.9	604.3	610.8	610.8	610.8
60°	498.6	501.9	501.9	505.3	508.5	515.2	518.5	515.2
62.5°	406.1	409.5	409.5	412.8	419.4	422.7	419.4	419.4
65°	320.3	323.6	323.6	326.9	333.6	333.6	330.2	333.6
67.5°	234.4	234.4	234.4	234.4	234.4	234.4	234.4	234.4
70°	148.6	145.3	142.0	145.3	145.3	145.3	142.0	148.6
72.5°	72.6	75.9	75.9	75.9	75.9	75.9	75.9	72.6
75°	33.0	33.0	29.8	29.8	29.8	33.0	33.0	29.8
77.5°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
80°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)