

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584827

Luminaire Tested: **HCC8W50D010BZ-HM82555835-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010BZ-HM82555835-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4473.9 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584827
CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584827

CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67		
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59		
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47		
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43		
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39		
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	74063	74063	74063
5°	77125	73900	70789
10°	79705	72960	67336
15°	81723	71290	63842
20°	81881	68331	60676
25°	80498	64010	57535
30°	76188	59061	54841
35°	69469	53116	51490
40°	60413	46827	47548
45°	51825	40548	43526
50°	44264	34967	39098
55°	38794	30112	33966
60°	34543	25687	28567
65°	30645	20956	22794
70°	27192	15534	12947
75°	22673	8137	3848
80°	17847	2557	639
85°	12702	1274	0



TEST NUMBER: P584827
 CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.3	5.1
10°-20°	634.3	14.2
20°-30°	897.8	20.1
30°-40°	939.3	21.0
40°-50°	783.5	17.5
50°-60°	555.6	12.4
60°-70°	320.0	7.2
70°-80°	103.0	2.3
80°-90°	14.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1758.5	39.3
0°-40°	2697.8	60.3
0°-60°	4036.8	90.2
0°-90°	4473.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4473.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2402	2402	2402	2402	2402	
5°	2492	2459	2387	2316	2287	239
15°	2560	2456	2233	2057	2000	720
25°	2366	2190	1881	1730	1691	1080
35°	1845	1684	1411	1336	1368	1144
45°	1188	1091	930	941	998	921
55°	722	646	560	589	632	652
65°	420	352	287	287	312	420
75°	190	140	68	32	32	206
85°	36	18	4	0	0	45
90°	0	0	0	0	0	



TEST NUMBER: P584827

CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8
2.5°	2452.1	2448.6	2445.0	2448.6	2445.0	2448.6	2445.0	2445.0	2441.3	2437.7	2437.7
5°	2491.6	2488.0	2488.0	2488.0	2484.5	2480.9	2480.9	2477.2	2470.1	2466.5	2459.3
7.5°	2516.7	2520.4	2520.4	2520.4	2513.1	2513.1	2506.0	2498.7	2491.6	2484.5	2473.6
10°	2545.5	2545.5	2541.9	2538.2	2531.1	2527.5	2523.9	2516.7	2506.0	2491.6	2480.9
12.5°	2556.3	2556.3	2552.6	2545.5	2541.9	2538.2	2534.7	2523.9	2509.6	2491.6	2477.2
15°	2559.9	2552.6	2549.0	2545.5	2538.2	2527.5	2527.5	2513.1	2495.2	2473.6	2455.7
17.5°	2531.1	2534.7	2527.5	2520.4	2509.6	2502.4	2491.6	2480.9	2459.3	2434.2	2416.2
20°	2495.2	2491.6	2488.0	2477.2	2462.8	2459.3	2448.6	2430.6	2412.6	2383.9	2358.8
22.5°	2437.7	2434.2	2427.0	2419.8	2405.5	2398.3	2387.4	2365.9	2340.8	2312.0	2283.4
25°	2365.9	2358.8	2348.1	2333.7	2322.9	2315.7	2301.3	2279.8	2251.0	2218.8	2190.0
27.5°	2251.0	2261.8	2254.7	2233.1	2222.4	2208.0	2204.4	2175.6	2150.5	2118.2	2086.0
30°	2139.7	2139.7	2129.0	2118.2	2100.2	2089.5	2075.1	2053.6	2028.4	1988.9	1963.8
32.5°	1999.8	1996.2	1981.8	1978.2	1963.8	1942.3	1938.7	1910.0	1884.9	1856.1	1823.9
35°	1845.4	1838.1	1823.9	1813.1	1805.9	1795.1	1784.4	1759.2	1734.1	1705.3	1683.8
37.5°	1669.4	1669.4	1665.8	1647.9	1640.7	1633.6	1622.8	1597.7	1583.3	1554.5	1533.0
40°	1500.8	1497.1	1486.4	1482.8	1475.6	1464.8	1457.6	1443.2	1421.7	1400.2	1378.6
42.5°	1335.6	1339.2	1324.8	1328.3	1314.1	1306.8	1303.2	1281.7	1270.9	1249.4	1231.4
45°	1188.4	1184.8	1177.7	1174.0	1166.8	1159.6	1152.5	1141.6	1123.8	1102.3	1091.4
47.5°	1052.0	1041.1	1041.1	1037.6	1034.0	1019.6	1016.0	1005.2	994.5	973.0	958.6
50°	922.7	922.7	922.7	919.1	908.3	904.7	897.6	886.8	876.0	861.7	840.2
52.5°	818.5	818.5	818.5	815.0	800.6	797.0	793.4	779.0	764.8	753.9	739.6
55°	721.6	725.2	721.6	714.5	703.7	703.7	692.9	685.7	671.4	660.6	646.2
57.5°	639.1	639.1	631.8	628.3	621.1	617.5	610.3	603.2	585.2	574.4	556.4
60°	560.1	556.4	556.4	549.3	542.1	534.9	531.3	520.6	513.4	495.4	481.0
62.5°	488.3	488.3	481.0	481.0	466.8	466.8	463.2	452.4	441.6	423.6	416.5
65°	420.0	420.0	416.5	412.9	402.1	398.5	394.9	384.1	373.4	362.6	351.9
67.5°	359.0	359.0	351.9	348.2	341.1	337.5	330.2	323.1	312.4	301.6	290.8
70°	301.6	298.0	294.4	290.8	283.6	280.1	272.8	265.7	255.0	247.7	237.0
72.5°	244.1	244.1	240.6	233.3	229.8	226.2	222.6	215.4	204.7	193.8	186.7
75°	190.3	190.3	190.3	183.1	175.9	172.3	172.3	165.2	157.9	147.2	140.0
77.5°	147.2	143.6	140.0	140.0	132.8	129.3	125.7	122.0	111.3	107.7	100.5
80°	100.5	104.2	100.5	96.9	93.4	89.8	89.8	82.5	79.0	71.8	64.6
82.5°	68.3	64.6	64.6	61.0	61.0	57.4	57.4	50.3	46.6	43.1	39.5
85°	35.9	35.9	32.3	32.3	32.3	28.8	28.8	25.1	25.1	21.5	18.0
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584827

CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8
2.5°	2434.2	2427.0	2423.5	2423.5	2419.8	2416.2	2412.6	2409.1	2401.8	2401.8	2394.7
5°	2452.1	2445.0	2441.3	2430.6	2423.5	2423.5	2409.1	2405.5	2394.7	2387.4	2380.3
7.5°	2466.5	2452.1	2441.3	2430.6	2423.5	2416.2	2401.8	2387.4	2373.2	2358.8	2351.6
10°	2466.5	2452.1	2434.2	2416.2	2409.1	2401.8	2383.9	2362.3	2344.4	2330.1	2312.0
12.5°	2459.3	2437.7	2416.2	2401.8	2387.4	2376.7	2355.2	2333.7	2312.0	2283.4	2269.0
15°	2437.7	2409.1	2387.4	2362.3	2351.6	2333.7	2315.7	2283.4	2258.3	2233.1	2215.1
17.5°	2394.7	2358.8	2333.7	2308.5	2290.5	2279.8	2251.0	2222.4	2193.6	2164.9	2143.4
20°	2330.1	2297.8	2269.0	2236.8	2222.4	2208.0	2172.1	2143.4	2114.6	2082.3	2060.8
22.5°	2251.0	2218.8	2179.2	2154.1	2132.6	2114.6	2082.3	2050.0	2021.3	1992.6	1963.8
25°	2154.1	2121.9	2086.0	2046.5	2032.1	2014.1	1978.2	1945.9	1913.5	1881.3	1856.1
27.5°	2050.0	2006.9	1978.2	1935.2	1920.8	1902.8	1863.3	1827.4	1798.7	1773.6	1744.8
30°	1924.4	1892.0	1852.5	1813.1	1798.7	1780.7	1748.5	1716.1	1687.5	1658.7	1629.9
32.5°	1788.0	1755.6	1716.1	1687.5	1665.8	1651.4	1619.2	1590.4	1561.8	1533.0	1507.9
35°	1644.3	1608.4	1579.7	1551.0	1533.0	1515.0	1482.8	1457.6	1436.1	1411.0	1385.8
37.5°	1497.1	1472.0	1443.2	1411.0	1393.0	1378.6	1353.5	1324.8	1306.8	1285.3	1267.3
40°	1353.5	1324.8	1299.7	1270.9	1256.6	1245.8	1220.7	1199.2	1181.2	1163.3	1152.5
42.5°	1206.3	1181.2	1156.0	1138.1	1127.4	1116.5	1098.6	1073.5	1062.7	1044.7	1034.0
45°	1069.9	1048.4	1030.4	1005.2	998.1	990.8	969.3	951.4	940.7	929.8	922.7
47.5°	940.7	926.3	904.7	890.4	879.6	872.4	858.0	843.7	832.9	825.8	818.5
50°	829.3	811.4	797.0	782.6	775.5	764.8	750.4	743.1	736.0	728.9	728.9
52.5°	725.2	707.2	692.9	682.1	675.0	667.7	657.0	653.5	646.2	646.2	642.6
55°	628.3	617.5	603.2	588.8	585.2	581.6	574.4	567.2	563.7	560.1	563.7
57.5°	545.7	534.9	520.6	509.8	506.2	502.7	499.0	491.9	488.3	488.3	488.3
60°	470.3	459.5	448.8	438.0	438.0	430.8	427.3	423.6	420.0	416.5	416.5
62.5°	402.1	391.4	380.5	373.4	369.8	366.2	359.0	355.4	351.9	351.9	348.2
65°	341.1	326.7	323.1	312.4	308.7	305.2	301.6	294.4	290.8	287.2	283.6
67.5°	280.1	272.8	262.1	255.0	251.3	247.7	244.1	237.0	233.3	229.8	222.6
70°	226.2	219.0	211.8	204.7	201.1	197.4	190.3	183.1	179.6	172.3	161.6
72.5°	175.9	168.7	161.6	154.4	150.8	147.2	140.0	132.8	125.7	118.4	111.3
75°	132.8	125.7	114.9	107.7	104.2	104.2	93.4	86.2	79.0	68.3	61.0
77.5°	93.4	82.5	79.0	71.8	68.3	61.0	53.9	46.6	39.5	35.9	28.8
80°	61.0	53.9	46.6	43.1	39.5	35.9	32.3	25.1	18.0	14.4	10.8
82.5°	35.9	32.3	28.8	25.1	21.5	18.0	14.4	14.4	10.8	7.1	3.6
85°	18.0	14.4	10.8	10.8	7.1	7.1	7.1	3.6	3.6	3.6	3.6
87.5°	7.1	3.6	3.6	3.6	3.6	3.6	3.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584827

CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8
2.5°	2391.1	2387.4	2383.9	2380.3	2380.3	2373.2	2373.2	2369.6	2362.3	2358.8	2358.8
5°	2369.6	2358.8	2351.6	2348.1	2344.4	2333.7	2330.1	2322.9	2315.7	2308.5	2304.9
7.5°	2337.2	2319.3	2312.0	2308.5	2297.8	2286.9	2279.8	2269.0	2258.3	2247.5	2243.9
10°	2297.8	2279.8	2261.8	2254.7	2243.9	2236.8	2222.4	2208.0	2197.3	2186.5	2175.6
12.5°	2247.5	2225.9	2208.0	2200.8	2190.0	2175.6	2154.1	2147.0	2129.0	2121.9	2107.5
15°	2190.0	2164.9	2147.0	2136.2	2125.4	2103.8	2089.5	2075.1	2057.2	2050.0	2035.7
17.5°	2118.2	2089.5	2071.6	2060.8	2053.6	2035.7	2014.1	1996.2	1978.2	1971.1	1960.3
20°	2032.1	2014.1	1988.9	1978.2	1971.1	1949.5	1927.9	1920.8	1906.4	1892.0	1881.3
22.5°	1935.2	1917.2	1892.0	1881.3	1877.6	1859.8	1841.8	1831.0	1820.2	1809.5	1798.7
25°	1834.6	1813.1	1791.5	1784.4	1777.1	1762.9	1748.5	1741.2	1730.5	1723.3	1716.1
27.5°	1726.8	1705.3	1687.5	1676.6	1669.4	1658.7	1651.4	1644.3	1637.2	1629.9	1626.3
30°	1612.1	1590.4	1576.2	1568.9	1561.8	1558.2	1547.4	1543.8	1540.2	1533.0	1536.7
32.5°	1497.1	1479.1	1464.8	1454.0	1454.0	1446.9	1443.2	1443.2	1439.6	1439.6	1439.6
35°	1371.5	1360.7	1350.0	1346.3	1342.7	1339.2	1335.6	1339.2	1335.6	1339.2	1342.7
37.5°	1256.6	1245.8	1238.7	1235.0	1231.4	1235.0	1231.4	1231.4	1235.0	1242.2	1245.8
40°	1138.1	1130.9	1123.8	1127.4	1123.8	1123.8	1123.8	1134.5	1138.1	1141.6	1145.3
42.5°	1026.8	1019.6	1016.0	1016.0	1019.6	1016.0	1023.2	1026.8	1034.0	1044.7	1052.0
45°	919.1	915.6	915.6	919.1	915.6	922.7	922.7	929.8	940.7	947.8	955.0
47.5°	818.5	818.5	818.5	822.2	822.2	825.8	832.9	836.5	843.7	850.9	858.0
50°	725.2	728.9	732.4	732.4	732.4	739.6	746.8	750.4	753.9	757.5	768.3
52.5°	642.6	646.2	646.2	649.8	653.5	657.0	660.6	667.7	671.4	678.6	682.1
55°	563.7	563.7	570.8	574.4	574.4	574.4	581.6	581.6	588.8	592.3	599.6
57.5°	488.3	491.9	491.9	495.4	495.4	499.0	502.7	506.2	509.8	513.4	517.0
60°	416.5	416.5	416.5	420.0	423.6	427.3	423.6	430.8	430.8	438.0	441.6
62.5°	348.2	351.9	351.9	351.9	351.9	351.9	351.9	355.4	359.0	362.6	366.2
65°	283.6	283.6	283.6	280.1	283.6	280.1	283.6	287.2	287.2	290.8	294.4
67.5°	219.0	219.0	211.8	211.8	215.4	215.4	215.4	215.4	211.8	219.0	219.0
70°	157.9	154.4	150.8	147.2	147.2	143.6	143.6	140.0	140.0	140.0	140.0
72.5°	104.2	96.9	89.8	86.2	82.5	82.5	75.4	71.8	75.4	75.4	75.4
75°	53.9	46.6	43.1	39.5	35.9	35.9	32.3	32.3	32.3	32.3	32.3
77.5°	21.5	18.0	14.4	14.4	10.8	10.8	10.8	10.8	10.8	10.8	10.8
80°	7.1	7.1	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	3.6	0.0	0.0	3.6	0.0	3.6	3.6	3.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584827

CATALOG NUMBER: HCC8W50D010BZ-HM82555835-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8	2401.8
2.5°	2355.2	2355.2	2351.6	2355.2	2348.1	2351.6	2348.1	2348.1
5°	2301.3	2294.2	2294.2	2294.2	2290.5	2290.5	2286.9	2286.9
7.5°	2236.8	2233.1	2229.5	2225.9	2222.4	2218.8	2218.8	2218.8
10°	2172.1	2164.9	2164.9	2161.4	2154.1	2150.5	2150.5	2150.5
12.5°	2096.7	2093.1	2089.5	2089.5	2075.1	2078.7	2075.1	2075.1
15°	2024.9	2021.3	2021.3	2010.6	2003.3	2003.3	2003.3	1999.8
17.5°	1949.5	1945.9	1942.3	1935.2	1927.9	1927.9	1924.4	1927.9
20°	1870.5	1866.9	1859.8	1859.8	1856.1	1852.5	1845.4	1849.0
22.5°	1791.5	1784.4	1780.7	1780.7	1777.1	1777.1	1770.0	1770.0
25°	1709.0	1705.3	1701.7	1705.3	1698.2	1698.2	1691.0	1691.0
27.5°	1622.8	1619.2	1619.2	1619.2	1615.6	1619.2	1615.6	1615.6
30°	1536.7	1536.7	1533.0	1533.0	1536.7	1533.0	1536.7	1540.2
32.5°	1443.2	1443.2	1446.9	1446.9	1450.5	1450.5	1450.5	1450.5
35°	1346.3	1353.5	1353.5	1357.1	1360.7	1364.3	1364.3	1367.8
37.5°	1256.6	1260.2	1263.8	1267.3	1274.6	1274.6	1274.6	1274.6
40°	1159.6	1163.3	1170.4	1166.8	1181.2	1184.8	1181.2	1181.2
42.5°	1059.1	1066.2	1069.9	1077.1	1080.6	1087.9	1091.4	1091.4
45°	965.8	969.3	976.6	983.7	987.3	998.1	998.1	998.1
47.5°	868.8	876.0	879.6	886.8	890.4	901.2	904.7	901.2
50°	775.5	782.6	789.9	789.9	800.6	804.2	811.4	815.0
52.5°	685.7	689.4	696.5	700.1	707.2	714.5	718.0	721.6
55°	599.6	603.2	610.3	610.3	621.1	624.7	631.8	631.8
57.5°	520.6	524.2	531.3	527.8	534.9	542.1	542.1	538.6
60°	445.2	445.2	445.2	452.4	455.9	459.5	463.2	463.2
62.5°	366.2	373.4	377.0	377.0	380.5	384.1	384.1	380.5
65°	294.4	301.6	305.2	305.2	308.7	308.7	308.7	312.4
67.5°	222.6	222.6	222.6	226.2	222.6	222.6	222.6	222.6
70°	140.0	140.0	140.0	140.0	136.4	140.0	140.0	143.6
72.5°	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4
75°	32.3	32.3	32.3	35.9	32.3	32.3	32.3	32.3
77.5°	14.4	10.8	14.4	14.4	10.8	10.8	10.8	10.8
80°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	0.0	3.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)