

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584653

Luminaire Tested: **HCC8W45D010SL-HM82555827-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555827-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5532.6 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584653
CATALOG NUMBER: HCC8W45D010SL-HM82555827-81WDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584653

CATALOG NUMBER: HCC8W45D010SL-HM82555827-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																																				
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84																																				
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77																																				
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70																																				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																																				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59																																				
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54																																				
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50																																				
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46																																				
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132741
5°	129168
10°	128188
15°	126276
20°	122450
25°	117887
30°	110117
35°	91125
40°	55019
45°	37055
50°	26702
55°	15231
60°	6704
65°	2408
70°	893
75°	393
80°	0
85°	0



TEST NUMBER: P584653
 CATALOG NUMBER: HCC8W45D010SL-HM82555827-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.4	7.2
10°-20°	1111.6	20.1
20°-30°	1585.8	28.7
30°-40°	1444.0	26.1
40°-50°	681.2	12.3
50°-60°	267.9	4.8
60°-70°	42.7	0.8
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3093.8	55.9
0°-40°	4537.8	82.0
0°-60°	5486.9	99.2
0°-90°	5532.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5532.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4305	
5°	4173	396
15°	3956	1112
25°	3465	1586
35°	2421	1444
45°	850	681
55°	283	268
65°	33	43
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P584653
CATALOG NUMBER: HCC8W45D010SL-HM82555827-81WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	4304.7
2.5°	4248.6
5°	4172.9
7.5°	4130.1
10°	4093.9
12.5°	4034.5
15°	3955.5
17.5°	3856.7
20°	3731.5
22.5°	3599.8
25°	3464.8
27.5°	3300.1
30°	3092.6
32.5°	2812.6
35°	2420.7
37.5°	1870.7
40°	1366.8
42.5°	1050.7
45°	849.7
47.5°	698.2
50°	556.6
52.5°	418.3
55°	283.3
57.5°	177.8
60°	108.7
62.5°	65.9
65°	33.0
67.5°	16.4
70°	9.9
72.5°	3.3
75°	3.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)