

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584856

Luminaire Tested: **HCC8W50D010SL-HM82555927-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584856  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W50D010SL-HM82555927-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4189.6 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584856  
CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584856  
 CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																												
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																												
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																												
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																												
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62																												
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56																												
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																												
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																												
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																												
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78500
5°	77846
10°	76821
15°	77694
20°	83902
25°	91756
30°	90644
35°	75191
40°	44255
45°	28908
50°	22408
55°	14887
60°	7247
65°	2240
70°	757
75°	667
80°	497
85°	991



TEST NUMBER: P584856  
 CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.2	5.7
10°-20°	699.2	16.7
20°-30°	1222.5	29.2
30°-40°	1189.2	28.4
40°-50°	540.8	12.9
50°-60°	250.7	6.0
60°-70°	42.0	1.0
70°-80°	5.2	0.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2159.9	51.6
0°-40°	3349.1	79.9
0°-60°	4140.6	98.8
0°-90°	4189.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4189.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2546	
5°	2515	238
15°	2434	699
25°	2697	1223
35°	1997	1189
45°	663	541
55°	277	251
65°	31	42
75°	6	5
85°	3	2
90°	0	



TEST NUMBER: P584856  
CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2545.7
2.5°	2540.1
5°	2514.9
7.5°	2486.9
10°	2453.4
12.5°	2428.2
15°	2433.7
17.5°	2478.5
20°	2556.8
22.5°	2646.4
25°	2696.8
27.5°	2668.8
30°	2545.7
32.5°	2330.3
35°	1997.4
37.5°	1538.6
40°	1099.4
42.5°	819.7
45°	662.9
47.5°	559.5
50°	467.1
52.5°	372.1
55°	276.9
57.5°	190.2
60°	117.5
62.5°	64.3
65°	30.7
67.5°	14.0
70°	8.4
72.5°	5.6
75°	5.6
77.5°	2.8
80°	2.8
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)