

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584854

Luminaire Tested: **HCC8S50D010BZ-HM82555927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010BZ-HM82555927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3982.7 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584854
CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584854

CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64617	64617	64617
5°	65474	64344	63741
10°	66143	63686	62724
15°	66808	62341	61093
20°	66471	60042	58667
25°	64918	56446	55687
30°	61667	52402	52199
35°	56135	47816	48233
40°	49219	42798	44376
45°	42462	38066	40753
50°	37179	33418	36910
55°	32940	28725	32493
60°	29683	24157	26920
65°	26742	19394	20613
70°	23459	14119	11351
75°	20004	7339	2990
80°	15396	1989	497
85°	9871	0	0



TEST NUMBER: P584854
 CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.7	5.0
10°-20°	555.8	14.0
20°-30°	788.9	19.8
30°-40°	830.4	20.9
40°-50°	706.4	17.7
50°-60°	510.5	12.8
60°-70°	290.4	7.3
70°-80°	91.5	2.3
80°-90°	11.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1542.4	38.7
0°-40°	2372.8	59.6
0°-60°	3589.8	90.1
0°-90°	3982.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3982.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2096	2096	2096	2096	2096	
5°	2115	2104	2079	2065	2059	202
15°	2093	2040	1953	1916	1914	589
25°	1908	1813	1659	1631	1637	874
35°	1491	1404	1270	1262	1281	928
45°	974	937	873	895	934	757
55°	613	568	534	565	604	552
65°	366	316	266	263	282	363
75°	168	129	62	28	25	181
85°	28	17	0	0	0	36
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584854

CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5
2.5°	2106.8	2109.6	2104.0	2104.0	2109.6	2104.0	2106.8	2106.8	2104.0	2104.0	2101.2
5°	2115.2	2112.4	2112.4	2112.4	2115.2	2109.6	2106.8	2109.6	2104.0	2104.0	2104.0
7.5°	2117.9	2117.9	2115.2	2112.4	2112.4	2112.4	2109.6	2106.8	2104.0	2098.4	2095.5
10°	2112.4	2112.4	2115.2	2109.6	2109.6	2104.0	2104.0	2098.4	2098.4	2092.7	2084.3
12.5°	2106.8	2104.0	2104.0	2098.4	2098.4	2092.7	2092.7	2084.3	2081.5	2073.2	2064.8
15°	2092.7	2089.9	2084.3	2081.5	2078.7	2075.9	2070.4	2067.6	2059.2	2048.0	2039.6
17.5°	2064.8	2062.0	2059.2	2053.6	2048.0	2045.2	2042.4	2033.9	2022.8	2014.4	2000.4
20°	2025.6	2022.8	2022.8	2014.4	2011.6	2003.2	2000.4	1989.3	1980.9	1964.0	1952.8
22.5°	1972.5	1975.3	1969.6	1964.0	1958.4	1950.0	1944.5	1933.3	1919.3	1902.5	1888.5
25°	1908.0	1910.8	1905.4	1899.7	1891.3	1885.7	1880.1	1863.4	1849.4	1829.7	1813.0
27.5°	1826.9	1826.9	1826.9	1821.4	1807.4	1804.6	1799.0	1782.1	1762.6	1745.8	1729.1
30°	1731.9	1729.1	1729.1	1720.7	1715.0	1703.8	1695.5	1681.5	1667.5	1647.9	1628.3
32.5°	1617.1	1619.9	1611.6	1606.0	1597.6	1597.6	1586.3	1575.1	1558.4	1538.8	1519.2
35°	1491.2	1494.0	1488.4	1485.7	1471.7	1468.8	1466.0	1452.0	1440.9	1426.9	1404.4
37.5°	1362.5	1359.8	1357.0	1357.0	1348.6	1342.9	1337.3	1328.9	1312.2	1301.0	1289.8
40°	1222.7	1222.7	1222.7	1219.9	1217.0	1211.4	1208.6	1203.0	1191.9	1180.7	1172.3
42.5°	1096.8	1096.8	1094.0	1091.1	1085.5	1088.3	1082.7	1077.1	1066.0	1057.6	1052.0
45°	973.7	973.7	973.7	976.5	970.9	962.4	962.4	956.8	951.2	945.6	937.3
47.5°	864.5	872.9	867.3	864.5	867.3	856.2	856.2	850.6	845.0	839.3	828.1
50°	775.0	775.0	775.0	769.4	766.6	766.6	758.2	752.6	749.8	744.2	733.1
52.5°	693.8	688.3	688.3	685.5	682.7	677.1	677.1	671.5	660.3	654.6	646.3
55°	612.7	612.7	609.9	607.2	604.4	601.6	598.8	590.3	584.7	576.3	567.9
57.5°	540.0	545.6	542.8	537.2	531.5	531.5	525.9	520.4	512.0	503.6	495.2
60°	481.3	478.5	478.5	475.7	470.1	467.2	464.4	456.0	447.6	439.3	430.9
62.5°	419.7	419.7	419.7	414.1	408.4	405.6	402.8	397.3	386.1	377.7	372.1
65°	366.5	363.7	360.9	358.1	355.4	349.8	347.0	341.3	332.9	324.5	316.1
67.5°	313.4	310.6	310.6	307.8	299.4	296.6	296.6	288.2	279.7	271.4	263.0
70°	260.2	260.2	260.2	254.6	251.8	249.0	246.2	240.6	232.2	223.9	215.4
72.5°	215.4	212.6	212.6	209.8	201.4	198.6	195.8	190.2	181.9	176.3	170.7
75°	167.9	167.9	165.1	162.3	159.5	156.6	153.8	148.2	139.9	131.5	128.7
77.5°	128.7	125.9	125.9	123.1	117.5	114.7	114.7	109.1	100.8	95.2	89.5
80°	86.7	89.5	86.7	83.9	81.1	78.3	75.5	72.7	67.1	61.6	56.0
82.5°	53.2	56.0	53.2	53.2	50.4	47.6	47.6	42.0	39.2	36.4	33.6
85°	27.9	27.9	27.9	27.9	25.1	25.1	25.1	22.3	19.6	16.8	16.8
87.5°	8.4	11.2	8.4	8.4	8.4	8.4	8.4	8.4	5.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584854

CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5
2.5°	2104.0	2101.2	2098.4	2098.4	2098.4	2098.4	2098.4	2095.5	2092.7	2092.7	2092.7
5°	2098.4	2098.4	2098.4	2095.5	2092.7	2092.7	2087.1	2084.3	2081.5	2078.7	2075.9
7.5°	2092.7	2087.1	2084.3	2081.5	2078.7	2078.7	2073.2	2067.6	2067.6	2062.0	2056.4
10°	2075.9	2073.2	2067.6	2062.0	2059.2	2056.4	2050.8	2042.4	2039.6	2033.9	2028.4
12.5°	2056.4	2050.8	2045.2	2033.9	2031.3	2028.4	2017.2	2008.8	2003.2	2000.4	1986.5
15°	2031.3	2020.0	2011.6	1997.6	1994.8	1989.3	1980.9	1972.5	1961.2	1952.8	1947.3
17.5°	1986.5	1975.3	1961.2	1947.3	1941.7	1941.7	1927.7	1916.5	1902.5	1896.9	1885.7
20°	1933.3	1919.3	1908.0	1891.3	1882.9	1874.5	1866.1	1849.4	1838.1	1829.7	1815.8
22.5°	1871.7	1852.2	1838.1	1821.4	1807.4	1799.0	1784.9	1771.0	1757.0	1748.6	1737.5
25°	1793.4	1776.6	1754.2	1737.5	1729.1	1717.8	1701.0	1687.1	1673.1	1659.0	1653.6
27.5°	1706.6	1684.3	1664.7	1645.1	1636.7	1628.3	1608.8	1591.9	1580.7	1566.8	1561.2
30°	1611.6	1589.1	1566.8	1550.0	1541.6	1527.6	1516.4	1496.8	1482.9	1471.7	1457.6
32.5°	1502.4	1485.7	1466.0	1440.9	1435.3	1424.1	1407.2	1398.9	1382.1	1373.7	1362.5
35°	1384.9	1373.7	1354.2	1334.5	1326.1	1320.5	1306.6	1289.8	1278.5	1270.2	1264.6
37.5°	1273.0	1259.0	1239.4	1225.5	1219.9	1211.4	1194.7	1186.3	1175.1	1169.5	1158.2
40°	1152.8	1138.7	1124.7	1116.3	1108.0	1102.4	1091.1	1082.7	1071.5	1063.2	1060.4
42.5°	1035.1	1026.8	1015.6	1004.4	1001.6	993.2	987.6	979.3	970.9	968.0	959.6
45°	928.9	920.5	909.2	898.1	895.3	889.7	886.9	878.5	872.9	872.9	872.9
47.5°	822.5	814.2	803.0	797.4	800.2	789.0	789.0	786.2	780.5	780.5	783.3
50°	727.5	716.2	713.4	707.8	702.2	696.6	699.4	691.1	691.1	696.6	693.8
52.5°	637.9	626.7	623.9	618.3	615.5	615.5	612.7	612.7	609.9	612.7	612.7
55°	556.8	548.4	542.8	537.2	534.3	534.3	534.3	531.5	528.7	534.3	537.2
57.5°	484.0	481.3	475.7	467.2	464.4	461.6	458.8	458.8	458.8	458.8	461.6
60°	419.7	414.1	408.4	400.0	400.0	397.3	394.5	391.7	391.7	391.7	391.7
62.5°	363.7	355.4	347.0	341.3	338.5	335.7	332.9	327.3	327.3	327.3	327.3
65°	307.8	299.4	293.8	288.2	282.5	282.5	276.9	274.1	268.6	265.8	260.2
67.5°	254.6	249.0	243.4	235.0	232.2	229.5	223.9	221.1	212.6	209.8	207.0
70°	207.0	198.6	193.0	187.5	184.7	179.1	173.5	167.9	162.3	156.6	151.0
72.5°	162.3	153.8	148.2	142.7	137.1	137.1	128.7	123.1	114.7	109.1	100.8
75°	120.3	111.9	106.3	98.0	95.2	92.4	83.9	78.3	69.9	61.6	56.0
77.5°	81.1	75.5	69.9	61.6	56.0	56.0	47.6	42.0	36.4	27.9	25.1
80°	50.4	44.8	39.2	33.6	33.6	27.9	25.1	19.6	14.0	11.2	8.4
82.5°	27.9	25.1	22.3	16.8	16.8	14.0	11.2	8.4	5.6	2.8	2.8
85°	14.0	11.2	8.4	8.4	5.6	5.6	5.6	2.8	2.8	0.0	0.0
87.5°	5.6	2.8	2.8	2.8	2.8	2.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584854

CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5
2.5°	2089.9	2089.9	2087.1	2087.1	2087.1	2084.3	2087.1	2084.3	2084.3	2084.3	2087.1
5°	2078.7	2073.2	2073.2	2070.4	2070.4	2067.6	2070.4	2067.6	2064.8	2062.0	2064.8
7.5°	2056.4	2050.8	2048.0	2045.2	2045.2	2045.2	2042.4	2039.6	2042.4	2033.9	2039.6
10°	2025.6	2022.8	2017.2	2014.4	2011.6	2014.4	2011.6	2006.0	2006.0	2006.0	2003.2
12.5°	1986.5	1980.9	1978.1	1975.3	1969.6	1969.6	1972.5	1966.8	1966.8	1961.2	1961.2
15°	1938.9	1933.3	1927.7	1927.7	1922.1	1922.1	1919.3	1919.3	1916.5	1913.7	1913.7
17.5°	1880.1	1871.7	1866.1	1868.9	1866.1	1863.4	1863.4	1857.8	1855.0	1857.8	1857.8
20°	1810.2	1804.6	1799.0	1801.8	1796.2	1793.4	1796.2	1787.8	1790.6	1790.6	1790.6
22.5°	1731.9	1729.1	1720.7	1720.7	1715.0	1712.2	1715.0	1715.0	1717.8	1715.0	1715.0
25°	1645.1	1639.5	1633.9	1633.9	1631.1	1628.3	1631.1	1633.9	1631.1	1633.9	1633.9
27.5°	1552.8	1544.4	1544.4	1538.8	1538.8	1541.6	1538.8	1541.6	1544.4	1544.4	1550.0
30°	1452.0	1449.2	1446.4	1443.7	1443.7	1446.4	1446.4	1446.4	1449.2	1454.8	1454.8
32.5°	1357.0	1351.4	1345.8	1345.8	1351.4	1348.6	1351.4	1351.4	1357.0	1357.0	1362.5
35°	1253.4	1253.4	1247.8	1250.6	1250.6	1250.6	1250.6	1256.2	1261.8	1264.6	1270.2
37.5°	1158.2	1149.9	1152.8	1152.8	1155.4	1152.8	1161.1	1161.1	1166.7	1166.7	1172.3
40°	1054.8	1054.8	1057.6	1054.8	1057.6	1057.6	1063.2	1068.8	1071.5	1077.1	1079.9
42.5°	956.8	962.4	956.8	959.6	962.4	965.2	968.0	970.9	982.1	987.6	996.0
45°	867.3	870.1	872.9	875.7	872.9	878.5	881.3	886.9	895.3	898.1	900.9
47.5°	780.5	783.3	786.2	789.0	789.0	794.6	797.4	803.0	808.6	811.4	814.2
50°	696.6	702.2	705.0	705.0	707.8	713.4	719.1	719.1	724.7	733.1	735.8
52.5°	621.1	621.1	626.7	629.5	632.3	632.3	640.7	643.5	646.3	651.8	657.4
55°	537.2	545.6	548.4	548.4	554.0	559.6	562.4	565.2	565.2	576.3	576.3
57.5°	464.4	467.2	472.9	472.9	472.9	481.3	481.3	486.8	489.6	492.4	498.0
60°	391.7	397.3	397.3	400.0	397.3	402.8	405.6	411.3	414.1	416.9	419.7
62.5°	324.5	324.5	327.3	327.3	327.3	327.3	332.9	332.9	338.5	341.3	344.2
65°	260.2	260.2	260.2	260.2	260.2	260.2	260.2	260.2	263.0	263.0	268.6
67.5°	201.4	198.6	193.0	195.8	193.0	193.0	190.2	190.2	193.0	193.0	198.6
70°	145.5	142.7	137.1	137.1	134.3	131.5	128.7	125.9	123.1	123.1	123.1
72.5°	95.2	89.5	81.1	78.3	78.3	72.7	67.1	64.3	64.3	64.3	64.3
75°	47.6	42.0	36.4	33.6	33.6	27.9	30.7	27.9	27.9	27.9	27.9
77.5°	19.6	14.0	11.2	11.2	11.2	8.4	8.4	8.4	8.4	8.4	8.4
80°	5.6	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584854

CATALOG NUMBER: HCC8S50D010BZ-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5	2095.5
2.5°	2084.3	2084.3	2078.7	2081.5	2081.5	2081.5	2081.5	2081.5
5°	2059.2	2062.0	2059.2	2062.0	2062.0	2059.2	2059.2	2059.2
7.5°	2033.9	2036.7	2033.9	2036.7	2036.7	2036.7	2033.9	2033.9
10°	2003.2	2003.2	2003.2	2003.2	2003.2	2000.4	2003.2	2003.2
12.5°	1961.2	1961.2	1961.2	1964.0	1964.0	1961.2	1961.2	1958.4
15°	1916.5	1910.8	1913.7	1916.5	1913.7	1913.7	1913.7	1913.7
17.5°	1855.0	1857.8	1855.0	1855.0	1855.0	1855.0	1857.8	1855.0
20°	1790.6	1790.6	1793.4	1790.6	1790.6	1790.6	1790.6	1787.8
22.5°	1717.8	1715.0	1715.0	1717.8	1717.8	1715.0	1717.8	1717.8
25°	1636.7	1639.5	1636.7	1636.7	1639.5	1639.5	1639.5	1636.7
27.5°	1550.0	1552.8	1555.6	1552.8	1552.8	1552.8	1555.6	1558.4
30°	1460.4	1466.0	1460.4	1460.4	1466.0	1463.2	1466.0	1466.0
32.5°	1365.3	1373.7	1368.1	1373.7	1373.7	1376.5	1373.7	1376.5
35°	1270.2	1278.5	1278.5	1278.5	1281.3	1284.1	1284.1	1281.3
37.5°	1180.7	1183.5	1183.5	1189.1	1191.9	1194.7	1194.7	1191.9
40°	1088.3	1094.0	1096.8	1096.8	1096.8	1102.4	1108.0	1102.4
42.5°	998.8	1001.6	1004.4	1004.4	1010.0	1012.8	1015.6	1015.6
45°	912.1	917.7	920.5	923.3	926.1	931.7	928.9	934.5
47.5°	822.5	830.9	833.7	836.5	842.1	845.0	847.8	850.6
50°	741.4	747.0	747.0	752.6	761.0	761.0	766.6	769.4
52.5°	660.3	663.1	665.9	668.7	674.3	679.9	679.9	685.5
55°	581.9	584.7	584.7	587.5	590.3	601.6	604.4	604.4
57.5°	500.8	500.8	506.4	509.2	512.0	517.6	517.6	517.6
60°	422.5	425.3	425.3	428.1	430.9	436.5	439.3	436.5
62.5°	344.2	347.0	347.0	349.8	355.4	358.1	355.4	355.4
65°	271.4	274.1	274.1	276.9	282.5	282.5	279.7	282.5
67.5°	198.6	198.6	198.6	198.6	198.6	198.6	198.6	198.6
70°	125.9	123.1	120.3	123.1	123.1	123.1	120.3	125.9
72.5°	61.6	64.3	64.3	64.3	64.3	64.3	64.3	61.6
75°	27.9	27.9	25.1	25.1	25.1	27.9	27.9	25.1
77.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)