

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584861

Luminaire Tested: **HCC8W50D010SL-HM82555927-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W50D010SL-HM82555927-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3484.9 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584861  
CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584861

CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	57692	57692	57692
5°	60076	57562	55142
10°	62082	56831	52454
15°	63657	55532	49728
20°	63780	53226	47261
25°	62703	49856	44817
30°	59349	46004	42717
35°	54110	41375	40106
40°	47057	36474	37038
45°	40365	31586	33902
50°	34478	27234	30453
55°	30219	23456	26456
60°	26908	20007	22251
65°	23874	16322	17752
70°	21178	12099	10089
75°	17657	6338	2990
80°	13904	1989	497
85°	9871	991	0



TEST NUMBER: P584861  
 CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.3	5.1
10°-20°	494.1	14.2
20°-30°	699.3	20.1
30°-40°	731.7	21.0
40°-50°	610.3	17.5
50°-60°	432.7	12.4
60°-70°	249.2	7.2
70°-80°	80.2	2.3
80°-90°	11.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1369.7	39.3
0°-40°	2101.4	60.3
0°-60°	3144.4	90.2
0°-90°	3484.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3484.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1871	1871	1871	1871	1871	
5°	1941	1916	1860	1804	1781	186
15°	1994	1913	1740	1602	1558	561
25°	1843	1706	1465	1348	1317	841
35°	1437	1312	1099	1040	1065	891
45°	926	850	724	733	777	717
55°	562	503	436	459	492	508
65°	327	274	224	224	243	327
75°	148	109	53	25	25	161
85°	28	14	3	0	0	35
90°	0	0	0	0	0	



TEST NUMBER: P584861

CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9
2.5°	1910.0	1907.2	1904.4	1907.2	1904.4	1907.2	1904.4	1904.4	1901.6	1898.8	1898.8
5°	1940.8	1938.0	1938.0	1938.0	1935.2	1932.4	1932.4	1929.7	1924.1	1921.3	1915.6
7.5°	1960.4	1963.2	1963.2	1963.2	1957.6	1957.6	1952.0	1946.4	1940.8	1935.2	1926.9
10°	1982.7	1982.7	1979.9	1977.1	1971.5	1968.7	1966.0	1960.4	1952.0	1940.8	1932.4
12.5°	1991.2	1991.2	1988.4	1982.7	1979.9	1977.1	1974.3	1966.0	1954.8	1940.8	1929.7
15°	1994.0	1988.4	1985.5	1982.7	1977.1	1968.7	1968.7	1957.6	1943.6	1926.9	1912.8
17.5°	1971.5	1974.3	1968.7	1963.2	1954.8	1949.2	1940.8	1932.4	1915.6	1896.0	1882.1
20°	1943.6	1940.8	1938.0	1929.7	1918.4	1915.6	1907.2	1893.3	1879.3	1857.0	1837.3
22.5°	1898.8	1896.0	1890.5	1884.9	1873.7	1868.1	1859.6	1842.9	1823.4	1801.0	1778.6
25°	1842.9	1837.3	1828.9	1817.8	1809.4	1803.8	1792.5	1775.8	1753.4	1728.2	1705.9
27.5°	1753.4	1761.8	1756.2	1739.5	1731.1	1719.8	1717.0	1694.7	1675.2	1649.9	1624.8
30°	1666.8	1666.8	1658.3	1649.9	1636.0	1627.6	1616.4	1599.7	1580.0	1549.3	1529.8
32.5°	1557.7	1554.9	1543.7	1540.9	1529.8	1512.9	1510.1	1487.8	1468.1	1445.8	1420.7
35°	1437.4	1431.8	1420.7	1412.3	1406.7	1398.2	1389.9	1370.3	1350.8	1328.3	1311.6
37.5°	1300.4	1300.4	1297.6	1283.6	1278.1	1272.5	1264.0	1244.5	1233.3	1210.9	1194.1
40°	1169.0	1166.2	1157.8	1155.0	1149.4	1140.9	1135.4	1124.2	1107.4	1090.7	1073.8
42.5°	1040.3	1043.1	1031.9	1034.7	1023.6	1018.0	1015.2	998.3	990.0	973.2	959.2
45°	925.6	922.8	917.3	914.5	908.9	903.3	897.7	889.3	875.3	858.5	850.1
47.5°	819.4	811.1	811.1	808.2	805.4	794.2	791.4	783.0	774.7	757.9	746.6
50°	718.7	718.7	718.7	715.9	707.5	704.7	699.2	690.8	682.3	671.1	654.4
52.5°	637.6	637.6	637.6	634.8	623.7	620.9	618.1	606.8	595.7	587.3	576.1
55°	562.1	564.9	562.1	556.6	548.1	548.1	539.7	534.1	523.0	514.6	503.4
57.5°	497.8	497.8	492.1	489.3	483.8	481.0	475.4	469.8	455.8	447.5	433.5
60°	436.3	433.5	433.5	427.9	422.2	416.6	413.9	405.5	399.9	385.9	374.8
62.5°	380.3	380.3	374.8	374.8	363.6	363.6	360.8	352.3	343.9	330.0	324.4
65°	327.2	327.2	324.4	321.6	313.2	310.4	307.6	299.3	290.8	282.4	274.0
67.5°	279.6	279.6	274.0	271.2	265.7	262.9	257.3	251.7	243.3	234.9	226.6
70°	234.9	232.2	229.4	226.6	220.9	218.1	212.5	206.9	198.6	193.0	184.6
72.5°	190.2	190.2	187.4	181.8	179.0	176.2	173.4	167.8	159.5	151.0	145.4
75°	148.2	148.2	148.2	142.6	137.0	134.2	134.2	128.6	123.1	114.7	109.1
77.5°	114.7	111.9	109.1	109.1	103.5	100.7	97.8	95.0	86.7	83.9	78.3
80°	78.3	81.1	78.3	75.5	72.7	69.9	69.9	64.3	61.5	55.9	50.4
82.5°	53.2	50.4	50.4	47.6	47.6	44.8	44.8	39.2	36.4	33.6	30.7
85°	27.9	27.9	25.1	25.1	25.1	22.3	22.3	19.5	19.5	16.8	14.0
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	5.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584861

CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9
2.5°	1896.0	1890.5	1887.7	1887.7	1884.9	1882.1	1879.3	1876.5	1870.9	1870.9	1865.3
5°	1910.0	1904.4	1901.6	1893.3	1887.7	1887.7	1876.5	1873.7	1865.3	1859.6	1854.2
7.5°	1921.3	1910.0	1901.6	1893.3	1887.7	1882.1	1870.9	1859.6	1848.5	1837.3	1831.7
10°	1921.3	1910.0	1896.0	1882.1	1876.5	1870.9	1857.0	1840.1	1826.1	1815.0	1801.0
12.5°	1915.6	1898.8	1882.1	1870.9	1859.6	1851.3	1834.5	1817.8	1801.0	1778.6	1767.4
15°	1898.8	1876.5	1859.6	1840.1	1831.7	1817.8	1803.8	1778.6	1759.0	1739.5	1725.4
17.5°	1865.3	1837.3	1817.8	1798.2	1784.2	1775.8	1753.4	1731.1	1708.7	1686.3	1669.6
20°	1815.0	1789.7	1767.4	1742.3	1731.1	1719.8	1691.9	1669.6	1647.1	1622.0	1605.3
22.5°	1753.4	1728.2	1697.5	1678.0	1661.1	1647.1	1622.0	1596.9	1574.4	1552.1	1529.8
25°	1678.0	1652.7	1624.8	1594.0	1582.8	1568.9	1540.9	1515.7	1490.6	1465.3	1445.8
27.5°	1596.9	1563.3	1540.9	1507.3	1496.2	1482.2	1451.4	1423.5	1401.0	1381.5	1359.1
30°	1498.9	1473.8	1443.0	1412.3	1401.0	1387.1	1361.9	1336.8	1314.4	1292.0	1269.7
32.5°	1392.6	1367.5	1336.8	1314.4	1297.6	1286.4	1261.2	1238.9	1216.5	1194.1	1174.5
35°	1280.9	1252.8	1230.5	1208.2	1194.1	1180.1	1155.0	1135.4	1118.6	1099.1	1079.5
37.5°	1166.2	1146.6	1124.2	1099.1	1085.1	1073.8	1054.3	1031.9	1018.0	1001.1	987.2
40°	1054.3	1031.9	1012.4	990.0	978.8	970.4	950.9	934.0	920.1	906.1	897.7
42.5°	939.6	920.1	900.5	886.5	878.2	869.7	855.7	836.2	827.8	813.7	805.4
45°	833.4	816.5	802.6	783.0	777.4	771.9	755.1	741.0	732.7	724.3	718.7
47.5°	732.7	721.5	704.7	693.6	685.2	679.5	668.3	657.2	648.8	643.2	637.6
50°	646.0	632.0	620.9	609.6	604.0	595.7	584.5	578.9	573.3	567.7	567.7
52.5°	564.9	550.9	539.7	531.3	525.7	520.2	511.8	509.0	503.4	503.4	500.6
55°	489.3	481.0	469.8	458.6	455.8	453.0	447.5	441.9	439.1	436.3	439.1
57.5°	425.0	416.6	405.5	397.1	394.3	391.5	388.7	383.1	380.3	380.3	380.3
60°	366.4	357.9	349.5	341.2	341.2	335.6	332.8	330.0	327.2	324.4	324.4
62.5°	313.2	304.9	296.5	290.8	288.0	285.2	279.6	276.8	274.0	274.0	271.2
65°	265.7	254.5	251.7	243.3	240.5	237.7	234.9	229.4	226.6	223.7	220.9
67.5°	218.1	212.5	204.1	198.6	195.8	193.0	190.2	184.6	181.8	179.0	173.4
70°	176.2	170.6	164.9	159.5	156.6	153.8	148.2	142.6	139.8	134.2	125.9
72.5°	137.0	131.4	125.9	120.3	117.5	114.7	109.1	103.5	97.8	92.2	86.7
75°	103.5	97.8	89.5	83.9	81.1	81.1	72.7	67.1	61.5	53.2	47.6
77.5°	72.7	64.3	61.5	55.9	53.2	47.6	42.0	36.4	30.7	27.9	22.3
80°	47.6	42.0	36.4	33.6	30.7	27.9	25.1	19.5	14.0	11.2	8.4
82.5°	27.9	25.1	22.3	19.5	16.8	14.0	11.2	11.2	8.4	5.6	2.8
85°	14.0	11.2	8.4	8.4	5.6	5.6	5.6	2.8	2.8	2.8	2.8
87.5°	5.6	2.8	2.8	2.8	2.8	2.8	2.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584861

CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9
2.5°	1862.5	1859.6	1857.0	1854.2	1854.2	1848.5	1848.5	1845.7	1840.1	1837.3	1837.3
5°	1845.7	1837.3	1831.7	1828.9	1826.1	1817.8	1815.0	1809.4	1803.8	1798.2	1795.4
7.5°	1820.6	1806.6	1801.0	1798.2	1789.7	1781.4	1775.8	1767.4	1759.0	1750.7	1747.9
10°	1789.7	1775.8	1761.8	1756.2	1747.9	1742.3	1731.1	1719.8	1711.5	1703.1	1694.7
12.5°	1750.7	1733.9	1719.8	1714.3	1705.9	1694.7	1678.0	1672.4	1658.3	1652.7	1641.6
15°	1705.9	1686.3	1672.4	1664.0	1655.5	1638.8	1627.6	1616.4	1602.5	1596.9	1585.6
17.5°	1649.9	1627.6	1613.6	1605.3	1599.7	1585.6	1568.9	1554.9	1540.9	1535.2	1526.9
20°	1582.8	1568.9	1549.3	1540.9	1535.2	1518.5	1501.7	1496.2	1485.0	1473.8	1465.3
22.5°	1507.3	1493.4	1473.8	1465.3	1462.5	1448.6	1434.6	1426.2	1417.9	1409.5	1401.0
25°	1429.0	1412.3	1395.4	1389.9	1384.3	1373.1	1361.9	1356.3	1348.0	1342.4	1336.8
27.5°	1345.2	1328.3	1314.4	1306.0	1300.4	1292.0	1286.4	1280.9	1275.3	1269.7	1266.8
30°	1255.6	1238.9	1227.7	1222.1	1216.5	1213.7	1205.4	1202.6	1199.7	1194.1	1196.9
32.5°	1166.2	1152.2	1140.9	1132.6	1132.6	1127.0	1124.2	1124.2	1121.4	1121.4	1121.4
35°	1068.2	1059.9	1051.5	1048.7	1045.9	1043.1	1040.3	1043.1	1040.3	1043.1	1045.9
37.5°	978.8	970.4	964.8	962.0	959.2	962.0	959.2	959.2	962.0	967.6	970.4
40°	886.5	881.0	875.3	878.2	875.3	875.3	875.3	883.8	886.5	889.3	892.1
42.5°	799.8	794.2	791.4	791.4	794.2	791.4	797.0	799.8	805.4	813.7	819.4
45°	715.9	713.1	713.1	715.9	713.1	718.7	718.7	724.3	732.7	738.3	743.8
47.5°	637.6	637.6	637.6	640.4	640.4	643.2	648.8	651.6	657.2	662.8	668.3
50°	564.9	567.7	570.5	570.5	570.5	576.1	581.7	584.5	587.3	590.1	598.4
52.5°	500.6	503.4	503.4	506.2	509.0	511.8	514.6	520.2	523.0	528.5	531.3
55°	439.1	439.1	444.7	447.5	447.5	447.5	453.0	453.0	458.6	461.4	467.0
57.5°	380.3	383.1	383.1	385.9	385.9	388.7	391.5	394.3	397.1	399.9	402.7
60°	324.4	324.4	324.4	327.2	330.0	332.8	330.0	335.6	335.6	341.2	343.9
62.5°	271.2	274.0	274.0	274.0	274.0	274.0	274.0	276.8	279.6	282.4	285.2
65°	220.9	220.9	220.9	218.1	220.9	218.1	220.9	223.7	223.7	226.6	229.4
67.5°	170.6	170.6	164.9	164.9	167.8	167.8	167.8	167.8	164.9	170.6	170.6
70°	123.1	120.3	117.5	114.7	114.7	111.9	111.9	109.1	109.1	109.1	109.1
72.5°	81.1	75.5	69.9	67.1	64.3	64.3	58.7	55.9	58.7	58.7	58.7
75°	42.0	36.4	33.6	30.7	27.9	27.9	25.1	25.1	25.1	25.1	25.1
77.5°	16.8	14.0	11.2	11.2	8.4	8.4	8.4	8.4	8.4	8.4	8.4
80°	5.6	5.6	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
85°	2.8	0.0	0.0	2.8	0.0	2.8	2.8	2.8	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584861

CATALOG NUMBER: HCC8W50D010SL-HM82555927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9	1870.9
2.5°	1834.5	1834.5	1831.7	1834.5	1828.9	1831.7	1828.9	1828.9
5°	1792.5	1787.1	1787.1	1787.1	1784.2	1784.2	1781.4	1781.4
7.5°	1742.3	1739.5	1736.7	1733.9	1731.1	1728.2	1728.2	1728.2
10°	1691.9	1686.3	1686.3	1683.5	1678.0	1675.2	1675.2	1675.2
12.5°	1633.2	1630.4	1627.6	1627.6	1616.4	1619.2	1616.4	1616.4
15°	1577.2	1574.4	1574.4	1566.1	1560.5	1560.5	1560.5	1557.7
17.5°	1518.5	1515.7	1512.9	1507.3	1501.7	1501.7	1498.9	1501.7
20°	1457.0	1454.2	1448.6	1448.6	1445.8	1443.0	1437.4	1440.2
22.5°	1395.4	1389.9	1387.1	1387.1	1384.3	1384.3	1378.7	1378.7
25°	1331.1	1328.3	1325.5	1328.3	1322.7	1322.7	1317.2	1317.2
27.5°	1264.0	1261.2	1261.2	1261.2	1258.4	1261.2	1258.4	1258.4
30°	1196.9	1196.9	1194.1	1194.1	1196.9	1194.1	1196.9	1199.7
32.5°	1124.2	1124.2	1127.0	1127.0	1129.8	1129.8	1129.8	1129.8
35°	1048.7	1054.3	1054.3	1057.1	1059.9	1062.7	1062.7	1065.4
37.5°	978.8	981.6	984.4	987.2	992.8	992.8	992.8	992.8
40°	903.3	906.1	911.7	908.9	920.1	922.8	920.1	920.1
42.5°	825.0	830.6	833.4	839.0	841.8	847.4	850.1	850.1
45°	752.3	755.1	760.7	766.3	769.1	777.4	777.4	777.4
47.5°	676.7	682.3	685.2	690.8	693.6	702.0	704.7	702.0
50°	604.0	609.6	615.2	615.2	623.7	626.5	632.0	634.8
52.5°	534.1	536.9	542.5	545.3	550.9	556.6	559.4	562.1
55°	467.0	469.8	475.4	475.4	483.8	486.7	492.1	492.1
57.5°	405.5	408.3	413.9	411.1	416.6	422.2	422.2	419.4
60°	346.7	346.7	346.7	352.3	355.1	357.9	360.8	360.8
62.5°	285.2	290.8	293.7	293.7	296.5	299.3	299.3	296.5
65°	229.4	234.9	237.7	237.7	240.5	240.5	240.5	243.3
67.5°	173.4	173.4	173.4	176.2	173.4	173.4	173.4	173.4
70°	109.1	109.1	109.1	109.1	106.3	109.1	109.1	111.9
72.5°	58.7	58.7	58.7	58.7	58.7	58.7	58.7	58.7
75°	25.1	25.1	25.1	27.9	25.1	25.1	25.1	25.1
77.5°	11.2	8.4	11.2	11.2	8.4	8.4	8.4	8.4
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
85°	0.0	2.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)