

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584868

Luminaire Tested: **HCC8S50D010MB-HM82555930-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584868  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MB-HM82555930-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4509.7 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584868  
CATALOG NUMBER: HCC8S50D010MB-HM82555930-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584868  
 CATALOG NUMBER: HCC8S50D010MB-HM82555930-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	99	94	91	102	97	93	90	95	91	88		92	90	87		90	88	86	84
4	100	93	88	84	98	92	87	84	90	86	83		88	85	82		86	83	81	80
5	96	88	83	79	94	87	82	79	86	81	78		84	80	77		82	79	77	75
6	92	84	78	75	90	83	78	74	81	77	74		80	76	73		79	76	73	72
7	88	80	74	70	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	70	67	83	75	70	67	74	70	66		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	358821
5°	303997
10°	220568
15°	165638
20°	130694
25°	105417
30°	78121
35°	31647
40°	13348
45°	7156
50°	3214
55°	1624
60°	1030
65°	737
70°	604
75°	405
80°	604
85°	1203



TEST NUMBER: P584868  
 CATALOG NUMBER: HCC8S50D010MB-HM82555930-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	843.2	18.7
10°-20°	1457.3	32.3
20°-30°	1408.9	31.2
30°-40°	618.8	13.7
40°-50°	133.8	3.0
50°-60°	30.1	0.7
60°-70°	10.3	0.2
70°-80°	4.0	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3709.4	82.3
0°-40°	4328.2	96.0
0°-60°	4492.1	99.6
0°-90°	4509.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4509.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11636	
5°	9821	843
15°	5188	1457
25°	3098	1409
35°	841	619
45°	164	134
55°	30	30
65°	10	10
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P584868  
CATALOG NUMBER: HCC8S50D010MB-HM82555930-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11636.3
1°	11549.3
2°	11311.5
3°	10882.7
4°	10370.2
5°	9820.9
6°	9221.3
7°	8618.5
8°	8052.3
9°	7526.5
10°	7044.2
11°	6588.6
12°	6179.9
13°	5808.2
14°	5479.9
15°	5188.5
17.5°	4535.3
20°	3982.7
22.5°	3496.9
25°	3098.3
27.5°	2693.0
30°	2194.0
32.5°	1490.6
35°	840.7
37.5°	495.8
40°	331.6
42.5°	234.5
45°	164.1
47.5°	107.2
50°	67.0
52.5°	40.2
55°	30.2
57.5°	23.5
60°	16.7
62.5°	13.4
65°	10.1
67.5°	6.7
70°	6.7
72.5°	3.4
75°	3.4
77.5°	3.4
80°	3.4
82.5°	3.4

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584868  
CATALOG NUMBER: HCC8S50D010MB-HM82555930-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	3.4
87.5°	3.4

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)