

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584879

Luminaire Tested: **HCC8S50D010BZ-HM82555930-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010BZ-HM82555930-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4529.5 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584879
CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584879

CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75682	75682	75682
5°	78342	75246	72259
10°	80080	73928	68191
15°	81221	71440	63682
20°	80975	67974	59117
25°	78970	63564	54272
30°	74820	58456	49803
35°	68068	52901	45256
40°	59785	47053	40886
45°	52135	41389	36449
50°	45368	36267	32113
55°	40461	31870	27929
60°	36763	27932	23818
65°	33046	24297	21620
70°	29428	20719	19519
75°	25794	17454	16656
80°	21878	14206	14775
85°	16487	10579	11782



TEST NUMBER: P584879
 CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.9	5.1
10°-20°	633.4	14.0
20°-30°	879.2	19.4
30°-40°	909.0	20.1
40°-50°	761.1	16.8
50°-60°	552.5	12.2
60°-70°	348.7	7.7
70°-80°	172.7	3.8
80°-90°	42.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1742.5	38.5
0°-40°	2651.5	58.5
0°-60°	3965.2	87.5
0°-90°	4529.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4529.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2454	2454	2454	2454	2454	
5°	2531	2501	2431	2364	2334	242
15°	2544	2448	2238	2058	1995	716
25°	2321	2171	1868	1665	1595	1064
35°	1808	1675	1405	1246	1202	1126
45°	1196	1109	949	856	836	925
55°	753	686	593	543	520	679
65°	453	396	333	293	296	452
75°	216	180	146	140	140	232
85°	47	37	30	33	33	57
90°	0	0	0	0	0	



TEST NUMBER: P584879

CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3
2.5°	2494.3	2494.3	2497.6	2494.3	2494.3	2494.3	2490.9	2490.9	2487.6	2487.6	2481.0
5°	2530.9	2524.2	2530.9	2524.2	2524.2	2524.2	2520.9	2514.3	2510.9	2504.2	2501.0
7.5°	2547.5	2544.2	2544.2	2540.9	2540.9	2537.5	2534.3	2530.9	2517.6	2514.3	2504.2
10°	2557.5	2554.1	2554.1	2550.9	2544.2	2544.2	2537.5	2534.3	2517.6	2510.9	2497.6
12.5°	2554.1	2554.1	2554.1	2550.9	2540.9	2537.5	2530.9	2520.9	2507.6	2494.3	2481.0
15°	2544.2	2544.2	2537.5	2534.3	2524.2	2517.6	2514.3	2497.6	2484.2	2467.6	2447.7
17.5°	2510.9	2510.9	2507.6	2501.0	2490.9	2484.2	2477.6	2461.0	2447.7	2421.0	2401.0
20°	2467.6	2464.3	2461.0	2450.9	2441.0	2437.6	2427.7	2404.4	2387.7	2367.7	2341.0
22.5°	2404.4	2401.0	2397.7	2391.1	2374.4	2367.7	2361.0	2344.4	2314.4	2294.4	2261.2
25°	2321.0	2321.0	2314.4	2304.4	2287.8	2281.2	2271.1	2254.5	2227.9	2197.8	2171.2
27.5°	2224.5	2221.2	2211.2	2204.5	2191.2	2181.2	2164.5	2144.6	2118.0	2094.6	2061.3
30°	2101.3	2101.3	2094.6	2084.7	2068.0	2061.3	2048.0	2024.7	1998.1	1968.1	1944.7
32.5°	1961.5	1961.5	1951.4	1944.7	1934.8	1918.1	1914.8	1888.2	1864.9	1841.5	1814.9
35°	1808.2	1811.6	1804.9	1791.6	1775.0	1775.0	1768.3	1745.0	1718.3	1695.0	1675.1
37.5°	1655.1	1645.1	1641.7	1635.1	1625.1	1611.8	1605.2	1595.1	1571.8	1555.1	1525.2
40°	1485.2	1488.6	1481.9	1475.3	1471.9	1462.0	1458.6	1442.0	1425.2	1405.3	1392.0
42.5°	1332.1	1332.1	1332.1	1325.4	1318.7	1308.7	1305.4	1295.4	1275.4	1262.2	1242.2
45°	1195.5	1185.5	1185.5	1182.2	1178.8	1172.2	1162.2	1155.6	1142.2	1132.3	1108.9
47.5°	1062.3	1065.7	1062.3	1059.0	1048.9	1045.7	1042.3	1029.0	1015.7	1005.7	989.1
50°	945.7	952.4	945.7	945.7	939.1	935.8	929.1	919.1	909.1	892.4	875.8
52.5°	849.2	849.2	845.9	842.5	832.6	825.9	822.5	819.2	802.5	789.2	775.9
55°	752.6	756.0	756.0	745.9	742.7	736.0	732.6	722.7	716.0	696.0	686.0
57.5°	669.4	666.0	669.4	662.7	656.0	649.4	646.0	639.3	629.4	616.1	602.7
60°	596.1	589.4	589.4	586.1	579.5	576.1	569.4	559.5	549.4	536.1	526.2
62.5°	522.8	519.5	516.1	512.8	506.2	502.9	499.5	489.6	479.5	469.6	459.5
65°	452.9	452.9	449.6	442.9	439.5	436.3	432.9	426.2	412.9	406.2	396.3
67.5°	389.6	386.2	386.2	379.7	373.0	369.6	369.6	363.0	353.0	343.0	336.3
70°	326.4	329.7	326.4	323.0	316.3	316.3	309.7	306.4	293.1	289.7	279.7
72.5°	269.7	269.7	266.4	266.4	259.8	256.4	256.4	249.8	243.2	236.5	229.8
75°	216.5	216.5	216.5	213.1	209.8	203.2	203.2	199.8	193.1	186.5	179.8
77.5°	169.9	166.5	166.5	163.2	159.8	156.5	156.5	153.1	146.5	143.2	136.5
80°	123.2	119.9	119.9	119.9	113.3	116.5	113.3	109.9	106.6	103.2	99.9
82.5°	80.0	83.2	83.2	80.0	76.6	76.6	76.6	73.3	73.3	69.9	66.6
85°	46.6	46.6	46.6	46.6	43.3	43.3	43.3	40.0	40.0	40.0	36.6
87.5°	20.0	20.0	20.0	20.0	20.0	20.0	16.6	16.6	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584879

CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3
2.5°	2481.0	2474.3	2470.9	2467.6	2467.6	2464.3	2461.0	2454.3	2454.3	2447.7	2444.3
5°	2494.3	2484.2	2477.6	2470.9	2467.6	2461.0	2454.3	2444.3	2441.0	2430.9	2421.0
7.5°	2497.6	2481.0	2474.3	2461.0	2454.3	2447.7	2434.3	2424.3	2411.1	2401.0	2387.7
10°	2484.2	2470.9	2454.3	2437.6	2434.3	2424.3	2404.4	2391.1	2374.4	2361.0	2341.0
12.5°	2464.3	2444.3	2427.7	2407.7	2397.7	2387.7	2367.7	2347.7	2324.4	2301.1	2281.2
15°	2430.9	2407.7	2384.4	2361.0	2347.7	2337.8	2314.4	2291.1	2267.9	2237.8	2217.8
17.5°	2381.0	2354.4	2331.1	2301.1	2287.8	2277.8	2247.9	2221.2	2191.2	2161.2	2141.3
20°	2317.8	2284.5	2257.8	2224.5	2214.6	2197.8	2167.9	2138.0	2104.7	2071.4	2048.0
22.5°	2234.5	2201.2	2171.2	2138.0	2121.3	2104.7	2074.6	2038.0	2004.7	1978.1	1954.8
25°	2138.0	2107.9	2071.4	2041.3	2021.4	2001.4	1968.1	1938.1	1908.2	1868.2	1844.9
27.5°	2031.4	1994.8	1968.1	1928.1	1908.2	1894.8	1858.2	1818.3	1791.6	1755.0	1728.4
30°	1911.4	1878.2	1848.2	1808.2	1788.2	1775.0	1741.7	1705.0	1678.3	1641.7	1615.1
32.5°	1784.9	1748.4	1711.6	1685.0	1661.7	1648.4	1611.8	1588.4	1555.1	1525.2	1495.3
35°	1648.4	1611.8	1585.2	1548.5	1535.1	1521.9	1491.9	1462.0	1431.9	1405.3	1382.0
37.5°	1501.9	1475.3	1445.2	1418.6	1408.6	1395.3	1358.7	1332.1	1308.7	1282.0	1262.2
40°	1358.7	1335.3	1315.4	1288.7	1272.1	1262.2	1235.5	1212.1	1185.5	1168.9	1148.9
42.5°	1228.9	1202.2	1182.2	1162.2	1145.6	1135.6	1112.3	1095.6	1075.6	1059.0	1035.6
45°	1092.3	1079.0	1055.6	1039.0	1029.0	1015.7	999.0	979.0	962.4	949.1	932.4
47.5°	972.4	959.0	942.4	922.5	915.8	905.7	889.1	875.8	862.5	849.2	832.6
50°	862.5	845.9	832.6	819.2	812.6	802.5	785.9	779.3	769.2	756.0	745.9
52.5°	762.7	749.3	736.0	719.3	716.0	709.3	699.3	686.0	676.0	669.4	662.7
55°	672.6	659.3	649.4	636.1	632.8	626.1	612.8	606.1	599.5	592.8	586.1
57.5°	592.8	579.5	566.1	559.5	552.8	546.2	542.8	532.8	526.2	522.8	516.1
60°	519.5	506.2	496.2	486.2	482.9	479.5	472.9	466.2	459.5	452.9	449.6
62.5°	449.6	436.3	429.6	422.9	416.3	416.3	409.6	403.0	396.3	392.9	386.2
65°	386.2	379.7	369.6	359.7	356.3	356.3	346.4	343.0	339.7	333.0	326.4
67.5°	326.4	319.7	309.7	306.4	303.0	299.7	296.3	289.7	283.0	279.7	273.1
70°	273.1	266.4	259.8	256.4	253.1	249.8	243.2	239.8	233.1	229.8	226.4
72.5°	219.8	216.5	209.8	206.4	203.2	199.8	196.5	193.1	186.5	183.2	179.8
75°	176.5	173.1	166.5	163.2	159.8	159.8	156.5	149.9	146.5	146.5	143.2
77.5°	133.1	129.9	126.6	123.2	119.9	119.9	116.5	113.3	109.9	109.9	106.6
80°	96.6	93.3	89.9	89.9	89.9	86.6	83.2	83.2	80.0	80.0	76.6
82.5°	63.2	63.2	60.0	60.0	60.0	56.6	56.6	53.3	53.3	53.3	53.3
85°	36.6	36.6	36.6	33.3	33.3	33.3	33.3	33.3	33.3	29.9	33.3
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584879

CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3
2.5°	2441.0	2437.6	2430.9	2430.9	2424.3	2424.3	2421.0	2417.7	2414.3	2411.1	2407.7
5°	2417.7	2404.4	2397.7	2394.3	2387.7	2384.4	2374.4	2367.7	2364.4	2357.8	2351.1
7.5°	2374.4	2361.0	2347.7	2344.4	2341.0	2327.7	2317.8	2307.7	2301.1	2294.4	2287.8
10°	2324.4	2311.1	2294.4	2287.8	2281.2	2264.5	2251.1	2241.2	2227.9	2214.6	2211.2
12.5°	2264.5	2244.5	2224.5	2217.8	2207.9	2191.2	2177.8	2161.2	2151.3	2134.6	2131.3
15°	2194.6	2171.2	2154.6	2138.0	2131.3	2114.6	2091.3	2078.0	2058.0	2051.4	2034.8
17.5°	2111.3	2088.0	2064.7	2058.0	2048.0	2024.7	2001.4	1984.7	1964.7	1954.8	1944.7
20°	2024.7	1994.8	1971.4	1964.7	1951.4	1931.4	1908.2	1891.6	1874.8	1854.9	1844.9
22.5°	1924.8	1891.6	1871.6	1854.9	1851.6	1828.2	1801.5	1788.2	1775.0	1758.3	1745.0
25°	1814.9	1784.9	1761.7	1748.4	1741.7	1721.7	1701.7	1685.0	1665.0	1655.1	1638.5
27.5°	1701.7	1681.7	1651.8	1638.5	1628.4	1611.8	1588.4	1578.5	1558.5	1545.2	1535.1
30°	1591.8	1561.8	1545.2	1528.5	1518.5	1501.9	1481.9	1471.9	1455.3	1442.0	1431.9
32.5°	1471.9	1451.9	1428.6	1422.0	1408.6	1392.0	1378.7	1362.0	1348.7	1335.3	1332.1
35°	1362.0	1335.3	1312.1	1305.4	1295.4	1278.8	1272.1	1262.2	1245.5	1242.2	1228.9
37.5°	1242.2	1228.9	1202.2	1192.1	1188.9	1175.5	1162.2	1155.6	1145.6	1135.6	1132.3
40°	1128.9	1112.3	1099.0	1088.9	1082.3	1072.3	1059.0	1055.6	1048.9	1035.6	1032.3
42.5°	1022.3	1005.7	992.4	989.1	979.0	969.1	962.4	952.4	949.1	945.7	939.1
45°	919.1	909.1	895.8	892.4	889.1	875.8	869.2	862.5	855.8	852.6	845.9
47.5°	825.9	815.8	805.9	802.5	795.9	792.6	782.5	779.3	769.2	765.9	762.7
50°	736.0	729.3	722.7	719.3	712.6	709.3	702.7	696.0	689.4	686.0	682.7
52.5°	656.0	649.4	642.7	639.3	636.1	629.4	622.7	616.1	612.8	609.4	606.1
55°	579.5	572.8	569.4	566.1	562.8	559.5	549.4	546.2	542.8	539.5	532.8
57.5°	509.5	502.9	496.2	496.2	492.9	489.6	482.9	476.3	476.3	469.6	462.9
60°	446.2	439.5	432.9	429.6	426.2	419.6	416.3	412.9	409.6	406.2	399.6
62.5°	379.7	376.3	369.6	369.6	363.0	359.7	356.3	353.0	349.6	343.0	339.7
65°	323.0	319.7	313.1	309.7	309.7	306.4	299.7	296.3	293.1	293.1	289.7
67.5°	269.7	266.4	259.8	256.4	256.4	253.1	249.8	249.8	246.4	243.2	246.4
70°	223.2	216.5	216.5	213.1	213.1	209.8	206.4	206.4	206.4	209.8	209.8
72.5°	176.5	173.1	169.9	169.9	169.9	169.9	166.5	166.5	169.9	173.1	173.1
75°	139.8	136.5	136.5	136.5	133.1	133.1	136.5	136.5	139.8	139.8	139.8
77.5°	103.2	103.2	103.2	103.2	103.2	103.2	106.6	106.6	109.9	109.9	109.9
80°	76.6	76.6	76.6	76.6	76.6	80.0	80.0	80.0	80.0	80.0	83.2
82.5°	53.3	53.3	53.3	53.3	53.3	53.3	53.3	56.6	56.6	56.6	56.6
85°	29.9	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584879

CATALOG NUMBER: HCC8S50D010BZ-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3	2454.3
2.5°	2404.4	2404.4	2404.4	2407.7	2401.0	2401.0	2401.0	2401.0
5°	2347.7	2344.4	2341.0	2344.4	2337.8	2337.8	2334.4	2334.4
7.5°	2277.8	2274.5	2271.1	2271.1	2264.5	2264.5	2261.2	2257.8
10°	2201.2	2194.6	2197.8	2191.2	2187.9	2184.5	2181.2	2177.8
12.5°	2118.0	2111.3	2107.9	2101.3	2094.6	2091.3	2094.6	2088.0
15°	2028.1	2018.0	2014.8	2008.1	2001.4	1998.1	1998.1	1994.8
17.5°	1928.1	1921.5	1918.1	1911.4	1908.2	1901.5	1898.2	1894.8
20°	1834.9	1818.3	1821.5	1814.9	1811.6	1798.3	1798.3	1801.5
22.5°	1731.6	1721.7	1715.0	1708.4	1705.0	1698.3	1698.3	1695.0
25°	1628.4	1618.5	1615.1	1608.4	1605.2	1598.5	1595.1	1595.1
27.5°	1528.5	1515.3	1515.3	1508.6	1501.9	1498.5	1495.3	1491.9
30°	1422.0	1411.9	1408.6	1408.6	1405.3	1405.3	1395.3	1398.7
32.5°	1322.0	1315.4	1312.1	1305.4	1305.4	1302.0	1302.0	1292.1
35°	1222.2	1212.1	1215.5	1208.9	1205.5	1202.2	1205.5	1202.2
37.5°	1125.6	1119.0	1119.0	1112.3	1112.3	1108.9	1105.6	1112.3
40°	1029.0	1025.7	1022.3	1019.0	1022.3	1019.0	1012.4	1015.7
42.5°	932.4	932.4	929.1	929.1	925.7	925.7	925.7	925.7
45°	845.9	842.5	842.5	839.2	839.2	839.2	839.2	835.8
47.5°	759.3	756.0	756.0	756.0	752.6	752.6	749.3	752.6
50°	676.0	676.0	672.6	672.6	676.0	672.6	669.4	669.4
52.5°	599.5	599.5	596.1	596.1	592.8	589.4	592.8	592.8
55°	529.4	526.2	522.8	522.8	519.5	516.1	516.1	519.5
57.5°	462.9	459.5	456.3	456.3	449.6	446.2	446.2	446.2
60°	399.6	392.9	392.9	389.6	389.6	386.2	386.2	386.2
62.5°	339.7	336.3	336.3	336.3	336.3	333.0	333.0	333.0
65°	289.7	289.7	289.7	293.1	293.1	296.3	296.3	296.3
67.5°	249.8	253.1	253.1	253.1	256.4	256.4	256.4	253.1
70°	213.1	213.1	213.1	216.5	216.5	216.5	216.5	216.5
72.5°	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5
75°	139.8	143.2	143.2	143.2	139.8	143.2	143.2	139.8
77.5°	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9
80°	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2
82.5°	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6
85°	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)