

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584727

Luminaire Tested: **HCC8S45D010MB-HM82555927-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MB-HM82555927-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3759.9 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584727
CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584727

CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57645	57645	57645
5°	59757	57457	55485
10°	61447	56957	53212
15°	62817	55950	50865
20°	62917	53765	48796
25°	61710	50778	47069
30°	58527	47086	45007
35°	53184	42884	42982
40°	46501	38483	40512
45°	40299	34277	37752
50°	35289	30448	34392
55°	31407	26983	31123
60°	28326	24237	27352
65°	25574	21313	23830
70°	22982	17960	17716
75°	20254	14238	13296
80°	16977	11791	12732
85°	13162	10331	11286



TEST NUMBER: P584727
 CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.4	4.7
10°-20°	496.7	13.2
20°-30°	709.9	18.9
30°-40°	754.3	20.1
40°-50°	649.4	17.3
50°-60°	485.5	12.9
60°-70°	309.7	8.2
70°-80°	140.9	3.7
80°-90°	37.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.0	36.8
0°-40°	2137.3	56.8
0°-60°	3272.3	87.0
0°-90°	3759.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3759.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1869	1869	1869	1869	1869	
5°	1930	1904	1856	1808	1792	185
15°	1968	1901	1753	1633	1593	554
25°	1814	1699	1492	1402	1383	830
35°	1413	1314	1139	1110	1142	880
45°	924	874	786	807	866	718
55°	584	536	502	544	579	525
65°	350	311	292	305	327	350
75°	170	146	120	109	112	181
85°	37	32	29	32	32	45
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584727

CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4
2.5°	1904.0	1898.6	1901.3	1898.6	1901.3	1901.3	1896.0	1896.0	1896.0	1896.0	1888.1
5°	1930.5	1927.8	1927.8	1925.2	1922.5	1925.2	1922.5	1919.8	1914.6	1911.9	1904.0
7.5°	1946.5	1946.5	1946.5	1946.5	1943.8	1941.1	1938.5	1933.2	1927.8	1922.5	1917.3
10°	1962.4	1965.0	1962.4	1959.7	1957.0	1951.8	1949.1	1943.8	1935.8	1927.8	1922.5
12.5°	1970.4	1970.4	1967.7	1967.7	1962.4	1959.7	1951.8	1943.8	1935.8	1927.8	1914.6
15°	1967.7	1967.7	1965.0	1962.4	1954.5	1951.8	1946.5	1938.5	1925.2	1914.6	1901.3
17.5°	1951.8	1949.1	1943.8	1943.8	1933.2	1930.5	1925.2	1914.6	1901.3	1885.4	1869.4
20°	1917.3	1917.3	1914.6	1911.9	1901.3	1893.3	1888.1	1874.8	1864.1	1845.6	1829.6
22.5°	1869.4	1874.8	1869.4	1864.1	1850.9	1848.2	1840.2	1824.2	1808.4	1787.1	1768.5
25°	1813.7	1811.0	1808.4	1803.0	1792.5	1787.1	1776.5	1760.6	1744.6	1720.8	1699.4
27.5°	1742.0	1731.3	1731.3	1720.8	1712.8	1704.8	1699.4	1683.6	1662.3	1643.7	1617.2
30°	1643.7	1646.4	1633.1	1630.5	1617.2	1611.8	1601.3	1585.3	1566.8	1545.4	1524.2
32.5°	1537.5	1529.6	1529.6	1518.9	1508.2	1500.4	1497.7	1479.0	1463.2	1442.0	1420.6
35°	1412.8	1412.8	1404.8	1402.1	1391.4	1386.1	1378.2	1367.6	1349.0	1330.4	1314.5
37.5°	1290.5	1285.3	1282.6	1277.3	1269.3	1261.3	1261.3	1242.8	1240.1	1218.9	1197.6
40°	1155.2	1160.4	1155.2	1147.2	1144.5	1139.2	1136.5	1126.0	1118.0	1099.3	1086.1
42.5°	1040.9	1035.6	1035.6	1032.9	1022.4	1022.4	1017.0	1011.7	998.5	993.2	977.2
45°	924.1	929.4	921.4	924.1	913.5	913.5	913.5	902.9	892.2	884.3	873.7
47.5°	823.2	825.8	825.8	817.9	815.2	815.2	810.0	804.6	796.6	786.0	778.1
50°	735.6	738.2	732.9	730.2	724.9	722.3	722.3	711.7	706.4	695.7	690.4
52.5°	655.9	655.9	653.2	653.2	645.3	645.3	640.0	632.0	626.7	621.3	608.1
55°	584.2	584.2	581.6	578.9	578.9	570.9	568.3	560.3	554.9	544.4	536.4
57.5°	515.2	517.8	515.2	512.5	509.9	507.2	501.9	494.0	488.6	480.7	475.3
60°	459.3	459.3	456.8	454.1	448.8	446.1	443.5	438.1	430.1	424.9	416.9
62.5°	406.3	403.6	400.9	398.4	393.0	393.0	387.7	382.4	374.4	369.1	363.7
65°	350.5	350.5	347.9	347.9	345.2	339.9	337.2	334.5	324.0	321.3	310.7
67.5°	300.1	302.8	297.4	297.4	292.1	292.1	289.5	281.5	278.8	273.5	268.1
70°	254.9	254.9	254.9	252.3	246.9	244.3	241.6	236.4	233.7	228.4	223.1
72.5°	209.7	209.7	207.2	207.2	204.5	201.9	199.2	193.9	193.9	188.5	183.2
75°	170.0	170.0	167.3	164.7	162.0	162.0	159.3	156.7	151.3	148.7	146.0
77.5°	130.1	130.1	130.1	127.5	124.8	124.8	124.8	119.5	114.1	114.1	111.6
80°	95.6	95.6	92.9	92.9	90.3	90.3	90.3	87.6	84.9	82.3	79.6
82.5°	63.7	63.7	63.7	63.7	61.1	61.1	61.1	58.4	55.7	55.7	55.7
85°	37.2	37.2	37.2	37.2	34.5	34.5	34.5	34.5	34.5	31.9	31.9
87.5°	16.0	13.3	16.0	13.3	16.0	13.3	16.0	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584727

CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4
2.5°	1890.6	1888.1	1885.4	1882.7	1882.7	1880.1	1874.8	1872.1	1869.4	1866.8	1866.8
5°	1901.3	1898.6	1893.3	1888.1	1885.4	1880.1	1874.8	1869.4	1864.1	1856.2	1853.5
7.5°	1909.3	1901.3	1896.0	1885.4	1882.7	1877.4	1869.4	1861.4	1850.9	1840.2	1832.2
10°	1909.3	1898.6	1890.6	1877.4	1872.1	1866.8	1856.2	1842.9	1829.6	1819.0	1805.7
12.5°	1904.0	1890.6	1877.4	1864.1	1856.2	1848.2	1832.2	1819.0	1803.0	1787.1	1776.5
15°	1885.4	1869.4	1853.5	1837.6	1829.6	1819.0	1803.0	1784.5	1768.5	1752.6	1734.0
17.5°	1850.9	1834.9	1816.4	1797.7	1787.1	1779.2	1755.3	1742.0	1718.1	1702.1	1686.2
20°	1805.7	1787.1	1763.3	1744.6	1731.3	1723.4	1704.8	1680.9	1662.3	1638.4	1622.5
22.5°	1747.3	1723.4	1699.4	1680.9	1667.7	1657.0	1633.1	1609.2	1593.3	1572.1	1553.4
25°	1678.2	1654.4	1630.5	1603.8	1590.6	1580.0	1558.8	1537.5	1516.2	1492.4	1476.5
27.5°	1596.0	1569.4	1548.1	1524.2	1510.9	1495.0	1471.2	1449.8	1428.6	1412.8	1391.4
30°	1505.7	1476.5	1455.2	1431.3	1418.0	1404.8	1380.9	1359.6	1341.0	1322.4	1311.8
32.5°	1396.8	1375.6	1354.2	1330.4	1319.7	1311.8	1288.0	1266.6	1245.4	1229.4	1221.6
35°	1293.2	1269.3	1250.8	1229.4	1216.2	1208.2	1187.0	1168.4	1157.8	1139.2	1128.5
37.5°	1184.4	1165.7	1144.5	1123.3	1115.3	1107.3	1091.4	1072.8	1056.9	1043.6	1038.3
40°	1070.1	1054.2	1035.6	1022.4	1014.4	1006.4	993.2	979.8	969.2	956.0	950.6
42.5°	961.3	950.6	934.8	918.8	910.8	908.1	892.2	881.6	876.3	871.0	865.7
45°	863.0	847.1	836.5	825.8	817.9	812.5	804.6	796.6	791.3	786.0	780.7
47.5°	767.4	754.1	743.6	735.6	727.6	724.9	719.6	711.7	706.4	706.4	706.4
50°	679.8	669.2	658.5	653.2	650.5	645.3	640.0	637.3	634.7	634.7	634.7
52.5°	602.8	592.1	584.2	578.9	578.9	573.6	568.3	565.6	565.6	565.6	565.6
55°	531.1	523.2	517.8	512.5	507.2	504.5	504.5	504.5	501.9	501.9	504.5
57.5°	467.3	462.0	454.1	448.8	446.1	446.1	443.5	440.8	443.5	446.1	448.8
60°	408.9	403.6	400.9	393.0	393.0	393.0	390.4	390.4	390.4	393.0	395.7
62.5°	355.9	353.2	347.9	345.2	342.5	342.5	339.9	339.9	339.9	339.9	342.5
65°	308.0	302.8	297.4	297.4	297.4	294.8	294.8	289.5	292.1	292.1	289.5
67.5°	262.9	257.6	254.9	252.3	249.6	249.6	246.9	244.3	241.6	241.6	241.6
70°	220.4	215.1	215.1	209.7	209.7	207.2	204.5	204.5	201.9	199.2	196.5
72.5°	177.9	175.2	172.5	170.0	170.0	170.0	167.3	164.7	162.0	159.3	154.0
75°	140.8	140.8	135.5	132.8	132.8	130.1	127.5	124.8	122.1	119.5	116.8
77.5°	108.9	106.3	100.9	98.3	98.3	98.3	95.6	92.9	90.3	87.6	84.9
80°	79.6	77.1	74.4	71.7	71.7	71.7	69.1	69.1	66.4	66.4	66.4
82.5°	53.1	53.1	50.4	50.4	50.4	50.4	47.7	47.7	47.7	47.7	47.7
85°	31.9	31.9	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.2
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584727

CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4
2.5°	1861.4	1861.4	1856.2	1853.5	1850.9	1853.5	1848.2	1845.6	1842.9	1842.9	1840.2
5°	1845.6	1842.9	1832.2	1829.6	1826.9	1824.2	1819.0	1813.7	1808.4	1805.7	1803.0
7.5°	1824.2	1816.4	1805.7	1803.0	1800.4	1792.5	1784.5	1779.2	1771.2	1768.5	1763.3
10°	1795.0	1784.5	1776.5	1768.5	1763.3	1755.3	1747.3	1739.3	1728.7	1726.1	1718.1
12.5°	1760.6	1747.3	1731.3	1728.7	1720.8	1710.1	1699.4	1691.6	1683.6	1678.2	1670.2
15°	1718.1	1704.8	1688.9	1680.9	1672.9	1665.0	1651.7	1641.0	1633.1	1625.2	1617.2
17.5°	1667.7	1651.7	1638.4	1630.5	1625.2	1611.8	1601.3	1588.0	1580.0	1572.1	1564.1
20°	1606.5	1593.3	1574.6	1566.8	1564.1	1553.4	1540.1	1534.9	1524.2	1516.2	1510.9
22.5°	1537.5	1524.2	1508.2	1503.0	1492.4	1487.0	1473.8	1468.5	1463.2	1455.2	1452.5
25°	1460.5	1447.2	1434.0	1431.3	1423.3	1418.0	1410.1	1402.1	1402.1	1394.1	1394.1
27.5°	1380.9	1367.6	1356.9	1351.6	1349.0	1343.7	1335.7	1333.0	1330.4	1327.7	1327.7
30°	1295.8	1280.0	1274.6	1272.0	1269.3	1264.0	1261.3	1256.0	1258.6	1261.3	1258.6
32.5°	1205.6	1200.2	1189.7	1184.4	1187.0	1184.4	1179.0	1184.4	1181.7	1187.0	1189.7
35°	1118.0	1112.6	1107.3	1107.3	1102.0	1102.0	1102.0	1104.6	1110.0	1112.6	1118.0
37.5°	1032.9	1025.0	1022.4	1019.7	1022.4	1022.4	1022.4	1027.7	1032.9	1038.3	1046.2
40°	942.7	937.3	937.3	937.3	937.3	945.3	942.7	948.0	953.3	961.3	969.2
42.5°	857.7	857.7	860.4	860.4	860.4	860.4	865.7	873.7	881.6	889.6	897.6
45°	778.1	778.1	778.1	783.3	783.3	786.0	796.6	802.0	807.3	815.2	823.2
47.5°	703.7	703.7	706.4	709.0	711.7	716.9	722.3	730.2	738.2	743.6	751.5
50°	634.7	637.3	642.6	648.0	648.0	650.5	658.5	663.9	669.2	677.2	679.8
52.5°	568.3	573.6	578.9	581.6	584.2	589.5	592.1	600.1	602.8	610.8	613.4
55°	507.2	509.9	517.8	520.5	520.5	525.7	531.1	536.4	544.4	544.4	549.7
57.5°	451.4	454.1	459.3	462.0	459.3	467.3	470.0	475.3	478.0	483.3	486.0
60°	395.7	400.9	403.6	403.6	406.3	408.9	414.3	414.3	419.6	424.9	424.9
62.5°	342.5	345.2	347.9	350.5	353.2	350.5	358.5	358.5	363.7	366.4	371.7
65°	292.1	294.8	294.8	297.4	297.4	300.1	300.1	302.8	305.3	310.7	313.3
67.5°	241.6	241.6	241.6	244.3	241.6	244.3	244.3	246.9	246.9	252.3	254.9
70°	196.5	193.9	191.2	191.2	191.2	191.2	188.5	191.2	191.2	193.9	193.9
72.5°	151.3	148.7	146.0	143.3	143.3	140.8	138.1	140.8	140.8	143.3	143.3
75°	114.1	108.9	108.9	108.9	106.3	106.3	106.3	108.9	108.9	108.9	111.6
77.5°	84.9	84.9	82.3	82.3	82.3	84.9	84.9	87.6	87.6	87.6	87.6
80°	63.7	66.4	66.4	66.4	66.4	69.1	69.1	69.1	69.1	71.7	71.7
82.5°	47.7	47.7	47.7	47.7	50.4	50.4	50.4	50.4	50.4	50.4	50.4
85°	29.2	31.9	31.9	29.2	31.9	31.9	31.9	31.9	31.9	31.9	31.9
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584727

CATALOG NUMBER: HCC8S45D010MB-HM82555927-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4	1869.4
2.5°	1837.6	1837.6	1837.6	1837.6	1834.9	1834.9	1834.9	1832.2
5°	1797.7	1797.7	1797.7	1792.5	1795.0	1795.0	1789.8	1792.5
7.5°	1757.9	1755.3	1752.6	1752.6	1750.0	1747.3	1744.6	1747.3
10°	1712.8	1704.8	1704.8	1702.1	1702.1	1696.9	1696.9	1699.4
12.5°	1662.3	1657.0	1657.0	1654.4	1651.7	1649.0	1646.4	1646.4
15°	1611.8	1606.5	1603.8	1601.3	1598.6	1593.3	1596.0	1593.3
17.5°	1561.4	1553.4	1553.4	1550.8	1548.1	1542.8	1542.8	1540.1
20°	1503.0	1500.4	1495.0	1497.7	1495.0	1489.7	1487.0	1487.0
22.5°	1444.5	1444.5	1442.0	1442.0	1439.3	1436.6	1434.0	1434.0
25°	1388.8	1386.1	1388.8	1388.8	1380.9	1380.9	1380.9	1383.4
27.5°	1325.0	1327.7	1325.0	1325.0	1325.0	1325.0	1327.7	1325.0
30°	1261.3	1261.3	1261.3	1264.0	1269.3	1266.6	1266.6	1264.0
32.5°	1192.4	1194.9	1194.9	1197.6	1200.2	1205.6	1205.6	1208.2
35°	1123.3	1128.5	1131.2	1128.5	1136.5	1136.5	1141.8	1141.8
37.5°	1051.6	1054.2	1059.6	1062.2	1067.5	1070.1	1072.8	1072.8
40°	974.5	985.2	987.8	990.5	998.5	998.5	1001.2	1006.4
42.5°	902.9	913.5	916.1	918.8	924.1	932.1	929.4	934.8
45°	833.8	841.7	844.4	847.1	855.0	857.7	857.7	865.7
47.5°	759.5	764.8	767.4	772.8	778.1	783.3	788.7	786.0
50°	685.1	693.1	698.4	701.0	709.0	711.7	714.4	716.9
52.5°	618.8	624.0	626.7	629.3	637.3	640.0	642.6	648.0
55°	554.9	557.6	562.9	560.3	568.3	570.9	573.6	578.9
57.5°	491.3	494.0	496.5	496.5	501.9	507.2	509.9	512.5
60°	430.1	435.5	438.1	438.1	438.1	443.5	443.5	443.5
62.5°	374.4	374.4	377.1	377.1	382.4	382.4	382.4	382.4
65°	316.0	318.7	321.3	321.3	326.6	324.0	329.3	326.6
67.5°	254.9	254.9	260.3	260.3	257.6	260.3	260.3	260.3
70°	193.9	193.9	196.5	196.5	196.5	196.5	196.5	196.5
72.5°	143.3	143.3	143.3	146.0	143.3	143.3	146.0	143.3
75°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
77.5°	87.6	87.6	90.3	90.3	90.3	90.3	90.3	90.3
80°	71.7	71.7	71.7	71.7	74.4	71.7	71.7	71.7
82.5°	53.1	50.4	53.1	50.4	53.1	53.1	53.1	53.1
85°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)