

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584871

Luminaire Tested: **HCC8S50D010MW-HM82555930-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MW-HM82555930-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4742.5 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584871  
CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	76946	76946	76946
5°	77964	76624	75903
10°	78759	75841	74695
15°	79558	74239	72749
20°	79154	71501	69861
25°	77310	67218	66313
30°	73428	62397	62162
35°	66845	56941	57441
40°	58606	50962	52841
45°	50560	45332	48528
50°	44269	39793	43948
55°	39224	34208	38687
60°	35338	28764	32051
65°	31842	23086	24545
70°	27931	16824	13515
75°	23817	8733	3562
80°	18326	2362	586
85°	11782	0	0



TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.4	5.0
10°-20°	661.9	14.0
20°-30°	939.4	19.8
30°-40°	988.9	20.9
40°-50°	841.2	17.7
50°-60°	607.9	12.8
60°-70°	345.7	7.3
70°-80°	108.9	2.3
80°-90°	13.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1836.7	38.7
0°-40°	2825.6	59.6
0°-60°	4274.7	90.1
0°-90°	4742.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4742.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2495	2495	2495	2495	2495	
5°	2519	2505	2475	2459	2452	240
15°	2492	2429	2326	2282	2279	702
25°	2272	2159	1976	1942	1949	1041
35°	1776	1672	1513	1502	1526	1105
45°	1159	1116	1040	1066	1113	901
55°	730	676	636	673	720	658
65°	436	376	316	313	336	433
75°	200	153	73	33	30	215
85°	33	20	0	0	0	43
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3
2.5°	2508.7	2512.1	2505.4	2505.4	2512.1	2505.4	2508.7	2508.7	2505.4	2505.4	2502.0
5°	2518.7	2515.3	2515.3	2515.3	2518.7	2512.1	2508.7	2512.1	2505.4	2505.4	2505.4
7.5°	2522.0	2522.0	2518.7	2515.3	2515.3	2515.3	2512.1	2508.7	2505.4	2498.7	2495.3
10°	2515.3	2515.3	2518.7	2512.1	2512.1	2505.4	2505.4	2498.7	2498.7	2492.1	2482.0
12.5°	2508.7	2505.4	2505.4	2498.7	2498.7	2492.1	2492.1	2482.0	2478.7	2468.7	2458.8
15°	2492.1	2488.7	2482.0	2478.7	2475.4	2472.1	2465.4	2462.0	2452.1	2438.8	2428.7
17.5°	2458.8	2455.4	2452.1	2445.4	2438.8	2435.4	2432.1	2422.1	2408.7	2398.8	2382.1
20°	2412.1	2408.7	2408.7	2398.8	2395.4	2385.5	2382.1	2368.7	2358.8	2338.8	2325.5
22.5°	2348.8	2352.1	2345.5	2338.8	2332.2	2322.1	2315.4	2302.1	2285.5	2265.5	2248.8
25°	2272.2	2275.5	2268.8	2262.1	2252.2	2245.5	2238.9	2218.9	2202.2	2178.9	2158.9
27.5°	2175.5	2175.5	2175.5	2168.8	2152.2	2148.9	2142.2	2122.2	2098.9	2078.9	2059.0
30°	2062.2	2059.0	2059.0	2048.9	2042.2	2028.9	2019.0	2002.3	1985.7	1962.3	1939.0
32.5°	1925.7	1929.0	1919.0	1912.4	1902.3	1902.3	1889.0	1875.7	1855.7	1832.4	1809.0
35°	1775.7	1779.1	1772.4	1769.0	1752.4	1749.1	1745.8	1729.1	1715.7	1699.1	1672.5
37.5°	1622.5	1619.2	1615.8	1615.8	1605.9	1599.2	1592.5	1582.5	1562.5	1549.2	1535.8
40°	1455.9	1455.9	1455.9	1452.6	1449.2	1442.5	1439.3	1432.6	1419.3	1406.0	1395.9
42.5°	1306.0	1306.0	1302.6	1299.3	1292.7	1296.0	1289.3	1282.6	1269.3	1259.4	1252.7
45°	1159.4	1159.4	1159.4	1162.7	1156.0	1146.1	1146.1	1139.4	1132.8	1126.1	1116.0
47.5°	1029.4	1039.5	1032.8	1029.4	1032.8	1019.5	1019.5	1012.8	1006.2	999.5	986.2
50°	922.8	922.8	922.8	916.1	912.9	912.9	902.8	896.2	892.9	886.2	872.9
52.5°	826.2	819.6	819.6	816.2	812.9	806.3	806.3	799.6	786.3	779.6	769.6
55°	729.6	729.6	726.3	722.9	719.6	716.2	713.0	702.9	696.3	686.3	676.3
57.5°	643.0	649.6	646.3	639.7	633.0	633.0	626.4	619.7	609.6	599.7	589.6
60°	573.0	569.7	569.7	566.4	559.7	556.3	553.1	543.0	533.1	523.0	513.1
62.5°	499.7	499.7	499.7	493.1	486.4	483.0	479.8	473.1	459.8	449.7	443.1
65°	436.4	433.1	429.7	426.5	423.1	416.4	413.1	406.5	396.4	386.5	376.4
67.5°	373.1	369.8	369.8	366.5	356.4	353.2	353.2	343.1	333.2	323.1	313.2
70°	309.8	309.8	309.8	303.1	299.8	296.5	293.2	286.5	276.5	266.5	256.5
72.5°	256.5	253.2	253.2	249.8	239.9	236.5	233.2	226.6	216.5	209.8	203.2
75°	199.9	199.9	196.5	193.2	189.8	186.6	183.2	176.5	166.6	156.5	153.3
77.5°	153.3	149.9	149.9	146.6	139.9	136.5	136.5	129.9	119.9	113.3	106.6
80°	103.2	106.6	103.2	99.9	96.6	93.3	89.9	86.6	80.0	73.3	66.6
82.5°	63.2	66.6	63.2	63.2	60.0	56.6	56.6	49.9	46.6	43.3	40.0
85°	33.3	33.3	33.3	33.3	29.9	29.9	29.9	26.7	23.3	20.0	20.0
87.5°	9.9	13.3	9.9	9.9	9.9	9.9	9.9	9.9	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3
2.5°	2505.4	2502.0	2498.7	2498.7	2498.7	2498.7	2498.7	2495.3	2492.1	2492.1	2492.1
5°	2498.7	2498.7	2498.7	2495.3	2492.1	2492.1	2485.4	2482.0	2478.7	2475.4	2472.1
7.5°	2492.1	2485.4	2482.0	2478.7	2475.4	2475.4	2468.7	2462.0	2462.0	2455.4	2448.7
10°	2472.1	2468.7	2462.0	2455.4	2452.1	2448.7	2442.0	2432.1	2428.7	2422.1	2415.4
12.5°	2448.7	2442.0	2435.4	2422.1	2418.8	2415.4	2402.1	2392.1	2385.5	2382.1	2365.5
15°	2418.8	2405.5	2395.4	2378.8	2375.4	2368.7	2358.8	2348.8	2335.4	2325.5	2318.8
17.5°	2365.5	2352.1	2335.4	2318.8	2312.2	2312.2	2295.4	2282.1	2265.5	2258.9	2245.5
20°	2302.1	2285.5	2272.2	2252.2	2242.1	2232.2	2222.2	2202.2	2188.8	2178.9	2162.2
22.5°	2228.8	2205.6	2188.8	2168.8	2152.2	2142.2	2125.6	2108.9	2092.3	2082.2	2068.9
25°	2135.5	2115.5	2088.9	2068.9	2059.0	2045.6	2025.6	2008.9	1992.3	1975.6	1968.9
27.5°	2032.3	2005.7	1982.3	1959.0	1949.0	1939.0	1915.6	1895.7	1882.3	1865.7	1859.1
30°	1919.0	1892.4	1865.7	1845.7	1835.7	1819.1	1805.8	1782.4	1765.8	1752.4	1735.7
32.5°	1789.0	1769.0	1745.8	1715.7	1709.1	1695.8	1675.8	1665.8	1645.8	1635.8	1622.5
35°	1649.1	1635.8	1612.5	1589.1	1579.2	1572.5	1555.8	1535.8	1522.5	1512.6	1505.9
37.5°	1515.8	1499.2	1475.9	1459.3	1452.6	1442.5	1422.6	1412.6	1399.3	1392.6	1379.3
40°	1372.6	1355.9	1339.3	1329.3	1319.3	1312.7	1299.3	1289.3	1276.0	1266.0	1262.6
42.5°	1232.7	1222.7	1209.3	1196.0	1192.7	1182.7	1176.0	1166.1	1156.0	1152.8	1142.7
45°	1106.1	1096.1	1082.7	1069.4	1066.1	1059.5	1056.1	1046.1	1039.5	1039.5	1039.5
47.5°	979.5	969.5	956.1	949.5	952.9	939.5	939.5	936.1	929.5	929.5	932.9
50°	866.2	852.9	849.5	842.8	836.2	829.5	832.9	822.9	822.9	829.5	826.2
52.5°	759.6	746.3	742.9	736.2	733.0	733.0	729.6	729.6	726.3	729.6	729.6
55°	662.9	653.0	646.3	639.7	636.3	636.3	636.3	633.0	629.6	636.3	639.7
57.5°	576.3	573.0	566.4	556.3	553.1	549.7	546.4	546.4	546.4	546.4	549.7
60°	499.7	493.1	486.4	476.4	476.4	473.1	469.7	466.4	466.4	466.4	466.4
62.5°	433.1	423.1	413.1	406.5	403.1	399.8	396.4	389.7	389.7	389.7	389.7
65°	366.5	356.4	349.8	343.1	336.4	336.4	329.8	326.5	319.8	316.4	309.8
67.5°	303.1	296.5	289.8	279.9	276.5	273.2	266.5	263.1	253.2	249.8	246.5
70°	246.5	236.5	229.8	223.2	219.9	213.2	206.6	199.9	193.2	186.6	179.9
72.5°	193.2	183.2	176.5	169.9	163.2	163.2	153.3	146.6	136.5	129.9	119.9
75°	143.2	133.3	126.6	116.5	113.3	109.9	99.9	93.3	83.2	73.3	66.6
77.5°	96.6	89.9	83.2	73.3	66.6	66.6	56.6	49.9	43.3	33.3	29.9
80°	60.0	53.3	46.6	40.0	40.0	33.3	29.9	23.3	16.6	13.3	9.9
82.5°	33.3	29.9	26.7	20.0	20.0	16.6	13.3	9.9	6.7	3.3	3.3
85°	16.6	13.3	9.9	9.9	6.7	6.7	6.7	3.3	3.3	0.0	0.0
87.5°	6.7	3.3	3.3	3.3	3.3	3.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3
2.5°	2488.7	2488.7	2485.4	2485.4	2485.4	2482.0	2485.4	2482.0	2482.0	2482.0	2485.4
5°	2475.4	2468.7	2468.7	2465.4	2465.4	2462.0	2465.4	2462.0	2458.8	2455.4	2458.8
7.5°	2448.7	2442.0	2438.8	2435.4	2435.4	2435.4	2432.1	2428.7	2432.1	2422.1	2428.7
10°	2412.1	2408.7	2402.1	2398.8	2395.4	2398.8	2395.4	2388.7	2388.7	2388.7	2385.5
12.5°	2365.5	2358.8	2355.4	2352.1	2345.5	2345.5	2348.8	2342.1	2342.1	2335.4	2335.4
15°	2308.8	2302.1	2295.4	2295.4	2288.8	2288.8	2285.5	2285.5	2282.1	2278.8	2278.8
17.5°	2238.9	2228.8	2222.2	2225.5	2222.2	2218.9	2218.9	2212.2	2208.8	2212.2	2212.2
20°	2155.5	2148.9	2142.2	2145.6	2138.9	2135.5	2138.9	2128.9	2132.3	2132.3	2132.3
22.5°	2062.2	2059.0	2048.9	2048.9	2042.2	2039.0	2042.2	2042.2	2045.6	2042.2	2042.2
25°	1959.0	1952.3	1945.7	1945.7	1942.3	1939.0	1942.3	1945.7	1942.3	1945.7	1945.7
27.5°	1849.0	1839.1	1839.1	1832.4	1832.4	1835.7	1832.4	1835.7	1839.1	1839.1	1845.7
30°	1729.1	1725.8	1722.4	1719.1	1719.1	1722.4	1722.4	1722.4	1725.8	1732.5	1732.5
32.5°	1615.8	1609.1	1602.5	1602.5	1609.1	1605.9	1609.1	1609.1	1615.8	1615.8	1622.5
35°	1492.6	1492.6	1485.9	1489.2	1489.2	1489.2	1489.2	1495.9	1502.5	1505.9	1512.6
37.5°	1379.3	1369.2	1372.6	1372.6	1375.9	1372.6	1382.6	1382.6	1389.2	1389.2	1395.9
40°	1256.0	1256.0	1259.4	1256.0	1259.4	1259.4	1266.0	1272.7	1276.0	1282.6	1286.0
42.5°	1139.4	1146.1	1139.4	1142.7	1146.1	1149.4	1152.8	1156.0	1169.4	1176.0	1186.1
45°	1032.8	1036.1	1039.5	1042.7	1039.5	1046.1	1049.4	1056.1	1066.1	1069.4	1072.8
47.5°	929.5	932.9	936.1	939.5	939.5	946.2	949.5	956.1	962.8	966.2	969.5
50°	829.5	836.2	839.6	839.6	842.8	849.5	856.2	856.2	862.8	872.9	876.2
52.5°	739.6	739.6	746.3	749.6	753.0	753.0	762.9	766.3	769.6	776.2	782.9
55°	639.7	649.6	653.0	653.0	659.7	666.3	669.6	673.0	673.0	686.3	686.3
57.5°	553.1	556.3	563.0	563.0	563.0	573.0	573.0	579.7	583.0	586.4	593.0
60°	466.4	473.1	473.1	476.4	473.1	479.8	483.0	489.7	493.1	496.4	499.7
62.5°	386.5	386.5	389.7	389.7	389.7	389.7	396.4	396.4	403.1	406.5	409.7
65°	309.8	309.8	309.8	309.8	309.8	309.8	309.8	309.8	313.2	313.2	319.8
67.5°	239.9	236.5	229.8	233.2	229.8	229.8	226.6	226.6	229.8	229.8	236.5
70°	173.2	169.9	163.2	163.2	159.9	156.5	153.3	149.9	146.6	146.6	146.6
72.5°	113.3	106.6	96.6	93.3	93.3	86.6	80.0	76.6	76.6	76.6	76.6
75°	56.6	49.9	43.3	40.0	40.0	33.3	36.6	33.3	33.3	33.3	33.3
77.5°	23.3	16.6	13.3	13.3	13.3	9.9	9.9	9.9	9.9	9.9	9.9
80°	6.7	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P584871

CATALOG NUMBER: HCC8S50D010MW-HM82555930-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3	2495.3
2.5°	2482.0	2482.0	2475.4	2478.7	2478.7	2478.7	2478.7	2478.7
5°	2452.1	2455.4	2452.1	2455.4	2455.4	2452.1	2452.1	2452.1
7.5°	2422.1	2425.4	2422.1	2425.4	2425.4	2425.4	2422.1	2422.1
10°	2385.5	2385.5	2385.5	2385.5	2385.5	2382.1	2385.5	2385.5
12.5°	2335.4	2335.4	2335.4	2338.8	2338.8	2335.4	2335.4	2332.2
15°	2282.1	2275.5	2278.8	2282.1	2278.8	2278.8	2278.8	2278.8
17.5°	2208.8	2212.2	2208.8	2208.8	2208.8	2208.8	2212.2	2208.8
20°	2132.3	2132.3	2135.5	2132.3	2132.3	2132.3	2132.3	2128.9
22.5°	2045.6	2042.2	2042.2	2045.6	2045.6	2042.2	2045.6	2045.6
25°	1949.0	1952.3	1949.0	1949.0	1952.3	1952.3	1952.3	1949.0
27.5°	1845.7	1849.0	1852.4	1849.0	1849.0	1849.0	1852.4	1855.7
30°	1739.1	1745.8	1739.1	1739.1	1745.8	1742.4	1745.8	1745.8
32.5°	1625.8	1635.8	1629.1	1635.8	1635.8	1639.2	1635.8	1639.2
35°	1512.6	1522.5	1522.5	1522.5	1525.9	1529.2	1529.2	1525.9
37.5°	1406.0	1409.2	1409.2	1415.9	1419.3	1422.6	1422.6	1419.3
40°	1296.0	1302.6	1306.0	1306.0	1306.0	1312.7	1319.3	1312.7
42.5°	1189.3	1192.7	1196.0	1196.0	1202.7	1206.1	1209.3	1209.3
45°	1086.1	1092.8	1096.1	1099.4	1102.7	1109.4	1106.1	1112.8
47.5°	979.5	989.4	992.8	996.1	1002.8	1006.2	1009.4	1012.8
50°	882.8	889.5	889.5	896.2	906.2	906.2	912.9	916.1
52.5°	786.3	789.5	792.9	796.2	802.9	809.5	809.5	816.2
55°	693.0	696.3	696.3	699.6	702.9	716.2	719.6	719.6
57.5°	596.3	596.3	603.0	606.4	609.6	616.3	616.3	616.3
60°	503.0	506.4	506.4	509.7	513.1	519.7	523.0	519.7
62.5°	409.7	413.1	413.1	416.4	423.1	426.5	423.1	423.1
65°	323.1	326.5	326.5	329.8	336.4	336.4	333.2	336.4
67.5°	236.5	236.5	236.5	236.5	236.5	236.5	236.5	236.5
70°	149.9	146.6	143.2	146.6	146.6	146.6	143.2	149.9
72.5°	73.3	76.6	76.6	76.6	76.6	76.6	76.6	73.3
75°	33.3	33.3	29.9	29.9	29.9	33.3	33.3	29.9
77.5°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
80°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)