

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584723

Luminaire Tested: **HCC8S45D010SL-HM82555927-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010SL-HM82555927-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4078.6 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584723
CATALOG NUMBER: HCC8S45D010SL-HM82555927-81WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584723

CATALOG NUMBER: HCC8S45D010SL-HM82555927-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81540
5°	81437
10°	80635
15°	79670
20°	78934
25°	78044
30°	73638
35°	59963
40°	33129
45°	22114
50°	19616
55°	18413
60°	18175
65°	18015
70°	16274
75°	14547
80°	12732
85°	11286



TEST NUMBER: P584723
 CATALOG NUMBER: HCC8S45D010SL-HM82555927-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.4	6.1
10°-20°	704.7	17.3
20°-30°	1047.0	25.7
30°-40°	942.9	23.1
40°-50°	418.0	10.2
50°-60°	309.6	7.6
60°-70°	240.7	5.9
70°-80°	130.5	3.2
80°-90°	35.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2001.0	49.1
0°-40°	2944.0	72.2
0°-60°	3671.6	90.0
0°-90°	4078.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4078.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2644	
5°	2631	249
15°	2496	705
25°	2294	1047
35°	1593	943
45°	507	418
55°	342	310
65°	247	241
75°	122	131
85°	32	36
90°	0	



TEST NUMBER: P584723

CATALOG NUMBER: HCC8S45D010SL-HM82555927-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2644.3
2.5°	2638.9
5°	2630.9
7.5°	2609.7
10°	2575.2
12.5°	2535.4
15°	2495.6
17.5°	2455.8
20°	2405.4
22.5°	2354.9
25°	2293.8
27.5°	2200.9
30°	2068.1
32.5°	1877.0
35°	1592.9
37.5°	1189.4
40°	823.0
42.5°	608.0
45°	507.1
47.5°	448.7
50°	408.9
52.5°	371.7
55°	342.5
57.5°	318.6
60°	294.7
62.5°	273.4
65°	246.9
67.5°	215.0
70°	180.5
72.5°	151.3
75°	122.1
77.5°	95.6
80°	71.7
82.5°	50.4
85°	31.9
87.5°	13.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)