

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584884

Luminaire Tested: **HCC8S50D010MB-HM82555935-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584884  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MB-HM82555935-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4972.6 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584884  
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584884  
 CATALOG NUMBER: HCC8S50D010MB-HM82555935-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96																												
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																												
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87																												
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83																												
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80																												
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76																												
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73																												
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71																												
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68																												
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	935916
5°	600318
10°	271187
15°	163627
20°	124688
25°	100691
30°	73788
35°	26716
40°	9971
45°	4527
50°	1449
55°	360
60°	210
65°	248
70°	0
75°	0
80°	604
85°	1203



TEST NUMBER: P584884  
 CATALOG NUMBER: HCC8S50D010MB-HM82555935-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1479.1	29.7
10°-20°	1502.4	30.2
20°-30°	1344.9	27.0
30°-40°	541.7	10.9
40°-50°	88.8	1.8
50°-60°	8.1	0.2
60°-70°	2.9	0.1
70°-80°	2.3	0.0
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4326.4	87.0
0°-40°	4868.1	97.9
0°-60°	4965.1	99.8
0°-90°	4973.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4972.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	30351	
5°	19394	###
15°	5126	1502
25°	2959	1345
35°	710	542
45°	104	89
55°	7	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584884  
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	30351.1
0.5°	30257.3
1°	29865.7
1.5°	29236.3
2°	28282.2
2.5°	27154.0
3°	25741.1
3.5°	24191.2
4°	22657.9
4.5°	20940.4
5°	19393.8
5.5°	17709.9
6°	16343.9
6.5°	14921.1
7°	13803.0
7.5°	12621.2
8°	11670.4
8.5°	10716.3
9°	9999.9
9.5°	9209.7
10°	8660.8
12.5°	6387.6
15°	5125.5
17.5°	4379.0
20°	3799.7
22.5°	3337.7
25°	2959.4
27.5°	2581.2
30°	2072.3
32.5°	1332.4
35°	709.7
37.5°	391.7
40°	247.7
42.5°	164.0
45°	103.8
47.5°	63.6
50°	30.2
52.5°	10.1
55°	6.7
57.5°	3.4
60°	3.4
62.5°	3.4
65°	3.4



TEST NUMBER: P584884  
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	3.4
80°	3.4
82.5°	3.4
85°	3.4
87.5°	3.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.4
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)