

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584888

Luminaire Tested: **HCC8S50D010MB-HM82555935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010MB-HM82555935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4768.2 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584888
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584888

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	77362	77362	77362
5°	78385	77035	76311
10°	79185	76248	75096
15°	79986	74639	73141
20°	79580	71885	70238
25°	77728	67579	66670
30°	73823	62735	62493
35°	67206	57249	57750
40°	58924	51235	53123
45°	50831	45576	48786
50°	44509	40014	44193
55°	39434	34397	38896
60°	35530	28918	32224
65°	32017	23217	24684
70°	28085	16914	13587
75°	23948	8769	3598
80°	18433	2380	604
85°	11888	0	0



TEST NUMBER: P584888
 CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.7	5.0
10°-20°	665.4	14.0
20°-30°	944.5	19.8
30°-40°	994.2	20.9
40°-50°	845.8	17.7
50°-60°	611.2	12.8
60°-70°	347.6	7.3
70°-80°	109.5	2.3
80°-90°	13.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.6	38.7
0°-40°	2840.8	59.6
0°-60°	4297.7	90.1
0°-90°	4768.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4768.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2509	2509	2509	2509	2509	
5°	2532	2519	2489	2472	2465	242
15°	2506	2442	2338	2294	2291	706
25°	2284	2170	1986	1953	1960	1046
35°	1785	1682	1521	1511	1534	1111
45°	1166	1122	1045	1072	1119	906
55°	734	680	640	677	724	661
65°	439	378	318	315	338	435
75°	201	154	74	34	30	216
85°	34	20	0	0	0	43
90°	0	0	0	0	0	



TEST NUMBER: P584888

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8
2.5°	2522.2	2525.6	2518.8	2518.8	2525.6	2518.8	2522.2	2522.2	2518.8	2518.8	2515.6
5°	2532.3	2528.9	2528.9	2528.9	2532.3	2525.6	2522.2	2525.6	2518.8	2518.8	2518.8
7.5°	2535.7	2535.7	2532.3	2528.9	2528.9	2528.9	2525.6	2522.2	2518.8	2512.2	2508.8
10°	2528.9	2528.9	2532.3	2525.6	2525.6	2518.8	2518.8	2512.2	2512.2	2505.5	2495.5
12.5°	2522.2	2518.8	2518.8	2512.2	2512.2	2505.5	2505.5	2495.5	2492.1	2482.0	2472.0
15°	2505.5	2502.1	2495.5	2492.1	2488.7	2485.4	2478.7	2475.4	2465.3	2451.9	2441.8
17.5°	2472.0	2468.7	2465.3	2458.6	2451.9	2448.6	2445.2	2435.1	2421.7	2411.6	2394.9
20°	2425.1	2421.7	2421.7	2411.6	2408.4	2398.3	2394.9	2381.6	2371.6	2351.4	2338.0
22.5°	2361.5	2364.8	2358.1	2351.4	2344.7	2334.6	2327.9	2314.5	2297.8	2277.7	2261.0
25°	2284.5	2287.7	2281.1	2274.4	2264.4	2257.6	2250.9	2230.8	2214.1	2190.6	2170.5
27.5°	2187.3	2187.3	2187.3	2180.5	2163.8	2160.4	2153.8	2133.7	2110.3	2090.2	2070.1
30°	2073.3	2070.1	2070.1	2060.0	2053.3	2039.9	2029.9	2013.1	1996.3	1972.9	1949.4
32.5°	1936.1	1939.4	1929.3	1922.7	1912.6	1912.6	1899.2	1885.8	1865.7	1842.2	1818.8
35°	1785.3	1788.7	1782.0	1778.6	1761.9	1758.5	1755.1	1738.4	1725.0	1708.3	1681.5
37.5°	1631.2	1627.9	1624.6	1624.6	1614.5	1607.8	1601.1	1591.0	1570.9	1557.6	1544.1
40°	1463.8	1463.8	1463.8	1460.4	1457.0	1450.4	1447.0	1440.3	1426.9	1413.6	1403.5
42.5°	1313.0	1313.0	1309.6	1306.4	1299.7	1303.0	1296.3	1289.6	1276.2	1266.1	1259.5
45°	1165.6	1165.6	1165.6	1169.0	1162.3	1152.3	1152.3	1145.5	1138.8	1132.2	1122.1
47.5°	1035.0	1045.1	1038.4	1035.0	1038.4	1025.0	1025.0	1018.3	1011.5	1004.9	991.4
50°	927.8	927.8	927.8	921.2	917.8	917.8	907.7	901.1	897.7	891.0	877.6
52.5°	830.7	824.0	824.0	820.6	817.2	810.6	810.6	803.9	790.5	783.8	773.8
55°	733.5	733.5	730.2	726.9	723.5	720.1	716.8	706.8	700.1	690.1	680.0
57.5°	646.5	653.1	649.8	643.1	636.4	636.4	629.7	623.1	613.0	603.0	592.9
60°	576.1	572.8	572.8	569.4	562.8	559.4	556.0	546.0	536.0	525.9	515.9
62.5°	502.4	502.4	502.4	495.8	489.0	485.7	482.3	475.7	462.2	452.2	445.5
65°	438.8	435.5	432.1	428.8	425.4	418.7	415.3	408.7	398.6	388.6	378.5
67.5°	375.1	371.9	371.9	368.5	358.4	355.0	355.0	345.0	334.9	324.9	314.8
70°	311.5	311.5	311.5	304.8	301.5	298.1	294.7	288.0	278.0	267.9	257.9
72.5°	257.9	254.6	254.6	251.2	241.2	237.8	234.5	227.7	217.7	211.0	204.3
75°	201.0	201.0	197.7	194.3	190.9	187.6	184.2	177.6	167.5	157.5	154.1
77.5°	154.1	150.7	150.7	147.4	140.6	137.4	137.4	130.6	120.6	113.9	107.2
80°	103.8	107.2	103.8	100.5	97.1	93.8	90.5	87.1	80.4	73.6	67.0
82.5°	63.6	67.0	63.6	63.6	60.3	56.9	56.9	50.3	46.9	43.5	40.2
85°	33.6	33.6	33.6	33.6	30.2	30.2	30.2	26.8	23.5	20.1	20.1
87.5°	10.1	13.4	10.1	10.1	10.1	10.1	10.1	10.1	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584888

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8
2.5°	2518.8	2515.6	2512.2	2512.2	2512.2	2512.2	2512.2	2508.8	2505.5	2505.5	2505.5
5°	2512.2	2512.2	2512.2	2508.8	2505.5	2505.5	2498.7	2495.5	2492.1	2488.7	2485.4
7.5°	2505.5	2498.7	2495.5	2492.1	2488.7	2488.7	2482.0	2475.4	2475.4	2468.7	2461.9
10°	2485.4	2482.0	2475.4	2468.7	2465.3	2461.9	2455.3	2445.2	2441.8	2435.1	2428.5
12.5°	2461.9	2455.3	2448.6	2435.1	2431.8	2428.5	2415.0	2405.0	2398.3	2394.9	2378.2
15°	2431.8	2418.4	2408.4	2391.7	2388.3	2381.6	2371.6	2361.5	2348.1	2338.0	2331.3
17.5°	2378.2	2364.8	2348.1	2331.3	2324.6	2324.6	2307.8	2294.5	2277.7	2271.0	2257.6
20°	2314.5	2297.8	2284.5	2264.4	2254.3	2244.2	2234.2	2214.1	2200.6	2190.6	2173.9
22.5°	2240.9	2217.5	2200.6	2180.5	2163.8	2153.8	2137.0	2120.3	2103.5	2093.4	2080.1
25°	2147.1	2127.0	2100.2	2080.1	2070.1	2056.6	2036.5	2019.8	2003.1	1986.2	1979.6
27.5°	2043.3	2016.4	1993.0	1969.5	1959.5	1949.4	1926.0	1905.9	1892.5	1875.8	1869.1
30°	1929.3	1902.5	1875.8	1855.7	1845.6	1828.9	1815.5	1792.1	1775.2	1761.9	1745.1
32.5°	1798.7	1778.6	1755.1	1725.0	1718.3	1705.0	1684.9	1674.8	1654.7	1644.7	1631.2
35°	1658.0	1644.7	1621.2	1597.8	1587.7	1581.0	1564.2	1544.1	1530.8	1520.8	1514.0
37.5°	1524.0	1507.3	1483.8	1467.1	1460.4	1450.4	1430.3	1420.2	1406.8	1400.1	1386.8
40°	1380.0	1363.3	1346.6	1336.5	1326.5	1319.7	1306.4	1296.3	1282.9	1272.8	1269.5
42.5°	1239.4	1229.3	1215.9	1202.6	1199.2	1189.1	1182.4	1172.4	1162.3	1158.9	1148.9
45°	1112.1	1102.0	1088.6	1075.2	1071.9	1065.2	1061.8	1051.7	1045.1	1045.1	1045.1
47.5°	984.8	974.7	961.4	954.6	958.0	944.6	944.6	941.3	934.5	934.5	937.9
50°	870.9	857.5	854.2	847.4	840.7	834.1	837.4	827.3	827.3	834.1	830.7
52.5°	763.7	750.3	747.0	740.2	736.9	736.9	733.5	733.5	730.2	733.5	733.5
55°	666.6	656.5	649.8	643.1	639.8	639.8	639.8	636.4	633.0	639.8	643.1
57.5°	579.5	576.1	569.4	559.4	556.0	552.7	549.3	549.3	549.3	549.3	552.7
60°	502.4	495.8	489.0	478.9	478.9	475.7	472.3	468.9	468.9	468.9	468.9
62.5°	435.5	425.4	415.3	408.7	405.3	401.9	398.6	391.8	391.8	391.8	391.8
65°	368.5	358.4	351.8	345.0	338.3	338.3	331.6	328.3	321.6	318.2	311.5
67.5°	304.8	298.1	291.4	281.4	278.0	274.7	267.9	264.7	254.6	251.2	247.8
70°	247.8	237.8	231.1	224.4	221.1	214.4	207.7	201.0	194.3	187.6	180.8
72.5°	194.3	184.2	177.6	170.8	164.1	164.1	154.1	147.4	137.4	130.6	120.6
75°	144.0	134.0	127.3	117.3	113.9	110.6	100.5	93.8	83.7	73.6	67.0
77.5°	97.1	90.5	83.7	73.6	67.0	67.0	56.9	50.3	43.5	33.6	30.2
80°	60.3	53.5	46.9	40.2	40.2	33.6	30.2	23.5	16.7	13.4	10.1
82.5°	33.6	30.2	26.8	20.1	20.1	16.7	13.4	10.1	6.7	3.4	3.4
85°	16.7	13.4	10.1	10.1	6.7	6.7	6.7	3.4	3.4	0.0	0.0
87.5°	6.7	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584888

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8
2.5°	2502.1	2502.1	2498.7	2498.7	2498.7	2495.5	2498.7	2495.5	2495.5	2495.5	2498.7
5°	2488.7	2482.0	2482.0	2478.7	2478.7	2475.4	2478.7	2475.4	2472.0	2468.7	2472.0
7.5°	2461.9	2455.3	2451.9	2448.6	2448.6	2448.6	2445.2	2441.8	2445.2	2435.1	2441.8
10°	2425.1	2421.7	2415.0	2411.6	2408.4	2411.6	2408.4	2401.6	2401.6	2401.6	2398.3
12.5°	2378.2	2371.6	2368.2	2364.8	2358.1	2358.1	2361.5	2354.7	2354.7	2348.1	2348.1
15°	2321.3	2314.5	2307.8	2307.8	2301.2	2301.2	2297.8	2297.8	2294.5	2291.1	2291.1
17.5°	2250.9	2240.9	2234.2	2237.5	2234.2	2230.8	2230.8	2224.1	2220.7	2224.1	2224.1
20°	2167.2	2160.4	2153.8	2157.2	2150.4	2147.1	2150.4	2140.4	2143.7	2143.7	2143.7
22.5°	2073.3	2070.1	2060.0	2060.0	2053.3	2050.0	2053.3	2053.3	2056.6	2053.3	2053.3
25°	1969.5	1962.9	1956.2	1956.2	1952.8	1949.4	1952.8	1956.2	1952.8	1956.2	1956.2
27.5°	1859.1	1849.0	1849.0	1842.2	1842.2	1845.6	1842.2	1845.6	1849.0	1849.0	1855.7
30°	1738.4	1735.0	1731.8	1728.4	1728.4	1731.8	1731.8	1731.8	1735.0	1741.8	1741.8
32.5°	1624.6	1617.9	1611.1	1611.1	1617.9	1614.5	1617.9	1617.9	1624.6	1624.6	1631.2
35°	1500.6	1500.6	1493.9	1497.3	1497.3	1497.3	1497.3	1503.9	1510.7	1514.0	1520.8
37.5°	1386.8	1376.7	1380.0	1380.0	1383.4	1380.0	1390.1	1390.1	1396.7	1396.7	1403.5
40°	1262.8	1262.8	1266.1	1262.8	1266.1	1266.1	1272.8	1279.6	1282.9	1289.6	1292.9
42.5°	1145.5	1152.3	1145.5	1148.9	1152.3	1155.6	1158.9	1162.3	1175.7	1182.4	1192.5
45°	1038.4	1041.7	1045.1	1048.5	1045.1	1051.7	1055.1	1061.8	1071.9	1075.2	1078.5
47.5°	934.5	937.9	941.3	944.6	944.6	951.3	954.6	961.4	968.0	971.3	974.7
50°	834.1	840.7	844.1	844.1	847.4	854.2	860.9	860.9	867.5	877.6	881.0
52.5°	743.6	743.6	750.3	753.7	757.0	757.0	767.1	770.4	773.8	780.4	787.2
55°	643.1	653.1	656.5	656.5	663.2	670.0	673.2	676.6	676.6	690.1	690.1
57.5°	556.0	559.4	566.0	566.0	566.0	576.1	576.1	582.9	586.1	589.5	596.2
60°	468.9	475.7	475.7	478.9	475.7	482.3	485.7	492.4	495.8	499.0	502.4
62.5°	388.6	388.6	391.8	391.8	391.8	391.8	398.6	398.6	405.3	408.7	412.0
65°	311.5	311.5	311.5	311.5	311.5	311.5	311.5	311.5	314.8	314.8	321.6
67.5°	241.2	237.8	231.1	234.5	231.1	231.1	227.7	227.7	231.1	231.1	237.8
70°	174.2	170.8	164.1	164.1	160.7	157.5	154.1	150.7	147.4	147.4	147.4
72.5°	113.9	107.2	97.1	93.8	93.8	87.1	80.4	77.0	77.0	77.0	77.0
75°	56.9	50.3	43.5	40.2	40.2	33.6	36.8	33.6	33.6	33.6	33.6
77.5°	23.5	16.7	13.4	13.4	13.4	10.1	10.1	10.1	10.1	10.1	10.1
80°	6.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584888

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8	2508.8
2.5°	2495.5	2495.5	2488.7	2492.1	2492.1	2492.1	2492.1	2492.1
5°	2465.3	2468.7	2465.3	2468.7	2468.7	2465.3	2465.3	2465.3
7.5°	2435.1	2438.5	2435.1	2438.5	2438.5	2438.5	2435.1	2435.1
10°	2398.3	2398.3	2398.3	2398.3	2398.3	2394.9	2398.3	2398.3
12.5°	2348.1	2348.1	2348.1	2351.4	2351.4	2348.1	2348.1	2344.7
15°	2294.5	2287.7	2291.1	2294.5	2291.1	2291.1	2291.1	2291.1
17.5°	2220.7	2224.1	2220.7	2220.7	2220.7	2220.7	2224.1	2220.7
20°	2143.7	2143.7	2147.1	2143.7	2143.7	2143.7	2143.7	2140.4
22.5°	2056.6	2053.3	2053.3	2056.6	2056.6	2053.3	2056.6	2056.6
25°	1959.5	1962.9	1959.5	1959.5	1962.9	1962.9	1962.9	1959.5
27.5°	1855.7	1859.1	1862.3	1859.1	1859.1	1859.1	1862.3	1865.7
30°	1748.5	1755.1	1748.5	1748.5	1755.1	1751.9	1755.1	1755.1
32.5°	1634.6	1644.7	1638.0	1644.7	1644.7	1647.9	1644.7	1647.9
35°	1520.8	1530.8	1530.8	1530.8	1534.1	1537.5	1537.5	1534.1
37.5°	1413.6	1416.8	1416.8	1423.6	1426.9	1430.3	1430.3	1426.9
40°	1303.0	1309.6	1313.0	1313.0	1313.0	1319.7	1326.5	1319.7
42.5°	1195.8	1199.2	1202.6	1202.6	1209.2	1212.6	1215.9	1215.9
45°	1092.0	1098.6	1102.0	1105.4	1108.7	1115.5	1112.1	1118.7
47.5°	984.8	994.8	998.2	1001.5	1008.3	1011.5	1014.9	1018.3
50°	887.6	894.3	894.3	901.1	911.1	911.1	917.8	921.2
52.5°	790.5	793.9	797.3	800.5	807.2	814.0	814.0	820.6
55°	696.7	700.1	700.1	703.4	706.8	720.1	723.5	723.5
57.5°	599.6	599.6	606.2	609.6	613.0	619.7	619.7	619.7
60°	505.8	509.1	509.1	512.5	515.9	522.5	525.9	522.5
62.5°	412.0	415.3	415.3	418.7	425.4	428.8	425.4	425.4
65°	324.9	328.3	328.3	331.6	338.3	338.3	334.9	338.3
67.5°	237.8	237.8	237.8	237.8	237.8	237.8	237.8	237.8
70°	150.7	147.4	144.0	147.4	147.4	147.4	144.0	150.7
72.5°	73.6	77.0	77.0	77.0	77.0	77.0	77.0	73.6
75°	33.6	33.6	30.2	30.2	30.2	33.6	33.6	30.2
77.5°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)