

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584914

Luminaire Tested: **HCC8W50D010SL-HM82555940-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010SL-HM82555940-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5241.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584914
CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584914

CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80353	80353	80353
5°	83294	80088	77339
10°	85648	79388	74178
15°	87561	77991	70900
20°	87699	74944	68023
25°	86016	70777	65615
30°	81582	65634	62735
35°	74129	59779	59914
40°	64817	53638	56468
45°	56173	47778	52619
50°	49187	42442	47944
55°	43778	37606	43386
60°	39495	33784	38126
65°	35651	29711	33221
70°	32043	25028	24695
75°	28213	19849	18527
80°	23671	16444	17740
85°	18327	14400	15709



TEST NUMBER: P584914
 CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.8	4.7
10°-20°	692.4	13.2
20°-30°	989.5	18.9
30°-40°	1051.4	20.1
40°-50°	905.2	17.3
50°-60°	676.8	12.9
60°-70°	431.7	8.2
70°-80°	196.5	3.7
80°-90°	51.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1927.8	36.8
0°-40°	2979.2	56.8
0°-60°	4561.2	87.0
0°-90°	5241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5241.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2606	2606	2606	2606	2606	
5°	2691	2654	2587	2521	2498	258
15°	2743	2650	2443	2276	2221	773
25°	2528	2369	2080	1954	1928	1157
35°	1969	1832	1588	1547	1592	1226
45°	1288	1218	1096	1125	1207	1001
55°	814	748	700	759	807	732
65°	489	433	407	426	455	487
75°	237	204	167	152	156	252
85°	52	44	41	44	44	62
90°	0	0	0	0	0	



TEST NUMBER: P584914

CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8
2.5°	2654.0	2646.5	2650.2	2646.5	2650.2	2650.2	2642.9	2642.9	2642.9	2642.9	2631.8
5°	2690.9	2687.3	2687.3	2683.6	2679.8	2683.6	2679.8	2676.2	2668.7	2665.1	2654.0
7.5°	2713.1	2713.1	2713.1	2713.1	2709.5	2705.8	2702.0	2694.7	2687.3	2679.8	2672.5
10°	2735.3	2739.1	2735.3	2731.7	2728.0	2720.6	2716.9	2709.5	2698.4	2687.3	2679.8
12.5°	2746.4	2746.4	2742.8	2742.8	2735.3	2731.7	2720.6	2709.5	2698.4	2687.3	2668.7
15°	2742.8	2742.8	2739.1	2735.3	2724.2	2720.6	2713.1	2702.0	2683.6	2668.7	2650.2
17.5°	2720.6	2716.9	2709.5	2709.5	2694.7	2690.9	2683.6	2668.7	2650.2	2628.0	2605.8
20°	2672.5	2672.5	2668.7	2665.1	2650.2	2639.1	2631.8	2613.2	2598.5	2572.5	2550.3
22.5°	2605.8	2613.2	2605.8	2598.5	2579.9	2576.2	2565.1	2542.9	2520.7	2491.1	2465.2
25°	2528.1	2524.3	2520.7	2513.2	2498.5	2491.1	2476.3	2454.1	2431.9	2398.6	2369.0
27.5°	2428.1	2413.4	2413.4	2398.6	2387.4	2376.3	2369.0	2346.8	2317.1	2291.2	2254.2
30°	2291.2	2294.9	2276.4	2272.7	2254.2	2246.8	2232.0	2209.8	2183.8	2154.2	2124.7
32.5°	2143.1	2132.0	2132.0	2117.2	2102.4	2091.3	2087.6	2061.8	2039.6	2009.9	1980.3
35°	1969.2	1969.2	1958.1	1954.3	1939.6	1932.1	1921.0	1906.3	1880.3	1854.4	1832.2
37.5°	1798.9	1791.5	1787.8	1780.4	1769.3	1758.2	1758.2	1732.2	1728.6	1699.0	1669.3
40°	1610.2	1617.5	1610.2	1599.1	1595.3	1588.0	1584.2	1569.4	1558.3	1532.4	1513.9
42.5°	1451.0	1443.6	1443.6	1439.9	1425.0	1425.0	1417.6	1410.3	1391.7	1384.3	1362.1
45°	1288.1	1295.5	1284.4	1288.1	1273.3	1273.3	1273.3	1258.5	1243.7	1232.6	1217.7
47.5°	1147.5	1151.1	1151.1	1140.0	1136.4	1136.4	1128.9	1121.5	1110.4	1095.6	1084.5
50°	1025.3	1029.0	1021.6	1017.8	1010.5	1006.7	1006.7	992.0	984.5	969.8	962.3
52.5°	914.3	914.3	910.5	910.5	899.4	899.4	892.1	881.0	873.6	866.1	847.6
55°	814.3	814.3	810.6	807.0	807.0	795.9	792.1	781.0	773.6	758.8	747.7
57.5°	718.1	721.7	718.1	714.4	710.6	707.0	699.5	688.4	681.1	670.0	662.6
60°	640.4	640.4	636.6	632.9	625.5	621.8	618.2	610.7	599.6	592.2	581.1
62.5°	566.4	562.6	558.9	555.3	547.8	547.8	540.4	533.1	522.0	514.5	507.1
65°	488.6	488.6	484.9	484.9	481.2	473.8	470.1	466.4	451.6	447.8	433.1
67.5°	418.3	422.0	414.5	414.5	407.2	407.2	403.4	392.3	388.7	381.2	373.8
70°	355.4	355.4	355.4	351.6	344.3	340.5	336.8	329.4	325.7	318.3	311.0
72.5°	292.4	292.4	288.7	288.7	285.0	281.3	277.6	270.2	270.2	262.8	255.4
75°	236.8	236.8	233.2	229.5	225.7	225.7	222.1	218.4	211.0	207.3	203.5
77.5°	181.4	181.4	181.4	177.7	173.9	173.9	173.9	166.6	159.2	159.2	155.5
80°	133.3	133.3	129.5	129.5	125.9	125.9	125.9	122.2	118.4	114.8	111.1
82.5°	88.8	88.8	88.8	88.8	85.1	85.1	85.1	81.5	77.7	77.7	77.7
85°	51.8	51.8	51.8	51.8	48.2	48.2	48.2	48.2	48.2	44.4	44.4
87.5°	22.2	18.5	22.2	18.5	22.2	18.5	22.2	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584914

CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8
2.5°	2635.4	2631.8	2628.0	2624.3	2624.3	2620.7	2613.2	2609.6	2605.8	2602.1	2602.1
5°	2650.2	2646.5	2639.1	2631.8	2628.0	2620.7	2613.2	2605.8	2598.5	2587.3	2583.6
7.5°	2661.3	2650.2	2642.9	2628.0	2624.3	2616.9	2605.8	2594.7	2579.9	2565.1	2554.0
10°	2661.3	2646.5	2635.4	2616.9	2609.6	2602.1	2587.3	2568.8	2550.3	2535.4	2517.0
12.5°	2654.0	2635.4	2616.9	2598.5	2587.3	2576.2	2554.0	2535.4	2513.2	2491.1	2476.3
15°	2628.0	2605.8	2583.6	2561.4	2550.3	2535.4	2513.2	2487.4	2465.2	2443.0	2417.0
17.5°	2579.9	2557.7	2531.8	2505.9	2491.1	2480.0	2446.7	2428.1	2394.8	2372.6	2350.4
20°	2517.0	2491.1	2457.8	2431.9	2413.4	2402.3	2376.3	2343.0	2317.1	2283.8	2261.5
22.5°	2435.6	2402.3	2369.0	2343.0	2324.6	2309.7	2276.4	2243.1	2220.9	2191.3	2165.3
25°	2339.3	2306.0	2272.7	2235.7	2217.1	2202.4	2172.7	2143.1	2113.6	2080.2	2058.0
27.5°	2224.6	2187.5	2158.0	2124.7	2106.2	2084.0	2050.7	2021.0	1991.4	1969.2	1939.6
30°	2098.7	2058.0	2028.4	1995.1	1976.5	1958.1	1924.8	1895.2	1869.2	1843.3	1828.5
32.5°	1947.0	1917.4	1887.7	1854.4	1839.7	1828.5	1795.2	1765.5	1736.0	1713.8	1702.6
35°	1802.6	1769.3	1743.3	1713.8	1695.3	1684.2	1654.6	1628.7	1613.8	1588.0	1573.1
37.5°	1650.9	1624.9	1595.3	1565.8	1554.7	1543.5	1521.3	1495.4	1473.2	1454.7	1447.2
40°	1491.6	1469.4	1443.6	1425.0	1413.9	1402.8	1384.3	1365.9	1351.0	1332.5	1325.2
42.5°	1339.9	1325.2	1303.0	1280.8	1269.7	1265.9	1243.7	1228.9	1221.5	1214.1	1206.6
45°	1203.0	1180.8	1166.0	1151.1	1140.0	1132.6	1121.5	1110.4	1103.1	1095.6	1088.2
47.5°	1069.8	1051.2	1036.4	1025.3	1014.2	1010.5	1003.1	992.0	984.5	984.5	984.5
50°	947.6	932.7	918.0	910.5	906.9	899.4	892.1	888.3	884.7	884.7	884.7
52.5°	840.3	825.4	814.3	807.0	807.0	799.5	792.1	788.4	788.4	788.4	788.4
55°	740.3	729.2	721.7	714.4	707.0	703.3	703.3	703.3	699.5	699.5	703.3
57.5°	651.5	644.0	632.9	625.5	621.8	621.8	618.2	614.4	618.2	621.8	625.5
60°	570.0	562.6	558.9	547.8	547.8	547.8	544.2	544.2	544.2	547.8	551.5
62.5°	496.0	492.3	484.9	481.2	477.5	477.5	473.8	473.8	473.8	473.8	477.5
65°	429.4	422.0	414.5	414.5	414.5	410.9	410.9	403.4	407.2	407.2	403.4
67.5°	366.5	359.0	355.4	351.6	347.9	347.9	344.3	340.5	336.8	336.8	336.8
70°	307.2	299.8	299.8	292.4	292.4	288.7	285.0	285.0	281.3	277.6	273.9
72.5°	247.9	244.3	240.6	236.8	236.8	236.8	233.2	229.5	225.7	222.1	214.6
75°	196.2	196.2	188.8	185.1	185.1	181.4	177.7	173.9	170.3	166.6	162.8
77.5°	151.7	148.1	140.6	137.0	137.0	137.0	133.3	129.5	125.9	122.2	118.4
80°	111.1	107.3	103.7	99.9	99.9	99.9	96.2	96.2	92.6	92.6	92.6
82.5°	74.0	74.0	70.4	70.4	70.4	70.4	66.6	66.6	66.6	66.6	66.6
85°	44.4	44.4	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584914

CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8
2.5°	2594.7	2594.7	2587.3	2583.6	2579.9	2583.6	2576.2	2572.5	2568.8	2568.8	2565.1
5°	2572.5	2568.8	2554.0	2550.3	2546.5	2542.9	2535.4	2528.1	2520.7	2517.0	2513.2
7.5°	2542.9	2531.8	2517.0	2513.2	2509.6	2498.5	2487.4	2480.0	2468.9	2465.2	2457.8
10°	2502.1	2487.4	2476.3	2465.2	2457.8	2446.7	2435.6	2424.5	2409.7	2405.9	2394.8
12.5°	2454.1	2435.6	2413.4	2409.7	2398.6	2383.7	2369.0	2357.9	2346.8	2339.3	2328.2
15°	2394.8	2376.3	2354.1	2343.0	2331.9	2320.8	2302.3	2287.5	2276.4	2265.3	2254.2
17.5°	2324.6	2302.3	2283.8	2272.7	2265.3	2246.8	2232.0	2213.5	2202.4	2191.3	2180.2
20°	2239.3	2220.9	2194.9	2183.8	2180.2	2165.3	2146.9	2139.4	2124.7	2113.6	2106.2
22.5°	2143.1	2124.7	2102.4	2095.1	2080.2	2072.9	2054.3	2046.9	2039.6	2028.4	2024.7
25°	2035.8	2017.3	1998.8	1995.1	1984.0	1976.5	1965.4	1954.3	1954.3	1943.2	1943.2
27.5°	1924.8	1906.3	1891.4	1884.1	1880.3	1873.0	1861.9	1858.1	1854.4	1850.8	1850.8
30°	1806.3	1784.1	1776.6	1773.0	1769.3	1761.9	1758.2	1750.8	1754.4	1758.2	1754.4
32.5°	1680.4	1673.1	1658.2	1650.9	1654.6	1650.9	1643.5	1650.9	1647.1	1654.6	1658.2
35°	1558.3	1550.9	1543.5	1543.5	1536.1	1536.1	1536.1	1539.8	1547.2	1550.9	1558.3
37.5°	1439.9	1428.8	1425.0	1421.4	1425.0	1425.0	1425.0	1432.5	1439.9	1447.2	1458.3
40°	1314.1	1306.6	1306.6	1306.6	1306.6	1317.7	1314.1	1321.4	1328.8	1339.9	1351.0
42.5°	1195.5	1195.5	1199.3	1199.3	1199.3	1199.3	1206.6	1217.7	1228.9	1240.0	1251.1
45°	1084.5	1084.5	1084.5	1092.0	1092.0	1095.6	1110.4	1117.8	1125.3	1136.4	1147.5
47.5°	980.9	980.9	984.5	988.3	992.0	999.4	1006.7	1017.8	1029.0	1036.4	1047.5
50°	884.7	888.3	895.8	903.2	903.2	906.9	918.0	925.4	932.7	943.9	947.6
52.5°	792.1	799.5	807.0	810.6	814.3	821.7	825.4	836.5	840.3	851.4	855.0
55°	707.0	710.6	721.7	725.5	725.5	732.8	740.3	747.7	758.8	758.8	766.2
57.5°	629.3	632.9	640.4	644.0	640.4	651.5	655.1	662.6	666.2	673.7	677.3
60°	551.5	558.9	562.6	562.6	566.4	570.0	577.4	577.4	584.9	592.2	592.2
62.5°	477.5	481.2	484.9	488.6	492.3	488.6	499.7	499.7	507.1	510.9	518.2
65°	407.2	410.9	410.9	414.5	414.5	418.3	418.3	422.0	425.6	433.1	436.7
67.5°	336.8	336.8	336.8	340.5	336.8	340.5	340.5	344.3	344.3	351.6	355.4
70°	273.9	270.2	266.5	266.5	266.5	266.5	262.8	266.5	266.5	270.2	270.2
72.5°	211.0	207.3	203.5	199.9	199.9	196.2	192.4	196.2	196.2	199.9	199.9
75°	159.2	151.7	151.7	151.7	148.1	148.1	148.1	151.7	151.7	151.7	155.5
77.5°	118.4	118.4	114.8	114.8	114.8	118.4	118.4	122.2	122.2	122.2	122.2
80°	88.8	92.6	92.6	92.6	92.6	96.2	96.2	96.2	96.2	99.9	99.9
82.5°	66.6	66.6	66.6	66.6	70.4	70.4	70.4	70.4	70.4	70.4	70.4
85°	40.7	44.4	44.4	40.7	44.4	44.4	44.4	44.4	44.4	44.4	44.4
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584914

CATALOG NUMBER: HCC8W50D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8	2605.8
2.5°	2561.4	2561.4	2561.4	2561.4	2557.7	2557.7	2557.7	2554.0
5°	2505.9	2505.9	2505.9	2498.5	2502.1	2502.1	2494.8	2498.5
7.5°	2450.3	2446.7	2443.0	2443.0	2439.2	2435.6	2431.9	2435.6
10°	2387.4	2376.3	2376.3	2372.6	2372.6	2365.2	2365.2	2369.0
12.5°	2317.1	2309.7	2309.7	2306.0	2302.3	2298.6	2294.9	2294.9
15°	2246.8	2239.3	2235.7	2232.0	2228.2	2220.9	2224.6	2220.9
17.5°	2176.4	2165.3	2165.3	2161.6	2158.0	2150.5	2150.5	2146.9
20°	2095.1	2091.3	2084.0	2087.6	2084.0	2076.5	2072.9	2072.9
22.5°	2013.6	2013.6	2009.9	2009.9	2006.2	2002.5	1998.8	1998.8
25°	1935.9	1932.1	1935.9	1935.9	1924.8	1924.8	1924.8	1928.5
27.5°	1847.0	1850.8	1847.0	1847.0	1847.0	1847.0	1850.8	1847.0
30°	1758.2	1758.2	1758.2	1761.9	1769.3	1765.5	1765.5	1761.9
32.5°	1662.0	1665.7	1665.7	1669.3	1673.1	1680.4	1680.4	1684.2
35°	1565.8	1573.1	1576.9	1573.1	1584.2	1584.2	1591.6	1591.6
37.5°	1465.8	1469.4	1476.9	1480.5	1488.0	1491.6	1495.4	1495.4
40°	1358.4	1373.2	1377.0	1380.6	1391.7	1391.7	1395.4	1402.8
42.5°	1258.5	1273.3	1277.0	1280.8	1288.1	1299.2	1295.5	1303.0
45°	1162.2	1173.3	1177.1	1180.8	1191.9	1195.5	1195.5	1206.6
47.5°	1058.6	1066.0	1069.8	1077.1	1084.5	1092.0	1099.3	1095.6
50°	955.0	966.1	973.4	977.2	988.3	992.0	995.6	999.4
52.5°	862.5	869.9	873.6	877.2	888.3	892.1	895.8	903.2
55°	773.6	777.3	784.7	781.0	792.1	795.9	799.5	807.0
57.5°	684.8	688.4	692.2	692.2	699.5	707.0	710.6	714.4
60°	599.6	607.1	610.7	610.7	610.7	618.2	618.2	618.2
62.5°	522.0	522.0	525.6	525.6	533.1	533.1	533.1	533.1
65°	440.5	444.2	447.8	447.8	455.3	451.6	458.9	455.3
67.5°	355.4	355.4	362.7	362.7	359.0	362.7	362.7	362.7
70°	270.2	270.2	273.9	273.9	273.9	273.9	273.9	273.9
72.5°	199.9	199.9	199.9	203.5	199.9	199.9	203.5	199.9
75°	155.5	155.5	155.5	155.5	155.5	155.5	155.5	155.5
77.5°	122.2	122.2	125.9	125.9	125.9	125.9	125.9	125.9
80°	99.9	99.9	99.9	99.9	103.7	99.9	99.9	99.9
82.5°	74.0	70.4	74.0	70.4	74.0	74.0	74.0	74.0
85°	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)