

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593808

Luminaire Tested: **HCC8S50D010SL-HM82555950-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593808  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010SL-HM82555950-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5011.5 lumens  
Efficiency: N/A  
Efficacy: 104.4 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593808  
CATALOG NUMBER: HCC8S50D010SL-HM82555950-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593808

CATALOG NUMBER: HCC8S50D010SL-HM82555950-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95																																				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																																				
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84																																				
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																																				
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75																																				
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72																																				
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68																																				
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																																				
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																																				
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	398763
5°	337833
10°	245117
15°	184074
20°	145241
25°	117152
30°	86816
35°	35171
40°	14834
45°	7954
50°	3574
55°	1806
60°	1147
65°	817
70°	676
75°	441
80°	657
85°	1309



TEST NUMBER: P593808  
 CATALOG NUMBER: HCC8S50D010SL-HM82555950-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	937.1	18.7
10°-20°	1619.5	32.3
20°-30°	1565.8	31.2
30°-40°	687.7	13.7
40°-50°	148.6	3.0
50°-60°	33.4	0.7
60°-70°	11.5	0.2
70°-80°	4.4	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4122.3	82.3
0°-40°	4810.0	96.0
0°-60°	4992.1	99.6
0°-90°	5011.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5011.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12932	
5°	10914	937
15°	5766	1619
25°	3443	1566
35°	934	688
45°	182	149
55°	34	33
65°	11	11
75°	4	4
85°	4	4
90°	0	



TEST NUMBER: P593808  
CATALOG NUMBER: HCC8S50D010SL-HM82555950-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12931.6
1°	12834.8
2°	12570.5
3°	12094.1
4°	11524.6
5°	10914.0
6°	10247.8
7°	9577.7
8°	8948.7
9°	8364.2
10°	7828.2
11°	7321.9
12°	6867.9
13°	6454.6
14°	6089.8
15°	5766.0
17.5°	5040.1
20°	4426.0
22.5°	3886.2
25°	3443.2
27.5°	2992.8
30°	2438.2
32.5°	1656.5
35°	934.3
37.5°	550.9
40°	368.5
42.5°	260.6
45°	182.4
47.5°	119.1
50°	74.5
52.5°	44.7
55°	33.6
57.5°	26.1
60°	18.6
62.5°	14.8
65°	11.2
67.5°	7.5
70°	7.5
72.5°	3.7
75°	3.7
77.5°	3.7
80°	3.7
82.5°	3.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P593808  
CATALOG NUMBER: HCC8S50D010SL-HM82555950-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	3.7
87.5°	3.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)