

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584750

Luminaire Tested: **HCC8S45D010SL-HM82555935-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584750  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S45D010SL-HM82555935-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4256.7 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584750  
CATALOG NUMBER: HCC8S45D010SL-HM82555935-81NDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584750

CATALOG NUMBER: HCC8S45D010SL-HM82555935-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	106102
5°	105817
10°	104053
15°	102534
20°	100074
25°	94995
30°	78353
35°	40343
40°	27010
45°	23156
50°	19981
55°	17435
60°	15498
65°	13922
70°	12613
75°	11366
80°	10158
85°	10119



TEST NUMBER: P584750  
 CATALOG NUMBER: HCC8S45D010SL-HM82555935-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	323.2	7.6
10°-20°	903.6	21.2
20°-30°	1252.0	29.4
30°-40°	752.0	17.7
40°-50°	411.7	9.7
50°-60°	292.4	6.9
60°-70°	189.9	4.5
70°-80°	101.5	2.4
80°-90°	30.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2478.9	58.2
0°-40°	3230.9	75.9
0°-60°	3935.0	92.4
0°-90°	4256.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4256.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3441	
5°	3418	323
15°	3212	904
25°	2792	1252
35°	1072	752
45°	531	412
55°	324	292
65°	191	190
75°	95	101
85°	29	30
90°	0	



TEST NUMBER: P584750  
CATALOG NUMBER: HCC8S45D010SL-HM82555935-81NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3440.8
2.5°	3434.4
5°	3418.5
7.5°	3380.4
10°	3323.1
12.5°	3269.0
15°	3211.8
17.5°	3138.6
20°	3049.6
22.5°	2941.5
25°	2792.0
27.5°	2556.7
30°	2200.5
32.5°	1612.3
35°	1071.7
37.5°	791.8
40°	671.0
42.5°	594.7
45°	531.0
47.5°	470.6
50°	416.5
52.5°	365.7
55°	324.3
57.5°	286.2
60°	251.3
62.5°	219.5
65°	190.8
67.5°	162.2
70°	139.9
72.5°	114.5
75°	95.4
77.5°	76.4
80°	57.2
82.5°	41.3
85°	28.6
87.5°	12.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)