

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593820

Luminaire Tested: **HCC8S50D010MW-HM82555950-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010MW-HM82555950-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5033.7 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593820
CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66		
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51		
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41		
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38		
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34		
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	84106	84106	84106
5°	87062	83626	80301
10°	88995	82156	75784
15°	90265	79392	70769
20°	89986	75538	65700
25°	87762	70637	60315
30°	83149	64964	55344
35°	75646	58793	50289
40°	66439	52290	45439
45°	57939	45995	40509
50°	50419	40297	35682
55°	44966	35413	31042
60°	40858	31040	26476
65°	36723	27004	24035
70°	32692	23018	21692
75°	28666	19396	18527
80°	24311	15769	16426
85°	18327	11782	13126



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.5	5.1
10°-20°	703.9	14.0
20°-30°	977.1	19.4
30°-40°	1010.2	20.1
40°-50°	845.8	16.8
50°-60°	614.0	12.2
60°-70°	387.5	7.7
70°-80°	192.0	3.8
80°-90°	47.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1936.5	38.5
0°-40°	2946.6	58.5
0°-60°	4406.5	87.5
0°-90°	5033.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5033.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2728	2728	2728	2728	2728	
5°	2813	2779	2702	2628	2594	269
15°	2828	2720	2487	2287	2217	796
25°	2579	2413	2076	1850	1773	1182
35°	2010	1862	1562	1384	1336	1251
45°	1329	1232	1055	951	929	1028
55°	836	762	659	603	577	755
65°	503	440	370	326	329	502
75°	241	200	163	156	156	258
85°	52	41	33	37	37	63
90°	0	0	0	0	0	



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5
2.5°	2771.9	2771.9	2775.6	2771.9	2771.9	2771.9	2768.2	2768.2	2764.5	2764.5	2757.1
5°	2812.6	2805.2	2812.6	2805.2	2805.2	2805.2	2801.5	2794.1	2790.4	2783.0	2779.3
7.5°	2831.1	2827.5	2827.5	2823.7	2823.7	2820.0	2816.4	2812.6	2797.8	2794.1	2783.0
10°	2842.2	2838.6	2838.6	2834.8	2827.5	2827.5	2820.0	2816.4	2797.8	2790.4	2775.6
12.5°	2838.6	2838.6	2838.6	2834.8	2823.7	2820.0	2812.6	2801.5	2786.7	2771.9	2757.1
15°	2827.5	2827.5	2820.0	2816.4	2805.2	2797.8	2794.1	2775.6	2760.8	2742.2	2720.0
17.5°	2790.4	2790.4	2786.7	2779.3	2768.2	2760.8	2753.3	2734.9	2720.0	2690.5	2668.2
20°	2742.2	2738.6	2734.9	2723.8	2712.7	2709.0	2697.9	2672.0	2653.5	2631.3	2601.6
22.5°	2672.0	2668.2	2664.6	2657.1	2638.7	2631.3	2623.8	2605.4	2572.0	2549.8	2512.9
25°	2579.4	2579.4	2572.0	2560.9	2542.5	2535.1	2524.0	2505.4	2475.8	2442.5	2412.9
27.5°	2472.1	2468.5	2457.4	2449.9	2435.1	2424.0	2405.6	2383.4	2353.7	2327.8	2290.8
30°	2335.2	2335.2	2327.8	2316.7	2298.3	2290.8	2276.0	2250.1	2220.5	2187.2	2161.2
32.5°	2179.7	2179.7	2168.6	2161.2	2150.1	2131.7	2127.9	2098.4	2072.4	2046.6	2017.0
35°	2009.5	2013.3	2005.9	1991.0	1972.6	1972.6	1965.1	1939.3	1909.6	1883.7	1861.5
37.5°	1839.3	1828.2	1824.5	1817.1	1806.0	1791.1	1783.8	1772.7	1746.7	1728.2	1694.9
40°	1650.5	1654.3	1646.9	1639.4	1635.8	1624.7	1620.9	1602.5	1584.0	1561.8	1546.9
42.5°	1480.3	1480.3	1480.3	1472.9	1465.5	1454.5	1450.7	1439.6	1417.4	1402.6	1380.4
45°	1328.6	1317.5	1317.5	1313.8	1310.1	1302.7	1291.6	1284.1	1269.4	1258.3	1232.4
47.5°	1180.6	1184.3	1180.6	1176.8	1165.7	1162.1	1158.4	1143.5	1128.8	1117.7	1099.1
50°	1051.0	1058.4	1051.0	1051.0	1043.7	1039.9	1032.6	1021.5	1010.4	991.8	973.3
52.5°	943.7	943.7	940.0	936.3	925.1	917.8	914.0	910.4	891.9	877.1	862.3
55°	836.4	840.0	840.0	828.9	825.3	817.8	814.2	803.1	795.6	773.4	762.4
57.5°	743.8	740.2	743.8	736.5	729.1	721.6	718.0	710.5	699.4	684.7	669.8
60°	662.5	655.0	655.0	651.4	643.9	640.3	632.8	621.8	610.7	595.8	584.7
62.5°	581.0	577.4	573.6	569.9	562.5	558.8	555.2	544.1	532.9	521.8	510.7
65°	503.3	503.3	499.6	492.1	488.5	484.8	481.2	473.7	458.9	451.5	440.4
67.5°	433.0	429.3	429.3	421.9	414.5	410.8	410.8	403.4	392.3	381.2	373.7
70°	362.6	366.4	362.6	359.0	351.5	351.5	344.2	340.5	325.7	321.9	310.8
72.5°	299.7	299.7	296.1	296.1	288.6	285.0	285.0	277.5	270.2	262.8	255.3
75°	240.6	240.6	240.6	236.8	233.1	225.7	225.7	222.0	214.6	207.3	199.9
77.5°	188.8	185.1	185.1	181.3	177.7	173.9	173.9	170.2	162.8	159.1	151.7
80°	136.9	133.3	133.3	133.3	125.8	129.5	125.8	122.2	118.4	114.7	111.1
82.5°	88.8	92.5	92.5	88.8	85.1	85.1	85.1	81.4	81.4	77.7	74.0
85°	51.8	51.8	51.8	51.8	48.2	48.2	48.2	44.4	44.4	44.4	40.7
87.5°	22.2	22.2	22.2	22.2	22.2	22.2	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5
2.5°	2757.1	2749.7	2746.0	2742.2	2742.2	2738.6	2734.9	2727.5	2727.5	2720.0	2716.4
5°	2771.9	2760.8	2753.3	2746.0	2742.2	2734.9	2727.5	2716.4	2712.7	2701.6	2690.5
7.5°	2775.6	2757.1	2749.7	2734.9	2727.5	2720.0	2705.3	2694.2	2679.3	2668.2	2653.5
10°	2760.8	2746.0	2727.5	2709.0	2705.3	2694.2	2672.0	2657.1	2638.7	2623.8	2601.6
12.5°	2738.6	2716.4	2697.9	2675.7	2664.6	2653.5	2631.3	2609.1	2583.1	2557.3	2535.1
15°	2701.6	2675.7	2649.8	2623.8	2609.1	2598.0	2572.0	2546.2	2520.2	2486.9	2464.7
17.5°	2646.0	2616.5	2590.5	2557.3	2542.5	2531.4	2498.0	2468.5	2435.1	2401.8	2379.6
20°	2575.8	2538.7	2509.1	2472.1	2461.0	2442.5	2409.2	2375.9	2338.9	2301.9	2276.0
22.5°	2483.2	2446.2	2412.9	2375.9	2357.4	2338.9	2305.6	2264.9	2227.9	2198.3	2172.4
25°	2375.9	2342.6	2301.9	2268.6	2246.4	2224.1	2187.2	2153.9	2120.6	2076.1	2050.2
27.5°	2257.5	2216.8	2187.2	2142.8	2120.6	2105.7	2065.0	2020.6	1991.0	1950.4	1920.7
30°	2124.3	2087.2	2053.9	2009.5	1987.3	1972.6	1935.5	1894.8	1865.3	1824.5	1794.9
32.5°	1983.7	1942.9	1902.2	1872.6	1846.7	1831.9	1791.1	1765.3	1728.2	1694.9	1661.6
35°	1831.9	1791.1	1761.6	1720.9	1706.0	1691.3	1658.0	1624.7	1591.4	1561.8	1535.8
37.5°	1669.1	1639.4	1606.1	1576.5	1565.4	1550.7	1509.9	1480.3	1454.5	1424.8	1402.6
40°	1509.9	1484.0	1461.8	1432.3	1413.7	1402.6	1373.0	1347.0	1317.5	1299.0	1276.8
42.5°	1365.6	1335.9	1313.8	1291.6	1273.0	1261.9	1236.1	1217.5	1195.3	1176.8	1151.0
45°	1213.9	1199.0	1173.2	1154.6	1143.5	1128.8	1110.2	1088.0	1069.5	1054.7	1036.2
47.5°	1080.6	1065.8	1047.3	1025.1	1017.7	1006.6	988.2	973.3	958.5	943.7	925.1
50°	958.5	940.0	925.1	910.4	903.1	891.9	873.4	866.0	854.9	840.0	828.9
52.5°	847.5	832.7	817.8	799.4	795.6	788.3	777.2	762.4	751.3	743.8	736.5
55°	747.6	732.7	721.6	706.9	703.2	695.8	680.9	673.6	666.1	658.7	651.4
57.5°	658.7	643.9	629.2	621.8	614.3	606.9	603.2	592.1	584.7	581.0	573.6
60°	577.4	562.5	551.4	540.3	536.6	532.9	525.5	518.1	510.7	503.3	499.6
62.5°	499.6	484.8	477.4	470.1	462.6	462.6	455.2	447.8	440.4	436.7	429.3
65°	429.3	421.9	410.8	399.7	395.9	395.9	384.8	381.2	377.5	370.1	362.6
67.5°	362.6	355.3	344.2	340.5	336.8	333.0	329.4	321.9	314.6	310.8	303.5
70°	303.5	296.1	288.6	285.0	281.3	277.5	270.2	266.4	259.1	255.3	251.7
72.5°	244.2	240.6	233.1	229.5	225.7	222.0	218.4	214.6	207.3	203.5	199.9
75°	196.2	192.4	185.1	181.3	177.7	177.7	173.9	166.6	162.8	162.8	159.1
77.5°	148.0	144.4	140.6	136.9	133.3	133.3	129.5	125.8	122.2	122.2	118.4
80°	107.3	103.6	99.9	99.9	99.9	96.2	92.5	92.5	88.8	88.8	85.1
82.5°	70.3	70.3	66.6	66.6	66.6	62.9	62.9	59.3	59.3	59.3	59.3
85°	40.7	40.7	40.7	37.1	37.1	37.1	37.1	37.1	37.1	33.3	37.1
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5
2.5°	2712.7	2709.0	2701.6	2701.6	2694.2	2694.2	2690.5	2686.8	2683.1	2679.3	2675.7
5°	2686.8	2672.0	2664.6	2660.9	2653.5	2649.8	2638.7	2631.3	2627.6	2620.2	2612.7
7.5°	2638.7	2623.8	2609.1	2605.4	2601.6	2586.9	2575.8	2564.7	2557.3	2549.8	2542.5
10°	2583.1	2568.4	2549.8	2542.5	2535.1	2516.5	2501.8	2490.7	2475.8	2461.0	2457.4
12.5°	2516.5	2494.3	2472.1	2464.7	2453.6	2435.1	2420.3	2401.8	2390.7	2372.3	2368.5
15°	2438.9	2412.9	2394.5	2375.9	2368.5	2350.0	2324.1	2309.2	2287.1	2279.7	2261.2
17.5°	2346.3	2320.3	2294.5	2287.1	2276.0	2250.1	2224.1	2205.7	2183.5	2172.4	2161.2
20°	2250.1	2216.8	2190.8	2183.5	2168.6	2146.5	2120.6	2102.1	2083.5	2061.3	2050.2
22.5°	2139.0	2102.1	2079.9	2061.3	2057.7	2031.7	2002.1	1987.3	1972.6	1954.0	1939.3
25°	2017.0	1983.7	1957.7	1942.9	1935.5	1913.3	1891.1	1872.6	1850.4	1839.3	1820.8
27.5°	1891.1	1868.9	1835.6	1820.8	1809.7	1791.1	1765.3	1754.2	1732.0	1717.1	1706.0
30°	1768.9	1735.7	1717.1	1698.7	1687.6	1669.1	1646.9	1635.8	1617.2	1602.5	1591.4
32.5°	1635.8	1613.6	1587.6	1580.3	1565.4	1546.9	1532.1	1513.6	1498.8	1484.0	1480.3
35°	1513.6	1484.0	1458.1	1450.7	1439.6	1421.2	1413.7	1402.6	1384.1	1380.4	1365.6
37.5°	1380.4	1365.6	1335.9	1324.8	1321.2	1306.4	1291.6	1284.1	1273.0	1261.9	1258.3
40°	1254.6	1236.1	1221.3	1210.1	1202.8	1191.7	1176.8	1173.2	1165.7	1151.0	1147.3
42.5°	1136.2	1117.7	1102.8	1099.1	1088.0	1076.9	1069.5	1058.4	1054.7	1051.0	1043.7
45°	1021.5	1010.4	995.5	991.8	988.2	973.3	965.9	958.5	951.1	947.4	940.0
47.5°	917.8	906.7	895.6	891.9	884.5	880.8	869.7	866.0	854.9	851.1	847.5
50°	817.8	810.5	803.1	799.4	792.0	788.3	780.9	773.4	766.0	762.4	758.7
52.5°	729.1	721.6	714.3	710.5	706.9	699.4	692.0	684.7	680.9	677.2	673.6
55°	643.9	636.5	632.8	629.2	625.4	621.8	610.7	606.9	603.2	599.6	592.1
57.5°	566.3	558.8	551.4	551.4	547.7	544.1	536.6	529.2	529.2	521.8	514.4
60°	495.9	488.5	481.2	477.4	473.7	466.3	462.6	458.9	455.2	451.5	444.1
62.5°	421.9	418.2	410.8	410.8	403.4	399.7	395.9	392.3	388.6	381.2	377.5
65°	359.0	355.3	347.9	344.2	344.2	340.5	333.0	329.4	325.7	325.7	321.9
67.5°	299.7	296.1	288.6	285.0	285.0	281.3	277.5	277.5	273.9	270.2	273.9
70°	247.9	240.6	240.6	236.8	236.8	233.1	229.5	229.5	229.5	233.1	233.1
72.5°	196.2	192.4	188.8	188.8	188.8	188.8	185.1	185.1	188.8	192.4	192.4
75°	155.5	151.7	151.7	151.7	148.0	148.0	151.7	151.7	155.5	155.5	155.5
77.5°	114.7	114.7	114.7	114.7	114.7	114.7	118.4	118.4	122.2	122.2	122.2
80°	85.1	85.1	85.1	85.1	85.1	88.8	88.8	88.8	88.8	88.8	92.5
82.5°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	62.9	62.9	62.9	62.9
85°	33.3	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593820

CATALOG NUMBER: HCC8S50D010MW-HM82555950-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5	2727.5
2.5°	2672.0	2672.0	2672.0	2675.7	2668.2	2668.2	2668.2	2668.2
5°	2609.1	2605.4	2601.6	2605.4	2598.0	2598.0	2594.2	2594.2
7.5°	2531.4	2527.6	2524.0	2524.0	2516.5	2516.5	2512.9	2509.1
10°	2446.2	2438.9	2442.5	2435.1	2431.4	2427.8	2424.0	2420.3
12.5°	2353.7	2346.3	2342.6	2335.2	2327.8	2324.1	2327.8	2320.3
15°	2253.8	2242.7	2239.0	2231.6	2224.1	2220.5	2220.5	2216.8
17.5°	2142.8	2135.4	2131.7	2124.3	2120.6	2113.2	2109.5	2105.7
20°	2039.1	2020.6	2024.4	2017.0	2013.3	1998.4	1998.4	2002.1
22.5°	1924.4	1913.3	1905.9	1898.5	1894.8	1887.4	1887.4	1883.7
25°	1809.7	1798.6	1794.9	1787.5	1783.8	1776.4	1772.7	1772.7
27.5°	1698.7	1683.8	1683.8	1676.5	1669.1	1665.4	1661.6	1658.0
30°	1580.3	1569.1	1565.4	1565.4	1561.8	1561.8	1550.7	1554.3
32.5°	1469.2	1461.8	1458.1	1450.7	1450.7	1447.0	1447.0	1435.9
35°	1358.1	1347.0	1350.8	1343.4	1339.7	1335.9	1339.7	1335.9
37.5°	1250.8	1243.5	1243.5	1236.1	1236.1	1232.4	1228.6	1236.1
40°	1143.5	1139.9	1136.2	1132.4	1136.2	1132.4	1125.0	1128.8
42.5°	1036.2	1036.2	1032.6	1032.6	1028.8	1028.8	1028.8	1028.8
45°	940.0	936.3	936.3	932.6	932.6	932.6	932.6	928.9
47.5°	843.8	840.0	840.0	840.0	836.4	836.4	832.7	836.4
50°	751.3	751.3	747.6	747.6	751.3	747.6	743.8	743.8
52.5°	666.1	666.1	662.5	662.5	658.7	655.0	658.7	658.7
55°	588.5	584.7	581.0	581.0	577.4	573.6	573.6	577.4
57.5°	514.4	510.7	507.0	507.0	499.6	495.9	495.9	495.9
60°	444.1	436.7	436.7	433.0	433.0	429.3	429.3	429.3
62.5°	377.5	373.7	373.7	373.7	373.7	370.1	370.1	370.1
65°	321.9	321.9	321.9	325.7	325.7	329.4	329.4	329.4
67.5°	277.5	281.3	281.3	281.3	285.0	285.0	285.0	281.3
70°	236.8	236.8	236.8	240.6	240.6	240.6	240.6	240.6
72.5°	196.2	196.2	196.2	196.2	196.2	196.2	196.2	196.2
75°	155.5	159.1	159.1	159.1	155.5	159.1	159.1	155.5
77.5°	122.2	122.2	122.2	122.2	122.2	122.2	122.2	122.2
80°	92.5	92.5	92.5	92.5	92.5	92.5	92.5	92.5
82.5°	62.9	62.9	62.9	62.9	62.9	62.9	62.9	62.9
85°	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)