

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593785

Luminaire Tested: **HCC8W45D010MW-HM82555950-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593785  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W45D010MW-HM82555950-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4378.3 lumens  
Efficiency: N/A  
Efficacy: 99.5 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593785  
CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	72484	72484	72484
5°	75478	72324	69278
10°	78001	71401	65899
15°	79976	69767	62475
20°	80135	66874	59379
25°	78779	62642	56306
30°	74560	57797	53670
35°	67985	51983	50391
40°	59117	45825	46534
45°	50717	39684	42597
50°	43319	34219	38258
55°	37972	29467	33246
60°	33803	25138	27950
65°	29996	20510	22305
70°	26606	15210	12667
75°	22196	7947	3777
80°	17474	2504	622
85°	12454	1238	0



TEST NUMBER: P593785  
 CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.5	5.1
10°-20°	620.8	14.2
20°-30°	878.6	20.1
30°-40°	919.2	21.0
40°-50°	766.7	17.5
50°-60°	543.7	12.4
60°-70°	313.1	7.2
70°-80°	100.8	2.3
80°-90°	13.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.9	39.3
0°-40°	2640.1	60.3
0°-60°	3950.6	90.2
0°-90°	4378.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4378.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2351	2351	2351	2351	2351	
5°	2438	2407	2336	2266	2238	234
15°	2505	2403	2185	2013	1957	704
25°	2315	2143	1841	1694	1655	1057
35°	1806	1648	1381	1307	1339	1120
45°	1163	1068	910	921	977	901
55°	706	632	548	576	618	638
65°	411	344	281	281	306	411
75°	186	137	67	32	32	202
85°	35	18	4	0	0	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2399.7	2396.2	2392.7	2396.2	2392.7	2396.2	2392.7	2392.7	2389.2	2385.6	2385.6
5°	2438.4	2434.9	2434.9	2434.9	2431.4	2427.9	2427.9	2424.4	2417.3	2413.8	2406.8
7.5°	2462.9	2466.5	2466.5	2466.5	2459.4	2459.4	2452.4	2445.4	2438.4	2431.4	2420.8
10°	2491.1	2491.1	2487.6	2484.1	2477.0	2473.5	2470.0	2462.9	2452.4	2438.4	2427.9
12.5°	2501.7	2501.7	2498.1	2491.1	2487.6	2484.1	2480.5	2470.0	2455.9	2438.4	2424.4
15°	2505.2	2498.1	2494.6	2491.1	2484.1	2473.5	2473.5	2459.4	2442.0	2420.8	2403.2
17.5°	2477.0	2480.5	2473.5	2466.5	2455.9	2448.9	2438.4	2427.9	2406.8	2382.1	2364.7
20°	2442.0	2438.4	2434.9	2424.4	2410.3	2406.8	2396.2	2378.6	2361.1	2333.0	2308.3
22.5°	2385.6	2382.1	2375.1	2368.1	2354.1	2347.1	2336.5	2315.4	2290.9	2262.7	2234.6
25°	2315.4	2308.3	2297.8	2283.8	2273.3	2266.2	2252.2	2231.0	2203.0	2171.3	2143.2
27.5°	2203.0	2213.6	2206.5	2185.4	2174.9	2160.8	2157.3	2129.2	2104.6	2072.9	2041.4
30°	2094.0	2094.0	2083.5	2072.9	2055.4	2044.9	2030.8	2009.7	1985.2	1946.5	1921.8
32.5°	1957.0	1953.5	1939.4	1935.9	1921.8	1900.8	1897.3	1869.2	1844.5	1816.5	1784.8
35°	1806.0	1798.9	1784.8	1774.3	1767.2	1756.8	1746.2	1721.6	1697.0	1668.9	1647.8
37.5°	1633.8	1633.8	1630.2	1612.8	1605.7	1598.7	1588.1	1563.5	1549.4	1521.4	1500.3
40°	1468.6	1465.2	1454.6	1451.1	1444.1	1433.5	1426.5	1412.4	1391.3	1370.3	1349.2
42.5°	1307.1	1310.6	1296.5	1300.0	1286.0	1278.9	1275.4	1254.3	1243.7	1222.7	1205.1
45°	1163.0	1159.5	1152.5	1149.0	1141.9	1134.9	1127.8	1117.3	1099.7	1078.7	1068.1
47.5°	1029.4	1018.9	1018.9	1015.3	1011.9	997.9	994.4	983.8	973.2	952.1	938.2
50°	903.0	903.0	903.0	899.5	888.9	885.4	878.3	867.8	857.3	843.3	822.2
52.5°	801.0	801.0	801.0	797.5	783.6	780.0	776.5	762.4	748.4	737.8	723.7
55°	706.3	709.8	706.3	699.2	688.7	688.7	678.1	671.1	657.0	646.4	632.5
57.5°	625.4	625.4	618.4	614.9	607.8	604.3	597.3	590.3	572.7	562.2	544.6
60°	548.1	544.6	544.6	537.6	530.5	523.5	520.0	509.4	502.4	484.9	470.8
62.5°	477.9	477.9	470.8	470.8	456.8	456.8	453.2	442.7	432.1	414.5	407.6
65°	411.1	411.1	407.6	404.1	393.5	390.0	386.5	375.9	365.4	354.8	344.3
67.5°	351.3	351.3	344.3	340.8	333.8	330.3	323.3	316.2	305.7	295.1	284.6
70°	295.1	291.6	288.1	284.6	277.5	274.0	267.0	260.1	249.5	242.5	231.9
72.5°	238.9	238.9	235.4	228.4	224.9	221.3	217.8	210.8	200.2	189.7	182.8
75°	186.3	186.3	186.3	179.2	172.2	168.7	168.7	161.6	154.6	144.0	137.0
77.5°	144.0	140.5	137.0	137.0	130.0	126.4	122.9	119.4	109.0	105.5	98.4
80°	98.4	101.9	98.4	94.9	91.4	87.9	87.9	80.8	77.3	70.3	63.2
82.5°	66.7	63.2	63.2	59.7	59.7	56.2	56.2	49.1	45.6	42.1	38.6
85°	35.2	35.2	31.7	31.7	31.7	28.2	28.2	24.6	24.6	21.1	17.6
87.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2382.1	2375.1	2371.6	2371.6	2368.1	2364.7	2361.1	2357.6	2350.6	2350.6	2343.5
5°	2399.7	2392.7	2389.2	2378.6	2371.6	2371.6	2357.6	2354.1	2343.5	2336.5	2329.5
7.5°	2413.8	2399.7	2389.2	2378.6	2371.6	2364.7	2350.6	2336.5	2322.4	2308.3	2301.3
10°	2413.8	2399.7	2382.1	2364.7	2357.6	2350.6	2333.0	2311.9	2294.3	2280.3	2262.7
12.5°	2406.8	2385.6	2364.7	2350.6	2336.5	2325.9	2304.8	2283.8	2262.7	2234.6	2220.5
15°	2385.6	2357.6	2336.5	2311.9	2301.3	2283.8	2266.2	2234.6	2210.0	2185.4	2167.8
17.5°	2343.5	2308.3	2283.8	2259.2	2241.6	2231.0	2203.0	2174.9	2146.7	2118.7	2097.6
20°	2280.3	2248.6	2220.5	2188.9	2174.9	2160.8	2125.7	2097.6	2069.4	2037.9	2016.7
22.5°	2203.0	2171.3	2132.7	2108.1	2087.0	2069.4	2037.9	2006.2	1978.1	1950.0	1921.8
25°	2108.1	2076.4	2041.4	2002.7	1988.7	1971.1	1935.9	1904.4	1872.7	1841.1	1816.5
27.5°	2006.2	1964.1	1935.9	1893.8	1879.7	1862.1	1823.5	1788.4	1760.3	1735.7	1707.5
30°	1883.3	1851.6	1813.0	1774.3	1760.3	1742.7	1711.1	1679.5	1651.3	1623.2	1595.2
32.5°	1749.8	1718.1	1679.5	1651.3	1630.2	1616.2	1584.6	1556.5	1528.4	1500.3	1475.6
35°	1609.2	1574.0	1545.9	1517.9	1500.3	1482.7	1451.1	1426.5	1405.4	1380.9	1356.2
37.5°	1465.2	1440.6	1412.4	1380.9	1363.3	1349.2	1324.6	1296.5	1278.9	1257.8	1240.3
40°	1324.6	1296.5	1271.9	1243.7	1229.8	1219.2	1194.6	1173.5	1156.0	1138.4	1127.8
42.5°	1180.5	1156.0	1131.4	1113.8	1103.2	1092.6	1075.2	1050.5	1040.0	1022.4	1011.9
45°	1047.0	1025.9	1008.4	983.8	976.8	969.7	948.6	931.1	920.6	910.0	903.0
47.5°	920.6	906.5	885.4	871.3	860.9	853.8	839.8	825.7	815.1	808.1	801.0
50°	811.6	794.0	780.0	766.0	758.9	748.4	734.3	727.3	720.2	713.3	713.3
52.5°	709.8	692.2	678.1	667.6	660.5	653.5	642.9	639.4	632.5	632.5	629.0
55°	614.9	604.3	590.3	576.2	572.7	569.1	562.2	555.2	551.7	548.1	551.7
57.5°	534.1	523.5	509.4	498.9	495.4	491.8	488.4	481.4	477.9	477.9	477.9
60°	460.3	449.7	439.2	428.6	428.6	421.6	418.1	414.5	411.1	407.6	407.6
62.5°	393.5	383.0	372.4	365.4	361.9	358.4	351.3	347.8	344.3	344.3	340.8
65°	333.8	319.8	316.2	305.7	302.2	298.6	295.1	288.1	284.6	281.1	277.5
67.5°	274.0	267.0	256.5	249.5	246.0	242.5	238.9	231.9	228.4	224.9	217.8
70°	221.3	214.3	207.3	200.2	196.7	193.2	186.3	179.2	175.7	168.7	158.1
72.5°	172.2	165.2	158.1	151.1	147.6	144.0	137.0	130.0	122.9	115.9	109.0
75°	130.0	122.9	112.5	105.5	101.9	101.9	91.4	84.3	77.3	66.7	59.7
77.5°	91.4	80.8	77.3	70.3	66.7	59.7	52.7	45.6	38.6	35.2	28.2
80°	59.7	52.7	45.6	42.1	38.6	35.2	31.7	24.6	17.6	14.1	10.6
82.5°	35.2	31.7	28.2	24.6	21.1	17.6	14.1	14.1	10.6	7.0	3.5
85°	17.6	14.1	10.6	10.6	7.0	7.0	7.0	3.5	3.5	3.5	3.5
87.5°	7.0	3.5	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2340.0	2336.5	2333.0	2329.5	2329.5	2322.4	2322.4	2318.9	2311.9	2308.3	2308.3
5°	2318.9	2308.3	2301.3	2297.8	2294.3	2283.8	2280.3	2273.3	2266.2	2259.2	2255.7
7.5°	2287.4	2269.8	2262.7	2259.2	2248.6	2238.1	2231.0	2220.5	2210.0	2199.5	2196.0
10°	2248.6	2231.0	2213.6	2206.5	2196.0	2188.9	2174.9	2160.8	2150.2	2139.8	2129.2
12.5°	2199.5	2178.4	2160.8	2153.7	2143.2	2129.2	2108.1	2101.1	2083.5	2076.4	2062.5
15°	2143.2	2118.7	2101.1	2090.5	2080.0	2059.0	2044.9	2030.8	2013.2	2006.2	1992.1
17.5°	2072.9	2044.9	2027.3	2016.7	2009.7	1992.1	1971.1	1953.5	1935.9	1928.9	1918.3
20°	1988.7	1971.1	1946.5	1935.9	1928.9	1907.9	1886.8	1879.7	1865.7	1851.6	1841.1
22.5°	1893.8	1876.2	1851.6	1841.1	1837.6	1820.0	1802.4	1791.9	1781.3	1770.8	1760.3
25°	1795.4	1774.3	1753.3	1746.2	1739.2	1725.1	1711.1	1704.0	1693.5	1686.5	1679.5
27.5°	1690.1	1668.9	1651.3	1640.8	1633.8	1623.2	1616.2	1609.2	1602.2	1595.2	1591.6
30°	1577.6	1556.5	1542.4	1535.5	1528.4	1524.9	1514.3	1510.8	1507.3	1500.3	1503.8
32.5°	1465.2	1447.6	1433.5	1423.0	1423.0	1415.9	1412.4	1412.4	1408.9	1408.9	1408.9
35°	1342.1	1331.6	1321.0	1317.5	1314.1	1310.6	1307.1	1310.6	1307.1	1310.6	1314.1
37.5°	1229.8	1219.2	1212.2	1208.7	1205.1	1208.7	1205.1	1205.1	1208.7	1215.7	1219.2
40°	1113.8	1106.7	1099.7	1103.2	1099.7	1099.7	1099.7	1110.2	1113.8	1117.3	1120.8
42.5°	1004.9	997.9	994.4	994.4	997.9	994.4	1001.4	1004.9	1011.9	1022.4	1029.4
45°	899.5	895.9	895.9	899.5	895.9	903.0	903.0	910.0	920.6	927.6	934.6
47.5°	801.0	801.0	801.0	804.6	804.6	808.1	815.1	818.6	825.7	832.7	839.8
50°	709.8	713.3	716.7	716.7	716.7	723.7	730.8	734.3	737.8	741.3	751.9
52.5°	629.0	632.5	632.5	636.0	639.4	642.9	646.4	653.5	657.0	664.0	667.6
55°	551.7	551.7	558.7	562.2	562.2	562.2	569.1	569.1	576.2	579.7	586.7
57.5°	477.9	481.4	481.4	484.9	484.9	488.4	491.8	495.4	498.9	502.4	505.9
60°	407.6	407.6	407.6	411.1	414.5	418.1	414.5	421.6	421.6	428.6	432.1
62.5°	340.8	344.3	344.3	344.3	344.3	344.3	344.3	347.8	351.3	354.8	358.4
65°	277.5	277.5	277.5	274.0	277.5	274.0	277.5	281.1	281.1	284.6	288.1
67.5°	214.3	214.3	207.3	207.3	210.8	210.8	210.8	210.8	207.3	214.3	214.3
70°	154.6	151.1	147.6	144.0	144.0	140.5	140.5	137.0	137.0	137.0	137.0
72.5°	101.9	94.9	87.9	84.3	80.8	80.8	73.8	70.3	73.8	73.8	73.8
75°	52.7	45.6	42.1	38.6	35.2	35.2	31.7	31.7	31.7	31.7	31.7
77.5°	21.1	17.6	14.1	14.1	10.6	10.6	10.6	10.6	10.6	10.6	10.6
80°	7.0	7.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	3.5	0.0	0.0	3.5	0.0	3.5	3.5	3.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593785

CATALOG NUMBER: HCC8W45D010MW-HM82555950-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6	2350.6
2.5°	2304.8	2304.8	2301.3	2304.8	2297.8	2301.3	2297.8	2297.8
5°	2252.2	2245.1	2245.1	2245.1	2241.6	2241.6	2238.1	2238.1
7.5°	2188.9	2185.4	2181.9	2178.4	2174.9	2171.3	2171.3	2171.3
10°	2125.7	2118.7	2118.7	2115.2	2108.1	2104.6	2104.6	2104.6
12.5°	2051.9	2048.4	2044.9	2044.9	2030.8	2034.3	2030.8	2030.8
15°	1981.7	1978.1	1978.1	1967.6	1960.6	1960.6	1960.6	1957.0
17.5°	1907.9	1904.4	1900.8	1893.8	1886.8	1886.8	1883.3	1886.8
20°	1830.6	1827.1	1820.0	1820.0	1816.5	1813.0	1806.0	1809.5
22.5°	1753.3	1746.2	1742.7	1742.7	1739.2	1739.2	1732.2	1732.2
25°	1672.5	1668.9	1665.4	1668.9	1661.9	1661.9	1654.9	1654.9
27.5°	1588.1	1584.6	1584.6	1584.6	1581.1	1584.6	1581.1	1581.1
30°	1503.8	1503.8	1500.3	1500.3	1503.8	1500.3	1503.8	1507.3
32.5°	1412.4	1412.4	1415.9	1415.9	1419.4	1419.4	1419.4	1419.4
35°	1317.5	1324.6	1324.6	1328.1	1331.6	1335.1	1335.1	1338.6
37.5°	1229.8	1233.3	1236.8	1240.3	1247.3	1247.3	1247.3	1247.3
40°	1134.9	1138.4	1145.4	1141.9	1156.0	1159.5	1156.0	1156.0
42.5°	1036.5	1043.5	1047.0	1054.1	1057.6	1064.6	1068.1	1068.1
45°	945.1	948.6	955.6	962.7	966.2	976.8	976.8	976.8
47.5°	850.3	857.3	860.9	867.8	871.3	881.9	885.4	881.9
50°	758.9	766.0	773.0	773.0	783.6	787.1	794.0	797.5
52.5°	671.1	674.6	681.6	685.1	692.2	699.2	702.7	706.3
55°	586.7	590.3	597.3	597.3	607.8	611.4	618.4	618.4
57.5°	509.4	513.0	520.0	516.5	523.5	530.5	530.5	527.0
60°	435.7	435.7	435.7	442.7	446.2	449.7	453.2	453.2
62.5°	358.4	365.4	368.9	368.9	372.4	375.9	375.9	372.4
65°	288.1	295.1	298.6	298.6	302.2	302.2	302.2	305.7
67.5°	217.8	217.8	217.8	221.3	217.8	217.8	217.8	217.8
70°	137.0	137.0	137.0	137.0	133.5	137.0	137.0	140.5
72.5°	73.8	73.8	73.8	73.8	73.8	73.8	73.8	73.8
75°	31.7	31.7	31.7	35.2	31.7	31.7	31.7	31.7
77.5°	14.1	10.6	14.1	14.1	10.6	10.6	10.6	10.6
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	0.0	3.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)