

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584930

Luminaire Tested: **HCC8W55D010BZ-HM82555827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010BZ-HM82555827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4938.2 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584930
CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584930

CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	82509	82509	82509
5°	85409	82041	78778
10°	87307	80600	74347
15°	88551	77888	69429
20°	88280	74104	64456
25°	86098	69297	59168
30°	81571	63732	54297
35°	74212	57678	49336
40°	65179	51296	44573
45°	56840	45127	39737
50°	49465	39539	35006
55°	44111	34741	30450
60°	40081	30454	25970
65°	36030	26494	23575
70°	32079	22585	21278
75°	28118	19027	18169
80°	23849	15467	16106
85°	18009	11569	12843



TEST NUMBER: P584930
 CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.6	5.1
10°-20°	690.6	14.0
20°-30°	958.5	19.4
30°-40°	991.0	20.1
40°-50°	829.8	16.8
50°-60°	602.4	12.2
60°-70°	380.2	7.7
70°-80°	188.3	3.8
80°-90°	46.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1899.7	38.5
0°-40°	2890.7	58.5
0°-60°	4322.9	87.5
0°-90°	4938.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4938.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2676	2676	2676	2676	2676	
5°	2759	2726	2650	2578	2545	264
15°	2774	2668	2440	2244	2175	781
25°	2530	2367	2037	1815	1739	1160
35°	1971	1826	1532	1358	1311	1228
45°	1303	1209	1035	933	911	1008
55°	820	748	646	592	566	741
65°	494	432	363	320	323	492
75°	236	196	160	152	152	253
85°	51	40	33	36	36	62
90°	0	0	0	0	0	



TEST NUMBER: P584930

CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7
2.5°	2719.3	2719.3	2722.9	2719.3	2719.3	2719.3	2715.6	2715.6	2712.0	2712.0	2704.7
5°	2759.2	2752.0	2759.2	2752.0	2752.0	2752.0	2748.3	2741.1	2737.4	2730.2	2726.5
7.5°	2777.4	2773.8	2773.8	2770.1	2770.1	2766.5	2762.9	2759.2	2744.7	2741.1	2730.2
10°	2788.3	2784.7	2784.7	2781.0	2773.8	2773.8	2766.5	2762.9	2744.7	2737.4	2722.9
12.5°	2784.7	2784.7	2784.7	2781.0	2770.1	2766.5	2759.2	2748.3	2733.8	2719.3	2704.7
15°	2773.8	2773.8	2766.5	2762.9	2752.0	2744.7	2741.1	2722.9	2708.4	2690.2	2668.5
17.5°	2737.4	2737.4	2733.8	2726.5	2715.6	2708.4	2701.1	2682.9	2668.5	2639.5	2617.7
20°	2690.2	2686.6	2682.9	2672.2	2661.3	2657.6	2646.7	2621.3	2603.1	2581.3	2552.3
22.5°	2621.3	2617.7	2614.0	2606.8	2588.6	2581.3	2574.1	2555.9	2523.2	2501.5	2465.2
25°	2530.5	2530.5	2523.2	2512.3	2494.3	2487.0	2476.1	2457.9	2428.9	2396.2	2367.1
27.5°	2425.2	2421.6	2410.7	2403.4	2388.9	2378.0	2359.8	2338.1	2309.1	2283.6	2247.3
30°	2290.9	2290.9	2283.6	2272.7	2254.6	2247.3	2232.8	2207.3	2178.4	2145.7	2120.3
32.5°	2138.4	2138.4	2127.5	2120.3	2109.4	2091.2	2087.6	2058.5	2033.1	2007.8	1978.7
35°	1971.4	1975.1	1967.8	1953.3	1935.1	1935.1	1927.8	1902.4	1873.3	1848.0	1826.2
37.5°	1804.4	1793.5	1789.9	1782.6	1771.7	1757.2	1749.9	1739.0	1713.6	1695.5	1662.8
40°	1619.2	1622.9	1615.6	1608.3	1604.7	1593.8	1590.2	1572.0	1553.8	1532.2	1517.6
42.5°	1452.2	1452.2	1452.2	1445.0	1437.7	1426.8	1423.2	1412.3	1390.5	1376.0	1354.2
45°	1303.4	1292.5	1292.5	1288.8	1285.2	1277.9	1267.0	1259.8	1245.2	1234.4	1209.0
47.5°	1158.2	1161.8	1158.2	1154.5	1143.6	1140.0	1136.4	1121.8	1107.3	1096.4	1078.2
50°	1031.1	1038.4	1031.1	1031.1	1023.9	1020.2	1013.0	1002.1	991.2	973.0	954.8
52.5°	925.8	925.8	922.1	918.5	907.6	900.3	896.7	893.1	875.0	860.5	845.9
55°	820.5	824.2	824.2	813.3	809.6	802.4	798.7	787.8	780.6	758.8	747.9
57.5°	729.7	726.2	729.7	722.5	715.3	708.0	704.4	697.1	686.2	671.7	657.1
60°	649.9	642.6	642.6	639.0	631.7	628.1	620.8	609.9	599.0	584.5	573.6
62.5°	569.9	566.4	562.8	559.2	551.9	548.3	544.6	533.7	522.8	511.9	501.0
65°	493.8	493.8	490.1	482.9	479.2	475.6	472.0	464.7	450.2	442.9	432.0
67.5°	424.7	421.1	421.1	413.8	406.6	403.1	403.1	395.8	384.9	374.0	366.7
70°	355.8	359.5	355.8	352.2	344.9	344.9	337.7	334.0	319.5	315.9	305.0
72.5°	294.1	294.1	290.4	290.4	283.2	279.5	279.5	272.3	265.0	257.7	250.5
75°	236.0	236.0	236.0	232.4	228.8	221.5	221.5	217.9	210.6	203.3	196.1
77.5°	185.2	181.5	181.5	177.9	174.3	170.6	170.6	167.0	159.7	156.1	148.8
80°	134.3	130.7	130.7	130.7	123.4	127.0	123.4	119.8	116.1	112.5	108.9
82.5°	87.1	90.7	90.7	87.1	83.4	83.4	83.4	79.9	79.9	76.3	72.7
85°	50.9	50.9	50.9	50.9	47.2	47.2	47.2	43.6	43.6	43.6	40.0
87.5°	21.8	21.8	21.8	21.8	21.8	21.8	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584930

CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7
2.5°	2704.7	2697.5	2693.8	2690.2	2690.2	2686.6	2682.9	2675.7	2675.7	2668.5	2664.9
5°	2719.3	2708.4	2701.1	2693.8	2690.2	2682.9	2675.7	2664.9	2661.3	2650.4	2639.5
7.5°	2722.9	2704.7	2697.5	2682.9	2675.7	2668.5	2654.0	2643.1	2628.6	2617.7	2603.1
10°	2708.4	2693.8	2675.7	2657.6	2654.0	2643.1	2621.3	2606.8	2588.6	2574.1	2552.3
12.5°	2686.6	2664.9	2646.7	2624.9	2614.0	2603.1	2581.3	2559.5	2534.1	2508.8	2487.0
15°	2650.4	2624.9	2599.5	2574.1	2559.5	2548.6	2523.2	2497.9	2472.5	2439.8	2418.0
17.5°	2595.9	2566.8	2541.4	2508.8	2494.3	2483.4	2450.7	2421.6	2388.9	2356.2	2334.5
20°	2526.8	2490.6	2461.6	2425.2	2414.3	2396.2	2363.5	2330.9	2294.5	2258.2	2232.8
22.5°	2436.1	2399.8	2367.1	2330.9	2312.7	2294.5	2261.8	2221.9	2185.7	2156.6	2131.2
25°	2330.9	2298.2	2258.2	2225.5	2203.7	2182.0	2145.7	2113.0	2080.3	2036.7	2011.4
27.5°	2214.6	2174.8	2145.7	2102.1	2080.3	2065.8	2025.8	1982.3	1953.3	1913.3	1884.2
30°	2083.9	2047.6	2015.0	1971.4	1949.6	1935.1	1898.8	1858.9	1829.8	1789.9	1760.8
32.5°	1946.0	1906.0	1866.1	1837.1	1811.7	1797.1	1757.2	1731.7	1695.5	1662.8	1630.1
35°	1797.1	1757.2	1728.1	1688.3	1673.7	1659.2	1626.5	1593.8	1561.1	1532.2	1506.7
37.5°	1637.4	1608.3	1575.6	1546.6	1535.8	1521.3	1481.3	1452.2	1426.8	1397.7	1376.0
40°	1481.3	1455.9	1434.1	1405.0	1386.8	1376.0	1347.0	1321.5	1292.5	1274.3	1252.5
42.5°	1339.7	1310.6	1288.8	1267.0	1248.9	1238.0	1212.7	1194.5	1172.7	1154.5	1129.1
45°	1190.9	1176.3	1150.9	1132.7	1121.8	1107.3	1089.1	1067.3	1049.3	1034.8	1016.6
47.5°	1060.1	1045.7	1027.5	1005.7	998.4	987.5	969.4	954.8	940.3	925.8	907.6
50°	940.3	922.1	907.6	893.1	885.9	875.0	856.8	849.6	838.7	824.2	813.3
52.5°	831.4	816.9	802.4	784.2	780.6	773.3	762.4	747.9	737.0	729.7	722.5
55°	733.3	718.9	708.0	693.5	689.8	682.6	668.0	660.8	653.5	646.2	639.0
57.5°	646.2	631.7	617.2	609.9	602.6	595.4	591.7	580.8	573.6	569.9	562.8
60°	566.4	551.9	541.0	530.1	526.5	522.8	515.6	508.3	501.0	493.8	490.1
62.5°	490.1	475.6	468.3	461.1	453.8	453.8	446.5	439.3	432.0	428.4	421.1
65°	421.1	413.8	403.1	392.2	388.5	388.5	377.6	374.0	370.4	363.1	355.8
67.5°	355.8	348.6	337.7	334.0	330.4	326.8	323.1	315.9	308.6	305.0	297.7
70°	297.7	290.4	283.2	279.5	275.9	272.3	265.0	261.4	254.1	250.5	246.8
72.5°	239.7	236.0	228.8	225.1	221.5	217.9	214.2	210.6	203.3	199.7	196.1
75°	192.4	188.8	181.5	177.9	174.3	174.3	170.6	163.4	159.7	159.7	156.1
77.5°	145.2	141.6	137.9	134.3	130.7	130.7	127.0	123.4	119.8	119.8	116.1
80°	105.2	101.6	98.0	98.0	98.0	94.3	90.7	90.7	87.1	87.1	83.4
82.5°	69.0	69.0	65.4	65.4	65.4	61.8	61.8	58.1	58.1	58.1	58.1
85°	40.0	40.0	40.0	36.3	36.3	36.3	36.3	36.3	36.3	32.7	36.3
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584930

CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7
2.5°	2661.3	2657.6	2650.4	2650.4	2643.1	2643.1	2639.5	2635.8	2632.2	2628.6	2624.9
5°	2635.8	2621.3	2614.0	2610.4	2603.1	2599.5	2588.6	2581.3	2577.7	2570.4	2563.2
7.5°	2588.6	2574.1	2559.5	2555.9	2552.3	2537.7	2526.8	2515.9	2508.8	2501.5	2494.3
10°	2534.1	2519.6	2501.5	2494.3	2487.0	2468.8	2454.3	2443.4	2428.9	2414.3	2410.7
12.5°	2468.8	2447.0	2425.2	2418.0	2407.1	2388.9	2374.4	2356.2	2345.4	2327.2	2323.6
15°	2392.5	2367.1	2349.0	2330.9	2323.6	2305.4	2280.0	2265.5	2243.7	2236.4	2218.2
17.5°	2301.8	2276.4	2250.9	2243.7	2232.8	2207.3	2182.0	2163.9	2142.1	2131.2	2120.3
20°	2207.3	2174.8	2149.3	2142.1	2127.5	2105.7	2080.3	2062.1	2044.0	2022.3	2011.4
22.5°	2098.5	2062.1	2040.3	2022.3	2018.7	1993.2	1964.2	1949.6	1935.1	1916.9	1902.4
25°	1978.7	1946.0	1920.6	1906.0	1898.8	1877.0	1855.3	1837.1	1815.3	1804.4	1786.2
27.5°	1855.3	1833.5	1800.8	1786.2	1775.3	1757.2	1731.7	1720.8	1699.2	1684.6	1673.7
30°	1735.4	1702.7	1684.6	1666.5	1655.6	1637.4	1615.6	1604.7	1586.5	1572.0	1561.1
32.5°	1604.7	1582.9	1557.5	1550.2	1535.8	1517.6	1503.1	1484.9	1470.4	1455.9	1452.2
35°	1484.9	1455.9	1430.4	1423.2	1412.3	1394.1	1386.8	1376.0	1357.9	1354.2	1339.7
37.5°	1354.2	1339.7	1310.6	1299.7	1296.1	1281.6	1267.0	1259.8	1248.9	1238.0	1234.4
40°	1230.7	1212.7	1198.1	1187.2	1180.0	1169.1	1154.5	1150.9	1143.6	1129.1	1125.5
42.5°	1114.6	1096.4	1081.9	1078.2	1067.3	1056.4	1049.3	1038.4	1034.8	1031.1	1023.9
45°	1002.1	991.2	976.6	973.0	969.4	954.8	947.6	940.3	933.0	929.4	922.1
47.5°	900.3	889.5	878.6	875.0	867.7	864.1	853.2	849.6	838.7	835.0	831.4
50°	802.4	795.1	787.8	784.2	776.9	773.3	766.0	758.8	751.5	747.9	744.2
52.5°	715.3	708.0	700.7	697.1	693.5	686.2	678.9	671.7	668.0	664.4	660.8
55°	631.7	624.4	620.8	617.2	613.5	609.9	599.0	595.4	591.7	588.1	580.8
57.5°	555.5	548.3	541.0	541.0	537.4	533.7	526.5	519.2	519.2	511.9	504.7
60°	486.5	479.2	472.0	468.3	464.7	457.4	453.8	450.2	446.5	442.9	435.6
62.5°	413.8	410.2	403.1	403.1	395.8	392.2	388.5	384.9	381.3	374.0	370.4
65°	352.2	348.6	341.3	337.7	337.7	334.0	326.8	323.1	319.5	319.5	315.9
67.5°	294.1	290.4	283.2	279.5	279.5	275.9	272.3	272.3	268.6	265.0	268.6
70°	243.2	236.0	236.0	232.4	232.4	228.8	225.1	225.1	225.1	228.8	228.8
72.5°	192.4	188.8	185.2	185.2	185.2	185.2	181.5	181.5	185.2	188.8	188.8
75°	152.5	148.8	148.8	148.8	145.2	145.2	148.8	148.8	152.5	152.5	152.5
77.5°	112.5	112.5	112.5	112.5	112.5	112.5	116.1	116.1	119.8	119.8	119.8
80°	83.4	83.4	83.4	83.4	83.4	87.1	87.1	87.1	87.1	87.1	90.7
82.5°	58.1	58.1	58.1	58.1	58.1	58.1	58.1	61.8	61.8	61.8	61.8
85°	32.7	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
87.5°	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584930

CATALOG NUMBER: HCC8W55D010BZ-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7	2675.7
2.5°	2621.3	2621.3	2621.3	2624.9	2617.7	2617.7	2617.7	2617.7
5°	2559.5	2555.9	2552.3	2555.9	2548.6	2548.6	2545.0	2545.0
7.5°	2483.4	2479.7	2476.1	2476.1	2468.8	2468.8	2465.2	2461.6
10°	2399.8	2392.5	2396.2	2388.9	2385.3	2381.6	2378.0	2374.4
12.5°	2309.1	2301.8	2298.2	2290.9	2283.6	2280.0	2283.6	2276.4
15°	2211.0	2200.1	2196.4	2189.2	2182.0	2178.4	2178.4	2174.8
17.5°	2102.1	2094.8	2091.2	2083.9	2080.3	2073.0	2069.4	2065.8
20°	2000.5	1982.3	1986.0	1978.7	1975.1	1960.5	1960.5	1964.2
22.5°	1887.9	1877.0	1869.7	1862.5	1858.9	1851.6	1851.6	1848.0
25°	1775.3	1764.4	1760.8	1753.5	1749.9	1742.6	1739.0	1739.0
27.5°	1666.5	1651.9	1651.9	1644.7	1637.4	1633.8	1630.1	1626.5
30°	1550.2	1539.4	1535.8	1535.8	1532.2	1532.2	1521.3	1524.9
32.5°	1441.3	1434.1	1430.4	1423.2	1423.2	1419.5	1419.5	1408.6
35°	1332.4	1321.5	1325.2	1317.9	1314.3	1310.6	1314.3	1310.6
37.5°	1227.1	1219.8	1219.8	1212.7	1212.7	1209.0	1205.4	1212.7
40°	1121.8	1118.2	1114.6	1110.9	1114.6	1110.9	1103.7	1107.3
42.5°	1016.6	1016.6	1013.0	1013.0	1009.3	1009.3	1009.3	1009.3
45°	922.1	918.5	918.5	914.9	914.9	914.9	914.9	911.2
47.5°	827.8	824.2	824.2	824.2	820.5	820.5	816.9	820.5
50°	737.0	737.0	733.3	733.3	737.0	733.3	729.7	729.7
52.5°	653.5	653.5	649.9	649.9	646.2	642.6	646.2	646.2
55°	577.2	573.6	569.9	569.9	566.4	562.8	562.8	566.4
57.5°	504.7	501.0	497.4	497.4	490.1	486.5	486.5	486.5
60°	435.6	428.4	428.4	424.7	424.7	421.1	421.1	421.1
62.5°	370.4	366.7	366.7	366.7	366.7	363.1	363.1	363.1
65°	315.9	315.9	315.9	319.5	319.5	323.1	323.1	323.1
67.5°	272.3	275.9	275.9	275.9	279.5	279.5	279.5	275.9
70°	232.4	232.4	232.4	236.0	236.0	236.0	236.0	236.0
72.5°	192.4	192.4	192.4	192.4	192.4	192.4	192.4	192.4
75°	152.5	156.1	156.1	156.1	152.5	156.1	156.1	152.5
77.5°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8
80°	90.7	90.7	90.7	90.7	90.7	90.7	90.7	90.7
82.5°	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8
85°	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
87.5°	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)