

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584810

Luminaire Tested: **HCC8W50D010BZ-HM82555830-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010BZ-HM82555830-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4220.6 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584810
CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67		
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59		
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47		
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43		
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39		
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69872	69872	69872
5°	72758	69718	66783
10°	75193	68827	63526
15°	77094	67255	60225
20°	77244	64462	57240
25°	75942	60386	54275
30°	71876	55717	51737
35°	65535	50104	48580
40°	56992	44171	44855
45°	48890	38254	41058
50°	41756	32986	36886
55°	36601	28408	32047
60°	32588	24231	26951
65°	28916	19773	21503
70°	25650	14660	12217
75°	21398	7661	3634
80°	16835	2415	604
85°	11994	1203	0



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.5	5.1
10°-20°	598.4	14.2
20°-30°	847.0	20.1
30°-40°	886.1	21.0
40°-50°	739.1	17.5
50°-60°	524.1	12.4
60°-70°	301.9	7.2
70°-80°	97.1	2.3
80°-90°	13.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1658.9	39.3
0°-40°	2545.0	60.3
0°-60°	3808.2	90.2
0°-90°	4220.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4220.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2266	2266	2266	2266	2266	
5°	2350	2320	2252	2185	2158	226
15°	2415	2317	2107	1941	1886	679
25°	2232	2066	1775	1632	1595	1018
35°	1741	1588	1331	1260	1290	1079
45°	1121	1030	877	887	942	869
55°	681	610	528	556	596	615
65°	396	332	271	271	295	396
75°	180	132	64	30	30	195
85°	34	17	3	0	0	42
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9
2.5°	2313.3	2309.9	2306.6	2309.9	2306.6	2309.9	2306.6	2306.6	2303.2	2299.8	2299.8
5°	2350.5	2347.1	2347.1	2347.1	2343.7	2340.3	2340.3	2336.9	2330.2	2326.8	2320.1
7.5°	2374.2	2377.6	2377.6	2377.6	2370.8	2370.8	2364.1	2357.3	2350.5	2343.7	2333.6
10°	2401.4	2401.4	2398.0	2394.6	2387.8	2384.4	2381.0	2374.2	2364.1	2350.5	2340.3
12.5°	2411.5	2411.5	2408.1	2401.4	2398.0	2394.6	2391.2	2381.0	2367.5	2350.5	2336.9
15°	2414.9	2408.1	2404.7	2401.4	2394.6	2384.4	2384.4	2370.8	2353.9	2333.6	2316.7
17.5°	2387.8	2391.2	2384.4	2377.6	2367.5	2360.7	2350.5	2340.3	2320.1	2296.4	2279.4
20°	2353.9	2350.5	2347.1	2336.9	2323.4	2320.1	2309.9	2293.0	2276.0	2248.9	2225.2
22.5°	2299.8	2296.4	2289.6	2282.8	2269.3	2262.5	2252.3	2232.0	2208.2	2181.2	2154.1
25°	2232.0	2225.2	2215.0	2201.5	2191.4	2184.6	2171.1	2150.7	2123.6	2093.1	2066.1
27.5°	2123.6	2133.8	2127.0	2106.7	2096.5	2082.9	2079.5	2052.5	2028.8	1998.3	1967.8
30°	2018.6	2018.6	2008.5	1998.3	1981.3	1971.2	1957.6	1937.4	1913.7	1876.4	1852.6
32.5°	1886.5	1883.1	1869.6	1866.2	1852.6	1832.3	1828.9	1801.9	1778.2	1751.0	1720.5
35°	1740.9	1734.1	1720.5	1710.4	1703.6	1693.5	1683.4	1659.6	1635.9	1608.8	1588.4
37.5°	1574.9	1574.9	1571.5	1554.7	1547.9	1541.1	1530.9	1507.2	1493.6	1466.5	1446.2
40°	1415.8	1412.4	1402.2	1398.8	1392.0	1381.9	1375.1	1361.5	1341.2	1320.9	1300.6
42.5°	1259.9	1263.3	1249.8	1253.2	1239.6	1232.8	1229.4	1209.1	1198.9	1178.7	1161.8
45°	1121.1	1117.7	1110.9	1107.5	1100.7	1094.0	1087.2	1077.0	1060.2	1039.8	1029.7
47.5°	992.4	982.2	982.2	978.8	975.4	961.9	958.5	948.3	938.2	917.9	904.3
50°	870.4	870.4	870.4	867.0	856.9	853.5	846.7	836.5	826.4	812.9	792.6
52.5°	772.2	772.2	772.2	768.9	755.3	751.9	748.5	735.0	721.4	711.2	697.7
55°	680.8	684.2	680.8	674.0	663.9	663.9	653.7	646.9	633.4	623.2	609.6
57.5°	602.9	602.9	596.1	592.7	585.9	582.5	575.7	569.0	552.1	541.9	525.0
60°	528.4	525.0	525.0	518.2	511.4	504.7	501.3	491.1	484.3	467.4	453.8
62.5°	460.6	460.6	453.8	453.8	440.2	440.2	437.0	426.8	416.6	399.7	392.9
65°	396.3	396.3	392.9	389.5	379.3	376.0	372.6	362.4	352.2	342.0	331.9
67.5°	338.7	338.7	331.9	328.5	321.7	318.3	311.7	304.9	294.7	284.5	274.4
70°	284.5	281.1	277.8	274.4	267.6	264.2	257.4	250.6	240.5	233.7	223.5
72.5°	230.3	230.3	226.9	220.1	216.7	213.3	210.0	203.2	193.0	182.9	176.2
75°	179.6	179.6	179.6	172.8	166.0	162.6	162.6	155.8	149.0	138.9	132.1
77.5°	138.9	135.5	132.1	132.1	125.3	121.9	118.5	115.1	105.0	101.6	94.8
80°	94.8	98.2	94.8	91.4	88.0	84.6	84.6	77.9	74.5	67.7	61.0
82.5°	64.3	61.0	61.0	57.6	57.6	54.2	54.2	47.5	44.1	40.7	37.3
85°	33.9	33.9	30.5	30.5	30.5	27.1	27.1	23.7	23.7	20.3	17.0
87.5°	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9
2.5°	2296.4	2289.6	2286.2	2286.2	2282.8	2279.4	2276.0	2272.7	2265.9	2265.9	2259.1
5°	2313.3	2306.6	2303.2	2293.0	2286.2	2286.2	2272.7	2269.3	2259.1	2252.3	2245.5
7.5°	2326.8	2313.3	2303.2	2293.0	2286.2	2279.4	2265.9	2252.3	2238.8	2225.2	2218.4
10°	2326.8	2313.3	2296.4	2279.4	2272.7	2265.9	2248.9	2228.6	2211.6	2198.1	2181.2
12.5°	2320.1	2299.8	2279.4	2265.9	2252.3	2242.1	2221.8	2201.5	2181.2	2154.1	2140.6
15°	2299.8	2272.7	2252.3	2228.6	2218.4	2201.5	2184.6	2154.1	2130.4	2106.7	2089.7
17.5°	2259.1	2225.2	2201.5	2177.8	2160.9	2150.7	2123.6	2096.5	2069.5	2042.4	2022.0
20°	2198.1	2167.7	2140.6	2110.0	2096.5	2082.9	2049.1	2022.0	1994.9	1964.4	1944.2
22.5°	2123.6	2093.1	2055.9	2032.2	2011.8	1994.9	1964.4	1934.0	1906.9	1879.8	1852.6
25°	2032.2	2001.7	1967.8	1930.6	1917.0	1900.1	1866.2	1835.7	1805.3	1774.8	1751.0
27.5°	1934.0	1893.3	1866.2	1825.5	1812.1	1795.1	1757.8	1723.9	1696.8	1673.2	1646.1
30°	1815.5	1784.9	1747.7	1710.4	1696.8	1680.0	1649.5	1618.9	1591.8	1564.8	1537.7
32.5°	1686.8	1656.2	1618.9	1591.8	1571.5	1558.0	1527.5	1500.4	1473.3	1446.2	1422.6
35°	1551.3	1517.4	1490.2	1463.1	1446.2	1429.3	1398.8	1375.1	1354.8	1331.0	1307.4
37.5°	1412.4	1388.7	1361.5	1331.0	1314.2	1300.6	1276.9	1249.8	1232.8	1212.5	1195.5
40°	1276.9	1249.8	1226.0	1198.9	1185.5	1175.3	1151.6	1131.2	1114.3	1097.3	1087.2
42.5°	1138.0	1114.3	1090.6	1073.6	1063.6	1053.4	1036.4	1012.7	1002.5	985.6	975.4
45°	1009.3	989.0	972.0	948.3	941.5	934.8	914.5	897.6	887.4	877.2	870.4
47.5°	887.4	873.8	853.5	839.9	829.8	823.0	809.5	796.0	785.8	779.0	772.2
50°	782.4	765.5	751.9	738.3	731.6	721.4	707.8	701.0	694.3	687.6	687.6
52.5°	684.2	667.3	653.7	643.5	636.8	630.0	619.8	616.4	609.6	609.6	606.2
55°	592.7	582.5	569.0	555.5	552.1	548.7	541.9	535.2	531.8	528.4	531.8
57.5°	514.8	504.7	491.1	480.9	477.5	474.1	470.8	464.0	460.6	460.6	460.6
60°	443.6	433.6	423.4	413.2	413.2	406.5	403.1	399.7	396.3	392.9	392.9
62.5°	379.3	369.2	359.0	352.2	348.8	345.4	338.7	335.3	331.9	331.9	328.5
65°	321.7	308.3	304.9	294.7	291.3	287.9	284.5	277.8	274.4	271.0	267.6
67.5°	264.2	257.4	247.2	240.5	237.1	233.7	230.3	223.5	220.1	216.7	210.0
70°	213.3	206.6	199.8	193.0	189.6	186.3	179.6	172.8	169.4	162.6	152.4
72.5°	166.0	159.2	152.4	145.7	142.3	138.9	132.1	125.3	118.5	111.8	105.0
75°	125.3	118.5	108.4	101.6	98.2	98.2	88.0	81.2	74.5	64.3	57.6
77.5°	88.0	77.9	74.5	67.7	64.3	57.6	50.9	44.1	37.3	33.9	27.1
80°	57.6	50.9	44.1	40.7	37.3	33.9	30.5	23.7	17.0	13.6	10.2
82.5°	33.9	30.5	27.1	23.7	20.3	17.0	13.6	13.6	10.2	6.8	3.4
85°	17.0	13.6	10.2	10.2	6.8	6.8	6.8	3.4	3.4	3.4	3.4
87.5°	6.8	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9
2.5°	2255.7	2252.3	2248.9	2245.5	2245.5	2238.8	2238.8	2235.4	2228.6	2225.2	2225.2
5°	2235.4	2225.2	2218.4	2215.0	2211.6	2201.5	2198.1	2191.4	2184.6	2177.8	2174.5
7.5°	2204.9	2188.0	2181.2	2177.8	2167.7	2157.5	2150.7	2140.6	2130.4	2120.2	2116.8
10°	2167.7	2150.7	2133.8	2127.0	2116.8	2110.0	2096.5	2082.9	2072.8	2062.7	2052.5
12.5°	2120.2	2099.9	2082.9	2076.1	2066.1	2052.5	2032.2	2025.4	2008.5	2001.7	1988.1
15°	2066.1	2042.4	2025.4	2015.2	2005.1	1984.7	1971.2	1957.6	1940.8	1934.0	1920.4
17.5°	1998.3	1971.2	1954.2	1944.2	1937.4	1920.4	1900.1	1883.1	1866.2	1859.4	1849.2
20°	1917.0	1900.1	1876.4	1866.2	1859.4	1839.1	1818.8	1812.1	1798.5	1784.9	1774.8
22.5°	1825.5	1808.7	1784.9	1774.8	1771.4	1754.4	1737.5	1727.3	1717.1	1707.0	1696.8
25°	1730.7	1710.4	1690.1	1683.4	1676.6	1663.0	1649.5	1642.7	1632.5	1625.7	1618.9
27.5°	1629.1	1608.8	1591.8	1581.7	1574.9	1564.8	1558.0	1551.3	1544.5	1537.7	1534.3
30°	1520.8	1500.4	1486.9	1480.1	1473.3	1469.9	1459.7	1456.3	1453.0	1446.2	1449.6
32.5°	1412.4	1395.4	1381.9	1371.7	1371.7	1364.9	1361.5	1361.5	1358.1	1358.1	1358.1
35°	1293.8	1283.7	1273.5	1270.1	1266.7	1263.3	1259.9	1263.3	1259.9	1263.3	1266.7
37.5°	1185.5	1175.3	1168.5	1165.1	1161.8	1165.1	1161.8	1161.8	1165.1	1171.9	1175.3
40°	1073.6	1066.8	1060.2	1063.6	1060.2	1060.2	1060.2	1070.2	1073.6	1077.0	1080.4
42.5°	968.6	961.9	958.5	958.5	961.9	958.5	965.2	968.6	975.4	985.6	992.4
45°	867.0	863.7	863.7	867.0	863.7	870.4	870.4	877.2	887.4	894.2	900.9
47.5°	772.2	772.2	772.2	775.6	775.6	779.0	785.8	789.2	796.0	802.8	809.5
50°	684.2	687.6	690.9	690.9	690.9	697.7	704.4	707.8	711.2	714.6	724.8
52.5°	606.2	609.6	609.6	613.0	616.4	619.8	623.2	630.0	633.4	640.1	643.5
55°	531.8	531.8	538.6	541.9	541.9	541.9	548.7	548.7	555.5	558.9	565.6
57.5°	460.6	464.0	464.0	467.4	467.4	470.8	474.1	477.5	480.9	484.3	487.7
60°	392.9	392.9	392.9	396.3	399.7	403.1	399.7	406.5	406.5	413.2	416.6
62.5°	328.5	331.9	331.9	331.9	331.9	331.9	331.9	335.3	338.7	342.0	345.4
65°	267.6	267.6	267.6	264.2	267.6	264.2	267.6	271.0	271.0	274.4	277.8
67.5°	206.6	206.6	199.8	199.8	203.2	203.2	203.2	203.2	199.8	206.6	206.6
70°	149.0	145.7	142.3	138.9	138.9	135.5	135.5	132.1	132.1	132.1	132.1
72.5°	98.2	91.4	84.6	81.2	77.9	77.9	71.1	67.7	71.1	71.1	71.1
75°	50.9	44.1	40.7	37.3	33.9	33.9	30.5	30.5	30.5	30.5	30.5
77.5°	20.3	17.0	13.6	13.6	10.2	10.2	10.2	10.2	10.2	10.2	10.2
80°	6.8	6.8	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	3.4	0.0	0.0	3.4	0.0	3.4	3.4	3.4	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584810

CATALOG NUMBER: HCC8W50D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9	2265.9
2.5°	2221.8	2221.8	2218.4	2221.8	2215.0	2218.4	2215.0	2215.0
5°	2171.1	2164.3	2164.3	2164.3	2160.9	2160.9	2157.5	2157.5
7.5°	2110.0	2106.7	2103.3	2099.9	2096.5	2093.1	2093.1	2093.1
10°	2049.1	2042.4	2042.4	2039.0	2032.2	2028.8	2028.8	2028.8
12.5°	1977.9	1974.6	1971.2	1971.2	1957.6	1961.0	1957.6	1957.6
15°	1910.3	1906.9	1906.9	1896.7	1889.9	1889.9	1889.9	1886.5
17.5°	1839.1	1835.7	1832.3	1825.5	1818.8	1818.8	1815.5	1818.8
20°	1764.6	1761.2	1754.4	1754.4	1751.0	1747.7	1740.9	1744.3
22.5°	1690.1	1683.4	1680.0	1680.0	1676.6	1676.6	1669.8	1669.8
25°	1612.2	1608.8	1605.4	1608.8	1602.0	1602.0	1595.2	1595.2
27.5°	1530.9	1527.5	1527.5	1527.5	1524.1	1527.5	1524.1	1524.1
30°	1449.6	1449.6	1446.2	1446.2	1449.6	1446.2	1449.6	1453.0
32.5°	1361.5	1361.5	1364.9	1364.9	1368.3	1368.3	1368.3	1368.3
35°	1270.1	1276.9	1276.9	1280.3	1283.7	1287.1	1287.1	1290.5
37.5°	1185.5	1188.9	1192.1	1195.5	1202.3	1202.3	1202.3	1202.3
40°	1094.0	1097.3	1104.1	1100.7	1114.3	1117.7	1114.3	1114.3
42.5°	999.1	1005.9	1009.3	1016.1	1019.5	1026.3	1029.7	1029.7
45°	911.1	914.5	921.3	928.1	931.5	941.5	941.5	941.5
47.5°	819.6	826.4	829.8	836.5	839.9	850.1	853.5	850.1
50°	731.6	738.3	745.1	745.1	755.3	758.7	765.5	768.9
52.5°	646.9	650.3	657.1	660.5	667.3	674.0	677.4	680.8
55°	565.6	569.0	575.7	575.7	585.9	589.3	596.1	596.1
57.5°	491.1	494.5	501.3	497.9	504.7	511.4	511.4	508.0
60°	420.0	420.0	420.0	426.8	430.2	433.6	437.0	437.0
62.5°	345.4	352.2	355.6	355.6	359.0	362.4	362.4	359.0
65°	277.8	284.5	287.9	287.9	291.3	291.3	291.3	294.7
67.5°	210.0	210.0	210.0	213.3	210.0	210.0	210.0	210.0
70°	132.1	132.1	132.1	132.1	128.7	132.1	132.1	135.5
72.5°	71.1	71.1	71.1	71.1	71.1	71.1	71.1	71.1
75°	30.5	30.5	30.5	33.9	30.5	30.5	30.5	30.5
77.5°	13.6	10.2	13.6	13.6	10.2	10.2	10.2	10.2
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	0.0	3.4	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)