

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584940

Luminaire Tested: **HCC8S55D010BZ-HM82555830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010BZ-HM82555830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4907.3 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584940
CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584940

CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80720	80720	80720
5°	82236	80369	78503
10°	83522	78966	75634
15°	84359	77001	72356
20°	84037	74028	69024
25°	81821	69756	65170
30°	77925	64662	61379
35°	70365	59019	57016
40°	61822	52970	52829
45°	53364	46561	48572
50°	46452	40834	43564
55°	41187	35466	37950
60°	36745	29967	31502
65°	33126	24327	24845
70°	29419	18230	14705
75°	25353	10568	6338
80°	19516	3782	1900
85°	12560	1238	1238



TEST NUMBER: P584940
 CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.7	5.0
10°-20°	684.1	13.9
20°-30°	967.5	19.7
30°-40°	1019.5	20.8
40°-50°	866.5	17.7
50°-60°	623.9	12.7
60°-70°	359.9	7.3
70°-80°	123.1	2.5
80°-90°	16.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1897.4	38.7
0°-40°	2916.9	59.4
0°-60°	4407.3	89.8
0°-90°	4907.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4907.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2618	2618	2618	2618	2618	
5°	2657	2639	2596	2550	2536	254
15°	2642	2561	2412	2306	2266	744
25°	2405	2281	2050	1944	1915	1103
35°	1869	1759	1568	1511	1515	1164
45°	1224	1167	1068	1075	1114	951
55°	766	706	660	685	706	689
65°	454	390	333	326	340	452
75°	213	160	89	57	53	225
85°	36	21	4	4	4	48
90°	0	0	0	0	0	



TEST NUMBER: P584940

CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7
2.5°	2642.5	2646.0	2642.5	2642.5	2639.0	2635.4	2631.8	2628.3	2621.2	2614.1	2614.1
5°	2656.7	2663.8	2656.7	2656.7	2646.0	2639.0	2631.8	2621.2	2607.0	2596.4	2596.4
7.5°	2667.4	2667.4	2667.4	2656.7	2649.5	2639.0	2621.2	2603.5	2585.8	2568.0	2560.9
10°	2667.4	2667.4	2663.8	2649.5	2642.5	2621.2	2603.5	2578.6	2553.8	2528.9	2521.9
12.5°	2656.7	2660.2	2653.2	2639.0	2621.2	2596.4	2571.6	2539.6	2511.2	2482.9	2468.7
15°	2642.5	2639.0	2631.8	2614.1	2592.8	2560.9	2536.1	2500.6	2461.6	2426.2	2412.0
17.5°	2607.0	2607.0	2596.4	2578.6	2550.3	2514.8	2475.8	2436.8	2394.2	2355.3	2337.4
20°	2560.9	2560.9	2546.8	2525.4	2497.1	2451.0	2408.5	2362.3	2312.6	2273.6	2255.9
22.5°	2493.5	2497.1	2479.4	2454.5	2422.6	2369.4	2326.8	2270.0	2220.4	2174.3	2160.1
25°	2404.8	2412.0	2394.2	2369.4	2326.8	2280.7	2227.5	2174.3	2117.6	2071.4	2050.2
27.5°	2302.0	2305.6	2287.9	2263.0	2220.4	2170.8	2117.6	2060.8	2007.6	1957.9	1936.6
30°	2188.5	2174.3	2167.3	2135.3	2089.2	2046.7	1986.3	1940.2	1883.4	1840.9	1816.0
32.5°	2028.8	2036.0	2014.7	1989.8	1954.4	1904.7	1855.0	1801.8	1748.6	1716.7	1699.0
35°	1869.2	1876.4	1865.7	1840.9	1801.8	1759.3	1709.6	1670.7	1624.5	1585.5	1567.8
37.5°	1702.6	1702.6	1695.4	1681.2	1652.9	1613.8	1564.3	1525.2	1486.2	1454.2	1443.7
40°	1535.8	1528.8	1525.2	1514.6	1489.7	1454.2	1422.3	1390.5	1351.4	1330.1	1315.9
42.5°	1372.6	1372.6	1365.6	1354.9	1330.1	1312.4	1280.4	1245.0	1216.7	1195.3	1195.3
45°	1223.7	1227.2	1216.7	1209.5	1195.3	1167.0	1138.6	1113.8	1088.9	1074.7	1067.7
47.5°	1092.4	1092.4	1081.9	1074.7	1060.5	1035.7	1010.8	989.6	971.8	961.3	957.6
50°	968.3	968.3	968.3	950.6	932.9	915.1	897.4	872.6	861.9	854.9	851.2
52.5°	861.9	858.4	858.4	844.2	826.5	805.2	787.5	766.1	755.5	748.4	752.0
55°	766.1	766.1	762.6	744.9	727.1	705.9	688.1	670.4	663.2	656.2	659.7
56°	727.1	727.1	723.6	709.4	688.1	670.4	649.1	631.4	620.7	624.3	624.3
57°	698.7	691.7	691.7	673.9	656.2	631.4	613.7	595.8	588.8	585.3	585.3
58°	663.2	659.7	656.2	638.5	620.7	599.5	581.7	564.0	553.3	553.3	549.8
59°	627.8	627.8	620.7	606.5	588.8	567.5	549.8	532.1	521.4	517.9	517.9
60°	595.8	599.5	588.8	574.6	560.5	535.6	514.3	500.1	489.4	485.9	485.9
61°	567.5	567.5	560.5	542.6	524.9	507.2	485.9	468.2	461.1	454.0	454.0
62°	542.6	535.6	532.1	514.3	496.6	475.2	457.5	439.9	429.2	422.0	425.7
63°	510.8	507.2	500.1	485.9	468.2	446.9	425.7	411.5	400.8	390.2	393.7
64°	485.9	482.4	471.7	457.5	439.9	418.5	397.3	383.1	376.0	365.3	361.8
65°	454.0	450.5	446.9	429.2	411.5	390.2	372.5	358.3	347.6	340.5	333.4
66°	425.7	429.2	422.0	407.9	386.6	368.8	344.1	329.9	322.8	312.1	305.1
67°	400.8	400.8	393.7	379.5	358.3	340.5	322.8	305.1	294.4	283.7	280.2
67.5°	386.6	386.6	379.5	361.8	347.6	326.3	308.6	294.4	280.2	273.1	266.0
68°	372.5	372.5	368.8	354.6	337.0	315.7	297.9	280.2	266.0	255.4	251.9
69°	347.6	351.1	344.1	329.9	312.1	290.9	273.1	258.9	244.7	234.0	227.0
70°	326.3	322.8	315.7	301.4	283.7	269.6	251.9	234.0	219.9	205.7	202.2
71°	297.9	297.9	290.9	280.2	262.5	244.7	227.0	212.8	198.7	180.8	177.3
72°	276.7	276.7	269.6	255.4	241.2	223.5	205.7	188.0	177.3	159.6	152.5
72.5°	262.5	266.0	258.9	244.7	230.5	209.3	195.1	180.8	163.1	149.0	141.9
73°	255.4	251.9	248.3	234.0	216.4	202.2	184.5	170.3	152.5	138.3	131.3



TEST NUMBER: P584940
 CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	159.6	159.6	156.1	141.9	127.7	113.4	99.3	85.1	70.9	56.7	49.7
80°	109.9	113.4	106.4	99.3	88.7	74.5	60.2	49.7	35.5	28.4	21.3
82.5°	70.9	70.9	67.4	60.2	53.2	42.5	35.5	24.8	17.7	14.2	10.7
85°	35.5	39.0	35.5	31.9	24.8	21.3	17.7	10.7	7.1	3.5	3.5
87.5°	14.2	14.2	14.2	10.7	10.7	7.1	3.5	3.5	3.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584940

CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7	2617.7
2.5°	2607.0	2607.0	2600.0	2596.4	2592.8	2589.3	2585.8	2582.2	2582.2	2585.8
5°	2585.8	2578.6	2564.5	2560.9	2550.3	2546.8	2539.6	2536.1	2539.6	2536.1
7.5°	2553.8	2539.6	2521.9	2514.8	2500.6	2493.5	2482.9	2482.9	2475.8	2479.4
10°	2511.2	2490.0	2468.7	2454.5	2443.9	2433.2	2426.2	2419.0	2415.5	2415.5
12.5°	2458.0	2433.2	2412.0	2390.6	2372.9	2365.8	2351.6	2351.6	2344.6	2341.0
15°	2397.8	2365.8	2341.0	2319.7	2305.6	2291.4	2280.7	2273.6	2266.5	2266.5
17.5°	2319.7	2291.4	2266.5	2241.7	2220.4	2209.8	2199.1	2188.5	2188.5	2181.4
20°	2234.7	2202.7	2181.4	2156.6	2138.8	2121.1	2106.9	2106.9	2099.9	2103.4
22.5°	2138.8	2099.9	2078.5	2060.8	2043.0	2028.8	2014.7	2014.7	2011.2	2007.6
25°	2032.4	2000.5	1975.6	1954.4	1943.8	1929.6	1926.1	1918.9	1915.4	1915.4
27.5°	1918.9	1894.1	1862.2	1851.5	1837.3	1830.2	1830.2	1826.7	1819.6	1823.2
30°	1798.3	1770.0	1752.3	1745.1	1730.9	1730.9	1727.4	1720.3	1720.3	1723.8
32.5°	1681.2	1652.9	1638.7	1635.2	1621.0	1621.0	1617.5	1621.0	1621.0	1624.5
35°	1553.6	1528.8	1525.2	1514.6	1511.1	1511.1	1511.1	1518.1	1525.2	1514.6
37.5°	1433.0	1415.2	1404.6	1401.0	1404.6	1404.6	1408.2	1418.8	1415.2	1411.7
40°	1308.9	1294.6	1287.6	1287.6	1294.6	1301.7	1301.7	1312.4	1315.9	1312.4
42.5°	1184.7	1174.1	1174.1	1177.6	1184.7	1188.3	1198.8	1209.5	1213.0	1216.7
45°	1067.7	1067.7	1067.7	1071.2	1074.7	1081.9	1096.1	1106.6	1110.2	1113.8
47.5°	954.1	950.6	961.3	964.8	975.5	979.0	989.6	1003.8	1007.3	1010.8
50°	847.7	854.9	858.4	869.0	876.1	876.1	890.3	897.4	908.1	908.1
52.5°	748.4	759.1	762.6	773.3	776.8	780.3	787.5	798.0	805.2	805.2
55°	659.7	663.2	670.4	673.9	684.6	688.1	695.2	698.7	709.4	705.9
56°	620.7	627.8	631.4	638.5	645.5	649.1	656.2	659.7	666.9	670.4
57°	585.3	588.8	599.5	603.0	610.0	610.0	613.7	624.3	624.3	627.8
58°	549.8	556.9	560.5	564.0	571.1	574.6	581.7	585.3	588.8	585.3
59°	517.9	521.4	524.9	524.9	532.1	532.1	542.6	549.8	553.3	553.3
60°	485.9	485.9	489.4	493.1	500.1	503.7	503.7	510.8	510.8	510.8
61°	454.0	454.0	457.5	461.1	464.7	464.7	471.7	471.7	475.2	478.9
62°	425.7	422.0	422.0	425.7	425.7	432.7	436.3	439.9	443.4	439.9
63°	393.7	390.2	390.2	390.2	390.2	397.3	397.3	400.8	407.9	404.3
64°	358.3	358.3	358.3	358.3	361.8	361.8	368.8	372.5	376.0	379.5
65°	333.4	326.3	322.8	322.8	326.3	329.9	333.4	337.0	340.5	340.5
66°	305.1	297.9	294.4	294.4	294.4	294.4	301.4	301.4	308.6	308.6
67°	273.1	266.0	262.5	258.9	258.9	258.9	269.6	266.0	266.0	266.0
67.5°	262.5	251.9	248.3	244.7	241.2	248.3	244.7	248.3	248.3	244.7
68°	248.3	241.2	234.0	227.0	227.0	227.0	230.5	234.0	230.5	227.0
69°	219.9	216.4	205.7	198.7	195.1	198.7	195.1	198.7	195.1	198.7
70°	195.1	184.5	173.8	170.3	166.7	166.7	166.7	163.1	166.7	163.1
71°	170.3	159.6	149.0	141.9	138.3	138.3	134.8	138.3	134.8	138.3
72°	145.4	134.8	120.6	113.4	113.4	113.4	113.4	109.9	113.4	109.9
72.5°	134.8	120.6	109.9	102.9	99.3	99.3	99.3	99.3	95.8	99.3
73°	124.1	109.9	95.8	92.2	92.2	92.2	88.7	85.1	88.7	88.7



TEST NUMBER: P584940
 CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	42.5	31.9	28.4	28.4	28.4	28.4	28.4	28.4	24.8	24.8
80°	17.7	14.2	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
82.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
85°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	230.5	230.5	223.5	212.8	195.1	177.3	163.1	149.0	131.3	113.4	106.4
75°	212.8	209.3	202.2	191.5	177.3	159.6	145.4	127.7	113.4	95.8	88.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	102.9	85.1	78.1	70.9	70.9	70.9	67.4	67.4	67.4	70.9
75°	81.6	67.4	60.2	53.2	56.7	53.2	56.7	53.2	53.2	53.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)