

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584812

Luminaire Tested: **HCC8W50D010MB-HM82555830-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010MB-HM82555830-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4796.5 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584812
CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584812

CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57				
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50				
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45				
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37				
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33				
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73538	73538	73538
5°	76231	73296	70780
10°	78386	72660	67884
15°	80136	71373	64886
20°	80260	68587	62254
25°	78722	64775	60053
30°	74660	60069	57412
35°	67839	54708	54836
40°	59314	49090	51682
45°	51406	43727	48162
50°	45018	38839	43876
55°	40063	34423	39703
60°	36140	30923	34888
65°	32623	27194	30397
70°	29320	22900	22594
75°	25830	18157	16954
80°	21647	15023	16231
85°	16806	13197	14400



TEST NUMBER: P584812
 CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.0	4.7
10°-20°	633.7	13.2
20°-30°	905.6	18.9
30°-40°	962.3	20.1
40°-50°	828.5	17.3
50°-60°	619.4	12.9
60°-70°	395.1	8.2
70°-80°	179.8	3.7
80°-90°	47.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1764.3	36.8
0°-40°	2726.5	56.8
0°-60°	4174.4	87.0
0°-90°	4796.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4796.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2385	2385	2385	2385	2385	
5°	2463	2429	2368	2307	2287	236
15°	2510	2425	2236	2083	2032	707
25°	2314	2168	1904	1789	1765	1059
35°	1802	1677	1453	1416	1457	1122
45°	1179	1114	1003	1030	1104	916
55°	745	684	640	694	738	670
65°	447	396	373	390	417	446
75°	217	186	152	139	142	230
85°	48	41	37	41	41	57
90°	0	0	0	0	0	



TEST NUMBER: P584812

CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8
2.5°	2428.8	2422.1	2425.4	2422.1	2425.4	2425.4	2418.7	2418.7	2418.7	2418.7	2408.5
5°	2462.7	2459.3	2459.3	2456.0	2452.6	2456.0	2452.6	2449.2	2442.4	2439.0	2428.8
7.5°	2483.1	2483.1	2483.1	2483.1	2479.7	2476.3	2472.9	2466.1	2459.3	2452.6	2445.8
10°	2503.4	2506.8	2503.4	2500.0	2496.6	2489.9	2486.5	2479.7	2469.5	2459.3	2452.6
12.5°	2513.6	2513.6	2510.2	2510.2	2503.4	2500.0	2489.9	2479.7	2469.5	2459.3	2442.4
15°	2510.2	2510.2	2506.8	2503.4	2493.2	2489.9	2483.1	2472.9	2456.0	2442.4	2425.4
17.5°	2489.9	2486.5	2479.7	2479.7	2466.1	2462.7	2456.0	2442.4	2425.4	2405.1	2384.8
20°	2445.8	2445.8	2442.4	2439.0	2425.4	2415.3	2408.5	2391.5	2378.1	2354.4	2334.0
22.5°	2384.8	2391.5	2384.8	2378.1	2361.1	2357.8	2347.6	2327.2	2306.9	2279.8	2256.1
25°	2313.7	2310.3	2306.9	2300.1	2286.6	2279.8	2266.2	2245.9	2225.7	2195.1	2168.0
27.5°	2222.3	2208.7	2208.7	2195.1	2185.0	2174.8	2168.0	2147.7	2120.6	2096.8	2063.1
30°	2096.8	2100.2	2083.3	2079.9	2063.1	2056.3	2042.7	2022.4	1998.6	1971.5	1944.4
32.5°	1961.3	1951.2	1951.2	1937.6	1924.1	1914.0	1910.6	1886.9	1866.5	1839.4	1812.3
35°	1802.1	1802.1	1792.0	1788.6	1775.0	1768.2	1758.2	1744.6	1720.9	1697.2	1676.8
37.5°	1646.3	1639.5	1636.1	1629.4	1619.2	1609.1	1609.1	1585.4	1582.0	1554.9	1527.8
40°	1473.5	1480.3	1473.5	1463.4	1460.0	1453.3	1449.9	1436.4	1426.2	1402.4	1385.5
42.5°	1327.9	1321.1	1321.1	1317.7	1304.3	1304.3	1297.5	1290.7	1273.7	1267.0	1246.6
45°	1178.8	1185.6	1175.4	1178.8	1165.3	1165.3	1165.3	1151.7	1138.3	1128.1	1114.5
47.5°	1050.1	1053.5	1053.5	1043.3	1039.9	1039.9	1033.2	1026.4	1016.2	1002.7	992.6
50°	938.4	941.7	935.0	931.6	924.8	921.4	921.4	907.8	901.1	887.5	880.7
52.5°	836.8	836.8	833.4	833.4	823.2	823.2	816.4	806.3	799.5	792.7	775.7
55°	745.2	745.2	741.8	738.5	738.5	728.3	724.9	714.7	707.9	694.4	684.3
57.5°	657.2	660.6	657.2	653.8	650.4	647.0	640.3	630.1	623.3	613.1	606.4
60°	586.0	586.0	582.6	579.2	572.5	569.1	565.7	558.9	548.7	541.9	531.9
62.5°	518.3	514.9	511.6	508.2	501.4	501.4	494.6	487.8	477.7	470.9	464.1
65°	447.1	447.1	443.8	443.8	440.4	433.6	430.2	426.8	413.2	409.9	396.3
67.5°	382.8	386.1	379.5	379.5	372.7	372.7	369.3	359.1	355.7	348.9	342.2
70°	325.2	325.2	325.2	321.8	315.0	311.7	308.3	301.5	298.1	291.3	284.5
72.5°	267.6	267.6	264.2	264.2	260.8	257.4	254.0	247.2	247.2	240.5	233.7
75°	216.8	216.8	213.5	210.1	206.7	206.7	203.3	199.9	193.1	189.7	186.3
77.5°	166.0	166.0	166.0	162.6	159.2	159.2	159.2	152.4	145.7	145.7	142.3
80°	121.9	121.9	118.5	118.5	115.1	115.1	115.1	111.8	108.4	105.0	101.6
82.5°	81.2	81.2	81.2	81.2	77.9	77.9	77.9	74.6	71.2	71.2	71.2
85°	47.5	47.5	47.5	47.5	44.1	44.1	44.1	44.1	44.1	40.7	40.7
87.5°	20.3	17.0	20.3	17.0	20.3	17.0	20.3	17.0	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584812

CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8
2.5°	2411.9	2408.5	2405.1	2401.7	2401.7	2398.3	2391.5	2388.2	2384.8	2381.4	2381.4
5°	2425.4	2422.1	2415.3	2408.5	2405.1	2398.3	2391.5	2384.8	2378.1	2367.9	2364.5
7.5°	2435.6	2425.4	2418.7	2405.1	2401.7	2394.9	2384.8	2374.7	2361.1	2347.6	2337.4
10°	2435.6	2422.1	2411.9	2394.9	2388.2	2381.4	2367.9	2351.0	2334.0	2320.5	2303.5
12.5°	2428.8	2411.9	2394.9	2378.1	2367.9	2357.8	2337.4	2320.5	2300.1	2279.8	2266.2
15°	2405.1	2384.8	2364.5	2344.2	2334.0	2320.5	2300.1	2276.4	2256.1	2235.7	2212.1
17.5°	2361.1	2340.8	2317.1	2293.3	2279.8	2269.6	2239.1	2222.3	2191.8	2171.4	2151.1
20°	2303.5	2279.8	2249.3	2225.7	2208.7	2198.5	2174.8	2144.3	2120.6	2090.1	2069.8
22.5°	2228.9	2198.5	2168.0	2144.3	2127.3	2113.8	2083.3	2052.9	2032.5	2005.4	1981.7
25°	2140.9	2110.4	2079.9	2046.1	2029.2	2015.6	1988.5	1961.3	1934.2	1903.8	1883.5
27.5°	2035.9	2002.0	1974.9	1944.4	1927.4	1907.2	1876.7	1849.6	1822.5	1802.1	1775.0
30°	1920.7	1883.5	1856.4	1825.9	1808.9	1792.0	1761.6	1734.4	1710.7	1687.0	1673.4
32.5°	1781.8	1754.8	1727.7	1697.2	1683.6	1673.4	1642.9	1615.8	1588.8	1568.4	1558.3
35°	1649.7	1619.2	1595.6	1568.4	1551.5	1541.3	1514.2	1490.5	1476.9	1453.3	1439.7
37.5°	1510.8	1487.1	1460.0	1433.0	1422.8	1412.6	1392.3	1368.5	1348.2	1331.3	1324.5
40°	1365.2	1344.8	1321.1	1304.3	1294.1	1283.9	1267.0	1250.0	1236.5	1219.5	1212.7
42.5°	1226.3	1212.7	1192.4	1172.0	1161.9	1158.5	1138.3	1124.7	1117.9	1111.1	1104.4
45°	1101.0	1080.6	1067.1	1053.5	1043.3	1036.6	1026.4	1016.2	1009.4	1002.7	996.0
47.5°	979.0	962.1	948.5	938.4	928.2	924.8	918.0	907.8	901.1	901.1	901.1
50°	867.2	853.6	840.2	833.4	830.0	823.2	816.4	813.0	809.6	809.6	809.6
52.5°	769.0	755.4	745.2	738.5	738.5	731.7	724.9	721.5	721.5	721.5	721.5
55°	677.6	667.4	660.6	653.8	647.0	643.7	643.7	643.7	640.3	640.3	643.7
57.5°	596.2	589.4	579.2	572.5	569.1	569.1	565.7	562.3	565.7	569.1	572.5
60°	521.7	514.9	511.6	501.4	501.4	501.4	498.0	498.0	498.0	501.4	504.8
62.5°	453.9	450.5	443.8	440.4	437.0	437.0	433.6	433.6	433.6	433.6	437.0
65°	392.9	386.1	379.5	379.5	379.5	376.1	376.1	369.3	372.7	372.7	369.3
67.5°	335.4	328.6	325.2	321.8	318.4	318.4	315.0	311.7	308.3	308.3	308.3
70°	281.1	274.4	274.4	267.6	267.6	264.2	260.8	260.8	257.4	254.0	250.6
72.5°	227.0	223.6	220.2	216.8	216.8	216.8	213.5	210.1	206.7	203.3	196.5
75°	179.6	179.6	172.8	169.4	169.4	166.0	162.6	159.2	155.8	152.4	149.0
77.5°	138.9	135.5	128.7	125.3	125.3	125.3	121.9	118.5	115.1	111.8	108.4
80°	101.6	98.2	94.8	91.4	91.4	91.4	88.0	88.0	84.6	84.6	84.6
82.5°	67.8	67.8	64.4	64.4	64.4	64.4	61.0	61.0	61.0	61.0	61.0
85°	40.7	40.7	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584812

CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8
2.5°	2374.7	2374.7	2367.9	2364.5	2361.1	2364.5	2357.8	2354.4	2351.0	2351.0	2347.6
5°	2354.4	2351.0	2337.4	2334.0	2330.6	2327.2	2320.5	2313.7	2306.9	2303.5	2300.1
7.5°	2327.2	2317.1	2303.5	2300.1	2296.7	2286.6	2276.4	2269.6	2259.4	2256.1	2249.3
10°	2290.0	2276.4	2266.2	2256.1	2249.3	2239.1	2228.9	2218.9	2205.3	2201.9	2191.8
12.5°	2245.9	2228.9	2208.7	2205.3	2195.1	2181.6	2168.0	2157.9	2147.7	2140.9	2130.7
15°	2191.8	2174.8	2154.5	2144.3	2134.1	2124.0	2107.0	2093.4	2083.3	2073.1	2063.1
17.5°	2127.3	2107.0	2090.1	2079.9	2073.1	2056.3	2042.7	2025.8	2015.6	2005.4	1995.2
20°	2049.5	2032.5	2008.8	1998.6	1995.2	1981.7	1964.7	1958.0	1944.4	1934.2	1927.4
22.5°	1961.3	1944.4	1924.1	1917.4	1903.8	1897.1	1880.1	1873.3	1866.5	1856.4	1853.0
25°	1863.2	1846.2	1829.3	1825.9	1815.7	1808.9	1798.7	1788.6	1788.6	1778.4	1778.4
27.5°	1761.6	1744.6	1731.1	1724.3	1720.9	1714.1	1703.9	1700.5	1697.2	1693.8	1693.8
30°	1653.1	1632.7	1626.0	1622.6	1619.2	1612.4	1609.1	1602.3	1605.7	1609.1	1605.7
32.5°	1537.9	1531.2	1517.6	1510.8	1514.2	1510.8	1504.0	1510.8	1507.4	1514.2	1517.6
35°	1426.2	1419.4	1412.6	1412.6	1405.8	1405.8	1405.8	1409.2	1416.0	1419.4	1426.2
37.5°	1317.7	1307.5	1304.3	1300.9	1304.3	1304.3	1304.3	1310.9	1317.7	1324.5	1334.6
40°	1202.6	1195.8	1195.8	1195.8	1195.8	1205.9	1202.6	1209.3	1216.1	1226.3	1236.5
42.5°	1094.2	1094.2	1097.6	1097.6	1097.6	1097.6	1104.4	1114.5	1124.7	1134.9	1145.0
45°	992.6	992.6	992.6	999.3	999.3	1002.7	1016.2	1023.0	1029.8	1039.9	1050.1
47.5°	897.7	897.7	901.1	904.5	907.8	914.6	921.4	931.6	941.7	948.5	958.7
50°	809.6	813.0	819.8	826.6	826.6	830.0	840.2	846.8	853.6	863.8	867.2
52.5°	724.9	731.7	738.5	741.8	745.2	752.0	755.4	765.6	769.0	779.1	782.5
55°	647.0	650.4	660.6	664.0	664.0	670.8	677.6	684.3	694.4	694.4	701.2
57.5°	575.8	579.2	586.0	589.4	586.0	596.2	599.6	606.4	609.8	616.5	619.9
60°	504.8	511.6	514.9	514.9	518.3	521.7	528.5	528.5	535.3	541.9	541.9
62.5°	437.0	440.4	443.8	447.1	450.5	447.1	457.3	457.3	464.1	467.5	474.3
65°	372.7	376.1	376.1	379.5	379.5	382.8	382.8	386.1	389.5	396.3	399.7
67.5°	308.3	308.3	308.3	311.7	308.3	311.7	311.7	315.0	315.0	321.8	325.2
70°	250.6	247.2	243.9	243.9	243.9	243.9	240.5	243.9	243.9	247.2	247.2
72.5°	193.1	189.7	186.3	182.9	182.9	179.6	176.2	179.6	179.6	182.9	182.9
75°	145.7	138.9	138.9	138.9	135.5	135.5	135.5	138.9	138.9	138.9	142.3
77.5°	108.4	108.4	105.0	105.0	105.0	108.4	108.4	111.8	111.8	111.8	111.8
80°	81.2	84.6	84.6	84.6	84.6	88.0	88.0	88.0	88.0	91.4	91.4
82.5°	61.0	61.0	61.0	61.0	64.4	64.4	64.4	64.4	64.4	64.4	64.4
85°	37.3	40.7	40.7	37.3	40.7	40.7	40.7	40.7	40.7	40.7	40.7
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584812

CATALOG NUMBER: HCC8W50D010MB-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8	2384.8
2.5°	2344.2	2344.2	2344.2	2344.2	2340.8	2340.8	2340.8	2337.4
5°	2293.3	2293.3	2293.3	2286.6	2290.0	2290.0	2283.2	2286.6
7.5°	2242.5	2239.1	2235.7	2235.7	2232.3	2228.9	2225.7	2228.9
10°	2185.0	2174.8	2174.8	2171.4	2171.4	2164.6	2164.6	2168.0
12.5°	2120.6	2113.8	2113.8	2110.4	2107.0	2103.6	2100.2	2100.2
15°	2056.3	2049.5	2046.1	2042.7	2039.3	2032.5	2035.9	2032.5
17.5°	1991.9	1981.7	1981.7	1978.3	1974.9	1968.1	1968.1	1964.7
20°	1917.4	1914.0	1907.2	1910.6	1907.2	1900.4	1897.1	1897.1
22.5°	1842.8	1842.8	1839.4	1839.4	1836.0	1832.6	1829.3	1829.3
25°	1771.6	1768.2	1771.6	1771.6	1761.6	1761.6	1761.6	1765.0
27.5°	1690.4	1693.8	1690.4	1690.4	1690.4	1690.4	1693.8	1690.4
30°	1609.1	1609.1	1609.1	1612.4	1619.2	1615.8	1615.8	1612.4
32.5°	1521.0	1524.4	1524.4	1527.8	1531.2	1537.9	1537.9	1541.3
35°	1433.0	1439.7	1443.1	1439.7	1449.9	1449.9	1456.7	1456.7
37.5°	1341.4	1344.8	1351.6	1355.0	1361.8	1365.2	1368.5	1368.5
40°	1243.2	1256.8	1260.2	1263.6	1273.7	1273.7	1277.1	1283.9
42.5°	1151.7	1165.3	1168.6	1172.0	1178.8	1189.0	1185.6	1192.4
45°	1063.7	1073.8	1077.2	1080.6	1090.8	1094.2	1094.2	1104.4
47.5°	968.9	975.6	979.0	985.8	992.6	999.3	1006.0	1002.7
50°	873.9	884.1	890.9	894.3	904.5	907.8	911.2	914.6
52.5°	789.3	796.1	799.5	802.9	813.0	816.4	819.8	826.6
55°	707.9	711.3	718.1	714.7	724.9	728.3	731.7	738.5
57.5°	626.7	630.1	633.5	633.5	640.3	647.0	650.4	653.8
60°	548.7	555.5	558.9	558.9	558.9	565.7	565.7	565.7
62.5°	477.7	477.7	481.0	481.0	487.8	487.8	487.8	487.8
65°	403.1	406.5	409.9	409.9	416.6	413.2	420.0	416.6
67.5°	325.2	325.2	332.0	332.0	328.6	332.0	332.0	332.0
70°	247.2	247.2	250.6	250.6	250.6	250.6	250.6	250.6
72.5°	182.9	182.9	182.9	186.3	182.9	182.9	186.3	182.9
75°	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3
77.5°	111.8	111.8	115.1	115.1	115.1	115.1	115.1	115.1
80°	91.4	91.4	91.4	91.4	94.8	91.4	91.4	91.4
82.5°	67.8	64.4	67.8	64.4	67.8	67.8	67.8	67.8
85°	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)