

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584957

Luminaire Tested: **HCC8W55D010MW-HM82555835-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MW-HM82555835-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5201.8 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584957
CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584957

CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77			77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59			59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35			35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85565	85565	85565
5°	87170	85192	83214
10°	88532	83703	80174
15°	89423	81620	76701
20°	89080	78468	73165
25°	86734	73941	69083
30°	82604	68543	65064
35°	74592	62561	60434
40°	65533	56150	56001
45°	56570	49352	51485
50°	49239	43286	46179
55°	43660	37595	40224
60°	38959	31768	33396
65°	35111	25793	26340
70°	31186	19330	15598
75°	26879	11199	6720
80°	20706	3996	2007
85°	13303	1344	1344



TEST NUMBER: P584957
 CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.5	5.0
10°-20°	725.1	13.9
20°-30°	1025.6	19.7
30°-40°	1080.7	20.8
40°-50°	918.5	17.7
50°-60°	661.4	12.7
60°-70°	381.5	7.3
70°-80°	130.6	2.5
80°-90°	18.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.2	38.7
0°-40°	3092.0	59.4
0°-60°	4671.8	89.8
0°-90°	5201.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5201.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2775	2775	2775	2775	2775	
5°	2816	2797	2752	2703	2688	269
15°	2801	2715	2557	2444	2403	789
25°	2549	2418	2173	2060	2030	1169
35°	1982	1865	1662	1602	1605	1234
45°	1297	1237	1132	1139	1181	1008
55°	812	748	699	726	748	731
65°	481	414	354	346	361	479
75°	226	169	94	60	56	238
85°	38	22	4	4	4	51
90°	0	0	0	0	0	



TEST NUMBER: P584957

CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8
2.5°	2801.1	2804.8	2801.1	2801.1	2797.3	2793.6	2789.8	2786.1	2778.6	2771.1	2771.1
5°	2816.1	2823.7	2816.1	2816.1	2804.8	2797.3	2789.8	2778.6	2763.5	2752.2	2752.2
7.5°	2827.4	2827.4	2827.4	2816.1	2808.6	2797.3	2778.6	2759.7	2741.0	2722.1	2714.6
10°	2827.4	2827.4	2823.7	2808.6	2801.1	2778.6	2759.7	2733.5	2707.1	2680.8	2673.2
12.5°	2816.1	2819.9	2812.3	2797.3	2778.6	2752.2	2726.0	2692.1	2662.0	2632.0	2616.8
15°	2801.1	2797.3	2789.8	2771.1	2748.5	2714.6	2688.3	2650.7	2609.3	2571.7	2556.7
17.5°	2763.5	2763.5	2752.2	2733.5	2703.3	2665.7	2624.3	2583.0	2538.0	2496.6	2477.7
20°	2714.6	2714.6	2699.6	2677.1	2647.0	2598.1	2553.0	2504.1	2451.5	2410.1	2391.2
22.5°	2643.2	2647.0	2628.1	2601.8	2568.0	2511.6	2466.5	2406.4	2353.7	2304.9	2289.7
25°	2549.2	2556.7	2538.0	2511.6	2466.5	2417.6	2361.2	2304.9	2244.6	2195.7	2173.2
27.5°	2440.1	2444.0	2425.1	2398.8	2353.7	2301.0	2244.6	2184.5	2128.1	2075.5	2052.9
30°	2319.9	2304.9	2297.2	2263.5	2214.6	2169.5	2105.5	2056.6	1996.5	1951.4	1925.0
32.5°	2150.6	2158.1	2135.6	2109.2	2071.7	2019.0	1966.4	1910.0	1853.6	1819.8	1801.0
35°	1981.5	1989.0	1977.6	1951.4	1910.0	1864.9	1812.3	1770.9	1722.0	1680.6	1661.9
37.5°	1804.8	1804.8	1797.3	1782.1	1752.1	1710.8	1658.1	1616.8	1575.4	1541.5	1530.3
40°	1628.0	1620.5	1616.8	1605.4	1579.2	1541.5	1507.7	1473.9	1432.5	1409.9	1394.9
42.5°	1455.0	1455.0	1447.5	1436.3	1409.9	1391.2	1357.3	1319.7	1289.7	1267.0	1267.0
45°	1297.2	1300.9	1289.7	1282.2	1267.0	1237.0	1206.9	1180.6	1154.3	1139.2	1131.7
47.5°	1158.1	1158.1	1146.8	1139.2	1124.2	1097.9	1071.6	1049.1	1030.2	1018.9	1015.2
50°	1026.4	1026.4	1026.4	1007.7	988.8	970.1	951.2	924.9	913.7	906.1	902.3
52.5°	913.7	909.9	909.9	894.8	876.1	853.5	834.7	812.1	800.8	793.3	797.1
55°	812.1	812.1	808.3	789.6	770.8	748.2	729.5	710.6	703.1	695.6	699.3
56°	770.8	770.8	767.0	752.0	729.5	710.6	688.1	669.2	658.0	661.7	661.7
57°	740.7	733.2	733.2	714.3	695.6	669.2	650.5	631.7	624.1	620.3	620.3
58°	703.1	699.3	695.6	676.8	658.0	635.5	616.6	597.8	586.6	586.6	582.8
59°	665.5	665.5	658.0	643.0	624.1	601.6	582.8	564.0	552.7	549.0	549.0
60°	631.7	635.5	624.1	609.1	594.1	567.7	545.2	530.1	518.8	515.1	515.1
61°	601.6	601.6	594.1	575.2	556.5	537.7	515.1	496.3	488.8	481.2	481.2
62°	575.2	567.7	564.0	545.2	526.3	503.8	485.0	466.2	455.0	447.5	451.2
63°	541.5	537.7	530.1	515.1	496.3	473.7	451.2	436.1	424.8	413.6	417.3
64°	515.1	511.3	500.1	485.0	466.2	443.7	421.1	406.1	398.6	387.2	383.5
65°	481.2	477.5	473.7	455.0	436.1	413.6	394.7	379.7	368.5	361.0	353.5
66°	451.2	455.0	447.5	432.4	409.8	391.0	364.7	349.7	342.1	330.9	323.4
67°	424.8	424.8	417.3	402.3	379.7	361.0	342.1	323.4	312.1	300.7	297.0
67.5°	409.8	409.8	402.3	383.5	368.5	345.9	327.1	312.1	297.0	289.5	282.0
68°	394.7	394.7	391.0	376.0	357.2	334.6	315.9	297.0	282.0	270.7	267.0
69°	368.5	372.2	364.7	349.7	330.9	308.4	289.5	274.5	259.5	248.1	240.6
70°	345.9	342.1	334.6	319.6	300.7	285.7	267.0	248.1	233.1	218.1	214.4
71°	315.9	315.9	308.4	297.0	278.2	259.5	240.6	225.6	210.6	191.7	188.0
72°	293.2	293.2	285.7	270.7	255.6	236.9	218.1	199.2	188.0	169.2	161.6
72.5°	278.2	282.0	274.5	259.5	244.4	221.9	206.7	191.7	173.0	157.9	150.4
73°	270.7	267.0	263.2	248.1	229.4	214.4	195.5	180.5	161.6	146.6	139.1



TEST NUMBER: P584957

CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	169.2	169.2	165.5	150.4	135.4	120.4	105.2	90.2	75.2	60.1	52.6
80°	116.6	120.4	112.7	105.2	94.0	79.0	63.9	52.6	37.6	30.1	22.5
82.5°	75.2	75.2	71.5	63.9	56.4	45.1	37.6	26.4	18.8	15.0	11.3
85°	37.6	41.4	37.6	33.9	26.4	22.5	18.8	11.3	7.5	3.8	3.8
87.5°	15.0	15.0	15.0	11.3	11.3	7.5	3.8	3.8	3.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584957

CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8	2774.8
2.5°	2763.5	2763.5	2756.0	2752.2	2748.5	2744.7	2741.0	2737.2	2737.2	2741.0
5°	2741.0	2733.5	2718.3	2714.6	2703.3	2699.6	2692.1	2688.3	2692.1	2688.3
7.5°	2707.1	2692.1	2673.2	2665.7	2650.7	2643.2	2632.0	2632.0	2624.3	2628.1
10°	2662.0	2639.5	2616.8	2601.8	2590.6	2579.2	2571.7	2564.2	2560.5	2560.5
12.5°	2605.6	2579.2	2556.7	2534.1	2515.3	2507.8	2492.8	2492.8	2485.2	2481.5
15°	2541.7	2507.8	2481.5	2459.0	2444.0	2428.9	2417.6	2410.1	2402.6	2402.6
17.5°	2459.0	2428.9	2402.6	2376.2	2353.7	2342.4	2331.1	2319.9	2319.9	2312.4
20°	2368.7	2334.9	2312.4	2286.0	2267.2	2248.4	2233.4	2233.4	2225.9	2229.6
22.5°	2267.2	2225.9	2203.2	2184.5	2165.7	2150.6	2135.6	2135.6	2131.9	2128.1
25°	2154.4	2120.6	2094.2	2071.7	2060.4	2045.4	2041.6	2034.1	2030.4	2030.4
27.5°	2034.1	2007.8	1973.9	1962.6	1947.6	1940.1	1940.1	1936.4	1928.8	1932.6
30°	1906.3	1876.1	1857.4	1849.9	1834.8	1834.8	1831.0	1823.5	1823.5	1827.3
32.5°	1782.1	1752.1	1737.0	1733.3	1718.3	1718.3	1714.5	1718.3	1718.3	1722.0
35°	1646.8	1620.5	1616.8	1605.4	1601.7	1601.7	1601.7	1609.3	1616.8	1605.4
37.5°	1519.0	1500.2	1488.9	1485.2	1488.9	1488.9	1492.7	1503.9	1500.2	1496.4
40°	1387.4	1372.3	1364.8	1364.8	1372.3	1379.9	1379.9	1391.2	1394.9	1391.2
42.5°	1255.8	1244.5	1244.5	1248.3	1255.8	1259.5	1270.8	1282.2	1285.9	1289.7
45°	1131.7	1131.7	1131.7	1135.4	1139.2	1146.8	1161.8	1173.1	1176.8	1180.6
47.5°	1011.4	1007.7	1018.9	1022.7	1033.9	1037.7	1049.1	1064.1	1067.8	1071.6
50°	898.6	906.1	909.9	921.2	928.7	928.7	943.7	951.2	962.6	962.6
52.5°	793.3	804.6	808.3	819.7	823.4	827.2	834.7	845.9	853.5	853.5
55°	699.3	703.1	710.6	714.3	725.7	729.5	737.0	740.7	752.0	748.2
56°	658.0	665.5	669.2	676.8	684.3	688.1	695.6	699.3	706.8	710.6
57°	620.3	624.1	635.5	639.2	646.7	646.7	650.5	661.7	661.7	665.5
58°	582.8	590.3	594.1	597.8	605.3	609.1	616.6	620.3	624.1	620.3
59°	549.0	552.7	556.5	556.5	564.0	564.0	575.2	582.8	586.6	586.6
60°	515.1	515.1	518.8	522.6	530.1	533.8	533.8	541.5	541.5	541.5
61°	481.2	481.2	485.0	488.8	492.6	492.6	500.1	500.1	503.8	507.6
62°	451.2	447.5	447.5	451.2	451.2	458.7	462.5	466.2	470.0	466.2
63°	417.3	413.6	413.6	413.6	413.6	421.1	421.1	424.8	432.4	428.6
64°	379.7	379.7	379.7	379.7	383.5	383.5	391.0	394.7	398.6	402.3
65°	353.5	345.9	342.1	342.1	345.9	349.7	353.5	357.2	361.0	361.0
66°	323.4	315.9	312.1	312.1	312.1	312.1	319.6	319.6	327.1	327.1
67°	289.5	282.0	278.2	274.5	274.5	274.5	285.7	282.0	282.0	282.0
67.5°	278.2	267.0	263.2	259.5	255.6	263.2	259.5	263.2	263.2	259.5
68°	263.2	255.6	248.1	240.6	240.6	240.6	244.4	248.1	244.4	240.6
69°	233.1	229.4	218.1	210.6	206.7	210.6	206.7	210.6	206.7	210.6
70°	206.7	195.5	184.2	180.5	176.7	176.7	176.7	173.0	176.7	173.0
71°	180.5	169.2	157.9	150.4	146.6	146.6	142.9	146.6	142.9	146.6
72°	154.1	142.9	127.9	120.4	120.4	120.4	120.4	116.6	120.4	116.6
72.5°	142.9	127.9	116.6	109.0	105.2	105.2	105.2	105.2	101.5	105.2
73°	131.6	116.6	101.5	97.7	97.7	97.7	94.0	90.2	94.0	94.0



TEST NUMBER: P584957
CATALOG NUMBER: HCC8W55D010MW-HM82555835-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	45.1	33.9	30.1	30.1	30.1	30.1	30.1	30.1	26.4	26.4
80°	18.8	15.0	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
82.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	244.4	244.4	236.9	225.6	206.7	188.0	173.0	157.9	139.1	120.4	112.7
75°	225.6	221.9	214.4	203.0	188.0	169.2	154.1	135.4	120.4	101.5	94.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	109.0	90.2	82.7	75.2	75.2	75.2	71.5	71.5	71.5	75.2
75°	86.5	71.5	63.9	56.4	60.1	56.4	60.1	56.4	56.4	56.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)