

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584831

Luminaire Tested: **HCC8S50D010MW-HM82555840-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010MW-HM82555840-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5743.9 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584831
CATALOG NUMBER: HCC8S50D010MW-HM82555840-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584831
 CATALOG NUMBER: HCC8S50D010MW-HM82555840-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87																												
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																												
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																												
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																												
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																												
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																												
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58																												
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55																												
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262679
5°	239374
10°	204524
15°	178360
20°	158974
25°	141016
30°	115458
35°	66299
40°	29426
45°	17125
50°	9887
55°	5645
60°	3114
65°	1985
70°	1397
75°	929
80°	693
85°	1380



TEST NUMBER: P584831
 CATALOG NUMBER: HCC8S50D010MW-HM82555840-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	700.0	12.2
10°-20°	1570.5	27.3
20°-30°	1879.9	32.7
30°-40°	1137.2	19.8
40°-50°	318.7	5.5
50°-60°	99.0	1.7
60°-70°	28.2	0.5
70°-80°	7.7	0.1
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4150.4	72.3
0°-40°	5287.6	92.1
0°-60°	5705.3	99.3
0°-90°	5743.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5743.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8518	
5°	7733	700
15°	5587	1570
25°	4145	1880
35°	1761	1137
45°	393	319
55°	105	99
65°	27	28
75°	8	8
85°	4	3
90°	0	



TEST NUMBER: P584831
CATALOG NUMBER: HCC8S50D010MW-HM82555840-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8518.5
2.5°	8277.5
5°	7733.2
7.5°	7118.9
10°	6531.8
12.5°	6018.6
15°	5587.0
17.5°	5206.0
20°	4844.5
22.5°	4510.0
25°	4144.6
27.5°	3732.5
30°	3242.6
32.5°	2608.9
35°	1761.2
37.5°	1096.4
40°	731.0
42.5°	524.9
45°	392.7
47.5°	287.7
50°	206.1
52.5°	143.9
55°	105.0
57.5°	70.0
60°	50.5
62.5°	35.0
65°	27.2
67.5°	19.4
70°	15.5
72.5°	7.8
75°	7.8
77.5°	3.9
80°	3.9
82.5°	3.9
85°	3.9
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)