

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593823

Luminaire Tested: **HCC8S55D010MB-HM82555850-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593823  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S55D010MB-HM82555850-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6704.5 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593823  
CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P593823  
 CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																			
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81																			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59																			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54																			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41																			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117745
5°	116935
10°	116634
15°	119690
20°	129578
25°	138920
30°	135818
35°	113094
40°	69478
45°	48110
50°	36714
55°	24074
60°	15060
65°	11288
70°	11378
75°	13094
80°	14473
85°	12985



TEST NUMBER: P593823  
 CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	358.9	5.4
10°-20°	1076.3	16.1
20°-30°	1852.8	27.6
30°-40°	1795.1	26.8
40°-50°	884.1	13.2
50°-60°	417.2	6.2
60°-70°	164.4	2.5
70°-80°	113.4	1.7
80°-90°	42.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3288.0	49.0
0°-40°	5083.1	75.8
0°-60°	6384.5	95.2
0°-90°	6704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6704.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3818	
5°	3778	359
15°	3749	1076
25°	4083	1853
35°	3004	1795
45°	1103	884
55°	448	417
65°	155	164
75°	110	113
85°	37	42
90°	0	



TEST NUMBER: P593823  
CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3818.4
2.5°	3806.2
5°	3777.7
7.5°	3749.2
10°	3724.9
12.5°	3720.7
15°	3749.2
17.5°	3834.7
20°	3948.7
22.5°	4050.4
25°	4083.0
27.5°	4009.8
30°	3814.4
32.5°	3492.8
35°	3004.3
37.5°	2332.6
40°	1726.0
42.5°	1339.2
45°	1103.2
47.5°	928.1
50°	765.3
52.5°	602.5
55°	447.8
57.5°	325.7
60°	244.2
62.5°	191.3
65°	154.7
67.5°	134.3
70°	126.2
72.5°	118.0
75°	109.9
77.5°	97.7
80°	81.5
82.5°	61.1
85°	36.7
87.5°	16.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)