

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584997

Luminaire Tested: **HCC8S55D010MB-HM82555927-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MB-HM82555927-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3647.9 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584997
CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584997

CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60390	60390	60390
5°	62883	60258	57720
10°	64988	59487	54902
15°	66632	58127	52052
20°	66763	55717	49469
25°	65636	52190	46909
30°	62119	48155	44715
35°	56639	43306	41985
40°	49255	38181	38765
45°	42253	33064	35489
50°	36090	28505	31878
55°	31628	24547	27698
60°	28160	20938	23288
65°	24990	17088	18584
70°	22170	12667	10558
75°	18491	6636	3145
80°	14544	2078	515
85°	10367	1026	0



TEST NUMBER: P584997
 CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.5	5.1
10°-20°	517.2	14.2
20°-30°	732.1	20.1
30°-40°	765.9	21.0
40°-50°	638.8	17.5
50°-60°	453.0	12.4
60°-70°	260.9	7.2
70°-80°	84.0	2.3
80°-90°	11.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1433.8	39.3
0°-40°	2199.7	60.3
0°-60°	3291.4	90.2
0°-90°	3647.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3647.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1958	1958	1958	1958	1958	
5°	2032	2005	1947	1888	1865	195
15°	2087	2002	1821	1677	1630	587
25°	1929	1786	1534	1411	1379	880
35°	1505	1373	1150	1089	1115	933
45°	969	890	758	767	814	751
55°	588	527	457	480	515	532
65°	342	287	234	234	255	342
75°	155	114	56	26	26	168
85°	29	15	3	0	0	37
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584997

CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4
2.5°	1999.3	1996.4	1993.5	1996.4	1993.5	1996.4	1993.5	1993.5	1990.5	1987.6	1987.6
5°	2031.5	2028.6	2028.6	2028.6	2025.7	2022.8	2022.8	2019.8	2014.0	2011.0	2005.2
7.5°	2052.1	2055.0	2055.0	2055.0	2049.1	2049.1	2043.3	2037.4	2031.5	2025.7	2016.9
10°	2075.5	2075.5	2072.6	2069.6	2063.8	2060.8	2057.9	2052.1	2043.3	2031.5	2022.8
12.5°	2084.3	2084.3	2081.4	2075.5	2072.6	2069.6	2066.7	2057.9	2046.2	2031.5	2019.8
15°	2087.2	2081.4	2078.4	2075.5	2069.6	2060.8	2060.8	2049.1	2034.5	2016.9	2002.2
17.5°	2063.8	2066.7	2060.8	2055.0	2046.2	2040.3	2031.5	2022.8	2005.2	1984.8	1970.1
20°	2034.5	2031.5	2028.6	2019.8	2008.1	2005.2	1996.4	1981.9	1967.2	1943.8	1923.3
22.5°	1987.6	1984.8	1978.9	1973.1	1961.3	1955.5	1946.7	1929.1	1908.6	1885.2	1861.7
25°	1929.1	1923.3	1914.5	1902.7	1894.0	1888.1	1876.4	1858.9	1835.5	1809.1	1785.7
27.5°	1835.5	1844.3	1838.4	1820.8	1812.0	1800.3	1797.4	1773.9	1753.4	1727.2	1700.8
30°	1744.6	1744.6	1735.8	1727.2	1712.5	1703.7	1692.0	1674.4	1653.9	1621.7	1601.3
32.5°	1630.5	1627.6	1615.8	1612.9	1601.3	1583.7	1580.8	1557.4	1536.8	1513.4	1487.0
35°	1504.6	1498.8	1487.0	1478.2	1472.5	1463.7	1454.9	1434.4	1413.9	1390.5	1372.9
37.5°	1361.2	1361.2	1358.2	1343.7	1337.8	1332.0	1323.2	1302.7	1291.0	1267.5	1249.9
40°	1223.6	1220.6	1212.0	1209.0	1203.2	1194.4	1188.5	1176.8	1159.2	1141.6	1124.1
42.5°	1089.0	1091.8	1080.2	1083.2	1071.4	1065.6	1062.7	1045.1	1036.3	1018.7	1004.1
45°	968.9	966.0	960.2	957.3	951.4	945.6	939.7	930.9	916.3	898.7	889.9
47.5°	857.7	848.9	848.9	845.9	843.0	831.4	828.5	819.7	810.9	793.3	781.6
50°	752.3	752.3	752.3	749.4	740.6	737.7	731.8	723.0	714.2	702.6	685.0
52.5°	667.5	667.5	667.5	664.5	652.8	649.9	646.9	635.2	623.5	614.7	603.0
55°	588.3	591.3	588.3	582.5	573.8	573.8	565.0	559.2	547.4	538.7	526.9
57.5°	521.1	521.1	515.2	512.3	506.4	503.5	497.6	491.8	477.1	468.3	453.7
60°	456.6	453.7	453.7	447.9	442.1	436.2	433.3	424.5	418.6	404.0	392.3
62.5°	398.1	398.1	392.3	392.3	380.5	380.5	377.6	368.8	360.0	345.4	339.5
65°	342.5	342.5	339.5	336.6	327.8	324.9	321.9	313.3	304.5	295.7	286.9
67.5°	292.8	292.8	286.9	284.0	278.1	275.2	269.3	263.5	254.7	245.9	237.1
70°	245.9	243.0	240.0	237.1	231.2	228.3	222.4	216.6	207.8	201.9	193.1
72.5°	199.0	199.0	196.1	190.3	187.4	184.5	181.5	175.7	166.9	158.1	152.2
75°	155.2	155.2	155.2	149.3	143.5	140.5	140.5	134.7	128.8	120.0	114.2
77.5°	120.0	117.1	114.2	114.2	108.3	105.4	102.4	99.5	90.7	87.8	81.9
80°	81.9	84.9	81.9	79.0	76.1	73.1	73.1	67.3	64.3	58.6	52.7
82.5°	55.7	52.7	52.7	49.8	49.8	46.9	46.9	41.0	38.1	35.2	32.2
85°	29.3	29.3	26.4	26.4	26.4	23.4	23.4	20.5	20.5	17.6	14.6
87.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584997

CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4
2.5°	1984.8	1978.9	1976.0	1976.0	1973.1	1970.1	1967.2	1964.3	1958.4	1958.4	1952.6
5°	1999.3	1993.5	1990.5	1981.9	1976.0	1976.0	1964.3	1961.3	1952.6	1946.7	1940.8
7.5°	2011.0	1999.3	1990.5	1981.9	1976.0	1970.1	1958.4	1946.7	1935.0	1923.3	1917.4
10°	2011.0	1999.3	1984.8	1970.1	1964.3	1958.4	1943.8	1926.2	1911.5	1899.8	1885.2
12.5°	2005.2	1987.6	1970.1	1958.4	1946.7	1937.9	1920.3	1902.7	1885.2	1861.7	1850.1
15°	1987.6	1964.3	1946.7	1926.2	1917.4	1902.7	1888.1	1861.7	1841.3	1820.8	1806.2
17.5°	1952.6	1923.3	1902.7	1882.2	1867.6	1858.9	1835.5	1812.0	1788.6	1765.1	1747.6
20°	1899.8	1873.4	1850.1	1823.7	1812.0	1800.3	1771.0	1747.6	1724.2	1697.9	1680.3
22.5°	1835.5	1809.1	1776.9	1756.4	1738.8	1724.2	1697.9	1671.5	1648.1	1624.6	1601.3
25°	1756.4	1730.1	1700.8	1668.6	1656.9	1642.2	1612.9	1586.7	1560.3	1533.9	1513.4
27.5°	1671.5	1636.3	1612.9	1577.9	1566.1	1551.5	1519.3	1490.0	1466.6	1446.1	1422.7
30°	1569.1	1542.7	1510.5	1478.2	1466.6	1452.0	1425.6	1399.3	1375.8	1352.4	1329.0
32.5°	1457.9	1431.5	1399.3	1375.8	1358.2	1346.5	1320.3	1296.8	1273.4	1249.9	1229.4
35°	1340.8	1311.5	1288.0	1264.6	1249.9	1235.3	1209.0	1188.5	1170.9	1150.4	1129.9
37.5°	1220.6	1200.2	1176.8	1150.4	1135.8	1124.1	1103.6	1080.2	1065.6	1048.0	1033.4
40°	1103.6	1080.2	1059.7	1036.3	1024.6	1015.8	995.3	977.7	963.0	948.5	939.7
42.5°	983.5	963.0	942.6	928.0	919.2	910.4	895.8	875.2	866.5	851.8	843.0
45°	872.3	854.7	840.1	819.7	813.8	808.0	790.4	775.7	767.0	758.2	752.3
47.5°	767.0	755.2	737.7	725.9	717.1	711.3	699.7	688.0	679.2	673.3	667.5
50°	676.2	661.6	649.9	638.2	632.3	623.5	611.8	605.9	600.1	594.2	594.2
52.5°	591.3	576.7	565.0	556.2	550.4	544.5	535.7	532.8	526.9	526.9	524.0
55°	512.3	503.5	491.8	480.1	477.1	474.2	468.3	462.5	459.5	456.6	459.5
57.5°	445.0	436.2	424.5	415.7	412.8	409.8	406.9	401.1	398.1	398.1	398.1
60°	383.5	374.7	365.9	357.1	357.1	351.2	348.3	345.4	342.5	339.5	339.5
62.5°	327.8	319.1	310.3	304.5	301.6	298.6	292.8	289.8	286.9	286.9	284.0
65°	278.1	266.4	263.5	254.7	251.7	248.8	245.9	240.0	237.1	234.2	231.2
67.5°	228.3	222.4	213.7	207.8	204.9	201.9	199.0	193.1	190.3	187.4	181.5
70°	184.5	178.6	172.8	166.9	164.0	161.0	155.2	149.3	146.4	140.5	131.7
72.5°	143.5	137.6	131.7	125.9	122.9	120.0	114.2	108.3	102.4	96.6	90.7
75°	108.3	102.4	93.6	87.8	84.9	84.9	76.1	70.2	64.3	55.7	49.8
77.5°	76.1	67.3	64.3	58.6	55.7	49.8	43.9	38.1	32.2	29.3	23.4
80°	49.8	43.9	38.1	35.2	32.2	29.3	26.4	20.5	14.6	11.7	8.8
82.5°	29.3	26.4	23.4	20.5	17.6	14.6	11.7	11.7	8.8	5.9	2.9
85°	14.6	11.7	8.8	8.8	5.9	5.9	5.9	2.9	2.9	2.9	2.9
87.5°	5.9	2.9	2.9	2.9	2.9	2.9	2.9	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584997

CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4
2.5°	1949.6	1946.7	1943.8	1940.8	1940.8	1935.0	1935.0	1932.0	1926.2	1923.3	1923.3
5°	1932.0	1923.3	1917.4	1914.5	1911.5	1902.7	1899.8	1894.0	1888.1	1882.2	1879.3
7.5°	1905.7	1891.0	1885.2	1882.2	1873.4	1864.7	1858.9	1850.1	1841.3	1832.5	1829.6
10°	1873.4	1858.9	1844.3	1838.4	1829.6	1823.7	1812.0	1800.3	1791.5	1782.7	1773.9
12.5°	1832.5	1815.0	1800.3	1794.4	1785.7	1773.9	1756.4	1750.5	1735.8	1730.1	1718.4
15°	1785.7	1765.1	1750.5	1741.7	1732.9	1715.5	1703.7	1692.0	1677.4	1671.5	1659.8
17.5°	1727.2	1703.7	1689.1	1680.3	1674.4	1659.8	1642.2	1627.6	1612.9	1607.0	1598.4
20°	1656.9	1642.2	1621.7	1612.9	1607.0	1589.6	1572.0	1566.1	1554.4	1542.7	1533.9
22.5°	1577.9	1563.2	1542.7	1533.9	1531.0	1516.3	1501.7	1492.9	1484.1	1475.3	1466.6
25°	1495.8	1478.2	1460.8	1454.9	1449.1	1437.3	1425.6	1419.8	1411.0	1405.1	1399.3
27.5°	1408.0	1390.5	1375.8	1367.0	1361.2	1352.4	1346.5	1340.8	1334.9	1329.0	1326.1
30°	1314.4	1296.8	1285.1	1279.2	1273.4	1270.4	1261.7	1258.7	1255.8	1249.9	1252.9
32.5°	1220.6	1206.1	1194.4	1185.6	1185.6	1179.7	1176.8	1176.8	1173.9	1173.9	1173.9
35°	1118.2	1109.4	1100.6	1097.7	1094.8	1091.8	1089.0	1091.8	1089.0	1091.8	1094.8
37.5°	1024.6	1015.8	1009.9	1007.0	1004.1	1007.0	1004.1	1004.1	1007.0	1012.8	1015.8
40°	928.0	922.1	916.3	919.2	916.3	916.3	916.3	925.1	928.0	930.9	933.8
42.5°	837.2	831.4	828.5	828.5	831.4	828.5	834.2	837.2	843.0	851.8	857.7
45°	749.4	746.4	746.4	749.4	746.4	752.3	752.3	758.2	767.0	772.8	778.7
47.5°	667.5	667.5	667.5	670.4	670.4	673.3	679.2	682.1	688.0	693.8	699.7
50°	591.3	594.2	597.1	597.1	597.1	603.0	608.9	611.8	614.7	617.6	626.4
52.5°	524.0	526.9	526.9	529.9	532.8	535.7	538.7	544.5	547.4	553.3	556.2
55°	459.5	459.5	465.4	468.3	468.3	468.3	474.2	474.2	480.1	483.0	488.8
57.5°	398.1	401.1	401.1	404.0	404.0	406.9	409.8	412.8	415.7	418.6	421.6
60°	339.5	339.5	339.5	342.5	345.4	348.3	345.4	351.2	351.2	357.1	360.0
62.5°	284.0	286.9	286.9	286.9	286.9	286.9	286.9	289.8	292.8	295.7	298.6
65°	231.2	231.2	231.2	228.3	231.2	228.3	231.2	234.2	234.2	237.1	240.0
67.5°	178.6	178.6	172.8	172.8	175.7	175.7	175.7	175.7	172.8	178.6	178.6
70°	128.8	125.9	122.9	120.0	120.0	117.1	117.1	114.2	114.2	114.2	114.2
72.5°	84.9	79.0	73.1	70.2	67.3	67.3	61.5	58.6	61.5	61.5	61.5
75°	43.9	38.1	35.2	32.2	29.3	29.3	26.4	26.4	26.4	26.4	26.4
77.5°	17.6	14.6	11.7	11.7	8.8	8.8	8.8	8.8	8.8	8.8	8.8
80°	5.9	5.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
82.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
85°	2.9	0.0	0.0	2.9	0.0	2.9	2.9	2.9	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584997

CATALOG NUMBER: HCC8S55D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4	1958.4
2.5°	1920.3	1920.3	1917.4	1920.3	1914.5	1917.4	1914.5	1914.5
5°	1876.4	1870.5	1870.5	1870.5	1867.6	1867.6	1864.7	1864.7
7.5°	1823.7	1820.8	1817.9	1815.0	1812.0	1809.1	1809.1	1809.1
10°	1771.0	1765.1	1765.1	1762.2	1756.4	1753.4	1753.4	1753.4
12.5°	1709.6	1706.7	1703.7	1703.7	1692.0	1694.9	1692.0	1692.0
15°	1651.0	1648.1	1648.1	1639.3	1633.4	1633.4	1633.4	1630.5
17.5°	1589.6	1586.7	1583.7	1577.9	1572.0	1572.0	1569.1	1572.0
20°	1525.1	1522.2	1516.3	1516.3	1513.4	1510.5	1504.6	1507.5
22.5°	1460.8	1454.9	1452.0	1452.0	1449.1	1449.1	1443.2	1443.2
25°	1393.4	1390.5	1387.5	1390.5	1384.6	1384.6	1378.7	1378.7
27.5°	1323.2	1320.3	1320.3	1320.3	1317.3	1320.3	1317.3	1317.3
30°	1252.9	1252.9	1249.9	1249.9	1252.9	1249.9	1252.9	1255.8
32.5°	1176.8	1176.8	1179.7	1179.7	1182.7	1182.7	1182.7	1182.7
35°	1097.7	1103.6	1103.6	1106.5	1109.4	1112.3	1112.3	1115.3
37.5°	1024.6	1027.5	1030.4	1033.4	1039.2	1039.2	1039.2	1039.2
40°	945.6	948.5	954.4	951.4	963.0	966.0	963.0	963.0
42.5°	863.5	869.4	872.3	878.2	881.1	887.0	889.9	889.9
45°	787.5	790.4	796.3	802.1	805.0	813.8	813.8	813.8
47.5°	708.4	714.2	717.1	723.0	725.9	734.7	737.7	734.7
50°	632.3	638.2	644.0	644.0	652.8	655.7	661.6	664.5
52.5°	559.2	562.1	568.0	570.9	576.7	582.5	585.4	588.3
55°	488.8	491.8	497.6	497.6	506.4	509.4	515.2	515.2
57.5°	424.5	427.4	433.3	430.4	436.2	442.1	442.1	439.1
60°	363.0	363.0	363.0	368.8	371.8	374.7	377.6	377.6
62.5°	298.6	304.5	307.4	307.4	310.3	313.3	313.3	310.3
65°	240.0	245.9	248.8	248.8	251.7	251.7	251.7	254.7
67.5°	181.5	181.5	181.5	184.5	181.5	181.5	181.5	181.5
70°	114.2	114.2	114.2	114.2	111.2	114.2	114.2	117.1
72.5°	61.5	61.5	61.5	61.5	61.5	61.5	61.5	61.5
75°	26.4	26.4	26.4	29.3	26.4	26.4	26.4	26.4
77.5°	11.7	8.8	11.7	11.7	8.8	8.8	8.8	8.8
80°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
82.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
85°	0.0	2.9	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)