

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584988

Luminaire Tested: **HCC8S55D010MW-HM82555927-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MW-HM82555927-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3920.2 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584988
CATALOG NUMBER: HCC8S55D010MW-HM82555927-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584988
 CATALOG NUMBER: HCC8S55D010MW-HM82555927-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																											
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81																											
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																											
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67																											
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																											
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52																											
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																											
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45																											
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97711
5°	97450
10°	95824
15°	94428
20°	92162
25°	87486
30°	72161
35°	37151
40°	24873
45°	21329
50°	18402
55°	16059
60°	14271
65°	12820
70°	11613
75°	10473
80°	9358
85°	9341



TEST NUMBER: P584988
 CATALOG NUMBER: HCC8S55D010MW-HM82555927-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.7	7.6
10°-20°	832.2	21.2
20°-30°	1153.0	29.4
30°-40°	692.6	17.7
40°-50°	379.1	9.7
50°-60°	269.3	6.9
60°-70°	174.8	4.5
70°-80°	93.5	2.4
80°-90°	27.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2282.9	58.2
0°-40°	2975.5	75.9
0°-60°	3624.0	92.4
0°-90°	3920.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3920.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3169	
5°	3148	298
15°	2958	832
25°	2571	1153
35°	987	693
45°	489	379
55°	299	269
65°	176	175
75°	88	93
85°	26	28
90°	0	



TEST NUMBER: P584988
CATALOG NUMBER: HCC8S55D010MW-HM82555927-81NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3168.7
2.5°	3162.9
5°	3148.2
7.5°	3113.1
10°	3060.3
12.5°	3010.6
15°	2957.9
17.5°	2890.5
20°	2808.5
22.5°	2709.0
25°	2571.3
27.5°	2354.5
30°	2026.6
32.5°	1484.8
35°	986.9
37.5°	729.2
40°	617.9
42.5°	547.7
45°	489.1
47.5°	433.4
50°	383.6
52.5°	336.8
55°	298.7
57.5°	263.6
60°	231.4
62.5°	202.1
65°	175.7
67.5°	149.3
70°	128.8
72.5°	105.5
75°	87.9
77.5°	70.3
80°	52.7
82.5°	38.1
85°	26.4
87.5°	11.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)