

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585027

Luminaire Tested: **HCC8W55D010MW-HM82555935-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MW-HM82555935-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5888.5 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585027
CATALOG NUMBER: HCC8W55D010MW-HM82555935-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P585027
 CATALOG NUMBER: HCC8W55D010MW-HM82555935-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92											92																	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84											84																	
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77											77																	
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70											70																	
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64											64																	
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59											59																	
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54											54																	
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50											50																	
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46											46																	
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43											43																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141277
5°	137476
10°	136430
15°	134397
20°	130329
25°	125471
30°	117203
35°	96986
40°	58557
45°	39440
50°	28419
55°	16204
60°	7136
65°	2554
70°	947
75°	417
80°	0
85°	0



TEST NUMBER: P585027
 CATALOG NUMBER: HCC8W55D010MW-HM82555935-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	421.9	7.2
10°-20°	1183.1	20.1
20°-30°	1687.8	28.7
30°-40°	1536.9	26.1
40°-50°	725.0	12.3
50°-60°	285.1	4.8
60°-70°	45.4	0.8
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3292.9	55.9
0°-40°	4829.7	82.0
0°-60°	5839.8	99.2
0°-90°	5888.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5888.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4582	
5°	4441	422
15°	4210	1183
25°	3688	1688
35°	2576	1537
45°	904	725
55°	301	285
65°	35	45
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P585027
CATALOG NUMBER: HCC8W55D010MW-HM82555935-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4581.5
2.5°	4521.9
5°	4441.3
7.5°	4395.7
10°	4357.1
12.5°	4294.1
15°	4209.9
17.5°	4104.8
20°	3971.6
22.5°	3831.4
25°	3687.7
27.5°	3512.4
30°	3291.6
32.5°	2993.5
35°	2576.4
37.5°	1991.0
40°	1454.7
42.5°	1118.2
45°	904.4
47.5°	743.2
50°	592.4
52.5°	445.1
55°	301.4
57.5°	189.3
60°	115.7
62.5°	70.1
65°	35.0
67.5°	17.6
70°	10.5
72.5°	3.5
75°	3.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)