

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584870

Luminaire Tested: **HCC8W50D010MW-HM82555930-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584870  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W50D010MW-HM82555930-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4952.5 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584870  
CATALOG NUMBER: HCC8W50D010MW-HM82555930-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584870

CATALOG NUMBER: HCC8W50D010MW-HM82555930-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79	79	79	79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64	64	64	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49	49	49	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45	45	45	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39	39	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116250
5°	114738
10°	110535
15°	106211
20°	103276
25°	100167
30°	89882
35°	58924
40°	32578
45°	27155
50°	24764
55°	23628
60°	21974
65°	19927
70°	18014
75°	16263
80°	14775
85°	14152



TEST NUMBER: P584870

CATALOG NUMBER: HCC8W50D010MW-HM82555930-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.3	7.0
10°-20°	938.6	19.0
20°-30°	1335.8	27.0
30°-40°	988.7	20.0
40°-50°	489.7	9.9
50°-60°	390.8	7.9
60°-70°	271.3	5.5
70°-80°	146.2	3.0
80°-90°	43.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2622.7	53.0
0°-40°	3611.4	72.9
0°-60°	4491.9	90.7
0°-90°	4952.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4952.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3770	
5°	3707	348
15°	3327	939
25°	2944	1336
35°	1565	989
45°	623	490
55°	440	391
65°	273	271
75°	136	146
85°	40	43
90°	0	



TEST NUMBER: P584870  
CATALOG NUMBER: HCC8W50D010MW-HM82555930-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3769.9
2.5°	3753.3
5°	3706.7
7.5°	3633.4
10°	3530.1
12.5°	3423.5
15°	3327.0
17.5°	3233.7
20°	3147.2
22.5°	3060.6
25°	2944.0
27.5°	2774.2
30°	2524.3
32.5°	2141.4
35°	1565.3
37.5°	1069.1
40°	809.3
42.5°	692.7
45°	622.7
47.5°	566.1
50°	516.2
52.5°	472.9
55°	439.5
57.5°	399.7
60°	356.3
62.5°	313.1
65°	273.1
67.5°	233.1
70°	199.8
72.5°	166.5
75°	136.5
77.5°	109.9
80°	83.2
82.5°	60.0
85°	40.0
87.5°	16.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)