

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584892

Luminaire Tested: **HCC8S50D010MB-HM82555935-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584892  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MB-HM82555935-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5327.5 lumens  
Efficiency: N/A  
Efficacy: 111.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584892  
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81WDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584892

CATALOG NUMBER: HCC8S50D010MB-HM82555935-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																												
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																												
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																												
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																												
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																												
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57																												
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52																												
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																												
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																												
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121964
5°	119217
10°	115560
15°	113222
20°	112209
25°	110527
30°	104702
35°	86992
40°	51231
45°	33884
50°	26673
55°	19628
60°	13636
65°	8311
70°	3624
75°	1597
80°	1190
85°	0



TEST NUMBER: P584892  
 CATALOG NUMBER: HCC8S50D010MB-HM82555935-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	362.7	6.8
10°-20°	1002.7	18.8
20°-30°	1485.6	27.9
30°-40°	1372.7	25.8
40°-50°	633.0	11.9
50°-60°	332.9	6.2
60°-70°	117.7	2.2
70°-80°	18.5	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2850.9	53.5
0°-40°	4223.6	79.3
0°-60°	5189.5	97.4
0°-90°	5327.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5327.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3955	
5°	3851	363
15°	3547	1003
25°	3248	1486
35°	2311	1373
45°	777	633
55°	365	333
65°	114	118
75°	13	19
85°	0	2
90°	0	



TEST NUMBER: P584892  
CATALOG NUMBER: HCC8S50D010MB-HM82555935-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3955.2
2.5°	3921.8
5°	3851.4
7.5°	3774.4
10°	3690.6
12.5°	3610.2
15°	3546.6
17.5°	3489.7
20°	3419.4
22.5°	3342.4
25°	3248.5
27.5°	3121.3
30°	2940.5
32.5°	2682.6
35°	2310.9
37.5°	1775.0
40°	1272.7
42.5°	954.5
45°	777.0
47.5°	659.8
50°	556.0
52.5°	455.4
55°	365.1
57.5°	288.0
60°	221.1
62.5°	167.4
65°	113.9
67.5°	67.0
70°	40.2
72.5°	23.5
75°	13.4
77.5°	10.1
80°	6.7
82.5°	3.4
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)